

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912145

Luminaire Tested: DFN2DIP-SQ4F0-060D120US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912145
REPORT IS A COMBINATION OF REPORTS P901687 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D120US850-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19762.3 lumens
Efficiency: N/A
Efficacy: 141.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 140.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912145

CATALOG NUMBER: DFN2DIP-SQ4F0-060D120US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912145

CATALOG NUMBER: DFN2DIP-SQ4F0-060D120US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1817	1817	1817
5°	1820	1792	1804
10°	1805	1768	1780
15°	1778	1739	1742
20°	1742	1699	1704
25°	1707	1651	1659
30°	1662	1606	1602
35°	1620	1554	1542
40°	1567	1501	1485
45°	1515	1447	1426
50°	1458	1391	1358
55°	1399	1327	1296
60°	1332	1250	1225
65°	1258	1170	1140
70°	1165	1073	1050
75°	1035	957	968
80°	879	810	808
85°	635	553	543

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2407 cd/sqm

TEST NUMBER: P912145

CATALOG NUMBER: DFN2DIP-SQ4F0-060D120US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	1.2
10°-20°	685.6	3.5
20°-30°	1007.6	5.1
30°-40°	1170.3	5.9
40°-50°	1168.8	5.9
50°-60°	1019.2	5.2
60°-70°	753.4	3.8
70°-80°	426.3	2.2
80°-90°	120.4	0.6
90°-100°	148.1	0.7
100°-110°	552.1	2.8
110°-120°	1464.2	7.4
120°-130°	2428.5	12.3
130°-140°	2579.6	13.1
140°-150°	2397.5	12.1
150°-160°	1927.5	9.8
160°-170°	1242.0	6.3
170°-180°	427.5	2.2
0°-30°	1937.0	9.8
0°-40°	3107.2	15.7
0°-60°	5295.3	26.8
0°-90°	6595.3	33.4
90°-120°	2164.4	11.0
90°-150°	9570.0	48.4
90°-180°	13167.0	66.6
0°-180°	19762.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	114
90°	3	39	65	81	88	18
95°	211	104	126	143	140	250
105°	988	1086	198	234	247	1056
115°	1869	1924	2005	500	267	1840
125°	2642	2684	2746	2769	2779	2356
135°	3269	3322	3350	3383	3377	2526
145°	3793	3789	3844	3867	3851	2372
155°	4176	4147	4186	4205	4180	1924
165°	4400	4381	4390	4413	4390	1243
175°	4501	4478	4485	4508	4475	428
180°	4491	4491	4491	4491	4491	

TEST NUMBER: P912145

CATALOG NUMBER: DFN2DIP-SQ4F0-060D120US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	3.1	38.9	64.9	81.4	87.6
92.5°	81.4	68.3	78.0	84.5	87.6
95°	211.0	103.8	126.5	143.2	139.7
97.5°	380.2	113.9	165.6	175.6	178.7
100°	575.3	130.1	185.2	211.0	217.7
102.5°	789.6	783.4	191.7	227.3	237.3
105°	987.9	1085.6	198.4	233.9	247.0
107.5°	1218.7	1299.7	204.9	240.4	253.5
110°	1439.8	1507.8	568.8	243.9	256.6

TEST NUMBER: P912145

CATALOG NUMBER: DFN2DIP-SQ4F0-060D120US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1647.9	1706.1	1651.0	250.1	260.1
115°	1868.6	1923.8	2005.2	500.5	266.7
117.5°	2060.4	2125.3	2180.8	1715.7	864.5
120°	2275.0	2323.6	2382.2	2421.3	1982.4
122.5°	2456.8	2508.9	2574.1	2593.4	2596.8
125°	2642.0	2684.4	2746.2	2769.0	2778.6
127.5°	2811.0	2856.6	2905.6	2938.0	2941.1
130°	2970.3	3022.5	3058.0	3093.9	3090.8
132.5°	3132.8	3175.3	3210.8	3240.2	3237.1
135°	3269.4	3321.6	3350.5	3383.3	3376.8
137.5°	3412.3	3451.2	3484.0	3516.4	3506.8
140°	3552.0	3578.2	3613.7	3643.1	3626.9
142.5°	3669.2	3692.1	3734.1	3760.0	3743.8
145°	3792.8	3789.3	3844.5	3867.3	3851.0
147.5°	3899.7	3890.0	3945.3	3961.5	3948.7
150°	4003.8	3981.1	4033.2	4052.5	4036.3
152.5°	4091.4	4065.6	4114.3	4133.9	4111.2
155°	4175.9	4147.0	4186.0	4205.3	4179.5
157.5°	4244.3	4218.4	4247.8	4270.5	4244.3
160°	4302.9	4283.3	4302.9	4322.2	4299.5
162.5°	4354.7	4335.4	4351.6	4374.3	4345.1
165°	4400.2	4380.9	4390.5	4413.4	4390.5
167.5°	4436.1	4416.4	4426.5	4449.2	4419.9
170°	4465.4	4445.8	4452.3	4475.0	4445.8
172.5°	4484.7	4465.4	4472.0	4494.8	4465.4
175°	4500.9	4478.1	4484.7	4507.5	4475.0
177.5°	4507.5	4484.7	4488.2	4511.0	4481.7
180°	4491.3	4491.3	4491.3	4491.3	4491.3

TEST NUMBER: P912145

CATALOG NUMBER: DFN2DIP-SQ4F0-060D120US850-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.59	8.32	8.67	9.40	10.89	7.14	7.87	8.23	8.96	10.45
	3H	9.24	9.89	10.34	10.99	12.50	8.75	9.40	9.85	10.50	12.01
	4H	9.82	10.44	10.93	11.54	13.06	9.33	9.95	10.44	11.05	12.56
	6H	10.22	10.79	11.34	11.89	13.42	9.72	10.29	10.84	11.39	12.92
	8H	10.32	10.87	11.44	11.98	13.50	9.82	10.37	10.94	11.48	13.00
	12H	10.37	10.89	11.49	11.99	13.54	9.86	10.38	10.98	11.48	13.03
4H	2H	8.03	8.65	9.15	9.75	11.26	7.68	8.30	8.79	9.39	10.91
	3H	9.89	10.41	11.01	11.53	13.06	9.48	10.00	10.60	11.12	12.65
	4H	10.60	11.08	11.73	12.19	13.74	10.18	10.65	11.30	11.77	13.31
	6H	11.11	11.52	12.25	12.66	14.20	10.68	11.09	11.81	12.22	13.76
	8H	11.26	11.64	12.39	12.77	14.33	10.83	11.21	11.96	12.33	13.89
	12H	11.33	11.68	12.48	12.82	14.38	10.88	11.23	12.03	12.37	13.93
8H	4H	10.79	11.17	11.92	12.30	13.85	10.41	10.79	11.54	11.92	13.47
	6H	11.42	11.73	12.57	12.90	14.45	11.04	11.35	12.19	12.52	14.07
	8H	11.64	11.92	12.80	13.06	14.64	11.25	11.52	12.41	12.67	14.24
	12H	11.77	12.01	12.93	13.16	14.76	11.36	11.60	12.52	12.75	14.35
12H	4H	10.77	11.11	11.92	12.25	13.81	10.40	10.74	11.55	11.88	13.44
	6H	11.45	11.72	12.61	12.87	14.44	11.08	11.35	12.23	12.50	14.07
	8H	11.69	11.93	12.85	13.07	14.68	11.31	11.55	12.47	12.69	14.30