

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904076

Luminaire Tested: DFN2DIP-SQ4F0-090D160US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904076
REPORT IS A COMBINATION OF REPORTS P900209 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D160US830-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21745.4 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 204.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904076

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904076

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	39
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	32
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	31	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2316	2316	2316
5°	2320	2284	2300
10°	2301	2254	2269
15°	2267	2217	2221
20°	2221	2166	2172
25°	2176	2105	2115
30°	2119	2048	2043
35°	2065	1981	1966
40°	1998	1913	1893
45°	1932	1845	1818
50°	1859	1774	1732
55°	1783	1691	1652
60°	1698	1593	1561
65°	1604	1492	1454
70°	1485	1368	1339
75°	1320	1221	1234
80°	1121	1032	1031
85°	810	706	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3754 cd/sqm

TEST NUMBER: P904076

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.7	1.4
10°-20°	874.1	4.0
20°-30°	1284.6	5.9
30°-40°	1492.0	6.9
40°-50°	1490.1	6.9
50°-60°	1299.3	6.0
60°-70°	960.5	4.4
70°-80°	543.4	2.5
80°-90°	157.0	0.7
90°-100°	295.1	1.4
100°-110°	937.8	4.3
110°-120°	1604.9	7.4
120°-130°	2110.7	9.7
130°-140°	2369.1	10.9
140°-150°	2323.2	10.7
150°-160°	1948.8	9.0
160°-170°	1292.4	5.9
170°-180°	451.7	2.1
0°-30°	2469.3	11.4
0°-40°	3961.3	18.2
0°-60°	6750.7	31.0
0°-90°	8411.6	38.7
90°-120°	2837.8	13.1
90°-150°	9640.8	44.3
90°-180°	13334.0	61.3
0°-180°	21745.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3301	3301	3301	3301	3301	
5°	3301	3288	3253	3278	3272	313
15°	3142	3123	3082	3095	3079	885
25°	2844	2818	2765	2771	2765	1309
35°	2454	2422	2371	2352	2336	1532
45°	1996	1974	1926	1892	1879	1541
55°	1511	1492	1454	1416	1400	1351
65°	1019	1000	968	940	924	1007
75°	533	527	511	492	498	569
85°	130	127	124	114	111	145
90°	4	52	141	132	137	21
95°	210	250	257	257	250	234
105°	866	877	886	893	893	914
115°	1610	1634	1626	1622	1610	1593
125°	2342	2378	2367	2354	2350	2093
135°	3030	3074	3083	3079	3067	2342
145°	3678	3707	3730	3734	3719	2298
155°	4206	4218	4230	4251	4238	1936
165°	4576	4571	4571	4600	4580	1291
175°	4761	4750	4741	4770	4745	452
180°	4770	4770	4770	4770	4770	

TEST NUMBER: P904076

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3300.7	3300.7	3300.7	3300.7	3300.7
2.5°	3319.9	3304.1	3269.1	3300.7	3294.7
5°	3300.7	3288.2	3253.3	3278.5	3272.4
7.5°	3278.5	3259.7	3224.6	3250.3	3243.9
10°	3243.9	3221.6	3183.5	3208.8	3199.4
12.5°	3196.0	3177.1	3139.1	3154.9	3148.6
15°	3142.2	3123.3	3081.8	3094.6	3078.8
17.5°	3075.4	3056.6	3015.2	3031.0	3015.2
20°	3002.4	2983.5	2939.0	2948.5	2936.0
22.5°	2929.6	2901.1	2859.6	2859.6	2853.2
25°	2843.7	2818.5	2764.7	2770.7	2764.7
27.5°	2748.5	2726.2	2685.2	2675.8	2659.9
30°	2653.5	2627.9	2580.4	2571.0	2558.2
32.5°	2551.8	2533.0	2482.1	2463.0	2450.1
35°	2453.5	2421.9	2371.0	2351.8	2336.0
37.5°	2342.4	2313.8	2262.9	2240.7	2224.9
40°	2228.2	2202.6	2151.7	2123.5	2110.7
42.5°	2117.0	2091.5	2041.0	2009.0	1990.2
45°	1996.5	1974.3	1926.5	1891.8	1879.1
47.5°	1879.1	1856.8	1805.9	1770.9	1752.1
50°	1755.1	1739.3	1694.8	1650.4	1634.6
52.5°	1634.6	1612.3	1571.2	1536.2	1514.0
55°	1511.0	1491.8	1453.7	1415.7	1399.9
57.5°	1387.0	1371.2	1329.8	1291.8	1278.9
60°	1263.1	1250.7	1206.2	1171.2	1161.8
62.5°	1142.5	1120.3	1088.6	1057.1	1044.2
65°	1019.0	999.8	968.1	939.5	923.7
67.5°	892.0	875.9	847.5	825.4	812.6
70°	774.5	761.7	733.1	710.9	698.4
72.5°	653.9	641.1	625.3	603.1	593.7
75°	533.1	527.0	510.9	492.0	498.4
77.5°	425.3	412.6	406.1	396.7	387.3
80°	317.5	314.1	307.7	298.3	292.0
82.5°	215.8	215.8	212.8	200.0	200.0
85°	130.0	127.0	123.9	114.1	111.1
87.5°	57.2	50.8	44.5	35.1	31.7
90°	4.3	51.7	140.9	132.3	136.6
92.5°	89.2	120.8	125.1	129.4	129.4
95°	209.9	250.2	257.4	257.4	250.2
97.5°	349.4	386.8	402.7	402.7	402.7
100°	510.5	543.6	555.1	555.1	550.7
102.5°	680.1	704.6	720.4	724.7	720.4
105°	865.6	877.1	885.8	893.0	893.0
107.5°	1049.7	1067.0	1067.0	1069.9	1049.7
110°	1228.0	1251.0	1251.0	1251.0	1239.5

TEST NUMBER: P904076

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1420.7	1445.2	1440.9	1429.4	1420.7
115°	1610.5	1633.5	1626.4	1622.0	1610.5
117.5°	1798.9	1830.5	1810.4	1798.9	1787.4
120°	1988.8	2020.3	1988.8	1988.8	1975.8
122.5°	2161.2	2201.6	2181.4	2169.9	2161.2
125°	2342.5	2378.4	2366.9	2354.0	2349.7
127.5°	2519.3	2563.9	2548.1	2530.8	2519.3
130°	2684.7	2736.5	2729.3	2720.6	2704.8
132.5°	2870.2	2910.5	2913.3	2893.2	2881.7
135°	3029.8	3074.4	3083.1	3078.7	3067.2
137.5°	3208.1	3244.0	3251.3	3248.4	3231.1
140°	3364.9	3400.8	3421.0	3421.0	3405.1
142.5°	3526.0	3561.9	3573.4	3577.7	3561.9
145°	3678.4	3707.1	3730.1	3734.4	3718.6
147.5°	3814.9	3850.9	3868.2	3875.4	3859.5
150°	3955.8	3980.4	3996.2	4009.1	3996.2
152.5°	4081.0	4105.4	4125.6	4141.3	4125.6
155°	4206.1	4217.6	4230.5	4250.7	4237.8
157.5°	4313.9	4322.6	4329.8	4358.5	4338.4
160°	4410.2	4418.9	4423.3	4447.7	4430.4
162.5°	4499.4	4499.4	4503.7	4531.1	4510.9
165°	4575.7	4571.3	4571.3	4600.1	4580.0
167.5°	4644.7	4631.7	4631.7	4660.5	4640.3
170°	4696.4	4684.9	4680.7	4709.4	4684.9
172.5°	4732.4	4720.9	4716.6	4745.3	4720.9
175°	4761.2	4749.7	4741.0	4769.8	4745.3
177.5°	4777.0	4765.5	4756.8	4781.3	4756.8
180°	4769.8	4769.8	4769.8	4769.8	4769.8

TEST NUMBER: P904076

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.05	9.82	10.10	10.88	12.30	8.61	9.38	9.66	10.43	11.86
	3H	10.71	11.40	11.77	12.46	13.90	10.22	10.91	11.28	11.97	13.41
	4H	11.30	11.95	12.37	13.01	14.46	10.80	11.46	11.87	12.52	13.97
	6H	11.70	12.30	12.78	13.36	14.83	11.20	11.80	12.28	12.86	14.33
	8H	11.80	12.37	12.88	13.46	14.91	11.30	11.87	12.38	12.95	14.41
	12H	11.85	12.39	12.94	13.47	14.95	11.34	11.88	12.43	12.96	14.44
4H	2H	9.50	10.16	10.58	11.22	12.67	9.15	9.80	10.23	10.87	12.32
	3H	11.37	11.91	12.45	13.00	14.46	10.96	11.50	12.04	12.59	14.06
	4H	12.08	12.58	13.17	13.66	15.15	11.66	12.16	12.75	13.24	14.72
	6H	12.59	13.02	13.69	14.13	15.60	12.16	12.59	13.26	13.70	15.17
	8H	12.74	13.14	13.84	14.24	15.73	12.31	12.71	13.40	13.80	15.30
	12H	12.81	13.18	13.93	14.29	15.79	12.36	12.73	13.48	13.84	15.34
8H	4H	12.27	12.67	13.37	13.77	15.26	11.89	12.29	12.99	13.39	14.88
	6H	12.90	13.23	14.02	14.37	15.86	12.52	12.85	13.64	13.99	15.48
	8H	13.12	13.41	14.25	14.53	16.04	12.73	13.02	13.86	14.14	15.65
	12H	13.25	13.51	14.38	14.63	16.17	12.84	13.10	13.97	14.21	15.76
12H	4H	12.25	12.61	13.37	13.72	15.22	11.88	12.25	13.00	13.36	14.85
	6H	12.93	13.22	14.06	14.34	15.85	12.56	12.85	13.69	13.97	15.48
	8H	13.17	13.43	14.30	14.54	16.09	12.79	13.05	13.92	14.16	15.71