

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904080

Luminaire Tested: DFN2DIP-SQ4F0-100D060US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904080
REPORT IS A COMBINATION OF REPORTS P900067 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D060US830-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14336.1 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 137.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904080

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904080

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2573	2573	2573
5°	2577	2538	2555
10°	2557	2504	2522
15°	2519	2464	2468
20°	2468	2407	2413
25°	2418	2339	2350
30°	2354	2276	2270
35°	2294	2201	2184
40°	2220	2126	2103
45°	2147	2050	2020
50°	2066	1971	1924
55°	1982	1879	1836
60°	1886	1770	1735
65°	1782	1658	1616
70°	1650	1520	1488
75°	1466	1356	1371
80°	1245	1147	1145
85°	900	785	770

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2147 cd/sqm

TEST NUMBER: P904080

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	2.4
10°-20°	971.2	6.8
20°-30°	1427.3	10.0
30°-40°	1657.7	11.6
40°-50°	1655.7	11.5
50°-60°	1443.7	10.1
60°-70°	1067.2	7.4
70°-80°	603.8	4.2
80°-90°	164.5	1.1
90°-100°	110.7	0.8
100°-110°	351.6	2.5
110°-120°	601.8	4.2
120°-130°	791.4	5.5
130°-140°	888.4	6.2
140°-150°	871.1	6.1
150°-160°	730.8	5.1
160°-170°	484.6	3.4
170°-180°	169.4	1.2
0°-30°	2743.7	19.1
0°-40°	4401.4	30.7
0°-60°	7500.8	52.3
0°-90°	9336.3	65.1
90°-120°	1064.1	7.4
90°-150°	3615.0	25.2
90°-180°	5000.0	34.9
0°-180°	14336.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3668	3668	3668	3668	3668	
5°	3668	3654	3615	3643	3636	348
15°	3491	3470	3424	3438	3421	983
25°	3160	3132	3072	3078	3072	1454
35°	2726	2691	2634	2613	2596	1702
45°	2218	2194	2140	2102	2088	1712
55°	1679	1658	1615	1573	1555	1501
65°	1132	1111	1076	1044	1026	1119
75°	592	586	568	547	554	632
85°	144	141	138	127	124	161
90°	2	19	53	50	51	14
95°	79	94	96	96	94	88
105°	325	329	332	335	335	343
115°	604	613	610	608	604	597
125°	878	892	888	883	881	785
135°	1136	1153	1156	1154	1150	878
145°	1379	1390	1399	1400	1394	862
155°	1577	1582	1586	1594	1589	726
165°	1716	1714	1714	1725	1717	484
175°	1785	1781	1778	1789	1779	170
180°	1789	1789	1789	1789	1789	

TEST NUMBER: P904080

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3667.5	3667.5	3667.5	3667.5	3667.5
2.5°	3688.8	3671.2	3632.3	3667.5	3660.7
5°	3667.5	3653.7	3614.7	3642.8	3636.0
7.5°	3642.8	3621.8	3582.9	3611.4	3604.3
10°	3604.3	3579.6	3537.3	3565.4	3554.9
12.5°	3551.1	3530.2	3487.9	3505.5	3498.3
15°	3491.3	3470.3	3424.3	3438.5	3421.0
17.5°	3417.2	3396.3	3350.2	3367.8	3350.2
20°	3335.9	3315.0	3265.6	3276.1	3262.2
22.5°	3255.2	3223.4	3177.3	3177.3	3170.2
25°	3159.8	3131.7	3071.8	3078.5	3071.8
27.5°	3053.8	3029.1	2983.5	2973.1	2955.4
30°	2948.4	2919.9	2867.1	2856.7	2842.4
32.5°	2835.4	2814.4	2757.9	2736.6	2722.3
35°	2726.1	2691.0	2634.4	2613.1	2595.5
37.5°	2602.6	2570.8	2514.3	2489.6	2472.0
40°	2475.8	2447.3	2390.9	2359.5	2345.2
42.5°	2352.3	2323.8	2267.8	2232.2	2211.3
45°	2218.4	2193.7	2140.5	2102.0	2087.8
47.5°	2087.8	2063.1	2006.6	1967.7	1946.7
50°	1950.1	1932.5	1883.1	1833.7	1816.2
52.5°	1816.2	1791.5	1745.8	1706.9	1682.2
55°	1678.9	1657.6	1615.2	1572.9	1555.4
57.5°	1541.2	1523.5	1477.5	1435.3	1421.1
60°	1403.4	1389.6	1340.2	1301.3	1290.8
62.5°	1269.5	1244.8	1209.7	1174.5	1160.3
65°	1132.2	1110.9	1075.7	1043.9	1026.3
67.5°	991.2	973.2	941.8	917.1	902.9
70°	860.5	846.3	814.5	789.9	776.0
72.5°	726.6	712.4	694.8	670.1	659.6
75°	592.3	585.6	567.6	546.7	553.7
77.5°	472.6	458.4	451.2	440.7	430.3
80°	352.8	349.1	342.0	331.5	324.4
82.5°	239.9	239.9	236.5	222.3	222.3
85°	144.4	141.1	137.7	126.9	123.5
87.5°	63.6	56.5	49.4	38.9	35.2
90°	1.6	19.4	52.9	49.6	51.2
92.5°	33.5	45.3	46.9	48.5	48.5
95°	78.7	93.8	96.5	96.5	93.8
97.5°	131.0	145.1	151.0	151.0	151.0
100°	191.4	203.8	208.1	208.1	206.5
102.5°	255.1	264.2	270.1	271.7	270.1
105°	324.6	328.9	332.2	334.9	334.9
107.5°	393.6	400.1	400.1	401.1	393.6
110°	460.5	469.1	469.1	469.1	464.8

TEST NUMBER: P904080

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US830-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	532.7	541.9	540.3	535.9	532.7
115°	603.9	612.6	609.8	608.2	603.9
117.5°	674.6	686.5	678.8	674.6	670.2
120°	745.7	757.6	745.7	745.7	740.8
122.5°	810.4	825.5	817.9	813.7	810.4
125°	878.4	891.8	887.5	882.7	881.1
127.5°	944.7	961.4	955.5	949.0	944.7
130°	1006.7	1026.1	1023.4	1020.2	1014.3
132.5°	1076.3	1091.4	1092.4	1084.9	1080.5
135°	1136.1	1152.8	1156.0	1154.4	1150.1
137.5°	1203.0	1216.4	1219.2	1218.0	1211.6
140°	1261.8	1275.3	1282.8	1282.8	1276.9
142.5°	1322.1	1335.6	1339.9	1341.5	1335.6
145°	1379.3	1390.1	1398.7	1400.3	1394.4
147.5°	1430.5	1444.0	1450.5	1453.1	1447.2
150°	1483.4	1492.5	1498.5	1503.3	1498.5
152.5°	1530.2	1539.5	1547.0	1552.9	1547.0
155°	1577.2	1581.5	1586.3	1593.9	1589.0
157.5°	1617.6	1620.9	1623.5	1634.4	1626.8
160°	1653.8	1657.0	1658.6	1667.7	1661.3
162.5°	1687.2	1687.2	1688.8	1699.0	1691.5
165°	1715.7	1714.1	1714.1	1724.9	1717.4
167.5°	1741.6	1736.8	1736.8	1747.6	1740.0
170°	1761.0	1756.7	1755.1	1765.9	1756.7
172.5°	1774.5	1770.2	1768.6	1779.3	1770.2
175°	1785.3	1781.0	1777.7	1788.6	1779.3
177.5°	1791.2	1787.0	1783.7	1792.8	1783.7
180°	1788.6	1788.6	1788.6	1788.6	1788.6

TEST NUMBER: P904080

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.86	12.87	12.67	13.71	14.75	11.41	12.43	12.23	13.27	14.30
	3H	13.53	14.45	14.36	15.29	16.36	13.04	13.96	13.87	14.80	15.87
	4H	14.13	14.99	14.98	15.85	16.92	13.64	14.50	14.48	15.35	16.43
	6H	14.54	15.34	15.40	16.20	17.29	14.04	14.84	14.90	15.70	16.79
	8H	14.65	15.41	15.52	16.29	17.38	14.15	14.91	15.02	15.79	16.88
	12H	14.71	15.43	15.58	16.31	17.42	14.20	14.92	15.07	15.80	16.91
4H	2H	12.34	13.20	13.19	14.05	15.13	11.98	12.84	12.83	13.70	14.78
	3H	14.22	14.94	15.08	15.83	16.92	13.81	14.53	14.68	15.42	16.51
	4H	14.95	15.60	15.82	16.49	17.60	14.52	15.18	15.40	16.06	17.18
	6H	15.47	16.04	16.36	16.95	18.07	15.04	15.61	15.93	16.52	17.64
	8H	15.63	16.16	16.52	17.06	18.20	15.19	15.72	16.08	16.63	17.76
	12H	15.71	16.19	16.62	17.11	18.25	15.26	15.74	16.17	16.66	17.80
8H	4H	15.16	15.69	16.05	16.59	17.72	14.78	15.31	15.67	16.21	17.35
	6H	15.80	16.24	16.72	17.18	18.32	15.41	15.85	16.33	16.80	17.93
	8H	16.02	16.41	16.95	17.35	18.50	15.63	16.02	16.56	16.96	18.11
	12H	16.16	16.51	17.10	17.44	18.64	15.75	16.10	16.69	17.03	18.23
12H	4H	15.15	15.63	16.06	16.55	17.69	14.78	15.26	15.69	16.18	17.32
	6H	15.83	16.22	16.76	17.16	18.31	15.46	15.85	16.39	16.78	17.94
	8H	16.08	16.42	17.01	17.35	18.56	15.70	16.04	16.63	16.97	18.18