

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912214

Luminaire Tested: DFN2DIP-SQ4F0-080D110US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912214
REPORT IS A COMBINATION OF REPORTS P900154 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D110US850-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18337.3 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 154.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912214

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912214

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27
5	68	57	49	43	62	52	45	40	43	38	34	36	32	29	28	26	23
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2573	2573	2573
5°	2577	2533	2549
10°	2551	2483	2467
15°	2516	2402	2339
20°	2470	2289	2182
25°	2422	2163	2031
30°	2358	2033	1839
35°	2296	1894	1670
40°	2232	1749	1476
45°	2158	1589	1300
50°	2081	1428	1129
55°	2001	1255	964
60°	1909	1074	794
65°	1802	890	715
70°	1673	718	649
75°	1511	634	592
80°	1276	534	516
85°	889	359	393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3037 cd/sqm

TEST NUMBER: P912214

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	1.9
10°-20°	943.4	5.1
20°-30°	1324.5	7.2
30°-40°	1443.8	7.9
40°-50°	1327.0	7.2
50°-60°	1042.1	5.7
60°-70°	678.3	3.7
70°-80°	349.2	1.9
80°-90°	100.1	0.5
90°-100°	238.7	1.3
100°-110°	758.6	4.1
110°-120°	1298.1	7.1
120°-130°	1707.2	9.3
130°-140°	1916.3	10.5
140°-150°	1879.1	10.2
150°-160°	1576.3	8.6
160°-170°	1045.4	5.7
170°-180°	365.4	2.0
0°-30°	2611.6	14.2
0°-40°	4055.4	22.1
0°-60°	6424.5	35.0
0°-90°	7552.2	41.2
90°-120°	2295.4	12.5
90°-150°	7798.0	42.5
90°-180°	10785.0	58.8
0°-180°	18337.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	3	42	114	107	110	18
95°	170	202	208	208	202	189
105°	700	710	716	722	722	739
115°	1303	1321	1316	1312	1303	1288
125°	1895	1924	1914	1904	1900	1693
135°	2451	2487	2494	2490	2481	1894
145°	2975	2998	3017	3021	3008	1859
155°	3402	3411	3422	3438	3428	1566
165°	3701	3698	3698	3721	3704	1044
175°	3851	3842	3835	3858	3838	366
180°	3858	3858	3858	3858	3858	

TEST NUMBER: P912214

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	3.4	41.9	114.0	107.0	110.5
92.5°	72.1	97.7	101.1	104.7	104.7
95°	169.8	202.4	208.2	208.2	202.4
97.5°	282.7	312.8	325.7	325.7	325.7
100°	412.9	439.6	448.9	448.9	445.5
102.5°	550.2	569.9	582.8	586.2	582.8
105°	700.2	709.5	716.5	722.3	722.3
107.5°	849.1	863.0	863.0	865.4	849.1
110°	993.3	1012.0	1012.0	1012.0	1002.6

TEST NUMBER: P912214

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1149.1	1168.9	1165.4	1156.1	1149.1
115°	1302.7	1321.3	1315.5	1312.1	1302.7
117.5°	1455.1	1480.6	1464.3	1455.1	1445.8
120°	1608.6	1634.2	1608.6	1608.6	1598.2
122.5°	1748.2	1780.7	1764.4	1755.1	1748.2
125°	1894.7	1923.8	1914.5	1904.0	1900.5
127.5°	2037.8	2073.8	2061.1	2047.1	2037.8
130°	2171.5	2213.5	2207.6	2200.6	2187.8
132.5°	2321.6	2354.2	2356.5	2340.2	2330.9
135°	2450.7	2486.7	2493.7	2490.3	2480.9
137.5°	2594.9	2624.0	2629.8	2627.4	2613.6
140°	2721.7	2750.8	2767.1	2767.1	2754.3
142.5°	2852.0	2881.1	2890.4	2893.8	2881.1
145°	2975.2	2998.5	3017.1	3020.6	3007.8
147.5°	3085.8	3114.8	3128.8	3134.6	3121.8
150°	3199.8	3219.5	3232.3	3242.8	3232.3
152.5°	3300.9	3320.7	3337.0	3349.8	3337.0
155°	3402.2	3411.4	3421.9	3438.2	3427.7
157.5°	3489.4	3496.3	3502.1	3525.4	3509.1
160°	3567.3	3574.3	3577.7	3597.6	3583.6
162.5°	3639.4	3639.4	3643.0	3665.0	3648.7
165°	3701.1	3697.5	3697.5	3720.8	3704.5
167.5°	3756.8	3746.4	3746.4	3769.7	3753.4
170°	3798.8	3789.5	3786.0	3809.2	3789.5
172.5°	3827.8	3818.5	3815.1	3838.4	3818.5
175°	3851.1	3841.8	3834.8	3858.1	3838.4
177.5°	3863.9	3854.6	3847.6	3867.4	3847.6
180°	3858.1	3858.1	3858.1	3858.1	3858.1

TEST NUMBER: P912214

CATALOG NUMBER: DFN2DIP-SQ4F0-080D110US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.56	10.32	10.59	11.36	12.75	5.52	6.28	6.55	7.32	8.71
	3H	11.24	11.92	12.28	12.96	14.38	6.70	7.39	7.75	8.43	9.85
	4H	11.84	12.49	12.90	13.54	14.96	7.15	7.80	8.21	8.85	10.27
	6H	12.27	12.86	13.33	13.91	15.35	7.47	8.06	8.54	9.12	10.55
	8H	12.39	12.96	13.46	14.03	15.45	7.56	8.12	8.63	9.19	10.62
	12H	12.45	12.99	13.53	14.05	15.50	7.60	8.14	8.68	9.20	10.65
4H	2H	9.57	10.21	10.63	11.26	12.68	6.11	6.75	7.17	7.80	9.22
	3H	11.40	11.93	12.47	13.01	14.44	7.45	7.99	8.52	9.07	10.50
	4H	12.09	12.58	13.17	13.65	15.10	8.00	8.49	9.08	9.56	11.01
	6H	12.60	13.03	13.69	14.12	15.57	8.42	8.84	9.50	9.93	11.38
	8H	12.78	13.18	13.87	14.26	15.72	8.54	8.94	9.63	10.02	11.49
	12H	12.88	13.23	13.98	14.33	15.80	8.61	8.96	9.71	10.06	11.53
8H	4H	12.05	12.45	13.14	13.53	14.99	8.28	8.67	9.36	9.75	11.22
	6H	12.62	12.95	13.73	14.07	15.53	8.79	9.12	9.90	10.24	11.71
	8H	12.84	13.12	13.95	14.23	15.71	8.99	9.27	10.10	10.38	11.86
	12H	12.98	13.23	14.10	14.33	15.85	9.10	9.35	10.22	10.46	11.98
12H	4H	12.00	12.36	13.10	13.45	14.92	8.28	8.64	9.38	9.73	11.20
	6H	12.60	12.88	13.71	13.99	15.47	8.84	9.13	9.96	10.24	11.72
	8H	12.82	13.07	13.93	14.17	15.69	9.05	9.30	10.17	10.41	11.93

END OF REPORT