

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912226

Luminaire Tested: DFN2DIP-SQ4F0-080D160US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912226
REPORT IS A COMBINATION OF REPORTS P900208 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D160US850-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23245.7 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912226

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912226

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2573	2573	2573
5°	2577	2533	2549
10°	2551	2483	2467
15°	2516	2402	2339
20°	2470	2289	2182
25°	2422	2163	2031
30°	2358	2033	1839
35°	2296	1894	1670
40°	2232	1749	1476
45°	2158	1589	1300
50°	2081	1428	1129
55°	2001	1255	964
60°	1909	1074	794
65°	1802	890	715
70°	1673	718	649
75°	1511	634	592
80°	1276	534	516
85°	889	359	393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 4416 cd/sqm

TEST NUMBER: P912226

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	1.5
10°-20°	943.4	4.1
20°-30°	1324.5	5.7
30°-40°	1443.8	6.2
40°-50°	1327.0	5.7
50°-60°	1042.1	4.5
60°-70°	678.3	2.9
70°-80°	349.2	1.5
80°-90°	105.1	0.5
90°-100°	347.3	1.5
100°-110°	1103.4	4.7
110°-120°	1888.3	8.1
120°-130°	2483.4	10.7
130°-140°	2787.5	12.0
140°-150°	2733.5	11.8
150°-160°	2293.0	9.9
160°-170°	1520.7	6.5
170°-180°	531.5	2.3
0°-30°	2611.6	11.2
0°-40°	4055.4	17.4
0°-60°	6424.5	27.6
0°-90°	7557.1	32.5
90°-120°	3339.0	14.4
90°-150°	11343.4	48.8
90°-180°	15689.0	67.5
0°-180°	23245.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	5	61	166	156	161	23
95°	247	294	303	303	294	275
105°	1018	1032	1042	1051	1051	1075
115°	1895	1922	1914	1908	1895	1874
125°	2756	2798	2785	2770	2765	2463
135°	3565	3617	3628	3622	3609	2756
145°	4328	4362	4389	4394	4375	2704
155°	4949	4962	4978	5001	4986	2278
165°	5384	5379	5379	5412	5389	1519
175°	5602	5588	5578	5612	5583	532
180°	5612	5612	5612	5612	5612	

TEST NUMBER: P912226

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	5.1	60.9	165.8	155.7	160.7
92.5°	104.9	142.2	147.2	152.3	152.3
95°	247.0	294.4	302.9	302.9	294.4
97.5°	411.1	455.1	473.8	473.8	473.8
100°	600.6	639.6	653.1	653.1	648.0
102.5°	800.3	829.1	847.6	852.7	847.6
105°	1018.5	1032.0	1042.2	1050.7	1050.7
107.5°	1235.1	1255.4	1255.4	1258.8	1235.1
110°	1444.9	1472.0	1472.0	1472.0	1458.4

TEST NUMBER: P912226

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1671.6	1700.4	1695.3	1681.8	1671.6
115°	1894.9	1922.0	1913.6	1908.5	1894.9
117.5°	2116.6	2153.8	2130.2	2116.6	2103.1
120°	2340.0	2377.1	2340.0	2340.0	2324.7
122.5°	2542.9	2590.4	2566.7	2553.1	2542.9
125°	2756.2	2798.5	2784.9	2769.7	2764.6
127.5°	2964.2	3016.7	2998.1	2977.8	2964.2
130°	3158.9	3219.8	3211.3	3201.1	3182.5
132.5°	3377.1	3424.5	3427.8	3404.2	3390.7
135°	3564.9	3617.3	3627.5	3622.4	3608.9
137.5°	3774.7	3817.0	3825.5	3822.1	3801.8
140°	3959.1	4001.4	4025.1	4025.1	4006.5
142.5°	4148.7	4190.9	4204.4	4209.5	4190.9
145°	4328.0	4361.8	4388.9	4394.0	4375.3
147.5°	4488.7	4531.0	4551.3	4559.8	4541.1
150°	4654.5	4683.3	4701.9	4717.1	4701.9
152.5°	4801.7	4830.5	4854.2	4872.7	4854.2
155°	4948.9	4962.4	4977.6	5001.4	4986.2
157.5°	5075.8	5086.0	5094.4	5128.2	5104.6
160°	5189.1	5199.3	5204.4	5233.1	5212.9
162.5°	5294.0	5294.0	5299.1	5331.3	5307.6
165°	5383.8	5378.6	5378.6	5412.5	5388.9
167.5°	5464.9	5449.7	5449.7	5483.6	5459.8
170°	5525.8	5512.3	5507.3	5541.1	5512.3
172.5°	5568.2	5554.6	5549.5	5583.4	5554.6
175°	5602.0	5588.5	5578.3	5612.2	5583.4
177.5°	5620.6	5607.1	5596.9	5625.7	5596.9
180°	5612.2	5612.2	5612.2	5612.2	5612.2

TEST NUMBER: P912226

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.54	9.25	9.64	10.34	11.84	4.50	5.21	5.60	6.30	7.80
	3H	10.21	10.84	11.32	11.95	13.47	5.68	6.31	6.79	7.41	8.93
	4H	10.82	11.42	11.94	12.52	14.05	6.13	6.73	7.24	7.83	9.35
	6H	11.24	11.79	12.36	12.89	14.43	6.44	6.99	7.57	8.10	9.63
	8H	11.36	11.89	12.49	13.01	14.54	6.53	7.05	7.66	8.17	9.70
	12H	11.42	11.92	12.56	13.03	14.59	6.57	7.07	7.70	8.18	9.73
4H	2H	8.54	9.14	9.67	10.24	11.77	5.08	5.68	6.21	6.78	8.31
	3H	10.37	10.86	11.50	11.99	13.53	6.42	6.92	7.55	8.05	9.59
	4H	11.06	11.51	12.19	12.63	14.19	6.97	7.43	8.10	8.54	10.10
	6H	11.57	11.96	12.71	13.10	14.65	7.38	7.77	8.52	8.91	10.46
	8H	11.75	12.11	12.89	13.24	14.81	7.51	7.87	8.65	9.01	10.57
	12H	11.84	12.17	12.99	13.31	14.88	7.57	7.90	8.72	9.04	10.61
8H	4H	11.02	11.38	12.16	12.51	14.08	7.24	7.61	8.38	8.74	10.31
	6H	11.58	11.88	12.74	13.06	14.62	7.76	8.06	8.92	9.23	10.80
	8H	11.80	12.06	12.97	13.22	14.80	7.95	8.21	9.11	9.37	10.95
	12H	11.94	12.17	13.11	13.32	14.94	8.06	8.29	9.23	9.44	11.06
12H	4H	10.96	11.29	12.12	12.44	14.01	7.24	7.57	8.40	8.72	10.29
	6H	11.56	11.82	12.72	12.98	14.56	7.81	8.07	8.97	9.22	10.81
	8H	11.78	12.01	12.95	13.16	14.78	8.01	8.24	9.18	9.39	11.01