

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904213

Luminaire Tested: DFN2DIP-SQ4F0-140D120US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904213
REPORT IS A COMBINATION OF REPORTS P901701 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D120US830-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24261.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 233.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904213

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904213

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	52	50
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	38	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	28	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3603	3603	3603
5°	3608	3553	3578
10°	3579	3506	3530
15°	3526	3449	3455
20°	3455	3370	3379
25°	3385	3274	3290
30°	3296	3186	3177
35°	3212	3081	3058
40°	3108	2976	2944
45°	3005	2870	2828
50°	2892	2759	2694
55°	2774	2631	2570
60°	2641	2478	2429
65°	2495	2321	2262
70°	2310	2128	2083
75°	2052	1899	1919
80°	1744	1606	1603
85°	1260	1098	1078

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3005 cd/sqm

TEST NUMBER: P904213

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.3	2.0
10°-20°	1359.7	5.6
20°-30°	1998.2	8.2
30°-40°	2320.8	9.6
40°-50°	2318.0	9.6
50°-60°	2021.2	8.3
60°-70°	1494.1	6.2
70°-80°	845.3	3.5
80°-90°	229.8	0.9
90°-100°	125.9	0.5
100°-110°	469.2	1.9
110°-120°	1244.4	5.1
120°-130°	2064.0	8.5
130°-140°	2192.4	9.0
140°-150°	2037.6	8.4
150°-160°	1638.2	6.8
160°-170°	1055.6	4.4
170°-180°	363.3	1.5
0°-30°	3841.2	15.8
0°-40°	6162.0	25.4
0°-60°	10501.1	43.3
0°-90°	13070.3	53.9
90°-120°	1839.5	7.6
90°-150°	8133.6	33.5
90°-180°	11191.0	46.1
0°-180°	24261.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5134	5134	5134	5134	5134	
5°	5134	5115	5061	5100	5090	487
15°	4888	4858	4794	4814	4789	1377
25°	4424	4384	4300	4310	4300	2036
35°	3816	3767	3688	3658	3634	2383
45°	3106	3071	2997	2943	2923	2397
55°	2350	2320	2261	2202	2178	2101
65°	1585	1555	1506	1461	1437	1567
75°	829	820	795	765	775	885
85°	202	198	193	178	173	226
90°	3	33	55	69	74	22
95°	179	88	108	122	119	212
105°	840	923	169	199	210	897
115°	1588	1635	1704	425	227	1563
125°	2245	2282	2334	2353	2362	2003
135°	2779	2823	2848	2876	2870	2146
145°	3224	3221	3267	3287	3273	2016
155°	3549	3524	3558	3574	3552	1635
165°	3740	3723	3732	3751	3732	1057
175°	3825	3806	3812	3831	3803	364
180°	3817	3817	3817	3817	3817	

TEST NUMBER: P904213

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5134.5	5134.5	5134.5	5134.5	5134.5
2.5°	5164.3	5139.7	5085.2	5134.5	5125.1
5°	5134.5	5115.1	5060.6	5099.9	5090.5
7.5°	5099.9	5070.6	5016.1	5055.9	5045.9
10°	5045.9	5011.4	4952.2	4991.5	4976.8
12.5°	4971.5	4942.2	4883.0	4907.6	4897.7
15°	4887.7	4858.4	4794.0	4813.9	4789.2
17.5°	4784.1	4754.7	4690.3	4714.9	4690.3
20°	4670.4	4641.1	4571.9	4586.6	4567.2
22.5°	4557.2	4512.7	4448.2	4448.2	4438.3
25°	4423.6	4384.3	4300.5	4310.0	4300.5
27.5°	4275.4	4240.9	4177.0	4162.3	4137.7
30°	4127.7	4087.9	4014.0	3999.4	3979.4
32.5°	3969.5	3940.2	3861.0	3831.2	3811.3
35°	3816.5	3767.3	3688.2	3658.4	3633.7
37.5°	3643.7	3599.2	3520.0	3485.5	3460.8
40°	3466.1	3426.3	3347.2	3303.2	3283.3
42.5°	3293.2	3253.5	3174.9	3125.1	3095.8
45°	3105.7	3071.2	2996.8	2942.8	2922.9
47.5°	2922.9	2888.3	2809.2	2754.8	2725.5
50°	2730.2	2705.6	2636.4	2567.2	2542.6
52.5°	2542.6	2508.0	2444.1	2389.6	2355.1
55°	2350.4	2320.5	2261.3	2202.2	2177.6
57.5°	2157.6	2133.0	2068.6	2009.4	1989.4
60°	1964.8	1945.5	1876.3	1821.8	1807.1
62.5°	1777.4	1742.8	1693.5	1644.3	1624.4
65°	1585.1	1555.2	1506.0	1461.4	1436.8
67.5°	1387.6	1362.4	1318.4	1283.8	1263.9
70°	1204.8	1184.9	1140.4	1105.8	1086.4
72.5°	1017.3	997.3	972.7	938.2	923.5
75°	829.2	819.8	794.7	765.3	775.2
77.5°	661.6	641.7	631.7	617.1	602.4
80°	494.0	488.7	478.8	464.1	454.1
82.5°	335.7	335.7	331.0	311.1	311.1
85°	202.2	197.5	192.7	177.6	172.9
87.5°	89.1	79.1	69.2	54.5	49.2
90°	2.6	33.1	55.1	69.2	74.5
92.5°	69.2	58.1	66.3	71.8	74.5
95°	179.4	88.2	107.5	121.7	118.8
97.5°	323.1	96.8	140.7	149.2	151.8
100°	489.0	110.6	157.4	179.4	185.0
102.5°	671.1	665.8	163.0	193.2	201.7
105°	839.6	922.7	168.6	198.8	209.9
107.5°	1035.8	1104.7	174.2	204.3	215.5
110°	1223.7	1281.5	483.4	207.3	218.1



TEST NUMBER: P904213

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1400.5	1450.0	1403.2	212.5	221.0
115°	1588.1	1635.0	1704.2	425.4	226.7
117.5°	1751.1	1806.3	1853.5	1458.2	734.7
120°	1933.5	1974.8	2024.7	2057.9	1684.9
122.5°	2088.0	2132.3	2187.7	2204.1	2207.1
125°	2245.4	2281.5	2334.0	2353.3	2361.5
127.5°	2389.1	2427.8	2469.5	2497.0	2499.6
130°	2524.5	2568.8	2599.0	2629.5	2626.9
132.5°	2662.6	2698.7	2728.8	2753.8	2751.2
135°	2778.7	2823.0	2847.6	2875.5	2869.9
137.5°	2900.1	2933.2	2961.1	2988.6	2980.4
140°	3018.9	3041.1	3071.3	3096.3	3082.5
142.5°	3118.5	3137.9	3173.6	3195.6	3181.8
145°	3223.5	3220.6	3267.4	3286.8	3273.0
147.5°	3314.4	3306.2	3353.1	3366.9	3356.0
150°	3402.9	3383.5	3427.8	3444.2	3430.5
152.5°	3477.3	3455.4	3496.7	3513.4	3494.1
155°	3549.1	3524.5	3557.7	3574.1	3552.2
157.5°	3607.2	3585.2	3610.2	3629.5	3607.2
160°	3657.1	3640.4	3657.1	3673.5	3654.1
162.5°	3701.1	3684.7	3698.4	3717.8	3692.9
165°	3739.7	3723.3	3731.5	3750.9	3731.5
167.5°	3770.3	3753.5	3762.1	3781.4	3756.5
170°	3795.1	3778.5	3784.0	3803.3	3778.5
172.5°	3811.5	3795.1	3800.8	3820.1	3795.1
175°	3825.3	3806.0	3811.5	3831.0	3803.3
177.5°	3831.0	3811.5	3814.6	3833.9	3809.0
180°	3817.2	3817.2	3817.2	3817.2	3817.2

TEST NUMBER: P904213

CATALOG NUMBER: DFN2DIP-SQ4F0-140D120US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.09	12.99	13.01	13.93	15.14	11.64	12.54	12.57	13.48	14.70
	3H	13.76	14.56	14.69	15.51	16.75	13.27	14.07	14.20	15.02	16.26
	4H	14.35	15.11	15.30	16.06	17.31	13.85	14.62	14.80	15.57	16.82
	6H	14.75	15.46	15.71	16.42	17.68	14.25	14.95	15.21	15.92	17.18
	8H	14.86	15.53	15.83	16.51	17.77	14.36	15.03	15.33	16.01	17.26
	12H	14.91	15.55	15.89	16.52	17.80	14.40	15.04	15.38	16.01	17.29
4H	2H	12.55	13.32	13.51	14.27	15.52	12.20	12.96	13.15	13.92	15.16
	3H	14.43	15.06	15.39	16.05	17.31	14.02	14.66	14.99	15.64	16.90
	4H	15.15	15.73	16.12	16.71	17.99	14.72	15.30	15.70	16.28	17.57
	6H	15.67	16.17	16.66	17.17	18.46	15.24	15.74	16.22	16.74	18.02
	8H	15.82	16.29	16.81	17.29	18.58	15.38	15.85	16.37	16.85	18.15
	12H	15.90	16.32	16.91	17.33	18.64	15.45	15.87	16.46	16.88	18.19
8H	4H	15.35	15.81	16.34	16.81	18.11	14.97	15.44	15.96	16.43	17.73
	6H	15.99	16.37	17.00	17.41	18.71	15.60	15.99	16.61	17.03	18.32
	8H	16.21	16.55	17.23	17.57	18.89	15.82	16.16	16.84	17.18	18.50
	12H	16.35	16.65	17.37	17.66	19.02	15.93	16.23	16.96	17.25	18.61
12H	4H	15.33	15.76	16.34	16.77	18.07	14.97	15.39	15.97	16.40	17.71
	6H	16.02	16.36	17.04	17.38	18.70	15.64	15.99	16.67	17.01	18.33
	8H	16.26	16.56	17.29	17.58	18.94	15.88	16.18	16.91	17.20	18.56

END OF REPORT