

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912261

Luminaire Tested: DFN2DIP-SQ4F0-090D160US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912261
REPORT IS A COMBINATION OF REPORTS P901729 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D160US850-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 27447.8 lumens
Efficiency: N/A
Efficacy: 134.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 204.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912261

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912261

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23
5	66	55	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2725	2725	2725
5°	2729	2688	2706
10°	2707	2652	2670
15°	2667	2609	2614
20°	2614	2549	2556
25°	2560	2477	2489
30°	2493	2410	2403
35°	2429	2331	2313
40°	2351	2251	2227
45°	2273	2171	2139
50°	2188	2087	2037
55°	2098	1990	1944
60°	1997	1874	1837
65°	1887	1755	1711
70°	1747	1610	1575
75°	1553	1436	1451
80°	1319	1214	1213
85°	953	831	815

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3210 cd/sqm

TEST NUMBER: P912261

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	1.3
10°-20°	1028.5	3.7
20°-30°	1511.4	5.5
30°-40°	1755.4	6.4
40°-50°	1753.3	6.4
50°-60°	1528.8	5.6
60°-70°	1130.1	4.1
70°-80°	639.4	2.3
80°-90°	179.3	0.7
90°-100°	197.5	0.7
100°-110°	736.1	2.7
110°-120°	1952.3	7.1
120°-130°	3238.0	11.8
130°-140°	3439.5	12.5
140°-150°	3196.6	11.6
150°-160°	2570.0	9.4
160°-170°	1656.0	6.0
170°-180°	570.0	2.1
0°-30°	2905.4	10.6
0°-40°	4660.9	17.0
0°-60°	7942.9	28.9
0°-90°	9891.7	36.0
90°-120°	2885.9	10.5
90°-150°	12760.0	46.5
90°-180°	17556.0	64.0
0°-180°	27447.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3884	3884	3884	3884	3884	
5°	3884	3869	3828	3858	3850	369
15°	3697	3675	3626	3641	3622	1041
25°	3346	3316	3253	3260	3253	1540
35°	2887	2850	2790	2767	2748	1803
45°	2349	2323	2267	2226	2211	1813
55°	1778	1755	1710	1666	1647	1589
65°	1199	1176	1139	1106	1087	1185
75°	627	620	601	579	586	670
85°	153	149	146	134	131	171
90°	4	52	86	109	117	25
95°	282	138	169	191	186	333
105°	1317	1448	264	312	329	1407
115°	2492	2565	2674	667	356	2453
125°	3523	3579	3662	3692	3705	3142
135°	4359	4429	4467	4511	4502	3367
145°	5057	5052	5126	5156	5135	3163
155°	5568	5529	5581	5607	5573	2566
165°	5867	5841	5854	5884	5854	1658
175°	6001	5971	5980	6010	5967	571
180°	5988	5988	5988	5988	5988	

TEST NUMBER: P912261

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3883.6	3883.6	3883.6	3883.6	3883.6
2.5°	3906.2	3887.6	3846.5	3883.6	3876.5
5°	3883.6	3869.0	3827.8	3857.5	3850.3
7.5°	3857.5	3835.4	3794.1	3824.3	3816.7
10°	3816.7	3790.6	3745.8	3775.5	3764.4
12.5°	3760.4	3738.2	3693.5	3712.0	3704.6
15°	3697.1	3674.9	3626.1	3641.2	3622.5
17.5°	3618.6	3596.4	3547.7	3566.3	3547.7
20°	3532.6	3510.4	3458.1	3469.2	3454.5
22.5°	3447.0	3413.4	3364.6	3364.6	3357.1
25°	3346.0	3316.2	3252.9	3260.0	3252.9
27.5°	3233.8	3207.7	3159.4	3148.3	3129.7
30°	3122.2	3092.0	3036.1	3025.0	3010.0
32.5°	3002.5	2980.3	2920.4	2897.9	2882.8
35°	2886.8	2849.6	2789.7	2767.2	2748.5
37.5°	2756.1	2722.4	2662.5	2636.4	2617.8
40°	2621.7	2591.6	2531.7	2498.5	2483.5
42.5°	2490.9	2460.9	2401.4	2363.8	2341.7
45°	2349.1	2323.0	2266.7	2225.9	2210.9
47.5°	2210.9	2184.7	2124.8	2083.7	2061.5
50°	2065.1	2046.4	1994.1	1941.9	1923.2
52.5°	1923.2	1897.1	1848.7	1807.6	1781.4
55°	1777.8	1755.2	1710.4	1665.7	1647.1
57.5°	1632.0	1613.4	1564.7	1519.9	1504.8
60°	1486.2	1471.5	1419.2	1378.0	1367.0
62.5°	1344.3	1318.2	1280.9	1243.7	1228.7
65°	1198.9	1176.3	1139.1	1105.5	1086.8
67.5°	1049.6	1030.6	997.2	971.2	956.1
70°	911.3	896.2	862.6	836.4	821.8
72.5°	769.4	754.3	735.7	709.6	698.6
75°	627.3	620.0	601.1	578.9	586.4
77.5°	500.4	485.4	477.9	466.8	455.7
80°	373.6	369.6	362.1	351.0	343.6
82.5°	254.0	254.0	250.4	235.3	235.3
85°	152.9	149.4	145.8	134.3	130.8
87.5°	67.3	59.8	52.3	41.3	37.3
90°	4.1	52.0	86.4	108.6	116.8
92.5°	108.6	91.0	103.9	112.7	116.8
95°	281.5	138.4	168.8	190.9	186.3
97.5°	506.8	151.8	220.7	234.1	238.2
100°	767.2	173.4	247.0	281.5	290.2
102.5°	1052.8	1044.6	255.7	303.1	316.4
105°	1317.3	1447.5	264.5	311.9	329.3
107.5°	1624.9	1733.0	273.3	320.6	338.0
110°	1919.8	2010.4	758.4	325.2	342.1

TEST NUMBER: P912261

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	2197.2	2274.9	2201.3	333.5	346.8
115°	2491.5	2565.0	2673.6	667.4	355.5
117.5°	2747.2	2833.6	2907.8	2287.8	1152.6
120°	3033.3	3098.1	3176.3	3228.3	2643.3
122.5°	3275.7	3345.1	3432.0	3457.8	3462.4
125°	3522.6	3579.2	3661.6	3692.0	3704.8
127.5°	3748.0	3808.7	3874.1	3917.3	3921.4
130°	3960.6	4030.0	4077.3	4125.1	4121.0
132.5°	4177.2	4233.7	4281.1	4320.2	4316.1
135°	4359.3	4428.8	4467.4	4511.1	4502.3
137.5°	4549.7	4601.7	4645.4	4688.6	4675.8
140°	4736.0	4770.9	4818.3	4857.4	4835.8
142.5°	4892.4	4922.7	4978.9	5013.3	4991.7
145°	5057.0	5052.4	5126.0	5156.3	5134.8
147.5°	5199.5	5186.7	5260.3	5281.9	5264.9
150°	5338.5	5308.1	5377.7	5403.4	5381.8
152.5°	5455.3	5420.8	5485.7	5512.0	5481.6
155°	5568.0	5529.4	5581.4	5607.1	5572.6
157.5°	5659.1	5624.6	5663.7	5694.0	5659.1
160°	5737.3	5711.0	5737.3	5763.0	5732.6
162.5°	5806.3	5780.6	5802.1	5832.5	5793.4
165°	5866.9	5841.2	5854.1	5884.5	5854.1
167.5°	5914.9	5888.6	5902.0	5932.3	5893.2
170°	5953.9	5927.7	5936.4	5966.8	5927.7
172.5°	5979.6	5953.9	5962.6	5993.0	5953.9
175°	6001.2	5970.9	5979.6	6010.0	5966.8
177.5°	6010.0	5979.6	5984.3	6014.7	5975.5
180°	5988.4	5988.4	5988.4	5988.4	5988.4

TEST NUMBER: P912261

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.32	10.07	10.39	11.14	12.59	8.87	9.62	9.94	10.69	12.15
	3H	10.97	11.64	12.05	12.72	14.20	10.48	11.15	11.56	12.23	13.71
	4H	11.56	12.20	12.65	13.28	14.76	11.07	11.70	12.15	12.78	14.26
	6H	11.96	12.54	13.06	13.63	15.12	11.46	12.04	12.55	13.13	14.62
	8H	12.06	12.62	13.16	13.72	15.21	11.56	12.12	12.66	13.22	14.70
	12H	12.11	12.64	13.21	13.73	15.24	11.60	12.13	12.70	13.22	14.73
4H	2H	9.77	10.40	10.86	11.48	12.96	9.41	10.05	10.51	11.13	12.61
	3H	11.63	12.16	12.73	13.26	14.76	11.22	11.75	12.32	12.86	14.35
	4H	12.34	12.83	13.45	13.92	15.44	11.92	12.40	13.02	13.50	15.02
	6H	12.85	13.27	13.97	14.39	15.90	12.42	12.84	13.53	13.96	15.47
	8H	13.00	13.39	14.12	14.50	16.03	12.56	12.95	13.68	14.07	15.59
	12H	13.07	13.42	14.20	14.55	16.08	12.62	12.98	13.75	14.10	15.63
8H	4H	12.53	12.92	13.64	14.03	15.55	12.15	12.54	13.27	13.65	15.18
	6H	13.16	13.48	14.29	14.64	16.16	12.78	13.10	13.91	14.25	15.77
	8H	13.38	13.66	14.52	14.80	16.34	12.99	13.27	14.13	14.41	15.95
	12H	13.51	13.76	14.66	14.89	16.47	13.10	13.35	14.25	14.48	16.06
12H	4H	12.51	12.86	13.64	13.99	15.52	12.14	12.49	13.27	13.62	15.15
	6H	13.19	13.47	14.33	14.60	16.15	12.82	13.10	13.96	14.23	15.77
	8H	13.43	13.68	14.57	14.81	16.38	13.05	13.30	14.19	14.43	16.00