

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904233

Luminaire Tested: DFN2DIP-SQ4F0-160D080US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904233
REPORT IS A COMBINATION OF REPORTS P901631 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D080US830-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22394.8 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 226.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904233

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904233

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4117	4117	4117
5°	4124	4061	4089
10°	4090	4007	4034
15°	4030	3942	3949
20°	3949	3851	3862
25°	3868	3742	3760
30°	3767	3641	3631
35°	3671	3521	3495
40°	3552	3401	3365
45°	3434	3280	3232
50°	3305	3153	3078
55°	3171	3007	2937
60°	3018	2832	2776
65°	2852	2652	2585
70°	2640	2432	2380
75°	2346	2170	2193
80°	1993	1835	1832
85°	1440	1255	1231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3434 cd/sqm

TEST NUMBER: P904233

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.3	2.5
10°-20°	1553.9	6.9
20°-30°	2283.7	10.2
30°-40°	2652.4	11.8
40°-50°	2649.1	11.8
50°-60°	2309.9	10.3
60°-70°	1707.5	7.6
70°-80°	966.1	4.3
80°-90°	259.5	1.2
90°-100°	83.9	0.4
100°-110°	312.8	1.4
110°-120°	829.6	3.7
120°-130°	1376.0	6.1
130°-140°	1461.6	6.5
140°-150°	1358.4	6.1
150°-160°	1092.1	4.9
160°-170°	703.7	3.1
170°-180°	242.2	1.1
0°-30°	4389.9	19.6
0°-40°	7042.3	31.4
0°-60°	12001.3	53.6
0°-90°	14934.3	66.7
90°-120°	1226.4	5.5
90°-150°	5422.4	24.2
90°-180°	7460.0	33.3
0°-180°	22394.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5868	5868	5868	5868	5868	
5°	5868	5846	5784	5828	5818	557
15°	5586	5552	5479	5502	5473	1573
25°	5056	5011	4915	4926	4915	2326
35°	4362	4306	4215	4181	4153	2724
45°	3549	3510	3425	3363	3340	2739
55°	2686	2652	2584	2517	2489	2402
65°	1812	1777	1721	1670	1642	1791
75°	948	937	908	875	886	1012
85°	231	226	220	203	198	258
90°	2	22	37	46	50	21
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	

TEST NUMBER: P904233

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5868.0	5868.0	5868.0	5868.0	5868.0
2.5°	5902.1	5873.9	5811.7	5868.0	5857.1
5°	5868.0	5845.8	5783.5	5828.5	5817.7
7.5°	5828.5	5794.9	5732.6	5778.2	5766.8
10°	5766.8	5727.3	5659.7	5704.5	5687.8
12.5°	5681.8	5648.3	5580.6	5608.8	5597.4
15°	5586.0	5552.5	5478.8	5501.6	5473.4
17.5°	5467.5	5433.9	5360.3	5388.4	5360.3
20°	5337.5	5304.1	5225.0	5241.8	5219.6
22.5°	5208.3	5157.4	5083.7	5083.7	5072.4
25°	5055.6	5010.7	4914.9	4925.7	4914.9
27.5°	4886.1	4846.6	4773.6	4756.9	4728.7
30°	4717.3	4671.9	4587.4	4570.7	4548.0
32.5°	4536.6	4503.1	4412.6	4378.5	4355.8
35°	4361.8	4305.5	4215.0	4180.9	4152.8
37.5°	4164.2	4113.3	4023.0	3983.4	3955.3
40°	3961.2	3915.8	3825.4	3775.1	3752.4
42.5°	3763.8	3718.2	3628.4	3571.6	3538.0
45°	3549.4	3509.8	3424.9	3363.2	3340.5
47.5°	3340.5	3301.0	3210.6	3148.3	3114.8
50°	3120.2	3092.0	3013.0	2933.9	2905.9
52.5°	2905.9	2866.4	2793.3	2731.0	2691.5
55°	2686.2	2652.0	2584.4	2516.7	2488.6
57.5°	2465.9	2437.7	2364.1	2296.4	2273.7
60°	2245.5	2223.4	2144.4	2082.1	2065.3
62.5°	2031.2	1991.7	1935.4	1879.1	1856.4
65°	1811.5	1777.4	1721.1	1670.3	1642.1
67.5°	1585.8	1557.1	1506.8	1467.3	1444.5
70°	1376.9	1354.2	1303.3	1263.8	1241.6
72.5°	1162.5	1139.8	1111.7	1072.1	1055.5
75°	947.6	936.9	908.1	874.6	886.0
77.5°	756.1	733.4	722.0	705.2	688.4
80°	564.5	558.6	547.1	530.4	519.1
82.5°	383.7	383.7	378.3	355.6	355.6
85°	231.1	225.6	220.3	202.9	197.6
87.5°	101.8	90.4	79.0	62.3	56.3
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4



TEST NUMBER: P904233

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8

TEST NUMBER: P904233

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.61	14.65	14.41	15.47	16.48	13.17	14.20	13.97	15.03	16.04
	3H	15.29	16.22	16.10	17.05	18.09	14.80	15.73	15.61	16.56	17.60
	4H	15.89	16.77	16.72	17.61	18.66	15.40	16.27	16.23	17.11	18.16
	6H	16.30	17.11	17.14	17.96	19.02	15.80	16.61	16.64	17.46	18.52
	8H	16.41	17.19	17.26	18.05	19.12	15.91	16.68	16.76	17.55	18.61
	12H	16.47	17.20	17.33	18.06	19.16	15.96	16.70	16.82	17.55	18.65
4H	2H	14.10	14.97	14.93	15.81	16.86	13.74	14.62	14.58	15.46	16.51
	3H	15.98	16.72	16.83	17.59	18.65	15.57	16.31	16.42	17.18	18.25
	4H	16.71	17.37	17.57	18.24	19.34	16.28	16.95	17.14	17.82	18.91
	6H	17.24	17.81	18.11	18.71	19.80	16.80	17.38	17.68	18.28	19.37
	8H	17.39	17.93	18.27	18.82	19.93	16.96	17.49	17.83	18.38	19.49
	12H	17.48	17.96	18.37	18.87	19.99	17.03	17.51	17.92	18.42	19.54
8H	4H	16.92	17.46	17.80	18.35	19.46	16.54	17.08	17.42	17.97	19.08
	6H	17.56	18.01	18.47	18.94	20.05	17.18	17.62	18.08	18.56	19.67
	8H	17.79	18.18	18.70	19.11	20.23	17.39	17.79	18.31	18.71	19.84
	12H	17.93	18.28	18.85	19.19	20.37	17.52	17.87	18.44	18.78	19.96
12H	4H	16.91	17.40	17.81	18.31	19.42	16.54	17.03	17.44	17.94	19.05
	6H	17.59	17.99	18.51	18.91	20.04	17.22	17.62	18.14	18.54	19.67
	8H	17.85	18.20	18.76	19.11	20.29	17.47	17.82	18.38	18.73	19.91