

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904248

Luminaire Tested: DFN2DIP-SQ4F0-160D120US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904248
REPORT IS A COMBINATION OF REPORTS P900183 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D120US830-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24939.6 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 256.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904248

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904248

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4117	4117	4117
5°	4124	4061	4089
10°	4090	4007	4034
15°	4030	3942	3949
20°	3949	3851	3862
25°	3868	3742	3760
30°	3767	3641	3631
35°	3671	3521	3495
40°	3552	3401	3365
45°	3434	3280	3232
50°	3305	3153	3078
55°	3171	3007	2937
60°	3018	2832	2776
65°	2852	2652	2585
70°	2640	2432	2380
75°	2346	2170	2193
80°	1993	1835	1832
85°	1440	1255	1231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3434 cd/sqm

TEST NUMBER: P904248

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.3	2.2
10°-20°	1553.9	6.2
20°-30°	2283.7	9.2
30°-40°	2652.4	10.6
40°-50°	2649.1	10.6
50°-60°	2309.9	9.3
60°-70°	1707.5	6.8
70°-80°	966.1	3.9
80°-90°	265.1	1.1
90°-100°	221.3	0.9
100°-110°	703.3	2.8
110°-120°	1203.6	4.8
120°-130°	1582.9	6.3
130°-140°	1776.7	7.1
140°-150°	1742.3	7.0
150°-160°	1461.5	5.9
160°-170°	969.3	3.9
170°-180°	338.8	1.4
0°-30°	4389.9	17.6
0°-40°	7042.3	28.2
0°-60°	12001.3	48.1
0°-90°	14940.0	59.9
90°-120°	2128.2	8.5
90°-150°	7230.1	29.0
90°-180°	10000.0	40.1
0°-180°	24939.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5868	5868	5868	5868	5868	
5°	5868	5846	5784	5828	5818	557
15°	5586	5552	5479	5502	5473	1573
25°	5056	5011	4915	4926	4915	2326
35°	4362	4306	4215	4181	4153	2724
45°	3549	3510	3425	3363	3340	2739
55°	2686	2652	2584	2517	2489	2402
65°	1812	1777	1721	1670	1642	1791
75°	948	937	908	875	886	1012
85°	231	226	220	203	198	258
90°	3	39	106	99	102	24
95°	157	188	193	193	188	175
105°	649	658	664	670	670	685
115°	1208	1225	1220	1216	1208	1195
125°	1757	1784	1775	1765	1762	1570
135°	2272	2306	2312	2309	2300	1756
145°	2758	2780	2797	2801	2789	1724
155°	3154	3163	3173	3188	3178	1452
165°	3432	3428	3428	3450	3435	968
175°	3571	3562	3556	3577	3559	339
180°	3577	3577	3577	3577	3577	

TEST NUMBER: P904248

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5868.0	5868.0	5868.0	5868.0	5868.0
2.5°	5902.1	5873.9	5811.7	5868.0	5857.1
5°	5868.0	5845.8	5783.5	5828.5	5817.7
7.5°	5828.5	5794.9	5732.6	5778.2	5766.8
10°	5766.8	5727.3	5659.7	5704.5	5687.8
12.5°	5681.8	5648.3	5580.6	5608.8	5597.4
15°	5586.0	5552.5	5478.8	5501.6	5473.4
17.5°	5467.5	5433.9	5360.3	5388.4	5360.3
20°	5337.5	5304.1	5225.0	5241.8	5219.6
22.5°	5208.3	5157.4	5083.7	5083.7	5072.4
25°	5055.6	5010.7	4914.9	4925.7	4914.9
27.5°	4886.1	4846.6	4773.6	4756.9	4728.7
30°	4717.3	4671.9	4587.4	4570.7	4548.0
32.5°	4536.6	4503.1	4412.6	4378.5	4355.8
35°	4361.8	4305.5	4215.0	4180.9	4152.8
37.5°	4164.2	4113.3	4023.0	3983.4	3955.3
40°	3961.2	3915.8	3825.4	3775.1	3752.4
42.5°	3763.8	3718.2	3628.4	3571.6	3538.0
45°	3549.4	3509.8	3424.9	3363.2	3340.5
47.5°	3340.5	3301.0	3210.6	3148.3	3114.8
50°	3120.2	3092.0	3013.0	2933.9	2905.9
52.5°	2905.9	2866.4	2793.3	2731.0	2691.5
55°	2686.2	2652.0	2584.4	2516.7	2488.6
57.5°	2465.9	2437.7	2364.1	2296.4	2273.7
60°	2245.5	2223.4	2144.4	2082.1	2065.3
62.5°	2031.2	1991.7	1935.4	1879.1	1856.4
65°	1811.5	1777.4	1721.1	1670.3	1642.1
67.5°	1585.8	1557.1	1506.8	1467.3	1444.5
70°	1376.9	1354.2	1303.3	1263.8	1241.6
72.5°	1162.5	1139.8	1111.7	1072.1	1055.5
75°	947.6	936.9	908.1	874.6	886.0
77.5°	756.1	733.4	722.0	705.2	688.4
80°	564.5	558.6	547.1	530.4	519.1
82.5°	383.7	383.7	378.3	355.6	355.6
85°	231.1	225.6	220.3	202.9	197.6
87.5°	101.8	90.4	79.0	62.3	56.3
90°	3.2	38.8	105.7	99.2	102.5
92.5°	66.8	90.6	93.8	97.1	97.1
95°	157.4	187.7	193.0	193.0	187.7
97.5°	262.0	290.1	302.0	302.0	302.0
100°	382.9	407.6	416.2	416.2	413.0
102.5°	510.1	528.4	540.3	543.6	540.3
105°	649.2	657.8	664.3	669.7	669.7
107.5°	787.2	800.2	800.2	802.3	787.2
110°	921.0	938.2	938.2	938.2	929.6

TEST NUMBER: P904248

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.4	1083.8	1080.5	1072.0	1065.4
115°	1207.8	1225.1	1219.6	1216.4	1207.8
117.5°	1349.1	1372.8	1357.7	1349.1	1340.5
120°	1491.5	1515.1	1491.5	1491.5	1481.8
122.5°	1620.9	1651.1	1636.0	1627.3	1620.9
125°	1756.7	1783.7	1775.1	1765.4	1762.1
127.5°	1889.4	1922.8	1910.9	1898.0	1889.4
130°	2013.4	2052.2	2046.8	2040.3	2028.4
132.5°	2152.5	2182.7	2184.8	2169.7	2161.2
135°	2272.2	2305.6	2312.2	2308.9	2300.3
137.5°	2405.9	2432.9	2438.3	2436.1	2423.2
140°	2523.5	2550.4	2565.5	2565.5	2553.6
142.5°	2644.3	2671.3	2679.8	2683.0	2671.3
145°	2758.5	2780.1	2797.4	2800.7	2788.8
147.5°	2861.0	2887.9	2901.0	2906.3	2894.5
150°	2966.7	2985.0	2996.9	3006.6	2996.9
152.5°	3060.5	3078.8	3094.0	3105.9	3094.0
155°	3154.3	3163.0	3172.7	3187.8	3178.1
157.5°	3235.3	3241.7	3247.1	3268.6	3253.6
160°	3307.5	3314.0	3317.2	3335.6	3322.6
162.5°	3374.3	3374.3	3377.6	3398.1	3383.0
165°	3431.5	3428.3	3428.3	3449.8	3434.7
167.5°	3483.3	3473.6	3473.6	3495.1	3480.1
170°	3522.1	3513.4	3510.2	3531.8	3513.4
172.5°	3549.0	3540.4	3537.2	3558.8	3540.4
175°	3570.6	3562.0	3555.6	3577.0	3558.8
177.5°	3582.5	3573.8	3567.3	3585.7	3567.3
180°	3577.0	3577.0	3577.0	3577.0	3577.0

TEST NUMBER: P904248

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.07	14.03	13.93	14.91	16.04	12.62	13.58	13.49	14.47	15.59
	3H	14.74	15.60	15.62	16.50	17.65	14.25	15.11	15.13	16.01	17.16
	4H	15.33	16.15	16.23	17.05	18.21	14.84	15.65	15.74	16.56	17.71
	6H	15.74	16.49	16.65	17.40	18.57	15.24	15.99	16.15	16.90	18.07
	8H	15.85	16.57	16.77	17.49	18.66	15.35	16.06	16.26	16.99	18.16
	12H	15.91	16.59	16.83	17.51	18.70	15.40	16.08	16.32	17.00	18.19
4H	2H	13.54	14.35	14.44	15.26	16.42	13.19	14.00	14.09	14.90	16.06
	3H	15.42	16.10	16.33	17.03	18.21	15.01	15.69	15.92	16.63	17.80
	4H	16.14	16.76	17.06	17.69	18.89	15.72	16.34	16.64	17.27	18.47
	6H	16.67	17.20	17.60	18.16	19.35	16.23	16.77	17.17	17.72	18.92
	8H	16.82	17.32	17.76	18.27	19.48	16.38	16.88	17.32	17.83	19.04
	12H	16.90	17.35	17.86	18.32	19.54	16.45	16.90	17.41	17.87	19.09
8H	4H	16.35	16.85	17.28	17.79	19.01	15.97	16.47	16.91	17.42	18.63
	6H	16.99	17.40	17.95	18.39	19.60	16.60	17.02	17.57	18.01	19.22
	8H	17.21	17.58	18.18	18.56	19.79	16.82	17.18	17.79	18.16	19.39
	12H	17.35	17.67	18.33	18.65	19.92	16.94	17.26	17.92	18.23	19.51
12H	4H	16.34	16.79	17.29	17.75	18.97	15.97	16.42	16.93	17.39	18.60
	6H	17.02	17.38	17.99	18.36	19.59	16.65	17.01	17.62	17.99	19.22
	8H	17.27	17.59	18.24	18.56	19.84	16.89	17.21	17.86	18.18	19.46