

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912329

Luminaire Tested: DFN2DIP-SQ4F0-110D140US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912329
REPORT IS A COMBINATION OF REPORTS P901715 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D140US850-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 27447.7 lumens
Efficiency: N/A
Efficacy: 130.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 210.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912329

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912329

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3331	3331	3331
5°	3336	3285	3307
10°	3309	3241	3263
15°	3260	3189	3194
20°	3194	3115	3124
25°	3129	3027	3042
30°	3047	2945	2937
35°	2969	2849	2827
40°	2873	2751	2722
45°	2778	2653	2615
50°	2674	2551	2490
55°	2565	2432	2376
60°	2441	2291	2245
65°	2307	2145	2091
70°	2135	1968	1925
75°	1897	1755	1774
80°	1612	1484	1482
85°	1165	1016	996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2809 cd/sqm

TEST NUMBER: P912329

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.8	1.6
10°-20°	1257.0	4.6
20°-30°	1847.3	6.7
30°-40°	2145.5	7.8
40°-50°	2142.9	7.8
50°-60°	1868.5	6.8
60°-70°	1381.3	5.0
70°-80°	781.5	2.8
80°-90°	215.5	0.8
90°-100°	172.8	0.6
100°-110°	644.1	2.3
110°-120°	1708.2	6.2
120°-130°	2833.3	10.3
130°-140°	3009.6	11.0
140°-150°	2797.1	10.2
150°-160°	2248.8	8.2
160°-170°	1449.0	5.3
170°-180°	498.7	1.8
0°-30°	3551.1	12.9
0°-40°	5696.6	20.8
0°-60°	9708.0	35.4
0°-90°	12086.2	44.0
90°-120°	2525.1	9.2
90°-150°	11165.0	40.7
90°-180°	15362.0	56.0
0°-180°	27447.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4747	4747	4747	4747	4747	
5°	4747	4729	4678	4715	4706	451
15°	4519	4491	4432	4450	4428	1273
25°	4090	4053	3976	3984	3976	1882
35°	3528	3483	3410	3382	3359	2203
45°	2871	2839	2770	2721	2702	2216
55°	2173	2145	2091	2036	2013	1943
65°	1465	1438	1392	1351	1328	1449
75°	766	758	735	708	717	818
85°	187	182	178	164	160	209
90°	4	46	76	95	102	25
95°	246	121	148	167	163	292
105°	1153	1266	231	273	288	1231
115°	2180	2244	2339	584	311	2146
125°	3082	3132	3204	3230	3242	2749
135°	3814	3875	3909	3947	3940	2947
145°	4425	4421	4485	4512	4493	2767
155°	4872	4838	4884	4906	4876	2245
165°	5134	5111	5122	5149	5122	1450
175°	5251	5224	5232	5259	5221	500
180°	5240	5240	5240	5240	5240	

TEST NUMBER: P912329

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US850-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4746.7	4746.7	4746.7	4746.7	4746.7
2.5°	4774.2	4751.5	4701.2	4746.7	4738.0
5°	4746.7	4728.8	4678.4	4714.7	4706.0
7.5°	4714.7	4687.6	4637.3	4674.1	4664.9
10°	4664.9	4632.8	4578.2	4614.4	4600.9
12.5°	4596.1	4569.0	4514.3	4537.0	4527.8
15°	4518.6	4491.4	4431.9	4450.3	4427.6
17.5°	4422.7	4395.6	4336.1	4358.8	4336.1
20°	4317.7	4290.5	4226.6	4240.2	4222.3
22.5°	4213.1	4171.8	4112.3	4112.3	4103.1
25°	4089.5	4053.3	3975.8	3984.5	3975.8
27.5°	3952.5	3920.5	3861.4	3847.9	3825.2
30°	3816.0	3779.1	3710.8	3697.3	3678.9
32.5°	3669.7	3642.6	3569.4	3541.8	3523.4
35°	3528.3	3482.8	3409.6	3382.0	3359.3
37.5°	3368.5	3327.3	3254.2	3222.2	3199.5
40°	3204.3	3167.5	3094.4	3053.7	3035.3
42.5°	3044.5	3007.7	2935.1	2889.1	2862.0
45°	2871.2	2839.2	2770.4	2720.6	2702.2
47.5°	2702.2	2670.3	2597.1	2546.7	2519.5
50°	2524.0	2501.2	2437.2	2373.4	2350.6
52.5°	2350.6	2318.6	2259.6	2209.1	2177.2
55°	2172.9	2145.2	2090.6	2035.8	2013.1
57.5°	1994.6	1971.9	1912.4	1857.6	1839.2
60°	1816.4	1798.6	1734.6	1684.2	1670.7
62.5°	1643.1	1611.2	1565.6	1520.1	1501.7
65°	1465.3	1437.7	1392.2	1351.1	1328.4
67.5°	1282.8	1259.6	1218.9	1187.0	1168.6
70°	1113.8	1095.4	1054.2	1022.3	1004.3
72.5°	940.4	922.0	899.3	867.3	853.7
75°	766.5	757.9	734.6	707.5	716.7
77.5°	611.6	593.2	584.0	570.5	556.9
80°	456.7	451.8	442.6	429.1	419.9
82.5°	310.4	310.4	306.1	287.7	287.7
85°	187.0	182.5	178.2	164.1	159.8
87.5°	82.3	73.1	63.9	50.3	45.5
90°	3.5	45.5	75.6	95.0	102.2
92.5°	95.0	79.7	90.9	98.6	102.2
95°	246.3	121.1	147.7	167.0	163.0
97.5°	443.5	132.9	193.2	204.8	208.5
100°	671.3	151.7	216.1	246.3	254.0
102.5°	921.1	913.9	223.8	265.2	276.9
105°	1152.6	1266.5	231.4	272.8	288.1
107.5°	1421.8	1516.3	239.1	280.5	295.8
110°	1679.8	1759.1	663.6	284.6	299.4

TEST NUMBER: P912329

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1922.5	1990.4	1926.1	291.8	303.4
115°	2180.1	2244.4	2339.4	584.0	311.1
117.5°	2403.8	2479.4	2544.3	2001.7	1008.5
120°	2654.2	2710.8	2779.3	2824.7	2312.8
122.5°	2866.2	2927.0	3003.1	3025.6	3029.7
125°	3082.4	3131.8	3203.9	3230.4	3241.7
127.5°	3279.5	3332.7	3389.8	3427.6	3431.2
130°	3465.4	3526.3	3567.7	3609.6	3605.9
132.5°	3655.0	3704.5	3746.0	3780.1	3776.6
135°	3814.4	3875.2	3908.9	3947.2	3939.5
137.5°	3981.0	4026.4	4064.7	4102.5	4091.3
140°	4144.0	4174.6	4216.0	4250.2	4231.3
142.5°	4280.9	4307.4	4356.5	4386.6	4367.7
145°	4424.9	4420.8	4485.2	4511.9	4492.9
147.5°	4549.7	4538.4	4602.8	4621.6	4606.8
150°	4671.2	4644.6	4705.4	4727.9	4709.0
152.5°	4773.4	4743.2	4800.0	4822.9	4796.3
155°	4871.9	4838.2	4883.7	4906.2	4876.1
157.5°	4951.7	4921.5	4955.8	4982.3	4951.7
160°	5020.1	4997.2	5020.1	5042.6	5016.1
162.5°	5080.4	5057.9	5076.9	5103.4	5069.2
165°	5133.6	5111.0	5122.4	5148.9	5122.4
167.5°	5175.5	5152.5	5164.2	5190.8	5156.5
170°	5209.6	5186.7	5194.3	5221.0	5186.7
172.5°	5232.2	5209.6	5217.3	5243.9	5209.6
175°	5251.1	5224.5	5232.2	5258.8	5221.0
177.5°	5258.8	5232.2	5236.3	5262.8	5228.6
180°	5239.8	5239.8	5239.8	5239.8	5239.8

TEST NUMBER: P912329

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.89	11.70	11.89	12.71	14.07	10.44	11.25	11.45	12.27	13.62
	3H	12.55	13.27	13.56	14.30	15.67	12.06	12.78	13.07	13.81	15.18
	4H	13.14	13.82	14.17	14.85	16.23	12.64	13.33	13.67	14.36	15.74
	6H	13.54	14.17	14.58	15.20	16.60	13.04	13.67	14.08	14.70	16.10
	8H	13.64	14.24	14.69	15.29	16.68	13.14	13.74	14.18	14.79	16.18
	12H	13.69	14.26	14.74	15.31	16.72	13.18	13.75	14.23	14.80	16.21
4H	2H	11.34	12.03	12.38	13.06	14.44	10.99	11.68	12.02	12.70	14.09
	3H	13.21	13.78	14.25	14.84	16.23	12.80	13.37	13.84	14.43	15.83
	4H	13.92	14.45	14.97	15.50	16.92	13.50	14.03	14.55	15.07	16.49
	6H	14.44	14.89	15.50	15.96	17.38	14.01	14.46	15.07	15.53	16.94
	8H	14.59	15.01	15.65	16.08	17.51	14.15	14.58	15.22	15.64	17.07
	12H	14.66	15.05	15.74	16.12	17.56	14.21	14.60	15.29	15.67	17.11
8H	4H	14.12	14.54	15.18	15.60	17.03	13.74	14.16	14.80	15.23	16.65
	6H	14.75	15.10	15.84	16.21	17.63	14.37	14.72	15.45	15.82	17.25
	8H	14.97	15.28	16.07	16.37	17.81	14.58	14.89	15.67	15.98	17.42
	12H	15.11	15.38	16.20	16.46	17.94	14.70	14.96	15.79	16.05	17.53
12H	4H	14.10	14.48	15.18	15.56	16.99	13.73	14.11	14.81	15.19	16.63
	6H	14.78	15.09	15.87	16.18	17.62	14.41	14.72	15.50	15.80	17.25
	8H	15.02	15.29	16.12	16.38	17.86	14.64	14.91	15.74	16.00	17.48

END OF REPORT