

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904256

Luminaire Tested: DFN2DIP-SQ4F0-160D160US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904256
REPORT IS A COMBINATION OF REPORTS P900219 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D160US830-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28277.2 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 288.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904256

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904256

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4117	4117	4117
5°	4124	4061	4089
10°	4090	4007	4034
15°	4030	3942	3949
20°	3949	3851	3862
25°	3868	3742	3760
30°	3767	3641	3631
35°	3671	3521	3495
40°	3552	3401	3365
45°	3434	3280	3232
50°	3305	3153	3078
55°	3171	3007	2937
60°	3018	2832	2776
65°	2852	2652	2585
70°	2640	2432	2380
75°	2346	2170	2193
80°	1993	1835	1832
85°	1440	1255	1231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3754 cd/sqm

TEST NUMBER: P904256

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.3	2.0
10°-20°	1553.9	5.5
20°-30°	2283.7	8.1
30°-40°	2652.4	9.4
40°-50°	2649.1	9.4
50°-60°	2309.9	8.2
60°-70°	1707.5	6.0
70°-80°	966.1	3.4
80°-90°	268.5	0.9
90°-100°	295.1	1.0
100°-110°	937.8	3.3
110°-120°	1604.9	5.7
120°-130°	2110.7	7.5
130°-140°	2369.1	8.4
140°-150°	2323.2	8.2
150°-160°	1948.8	6.9
160°-170°	1292.4	4.6
170°-180°	451.7	1.6
0°-30°	4389.9	15.5
0°-40°	7042.3	24.9
0°-60°	12001.3	42.4
0°-90°	14943.4	52.8
90°-120°	2837.8	10.0
90°-150°	9640.8	34.1
90°-180°	13334.0	47.2
0°-180°	28277.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5868	5868	5868	5868	5868	
5°	5868	5846	5784	5828	5818	557
15°	5586	5552	5479	5502	5473	1573
25°	5056	5011	4915	4926	4915	2326
35°	4362	4306	4215	4181	4153	2724
45°	3549	3510	3425	3363	3340	2739
55°	2686	2652	2584	2517	2489	2402
65°	1812	1777	1721	1670	1642	1791
75°	948	937	908	875	886	1012
85°	231	226	220	203	198	258
90°	4	52	141	132	137	27
95°	210	250	257	257	250	234
105°	866	877	886	893	893	914
115°	1610	1634	1626	1622	1610	1593
125°	2342	2378	2367	2354	2350	2093
135°	3030	3074	3083	3079	3067	2342
145°	3678	3707	3730	3734	3719	2298
155°	4206	4218	4230	4251	4238	1936
165°	4576	4571	4571	4600	4580	1291
175°	4761	4750	4741	4770	4745	452
180°	4770	4770	4770	4770	4770	

TEST NUMBER: P904256

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5868.0	5868.0	5868.0	5868.0	5868.0
2.5°	5902.1	5873.9	5811.7	5868.0	5857.1
5°	5868.0	5845.8	5783.5	5828.5	5817.7
7.5°	5828.5	5794.9	5732.6	5778.2	5766.8
10°	5766.8	5727.3	5659.7	5704.5	5687.8
12.5°	5681.8	5648.3	5580.6	5608.8	5597.4
15°	5586.0	5552.5	5478.8	5501.6	5473.4
17.5°	5467.5	5433.9	5360.3	5388.4	5360.3
20°	5337.5	5304.1	5225.0	5241.8	5219.6
22.5°	5208.3	5157.4	5083.7	5083.7	5072.4
25°	5055.6	5010.7	4914.9	4925.7	4914.9
27.5°	4886.1	4846.6	4773.6	4756.9	4728.7
30°	4717.3	4671.9	4587.4	4570.7	4548.0
32.5°	4536.6	4503.1	4412.6	4378.5	4355.8
35°	4361.8	4305.5	4215.0	4180.9	4152.8
37.5°	4164.2	4113.3	4023.0	3983.4	3955.3
40°	3961.2	3915.8	3825.4	3775.1	3752.4
42.5°	3763.8	3718.2	3628.4	3571.6	3538.0
45°	3549.4	3509.8	3424.9	3363.2	3340.5
47.5°	3340.5	3301.0	3210.6	3148.3	3114.8
50°	3120.2	3092.0	3013.0	2933.9	2905.9
52.5°	2905.9	2866.4	2793.3	2731.0	2691.5
55°	2686.2	2652.0	2584.4	2516.7	2488.6
57.5°	2465.9	2437.7	2364.1	2296.4	2273.7
60°	2245.5	2223.4	2144.4	2082.1	2065.3
62.5°	2031.2	1991.7	1935.4	1879.1	1856.4
65°	1811.5	1777.4	1721.1	1670.3	1642.1
67.5°	1585.8	1557.1	1506.8	1467.3	1444.5
70°	1376.9	1354.2	1303.3	1263.8	1241.6
72.5°	1162.5	1139.8	1111.7	1072.1	1055.5
75°	947.6	936.9	908.1	874.6	886.0
77.5°	756.1	733.4	722.0	705.2	688.4
80°	564.5	558.6	547.1	530.4	519.1
82.5°	383.7	383.7	378.3	355.6	355.6
85°	231.1	225.6	220.3	202.9	197.6
87.5°	101.8	90.4	79.0	62.3	56.3
90°	4.3	51.7	140.9	132.3	136.6
92.5°	89.2	120.8	125.1	129.4	129.4
95°	209.9	250.2	257.4	257.4	250.2
97.5°	349.4	386.8	402.7	402.7	402.7
100°	510.5	543.6	555.1	555.1	550.7
102.5°	680.1	704.6	720.4	724.7	720.4
105°	865.6	877.1	885.8	893.0	893.0
107.5°	1049.7	1067.0	1067.0	1069.9	1049.7
110°	1228.0	1251.0	1251.0	1251.0	1239.5

TEST NUMBER: P904256

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US830-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1420.7	1445.2	1440.9	1429.4	1420.7
115°	1610.5	1633.5	1626.4	1622.0	1610.5
117.5°	1798.9	1830.5	1810.4	1798.9	1787.4
120°	1988.8	2020.3	1988.8	1988.8	1975.8
122.5°	2161.2	2201.6	2181.4	2169.9	2161.2
125°	2342.5	2378.4	2366.9	2354.0	2349.7
127.5°	2519.3	2563.9	2548.1	2530.8	2519.3
130°	2684.7	2736.5	2729.3	2720.6	2704.8
132.5°	2870.2	2910.5	2913.3	2893.2	2881.7
135°	3029.8	3074.4	3083.1	3078.7	3067.2
137.5°	3208.1	3244.0	3251.3	3248.4	3231.1
140°	3364.9	3400.8	3421.0	3421.0	3405.1
142.5°	3526.0	3561.9	3573.4	3577.7	3561.9
145°	3678.4	3707.1	3730.1	3734.4	3718.6
147.5°	3814.9	3850.9	3868.2	3875.4	3859.5
150°	3955.8	3980.4	3996.2	4009.1	3996.2
152.5°	4081.0	4105.4	4125.6	4141.3	4125.6
155°	4206.1	4217.6	4230.5	4250.7	4237.8
157.5°	4313.9	4322.6	4329.8	4358.5	4338.4
160°	4410.2	4418.9	4423.3	4447.7	4430.4
162.5°	4499.4	4499.4	4503.7	4531.1	4510.9
165°	4575.7	4571.3	4571.3	4600.1	4580.0
167.5°	4644.7	4631.7	4631.7	4660.5	4640.3
170°	4696.4	4684.9	4680.7	4709.4	4684.9
172.5°	4732.4	4720.9	4716.6	4745.3	4720.9
175°	4761.2	4749.7	4741.0	4769.8	4745.3
177.5°	4777.0	4765.5	4756.8	4781.3	4756.8
180°	4769.8	4769.8	4769.8	4769.8	4769.8

TEST NUMBER: P904256

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.46	13.35	13.39	14.30	15.53	12.02	12.90	12.95	13.85	15.08
	3H	14.13	14.92	15.07	15.88	17.13	13.64	14.43	14.58	15.39	16.64
	4H	14.72	15.47	15.68	16.43	17.70	14.22	14.98	15.18	15.94	17.20
	6H	15.12	15.82	16.09	16.79	18.06	14.62	15.32	15.59	16.29	17.56
	8H	15.23	15.89	16.21	16.88	18.15	14.73	15.39	15.70	16.38	17.65
	12H	15.28	15.91	16.26	16.89	18.19	14.77	15.40	15.75	16.38	17.68
4H	2H	12.92	13.68	13.89	14.64	15.90	12.57	13.32	13.53	14.29	15.55
	3H	14.80	15.43	15.77	16.42	17.70	14.39	15.02	15.36	16.01	17.29
	4H	15.52	16.09	16.50	17.08	18.38	15.09	15.67	16.07	16.65	17.95
	6H	16.04	16.53	17.03	17.54	18.84	15.60	16.10	16.60	17.11	18.41
	8H	16.19	16.65	17.19	17.66	18.97	15.75	16.21	16.75	17.22	18.53
	12H	16.27	16.68	17.28	17.70	19.02	15.82	16.23	16.83	17.25	18.57
8H	4H	15.72	16.18	16.71	17.18	18.49	15.34	15.80	16.33	16.80	18.12
	6H	16.35	16.74	17.37	17.78	19.09	15.97	16.35	16.99	17.40	18.71
	8H	16.58	16.91	17.61	17.95	19.28	16.18	16.52	17.21	17.55	18.88
	12H	16.71	17.01	17.75	18.04	19.41	16.30	16.60	17.33	17.62	19.00
12H	4H	15.70	16.12	16.72	17.14	18.46	15.33	15.75	16.35	16.77	18.09
	6H	16.38	16.72	17.41	17.75	19.08	16.01	16.35	17.04	17.38	18.71
	8H	16.63	16.93	17.66	17.95	19.33	16.25	16.55	17.28	17.57	18.95

END OF REPORT