

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912385

Luminaire Tested: DFN2DIP-SQ4F0-140D090US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912385
REPORT IS A COMBINATION OF REPORTS P901647 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D090US850-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25251.9 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 210.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912385

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912385

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	58	57	56
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	51	49	47
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4239	4239	4239
5°	4246	4181	4209
10°	4211	4125	4153
15°	4149	4058	4066
20°	4066	3965	3976
25°	3982	3853	3871
30°	3878	3748	3739
35°	3779	3626	3598
40°	3657	3501	3464
45°	3536	3377	3328
50°	3403	3246	3169
55°	3264	3095	3024
60°	3107	2916	2858
65°	2936	2731	2661
70°	2717	2504	2450
75°	2415	2234	2258
80°	2051	1890	1886
85°	1483	1293	1268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3536 cd/sqm

TEST NUMBER: P912385

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	568.6	2.3
10°-20°	1599.8	6.3
20°-30°	2351.1	9.3
30°-40°	2730.7	10.8
40°-50°	2727.3	10.8
50°-60°	2378.1	9.4
60°-70°	1757.9	7.0
70°-80°	994.6	3.9
80°-90°	268.4	1.1
90°-100°	111.1	0.4
100°-110°	414.0	1.6
110°-120°	1098.2	4.3
120°-130°	1821.4	7.2
130°-140°	1934.7	7.7
140°-150°	1798.1	7.1
150°-160°	1445.6	5.7
160°-170°	931.5	3.7
170°-180°	320.6	1.3
0°-30°	4519.6	17.9
0°-40°	7250.2	28.7
0°-60°	12355.7	48.9
0°-90°	15376.7	60.9
90°-120°	1623.3	6.4
90°-150°	7177.5	28.4
90°-180°	9875.0	39.1
0°-180°	25251.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6041	6041	6041	6041	6041	
5°	6041	6018	5954	6001	5990	573
15°	5751	5716	5641	5664	5635	1620
25°	5205	5159	5060	5071	5060	2395
35°	4491	4433	4340	4304	4275	2804
45°	3654	3614	3526	3462	3439	2820
55°	2766	2730	2661	2591	2562	2472
65°	1865	1830	1772	1720	1691	1844
75°	976	965	935	900	912	1042
85°	238	232	227	209	203	265
90°	2	29	49	61	66	23
95°	158	78	95	107	105	188
105°	741	814	149	175	185	792
115°	1401	1443	1504	375	200	1380
125°	1982	2013	2060	2077	2084	1767
135°	2452	2491	2513	2538	2533	1894
145°	2845	2842	2883	2900	2888	1779
155°	3132	3110	3140	3154	3135	1443
165°	3300	3286	3293	3310	3293	932
175°	3376	3359	3364	3381	3356	321
180°	3368	3368	3368	3368	3368	

TEST NUMBER: P912385

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6041.3	6041.3	6041.3	6041.3	6041.3
2.5°	6076.3	6047.4	5983.3	6041.3	6030.2
5°	6041.3	6018.4	5954.3	6000.6	5989.5
7.5°	6000.6	5966.1	5902.0	5948.8	5937.0
10°	5937.0	5896.4	5826.8	5873.0	5855.7
12.5°	5849.5	5815.0	5745.4	5774.3	5762.7
15°	5750.9	5716.5	5640.6	5664.1	5635.1
17.5°	5629.0	5594.5	5518.6	5547.6	5518.6
20°	5495.2	5460.7	5379.3	5396.6	5373.8
22.5°	5362.0	5309.7	5233.8	5233.8	5222.2
25°	5204.9	5158.6	5060.0	5071.1	5060.0
27.5°	5030.4	4989.8	4914.6	4897.3	4868.4
30°	4856.6	4809.8	4722.9	4705.7	4682.2
32.5°	4670.6	4636.1	4542.9	4507.9	4484.4
35°	4490.6	4432.7	4339.5	4304.5	4275.4
37.5°	4287.2	4234.8	4141.7	4101.1	4072.0
40°	4078.2	4031.4	3938.3	3886.6	3863.1
42.5°	3874.8	3828.0	3735.6	3677.0	3642.5
45°	3654.2	3613.6	3526.1	3462.5	3439.1
47.5°	3439.1	3398.4	3305.4	3241.3	3206.8
50°	3212.3	3183.4	3102.0	3020.6	2991.6
52.5°	2991.6	2950.9	2875.7	2811.6	2771.1
55°	2765.5	2730.4	2660.7	2591.1	2562.1
57.5°	2538.6	2509.7	2433.9	2364.3	2340.8
60°	2311.8	2289.1	2207.7	2143.6	2126.3
62.5°	2091.2	2050.5	1992.5	1934.7	1911.3
65°	1865.0	1829.8	1772.0	1719.5	1690.6
67.5°	1632.7	1603.1	1551.3	1510.6	1487.2
70°	1417.5	1394.1	1341.8	1301.1	1278.2
72.5°	1196.9	1173.4	1144.5	1103.9	1086.6
75°	975.7	964.6	935.0	900.5	912.2
77.5°	778.4	755.0	743.3	726.1	708.8
80°	581.2	575.0	563.4	546.1	534.3
82.5°	395.0	395.0	389.5	366.1	366.1
85°	237.9	232.3	226.8	208.9	203.4
87.5°	104.8	93.0	81.4	64.1	57.9
90°	2.3	29.3	48.6	61.1	65.7
92.5°	61.1	51.2	58.4	63.4	65.7
95°	158.4	77.9	94.9	107.4	104.8
97.5°	285.1	85.4	124.2	131.6	134.0
100°	431.5	97.6	139.0	158.4	163.2
102.5°	592.2	587.5	143.8	170.5	178.0
105°	740.9	814.2	148.7	175.4	185.2
107.5°	914.0	974.8	153.7	180.3	190.2
110°	1079.8	1130.8	426.6	182.9	192.5

TEST NUMBER: P912385

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1235.9	1279.6	1238.2	187.5	195.1
115°	1401.4	1442.8	1503.9	375.4	200.0
117.5°	1545.3	1594.0	1635.6	1286.9	648.3
120°	1706.2	1742.7	1786.7	1815.9	1486.8
122.5°	1842.6	1881.6	1930.5	1945.0	1947.6
125°	1981.5	2013.3	2059.6	2076.7	2083.9
127.5°	2108.2	2142.4	2179.2	2203.5	2205.8
130°	2227.8	2266.9	2293.5	2320.4	2318.1
132.5°	2349.6	2381.5	2408.1	2430.2	2427.8
135°	2452.1	2491.1	2512.9	2537.5	2532.6
137.5°	2559.2	2588.4	2613.0	2637.3	2630.1
140°	2663.9	2683.7	2710.3	2732.2	2720.2
142.5°	2752.0	2769.1	2800.6	2820.0	2807.9
145°	2844.6	2841.9	2883.4	2900.5	2888.3
147.5°	2924.8	2917.6	2958.9	2971.1	2961.5
150°	3003.0	2985.9	3024.9	3039.3	3027.2
152.5°	3068.6	3049.2	3085.7	3100.4	3083.4
155°	3132.0	3110.3	3139.5	3154.0	3134.6
157.5°	3183.3	3163.9	3185.8	3202.9	3183.3
160°	3227.2	3212.4	3227.2	3241.7	3224.6
162.5°	3266.0	3251.5	3263.7	3280.8	3258.8
165°	3300.2	3285.6	3293.0	3310.0	3293.0
167.5°	3327.1	3312.4	3319.8	3336.9	3314.9
170°	3349.1	3334.3	3339.2	3356.3	3334.3
172.5°	3363.6	3349.1	3353.9	3371.0	3349.1
175°	3375.7	3358.6	3363.6	3380.6	3356.3
177.5°	3380.6	3363.6	3366.1	3383.2	3361.3
180°	3368.5	3368.5	3368.5	3368.5	3368.5

TEST NUMBER: P912385

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.25	14.22	14.11	15.10	16.21	12.81	13.78	13.66	14.65	15.76
	3H	14.92	15.79	15.79	16.68	17.82	14.43	15.30	15.30	16.19	17.32
	4H	15.52	16.34	16.41	17.24	18.38	15.03	15.85	15.91	16.74	17.88
	6H	15.93	16.69	16.83	17.59	18.74	15.43	16.19	16.33	17.09	18.24
	8H	16.04	16.76	16.94	17.68	18.83	15.54	16.26	16.44	17.18	18.33
	12H	16.09	16.78	17.00	17.69	18.87	15.58	16.27	16.49	17.18	18.36
4H	2H	13.73	14.55	14.62	15.44	16.59	13.37	14.19	14.26	15.09	16.23
	3H	15.61	16.29	16.51	17.22	18.38	15.20	15.88	16.10	16.81	17.97
	4H	16.33	16.95	17.24	17.88	19.06	15.90	16.53	16.82	17.45	18.64
	6H	16.85	17.39	17.78	18.34	19.52	16.42	16.96	17.35	17.91	19.09
	8H	17.01	17.51	17.94	18.45	19.65	16.57	17.08	17.50	18.02	19.21
	12H	17.09	17.54	18.04	18.50	19.71	16.64	17.09	17.59	18.05	19.26
8H	4H	16.53	17.04	17.46	17.98	19.18	16.16	16.66	17.09	17.60	18.80
	6H	17.17	17.59	18.13	18.57	19.77	16.79	17.21	17.75	18.19	19.39
	8H	17.40	17.77	18.36	18.74	19.96	17.01	17.38	17.97	18.35	19.56
	12H	17.54	17.86	18.51	18.83	20.09	17.13	17.45	18.10	18.42	19.68
12H	4H	16.52	16.98	17.47	17.94	19.14	16.16	16.61	17.11	17.57	18.77
	6H	17.21	17.58	18.17	18.55	19.76	16.83	17.20	17.80	18.18	19.39
	8H	17.46	17.78	18.42	18.75	20.01	17.08	17.40	18.04	18.37	19.63