

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906728

Luminaire Tested: DFN2DIP-SQ4F0-070D140US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906728
REPORT IS A COMBINATION OF REPORTS P900187 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D140US835-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19320.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 167.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906728

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906728

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1911	1911	1911
5°	1914	1885	1898
10°	1899	1860	1873
15°	1871	1830	1833
20°	1833	1788	1792
25°	1795	1737	1746
30°	1748	1690	1686
35°	1704	1635	1622
40°	1649	1579	1562
45°	1594	1523	1500
50°	1534	1464	1429
55°	1472	1396	1363
60°	1401	1315	1288
65°	1324	1231	1200
70°	1225	1129	1105
75°	1089	1007	1018
80°	925	852	850
85°	669	583	571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3485 cd/sqm

TEST NUMBER: P906728

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	1.3
10°-20°	721.3	3.7
20°-30°	1060.0	5.5
30°-40°	1231.1	6.4
40°-50°	1229.6	6.4
50°-60°	1072.2	5.5
60°-70°	792.6	4.1
70°-80°	448.4	2.3
80°-90°	130.9	0.7
90°-100°	274.0	1.4
100°-110°	870.6	4.5
110°-120°	1489.8	7.7
120°-130°	1959.3	10.1
130°-140°	2199.2	11.4
140°-150°	2156.6	11.2
150°-160°	1809.1	9.4
160°-170°	1199.7	6.2
170°-180°	419.3	2.2
0°-30°	2037.7	10.5
0°-40°	3268.8	16.9
0°-60°	5570.6	28.8
0°-90°	6942.6	35.9
90°-120°	2634.3	13.6
90°-150°	8949.3	46.3
90°-180°	12377.0	64.1
0°-180°	19320.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	120
90°	4	48	131	123	127	19
95°	195	232	239	239	232	217
105°	804	814	822	829	829	848
115°	1495	1516	1510	1506	1495	1479
125°	2174	2208	2197	2185	2181	1943
135°	2812	2854	2862	2858	2847	2174
145°	3414	3441	3463	3467	3452	2133
155°	3904	3915	3927	3946	3934	1797
165°	4248	4244	4244	4270	4252	1198
175°	4420	4409	4401	4428	4405	420
180°	4428	4428	4428	4428	4428	

TEST NUMBER: P906728

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	4.0	48.1	130.8	122.8	126.8
92.5°	82.8	112.1	116.1	120.1	120.1
95°	194.9	232.3	238.9	238.9	232.3
97.5°	324.4	359.1	373.8	373.8	373.8
100°	473.9	504.6	515.2	515.2	511.2
102.5°	631.4	654.1	668.8	672.8	668.8
105°	803.6	814.3	822.3	828.9	828.9
107.5°	974.4	990.5	990.5	993.1	974.4
110°	1140.0	1161.3	1161.3	1161.3	1150.6

TEST NUMBER: P906728

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US835-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1318.8	1341.5	1337.5	1326.8	1318.8
115°	1495.0	1516.4	1509.7	1505.7	1495.0
117.5°	1669.9	1699.3	1680.6	1669.9	1659.2
120°	1846.1	1875.5	1846.1	1846.1	1834.1
122.5°	2006.3	2043.6	2025.0	2014.3	2006.3
125°	2174.5	2207.8	2197.1	2185.1	2181.1
127.5°	2338.6	2380.0	2365.3	2349.3	2338.6
130°	2492.1	2540.2	2533.5	2525.5	2510.8
132.5°	2664.3	2701.7	2704.4	2685.7	2675.0
135°	2812.5	2853.9	2861.9	2857.9	2847.2
137.5°	2978.0	3011.4	3018.1	3015.4	2999.4
140°	3123.5	3156.9	3175.6	3175.6	3160.9
142.5°	3273.0	3306.4	3317.1	3321.1	3306.4
145°	3414.5	3441.2	3462.6	3466.6	3451.9
147.5°	3541.3	3574.7	3590.7	3597.4	3582.7
150°	3672.1	3694.8	3709.5	3721.5	3709.5
152.5°	3788.3	3811.0	3829.7	3844.3	3829.7
155°	3904.4	3915.1	3927.1	3945.8	3933.8
157.5°	4004.5	4012.5	4019.2	4045.9	4027.2
160°	4094.0	4102.0	4106.0	4128.7	4112.6
162.5°	4176.7	4176.7	4180.7	4206.1	4187.4
165°	4247.5	4243.5	4243.5	4270.2	4251.5
167.5°	4311.5	4299.5	4299.5	4326.2	4307.5
170°	4359.6	4348.9	4344.9	4371.6	4348.9
172.5°	4393.0	4382.3	4378.3	4405.0	4382.3
175°	4419.7	4409.0	4401.0	4427.7	4405.0
177.5°	4434.3	4423.7	4415.7	4438.3	4415.7
180°	4427.7	4427.7	4427.7	4427.7	4427.7

TEST NUMBER: P906728

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.07	8.82	9.14	9.89	11.35	7.63	8.37	8.70	9.44	10.90
	3H	9.73	10.40	10.81	11.48	12.95	9.24	9.91	10.31	10.99	12.46
	4H	10.31	10.95	11.40	12.03	13.51	9.82	10.45	10.91	11.53	13.02
	6H	10.71	11.29	11.81	12.38	13.87	10.21	10.79	11.31	11.88	13.37
	8H	10.81	11.37	11.92	12.47	13.96	10.31	10.87	11.41	11.97	13.46
	12H	10.86	11.39	11.97	12.48	13.99	10.35	10.88	11.46	11.97	13.48
4H	2H	8.52	9.15	9.61	10.24	11.72	8.16	8.80	9.26	9.88	11.36
	3H	10.38	10.91	11.48	12.02	13.51	9.97	10.50	11.07	11.61	13.11
	4H	11.09	11.58	12.20	12.68	14.19	10.67	11.15	11.78	12.25	13.77
	6H	11.60	12.02	12.72	13.14	14.65	11.17	11.59	12.29	12.71	14.22
	8H	11.75	12.14	12.87	13.26	14.78	11.32	11.71	12.43	12.82	14.34
	12H	11.82	12.18	12.96	13.30	14.83	11.37	11.73	12.51	12.85	14.38
8H	4H	11.28	11.67	12.39	12.78	14.31	10.90	11.29	12.02	12.41	13.93
	6H	11.91	12.23	13.05	13.39	14.91	11.53	11.85	12.66	13.00	14.53
	8H	12.13	12.42	13.28	13.55	15.09	11.74	12.02	12.88	13.16	14.70
	12H	12.26	12.51	13.41	13.64	15.22	11.85	12.10	13.00	13.23	14.81
12H	4H	11.26	11.61	12.39	12.74	14.27	10.89	11.24	12.02	12.37	13.90
	6H	11.94	12.22	13.08	13.36	14.90	11.57	11.85	12.71	12.99	14.53
	8H	12.18	12.43	13.33	13.56	15.14	11.80	12.05	12.95	13.18	14.76