

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912407

Luminaire Tested: DFN2DIP-SQ4F0-140D160US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912407
REPORT IS A COMBINATION OF REPORTS P901738 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D160US850-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 30763.7 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 265.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912407

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912407

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	44	43
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4503	4503	4503
5°	4510	4432	4461
10°	4465	4346	4317
15°	4403	4203	4094
20°	4322	4006	3819
25°	4239	3785	3554
30°	4127	3558	3218
35°	4017	3314	2922
40°	3906	3061	2583
45°	3776	2781	2276
50°	3642	2498	1975
55°	3502	2195	1686
60°	3340	1879	1389
65°	3154	1557	1252
70°	2928	1257	1135
75°	2644	1110	1035
80°	2234	934	903
85°	1555	628	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3776 cd/sqm

TEST NUMBER: P912407

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	601.4	2.0
10°-20°	1651.0	5.4
20°-30°	2317.9	7.5
30°-40°	2526.6	8.2
40°-50°	2322.3	7.5
50°-60°	1823.8	5.9
60°-70°	1187.1	3.9
70°-80°	611.1	2.0
80°-90°	166.5	0.5
90°-100°	197.5	0.6
100°-110°	736.1	2.4
110°-120°	1952.3	6.3
120°-130°	3238.0	10.5
130°-140°	3439.5	11.2
140°-150°	3196.6	10.4
150°-160°	2570.0	8.4
160°-170°	1656.0	5.4
170°-180°	570.0	1.9
0°-30°	4570.2	14.9
0°-40°	7096.9	23.1
0°-60°	11242.9	36.5
0°-90°	13207.6	42.9
90°-120°	2885.9	9.4
90°-150°	12760.0	41.5
90°-180°	17556.0	57.1
0°-180°	30763.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6417	6417	6417	6417	6417	
5°	6417	6388	6312	6365	6347	608
15°	6103	6039	5842	5732	5674	1720
25°	5540	5354	4971	4733	4646	2548
35°	4774	4477	3967	3601	3472	2988
45°	3902	3513	2904	2491	2352	3014
55°	2967	2514	1887	1539	1429	2651
65°	2004	1533	1010	813	795	1986
75°	1068	662	465	424	418	1130
85°	250	128	110	110	110	286
90°	4	52	86	109	117	29
95°	282	138	169	191	186	333
105°	1317	1448	264	312	329	1407
115°	2492	2565	2674	667	356	2453
125°	3523	3579	3662	3692	3705	3142
135°	4359	4429	4467	4511	4502	3367
145°	5057	5052	5126	5156	5135	3163
155°	5568	5529	5581	5607	5573	2566
165°	5867	5841	5854	5884	5854	1658
175°	6001	5971	5980	6010	5967	571
180°	5988	5988	5988	5988	5988	

TEST NUMBER: P912407

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6416.9	6416.9	6416.9	6416.9	6416.9
2.5°	6445.8	6416.9	6352.8	6411.4	6399.6
5°	6416.9	6388.0	6312.1	6364.6	6347.3
7.5°	6364.6	6330.0	6248.7	6271.5	6242.6
10°	6294.9	6254.2	6138.4	6120.5	6086.0
12.5°	6208.0	6155.6	5998.5	5964.0	5900.0
15°	6103.3	6039.2	5842.0	5731.8	5673.9
17.5°	5981.3	5888.2	5644.3	5516.7	5423.7
20°	5842.0	5725.5	5435.4	5290.6	5162.5
22.5°	5691.1	5557.4	5220.4	5023.2	4936.4
25°	5540.1	5354.0	4970.9	4733.0	4645.5
27.5°	5360.2	5162.5	4738.5	4465.6	4332.0
30°	5168.6	4947.5	4482.9	4187.1	4030.0
32.5°	4982.5	4715.1	4239.5	3890.8	3745.4
35°	4773.7	4477.4	3966.6	3600.6	3472.4
37.5°	4570.4	4250.6	3710.8	3309.8	3165.0
40°	4355.4	4007.3	3443.4	3031.3	2880.4
42.5°	4134.8	3763.3	3176.7	2746.7	2601.8
45°	3902.5	3513.1	2903.8	2490.9	2351.7
47.5°	3681.9	3269.8	2642.5	2229.8	2102.2
50°	3437.9	3025.8	2386.8	1985.8	1864.3
52.5°	3199.5	2763.8	2142.8	1759.7	1649.3
55°	2967.2	2514.3	1887.2	1539.1	1428.7
57.5°	2729.4	2264.8	1661.1	1335.8	1242.7
60°	2485.4	2020.8	1422.6	1126.9	1033.8
62.5°	2247.6	1783.1	1219.3	940.8	894.6
65°	2003.6	1532.9	1010.4	813.2	795.4
67.5°	1771.3	1300.6	813.2	714.1	696.8
70°	1527.3	1074.5	673.4	615.5	592.1
72.5°	1295.1	865.0	563.2	516.9	505.3
75°	1068.3	661.7	464.6	423.9	418.3
77.5°	842.3	470.1	366.0	342.6	330.8
80°	632.8	337.0	278.5	255.7	255.7
82.5°	441.2	226.7	191.6	179.9	179.9
85°	249.5	127.5	110.2	110.2	110.2
87.5°	93.0	46.2	46.2	40.7	40.7
90°	4.1	52.0	86.4	108.6	116.8
92.5°	108.6	91.0	103.9	112.7	116.8
95°	281.5	138.4	168.8	190.9	186.3
97.5°	506.8	151.8	220.7	234.1	238.2
100°	767.2	173.4	247.0	281.5	290.2
102.5°	1052.8	1044.6	255.7	303.1	316.4
105°	1317.3	1447.5	264.5	311.9	329.3
107.5°	1624.9	1733.0	273.3	320.6	338.0
110°	1919.8	2010.4	758.4	325.2	342.1

TEST NUMBER: P912407

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	2197.2	2274.9	2201.3	333.5	346.8
115°	2491.5	2565.0	2673.6	667.4	355.5
117.5°	2747.2	2833.6	2907.8	2287.8	1152.6
120°	3033.3	3098.1	3176.3	3228.3	2643.3
122.5°	3275.7	3345.1	3432.0	3457.8	3462.4
125°	3522.6	3579.2	3661.6	3692.0	3704.8
127.5°	3748.0	3808.7	3874.1	3917.3	3921.4
130°	3960.6	4030.0	4077.3	4125.1	4121.0
132.5°	4177.2	4233.7	4281.1	4320.2	4316.1
135°	4359.3	4428.8	4467.4	4511.1	4502.3
137.5°	4549.7	4601.7	4645.4	4688.6	4675.8
140°	4736.0	4770.9	4818.3	4857.4	4835.8
142.5°	4892.4	4922.7	4978.9	5013.3	4991.7
145°	5057.0	5052.4	5126.0	5156.3	5134.8
147.5°	5199.5	5186.7	5260.3	5281.9	5264.9
150°	5338.5	5308.1	5377.7	5403.4	5381.8
152.5°	5455.3	5420.8	5485.7	5512.0	5481.6
155°	5568.0	5529.4	5581.4	5607.1	5572.6
157.5°	5659.1	5624.6	5663.7	5694.0	5659.1
160°	5737.3	5711.0	5737.3	5763.0	5732.6
162.5°	5806.3	5780.6	5802.1	5832.5	5793.4
165°	5866.9	5841.2	5854.1	5884.5	5854.1
167.5°	5914.9	5888.6	5902.0	5932.3	5893.2
170°	5953.9	5927.7	5936.4	5966.8	5927.7
172.5°	5979.6	5953.9	5962.6	5993.0	5953.9
175°	6001.2	5970.9	5979.6	6010.0	5966.8
177.5°	6010.0	5979.6	5984.3	6014.7	5975.5
180°	5988.4	5988.4	5988.4	5988.4	5988.4

TEST NUMBER: P912407

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	12.47	12.71	13.49	14.86	7.65	8.43	8.67	9.45	10.82
	3H	13.37	14.06	14.40	15.10	16.49	8.84	9.53	9.87	10.56	11.96
	4H	13.98	14.63	15.02	15.67	17.07	9.28	9.94	10.33	10.98	12.38
	6H	14.40	15.00	15.45	16.04	17.46	9.60	10.21	10.66	11.25	12.66
	8H	14.53	15.10	15.59	16.16	17.56	9.69	10.27	10.75	11.32	12.73
	12H	14.59	15.13	15.65	16.18	17.61	9.73	10.28	10.80	11.33	12.76
4H	2H	11.70	12.36	12.75	13.39	14.79	8.24	8.90	9.29	9.94	11.33
	3H	13.53	14.08	14.59	15.14	16.55	9.59	10.13	10.65	11.20	12.61
	4H	14.22	14.72	15.29	15.78	17.21	10.13	10.63	11.20	11.69	13.12
	6H	14.74	15.17	15.81	16.25	17.68	10.55	10.98	11.63	12.06	13.49
	8H	14.92	15.32	15.99	16.39	17.83	10.68	11.08	11.75	12.15	13.60
	12H	15.01	15.37	16.10	16.46	17.91	10.74	11.10	11.83	12.19	13.64
8H	4H	14.19	14.59	15.26	15.66	17.10	10.41	10.81	11.49	11.89	13.33
	6H	14.76	15.09	15.85	16.20	17.64	10.93	11.26	12.03	12.38	13.82
	8H	14.98	15.27	16.08	16.36	17.82	11.12	11.41	12.23	12.51	13.97
	12H	15.12	15.37	16.22	16.46	17.96	11.24	11.49	12.35	12.59	14.09
12H	4H	14.14	14.50	15.23	15.58	17.03	10.42	10.78	11.51	11.86	13.31
	6H	14.73	15.02	15.83	16.12	17.58	10.98	11.27	12.08	12.37	13.83
	8H	14.95	15.21	16.06	16.30	17.80	11.19	11.44	12.30	12.54	14.04

END OF REPORT