

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912439

Luminaire Tested: DFN2DIP-SQ4F0-160D140US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912439
REPORT IS A COMBINATION OF REPORTS P901722 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D140US850-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 30453.1 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 272.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912439

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912439

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36
4	75	65	57	52	69	60	54	48	52	47	42	44	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20
9	51	39	32	27	48	37	30	26	32	27	23	28	23	21	23	20	18
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5146	5146	5146
5°	5154	5065	5098
10°	5103	4967	4934
15°	5033	4804	4678
20°	4940	4578	4365
25°	4844	4325	4062
30°	4716	4066	3678
35°	4591	3787	3340
40°	4464	3499	2952
45°	4316	3178	2601
50°	4162	2855	2257
55°	4003	2509	1927
60°	3817	2147	1588
65°	3605	1780	1431
70°	3346	1436	1297
75°	3022	1268	1183
80°	2553	1068	1031
85°	1777	719	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4316 cd/sqm

TEST NUMBER: P912439

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	687.3	2.3
10°-20°	1886.8	6.2
20°-30°	2649.0	8.7
30°-40°	2887.6	9.5
40°-50°	2654.0	8.7
50°-60°	2084.3	6.8
60°-70°	1356.7	4.5
70°-80°	698.4	2.3
80°-90°	187.5	0.6
90°-100°	172.8	0.6
100°-110°	644.1	2.1
110°-120°	1708.2	5.6
120°-130°	2833.3	9.3
130°-140°	3009.6	9.9
140°-150°	2797.1	9.2
150°-160°	2248.8	7.4
160°-170°	1449.0	4.8
170°-180°	498.7	1.6
0°-30°	5223.1	17.2
0°-40°	8110.7	26.6
0°-60°	12849.0	42.2
0°-90°	15091.6	49.6
90°-120°	2525.1	8.3
90°-150°	11165.0	36.7
90°-180°	15362.0	50.4
0°-180°	30453.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7334	7334	7334	7334	7334	
5°	7334	7300	7214	7274	7254	695
15°	6975	6902	6677	6550	6484	1966
25°	6332	6119	5681	5409	5309	2912
35°	5456	5117	4533	4115	3969	3415
45°	4460	4015	3319	2847	2688	3444
55°	3391	2874	2157	1759	1633	3030
65°	2290	1752	1155	930	909	2270
75°	1221	756	531	484	478	1291
85°	285	146	126	126	126	327
90°	4	46	76	95	102	29
95°	246	121	148	167	163	292
105°	1153	1266	231	273	288	1231
115°	2180	2244	2339	584	311	2146
125°	3082	3132	3204	3230	3242	2749
135°	3814	3875	3909	3947	3940	2947
145°	4425	4421	4485	4512	4493	2767
155°	4872	4838	4884	4906	4876	2245
165°	5134	5111	5122	5149	5122	1450
175°	5251	5224	5232	5259	5221	500
180°	5240	5240	5240	5240	5240	

TEST NUMBER: P912439

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7333.6	7333.6	7333.6	7333.6	7333.6
2.5°	7366.6	7333.6	7260.3	7327.3	7313.9
5°	7333.6	7300.4	7213.8	7273.7	7254.0
7.5°	7273.7	7234.2	7141.3	7167.4	7134.3
10°	7194.2	7147.7	7015.3	6994.9	6955.4
12.5°	7094.8	7035.1	6855.5	6816.0	6742.8
15°	6975.2	6902.0	6676.6	6550.5	6484.3
17.5°	6835.8	6729.4	6450.6	6304.8	6198.5
20°	6676.6	6543.5	6211.8	6046.4	5900.0
22.5°	6504.1	6351.2	5966.1	5740.8	5641.5
25°	6331.6	6118.9	5681.0	5409.1	5309.2
27.5°	6126.0	5900.0	5415.5	5103.6	4950.8
30°	5907.0	5654.2	5123.2	4785.3	4605.8
32.5°	5694.4	5388.7	4845.1	4446.6	4280.4
35°	5455.6	5116.9	4533.3	4114.9	3968.6
37.5°	5223.3	4857.9	4241.0	3782.6	3617.1
40°	4977.5	4579.7	3935.4	3464.3	3291.8
42.5°	4725.4	4300.8	3630.5	3139.0	2973.6
45°	4460.0	4015.0	3318.6	2846.8	2687.7
47.5°	4207.9	3736.9	3020.0	2548.3	2402.5
50°	3929.1	3458.0	2727.8	2269.5	2130.7
52.5°	3656.6	3158.8	2449.0	2011.1	1885.0
55°	3391.1	2873.5	2156.8	1758.9	1632.9
57.5°	3119.3	2588.4	1898.4	1526.5	1420.2
60°	2840.5	2309.6	1625.8	1287.9	1181.5
62.5°	2568.7	2037.8	1393.5	1075.2	1022.4
65°	2289.9	1751.9	1154.8	929.5	909.0
67.5°	2024.4	1486.4	929.5	816.1	796.4
70°	1745.6	1228.0	769.6	703.4	676.7
72.5°	1480.1	988.6	643.6	590.8	577.3
75°	1221.0	756.2	530.9	484.4	478.1
77.5°	962.5	537.2	418.2	391.5	378.2
80°	723.2	385.2	318.3	292.2	292.2
82.5°	504.2	259.2	219.0	205.6	205.6
85°	285.1	145.7	126.1	126.1	126.1
87.5°	106.4	52.8	52.8	46.5	46.5
90°	3.5	45.5	75.6	95.0	102.2
92.5°	95.0	79.7	90.9	98.6	102.2
95°	246.3	121.1	147.7	167.0	163.0
97.5°	443.5	132.9	193.2	204.8	208.5
100°	671.3	151.7	216.1	246.3	254.0
102.5°	921.1	913.9	223.8	265.2	276.9
105°	1152.6	1266.5	231.4	272.8	288.1
107.5°	1421.8	1516.3	239.1	280.5	295.8
110°	1679.8	1759.1	663.6	284.6	299.4

TEST NUMBER: P912439

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1922.5	1990.4	1926.1	291.8	303.4
115°	2180.1	2244.4	2339.4	584.0	311.1
117.5°	2403.8	2479.4	2544.3	2001.7	1008.5
120°	2654.2	2710.8	2779.3	2824.7	2312.8
122.5°	2866.2	2927.0	3003.1	3025.6	3029.7
125°	3082.4	3131.8	3203.9	3230.4	3241.7
127.5°	3279.5	3332.7	3389.8	3427.6	3431.2
130°	3465.4	3526.3	3567.7	3609.6	3605.9
132.5°	3655.0	3704.5	3746.0	3780.1	3776.6
135°	3814.4	3875.2	3908.9	3947.2	3939.5
137.5°	3981.0	4026.4	4064.7	4102.5	4091.3
140°	4144.0	4174.6	4216.0	4250.2	4231.3
142.5°	4280.9	4307.4	4356.5	4386.6	4367.7
145°	4424.9	4420.8	4485.2	4511.9	4492.9
147.5°	4549.7	4538.4	4602.8	4621.6	4606.8
150°	4671.2	4644.6	4705.4	4727.9	4709.0
152.5°	4773.4	4743.2	4800.0	4822.9	4796.3
155°	4871.9	4838.2	4883.7	4906.2	4876.1
157.5°	4951.7	4921.5	4955.8	4982.3	4951.7
160°	5020.1	4997.2	5020.1	5042.6	5016.1
162.5°	5080.4	5057.9	5076.9	5103.4	5069.2
165°	5133.6	5111.0	5122.4	5148.9	5122.4
167.5°	5175.5	5152.5	5164.2	5190.8	5156.5
170°	5209.6	5186.7	5194.3	5221.0	5186.7
172.5°	5232.2	5209.6	5217.3	5243.9	5209.6
175°	5251.1	5224.5	5232.2	5258.8	5221.0
177.5°	5258.8	5232.2	5236.3	5262.8	5228.6
180°	5239.8	5239.8	5239.8	5239.8	5239.8

TEST NUMBER: P912439

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.81	13.64	13.78	14.61	15.89	8.77	9.60	9.74	10.57	11.85
	3H	14.49	15.23	15.47	16.22	17.52	9.96	10.70	10.94	11.68	12.99
	4H	15.10	15.80	16.10	16.79	18.10	10.41	11.11	11.40	12.10	13.41
	6H	15.53	16.17	16.53	17.17	18.49	10.73	11.37	11.73	12.37	13.69
	8H	15.66	16.27	16.67	17.28	18.60	10.82	11.43	11.83	12.45	13.77
	12H	15.72	16.30	16.73	17.31	18.65	10.87	11.45	11.88	12.45	13.80
4H	2H	12.83	13.53	13.83	14.52	15.83	9.37	10.07	10.37	11.06	12.37
	3H	14.66	15.24	15.67	16.26	17.59	10.72	11.30	11.73	12.32	13.64
	4H	15.36	15.89	16.37	16.90	18.25	11.27	11.80	12.28	12.81	14.16
	6H	15.88	16.33	16.90	17.37	18.71	11.69	12.14	12.71	13.18	14.52
	8H	16.05	16.48	17.08	17.51	18.87	11.82	12.24	12.84	13.27	14.63
	12H	16.15	16.53	17.20	17.58	18.94	11.88	12.27	12.93	13.31	14.67
8H	4H	15.32	15.75	16.35	16.78	18.14	11.55	11.97	12.58	13.00	14.36
	6H	15.89	16.25	16.95	17.32	18.67	12.07	12.42	13.12	13.49	14.85
	8H	16.11	16.42	17.17	17.48	18.85	12.26	12.57	13.32	13.63	15.00
	12H	16.26	16.53	17.32	17.58	19.00	12.38	12.65	13.44	13.70	15.12
12H	4H	15.28	15.66	16.32	16.70	18.07	11.55	11.94	12.60	12.98	14.35
	6H	15.87	16.18	16.93	17.24	18.61	12.12	12.43	13.18	13.48	14.86
	8H	16.09	16.37	17.16	17.42	18.83	12.33	12.60	13.39	13.65	15.07