

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906763

Luminaire Tested: DFN2DIP-SQ4F0-080D120US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906763
REPORT IS A COMBINATION OF REPORTS P901692 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D120US835-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18680.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 161.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906763

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906763

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2320	2320	2320
5°	2324	2284	2298
10°	2301	2239	2224
15°	2269	2166	2109
20°	2227	2064	1968
25°	2184	1950	1831
30°	2126	1833	1658
35°	2070	1708	1506
40°	2013	1577	1331
45°	1946	1433	1173
50°	1877	1287	1018
55°	1805	1131	869
60°	1721	968	716
65°	1625	802	645
70°	1509	648	585
75°	1363	572	534
80°	1151	481	465
85°	801	324	354

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2171 cd/sqm

TEST NUMBER: P906763

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.9	1.7
10°-20°	850.7	4.6
20°-30°	1194.3	6.4
30°-40°	1301.9	7.0
40°-50°	1196.6	6.4
50°-60°	939.7	5.0
60°-70°	611.7	3.3
70°-80°	314.9	1.7
80°-90°	87.5	0.5
90°-100°	133.5	0.7
100°-110°	497.8	2.7
110°-120°	1320.3	7.1
120°-130°	2189.8	11.7
130°-140°	2326.1	12.5
140°-150°	2161.8	11.6
150°-160°	1738.1	9.3
160°-170°	1119.9	6.0
170°-180°	385.5	2.1
0°-30°	2354.9	12.6
0°-40°	3656.8	19.6
0°-60°	5793.1	31.0
0°-90°	6807.1	36.4
90°-120°	1951.7	10.4
90°-150°	8629.4	46.2
90°-180°	11873.0	63.6
0°-180°	18680.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3306	3306	3306	3306	3306	
5°	3306	3292	3252	3279	3270	314
15°	3145	3112	3010	2953	2924	886
25°	2855	2759	2561	2439	2394	1313
35°	2460	2307	2044	1855	1789	1540
45°	2011	1810	1496	1284	1212	1553
55°	1529	1296	972	793	736	1366
65°	1032	790	521	419	410	1024
75°	550	341	239	218	216	582
85°	129	66	57	57	57	148
90°	3	35	58	73	79	17
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	

TEST NUMBER: P906763

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3306.4	3306.4	3306.4	3306.4	3306.4
2.5°	3321.3	3306.4	3273.4	3303.5	3297.5
5°	3306.4	3291.5	3252.4	3279.4	3270.5
7.5°	3279.4	3261.6	3219.7	3231.5	3216.5
10°	3243.5	3222.6	3162.9	3153.7	3135.9
12.5°	3198.8	3171.8	3090.8	3073.0	3040.0
15°	3144.8	3111.8	3010.2	2953.4	2923.5
17.5°	3081.9	3034.0	2908.3	2842.6	2794.6
20°	3010.2	2950.2	2800.7	2726.1	2660.0
22.5°	2932.4	2863.5	2689.9	2588.3	2543.5
25°	2854.6	2758.8	2561.3	2438.8	2393.7
27.5°	2761.9	2660.0	2441.6	2301.0	2232.1
30°	2663.2	2549.2	2309.9	2157.5	2076.5
32.5°	2567.3	2429.6	2184.5	2004.8	1929.9
35°	2459.7	2307.0	2043.8	1855.3	1789.2
37.5°	2354.9	2190.2	1912.1	1705.4	1630.8
40°	2244.2	2064.8	1774.3	1561.9	1484.1
42.5°	2130.5	1939.1	1636.8	1415.3	1340.6
45°	2010.8	1810.2	1496.2	1283.5	1211.8
47.5°	1897.2	1684.8	1361.6	1148.9	1083.2
50°	1771.4	1559.1	1229.9	1023.2	960.6
52.5°	1648.6	1424.1	1104.1	906.7	849.9
55°	1528.9	1295.6	972.4	793.0	736.2
57.5°	1406.4	1167.0	855.9	688.3	640.3
60°	1280.6	1041.3	733.0	580.6	532.7
62.5°	1158.1	918.7	628.3	484.8	461.0
65°	1032.4	789.8	520.6	419.1	409.8
67.5°	912.7	670.2	419.1	367.9	359.1
70°	787.0	553.7	347.0	317.1	305.1
72.5°	667.3	445.7	290.2	266.4	260.3
75°	550.5	341.0	239.4	218.4	215.6
77.5°	434.0	242.2	188.6	176.5	170.5
80°	326.0	173.7	143.5	131.7	131.7
82.5°	227.3	116.8	98.7	92.7	92.7
85°	128.6	65.7	56.8	56.8	56.8
87.5°	47.9	23.8	23.8	21.0	21.0
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4

TEST NUMBER: P906763

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9

TEST NUMBER: P906763

CATALOG NUMBER: DFN2DIP-SQ4F0-080D120US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.67	9.40	9.74	10.47	11.92	4.63	5.36	5.70	6.43	7.88
	3H	10.34	11.00	11.42	12.07	13.55	5.81	6.46	6.89	7.54	9.01
	4H	10.95	11.57	12.04	12.65	14.13	6.26	6.88	7.35	7.96	9.43
	6H	11.37	11.94	12.47	13.02	14.51	6.57	7.14	7.67	8.23	9.72
	8H	11.50	12.04	12.60	13.14	14.62	6.66	7.20	7.77	8.30	9.79
	12H	11.56	12.07	12.66	13.16	14.67	6.70	7.22	7.81	8.31	9.82
4H	2H	8.67	9.29	9.77	10.37	11.85	5.21	5.83	6.31	6.91	8.39
	3H	10.50	11.01	11.60	12.12	13.61	6.56	7.07	7.66	8.18	9.67
	4H	11.19	11.66	12.30	12.76	14.27	7.10	7.57	8.21	8.67	10.18
	6H	11.71	12.11	12.82	13.23	14.73	7.52	7.92	8.63	9.04	10.55
	8H	11.88	12.26	13.00	13.37	14.89	7.64	8.02	8.76	9.13	10.65
	12H	11.97	12.32	13.11	13.44	14.97	7.70	8.05	8.84	9.17	10.70
8H	4H	11.15	11.53	12.27	12.64	14.16	7.38	7.75	8.49	8.87	10.39
	6H	11.72	12.03	12.86	13.18	14.70	7.89	8.20	9.03	9.36	10.88
	8H	11.94	12.21	13.08	13.34	14.88	8.08	8.36	9.23	9.49	11.03
	12H	12.08	12.31	13.22	13.44	15.02	8.20	8.44	9.35	9.57	11.14
12H	4H	11.10	11.44	12.23	12.56	14.09	7.38	7.72	8.51	8.84	10.37
	6H	11.69	11.97	12.84	13.10	14.64	7.94	8.22	9.09	9.35	10.89
	8H	11.91	12.15	13.06	13.28	14.86	8.15	8.39	9.30	9.52	11.09