

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906767

Luminaire Tested: DFN2DIP-SQ4F0-080D140US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906767
REPORT IS A COMBINATION OF REPORTS P901710 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D140US835-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20660.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 177.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906767

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906767

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	35	35
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30
3	79	70	63	57	71	63	57	53	51	47	43	39	37	34	29	27	26
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	24	21	20
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16
8	52	41	33	28	47	37	31	26	30	25	22	24	21	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2320	2320	2320
5°	2324	2284	2298
10°	2301	2239	2224
15°	2269	2166	2109
20°	2227	2064	1968
25°	2184	1950	1831
30°	2126	1833	1658
35°	2070	1708	1506
40°	2013	1577	1331
45°	1946	1433	1173
50°	1877	1287	1018
55°	1805	1131	869
60°	1721	968	716
65°	1625	802	645
70°	1509	648	585
75°	1363	572	534
80°	1151	481	465
85°	801	324	354

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2534 cd/sqm

TEST NUMBER: P906767

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.9	1.5
10°-20°	850.7	4.1
20°-30°	1194.3	5.8
30°-40°	1301.9	6.3
40°-50°	1196.6	5.8
50°-60°	939.7	4.5
60°-70°	611.7	3.0
70°-80°	314.9	1.5
80°-90°	88.7	0.4
90°-100°	155.8	0.8
100°-110°	580.8	2.8
110°-120°	1540.3	7.5
120°-130°	2554.8	12.4
130°-140°	2713.8	13.1
140°-150°	2522.1	12.2
150°-160°	2027.7	9.8
160°-170°	1306.6	6.3
170°-180°	449.7	2.2
0°-30°	2354.9	11.4
0°-40°	3656.8	17.7
0°-60°	5793.1	28.0
0°-90°	6808.3	33.0
90°-120°	2276.9	11.0
90°-150°	10067.6	48.7
90°-180°	13852.0	67.0
0°-180°	20660.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3306	3306	3306	3306	3306	
5°	3306	3292	3252	3279	3270	314
15°	3145	3112	3010	2953	2924	886
25°	2855	2759	2561	2439	2394	1313
35°	2460	2307	2044	1855	1789	1540
45°	2011	1810	1496	1284	1212	1553
55°	1529	1296	972	793	736	1366
65°	1032	790	521	419	410	1024
75°	550	341	239	218	216	582
85°	129	66	57	57	57	148
90°	3	41	68	86	92	19
95°	222	109	133	151	147	263
105°	1039	1142	209	246	260	1110
115°	1966	2024	2110	527	280	1935
125°	2779	2824	2889	2913	2923	2479
135°	3440	3494	3525	3559	3552	2657
145°	3990	3986	4044	4068	4051	2495
155°	4393	4363	4404	4424	4397	2024
165°	4629	4609	4619	4643	4619	1308
175°	4735	4711	4718	4742	4708	451
180°	4725	4725	4725	4725	4725	

TEST NUMBER: P906767

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3306.4	3306.4	3306.4	3306.4	3306.4
2.5°	3321.3	3306.4	3273.4	3303.5	3297.5
5°	3306.4	3291.5	3252.4	3279.4	3270.5
7.5°	3279.4	3261.6	3219.7	3231.5	3216.5
10°	3243.5	3222.6	3162.9	3153.7	3135.9
12.5°	3198.8	3171.8	3090.8	3073.0	3040.0
15°	3144.8	3111.8	3010.2	2953.4	2923.5
17.5°	3081.9	3034.0	2908.3	2842.6	2794.6
20°	3010.2	2950.2	2800.7	2726.1	2660.0
22.5°	2932.4	2863.5	2689.9	2588.3	2543.5
25°	2854.6	2758.8	2561.3	2438.8	2393.7
27.5°	2761.9	2660.0	2441.6	2301.0	2232.1
30°	2663.2	2549.2	2309.9	2157.5	2076.5
32.5°	2567.3	2429.6	2184.5	2004.8	1929.9
35°	2459.7	2307.0	2043.8	1855.3	1789.2
37.5°	2354.9	2190.2	1912.1	1705.4	1630.8
40°	2244.2	2064.8	1774.3	1561.9	1484.1
42.5°	2130.5	1939.1	1636.8	1415.3	1340.6
45°	2010.8	1810.2	1496.2	1283.5	1211.8
47.5°	1897.2	1684.8	1361.6	1148.9	1083.2
50°	1771.4	1559.1	1229.9	1023.2	960.6
52.5°	1648.6	1424.1	1104.1	906.7	849.9
55°	1528.9	1295.6	972.4	793.0	736.2
57.5°	1406.4	1167.0	855.9	688.3	640.3
60°	1280.6	1041.3	733.0	580.6	532.7
62.5°	1158.1	918.7	628.3	484.8	461.0
65°	1032.4	789.8	520.6	419.1	409.8
67.5°	912.7	670.2	419.1	367.9	359.1
70°	787.0	553.7	347.0	317.1	305.1
72.5°	667.3	445.7	290.2	266.4	260.3
75°	550.5	341.0	239.4	218.4	215.6
77.5°	434.0	242.2	188.6	176.5	170.5
80°	326.0	173.7	143.5	131.7	131.7
82.5°	227.3	116.8	98.7	92.7	92.7
85°	128.6	65.7	56.8	56.8	56.8
87.5°	47.9	23.8	23.8	21.0	21.0
90°	3.2	41.0	68.2	85.7	92.2
92.5°	85.7	71.9	82.0	88.9	92.2
95°	222.1	109.2	133.2	150.6	147.0
97.5°	399.9	119.8	174.2	184.7	188.0
100°	605.3	136.8	194.9	222.1	229.0
102.5°	830.6	824.1	201.8	239.1	249.7
105°	1039.3	1142.0	208.7	246.0	259.8
107.5°	1282.1	1367.3	215.6	252.9	266.7
110°	1514.7	1586.2	598.4	256.6	270.0

TEST NUMBER: P906767

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1733.5	1794.8	1736.8	263.1	273.6
115°	1965.8	2023.8	2109.5	526.6	280.5
117.5°	2167.5	2235.7	2294.2	1805.0	909.4
120°	2393.3	2444.4	2506.1	2547.1	2085.5
122.5°	2584.5	2639.3	2707.9	2728.2	2731.9
125°	2779.4	2824.0	2889.0	2912.9	2923.1
127.5°	2957.2	3005.1	3056.6	3090.7	3094.0
130°	3124.8	3179.7	3217.0	3254.8	3251.5
132.5°	3295.8	3340.4	3377.8	3408.6	3405.4
135°	3439.5	3494.3	3524.7	3559.2	3552.3
137.5°	3589.7	3630.7	3665.2	3699.3	3689.2
140°	3736.7	3764.3	3801.6	3832.5	3815.4
142.5°	3860.1	3884.0	3928.3	3955.5	3938.4
145°	3990.0	3986.3	4044.4	4068.4	4051.3
147.5°	4102.5	4092.3	4150.4	4167.4	4154.0
150°	4212.1	4188.1	4242.9	4263.2	4246.2
152.5°	4304.2	4277.0	4328.2	4348.9	4324.9
155°	4393.1	4362.7	4403.7	4424.0	4396.8
157.5°	4465.0	4437.8	4468.7	4492.6	4465.0
160°	4526.7	4506.0	4526.7	4547.0	4523.1
162.5°	4581.1	4560.8	4577.9	4601.8	4571.0
165°	4629.0	4608.7	4618.9	4642.8	4618.9
167.5°	4666.8	4646.1	4656.6	4680.6	4649.7
170°	4697.6	4676.9	4683.8	4707.8	4676.9
172.5°	4717.9	4697.6	4704.5	4728.5	4697.6
175°	4735.0	4711.0	4717.9	4741.9	4707.8
177.5°	4741.9	4717.9	4721.6	4745.5	4714.7
180°	4724.8	4724.8	4724.8	4724.8	4724.8

TEST NUMBER: P906767

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.24	8.95	9.34	10.04	11.54	4.20	4.91	5.30	6.00	7.50
	3H	9.91	10.55	11.02	11.65	13.16	5.38	6.02	6.49	7.11	8.63
	4H	10.52	11.12	11.64	12.22	13.74	5.83	6.43	6.94	7.53	9.05
	6H	10.94	11.49	12.06	12.59	14.13	6.14	6.70	7.27	7.80	9.33
	8H	11.06	11.59	12.19	12.71	14.23	6.23	6.76	7.36	7.87	9.40
	12H	11.12	11.62	12.26	12.73	14.28	6.27	6.77	7.40	7.88	9.43
4H	2H	8.25	8.85	9.37	9.95	11.47	4.79	5.39	5.91	6.49	8.01
	3H	10.07	10.57	11.20	11.69	13.23	6.13	6.62	7.25	7.75	9.28
	4H	10.76	11.22	11.89	12.33	13.89	6.67	7.13	7.80	8.24	9.80
	6H	11.27	11.66	12.41	12.80	14.35	7.08	7.48	8.22	8.61	10.16
	8H	11.45	11.81	12.58	12.94	14.50	7.21	7.58	8.35	8.71	10.27
	12H	11.54	11.87	12.69	13.01	14.58	7.27	7.60	8.42	8.74	10.31
8H	4H	10.72	11.08	11.86	12.21	13.78	6.94	7.31	8.08	8.44	10.00
	6H	11.28	11.59	12.44	12.76	14.32	7.46	7.76	8.62	8.93	10.49
	8H	11.50	11.77	12.67	12.92	14.50	7.65	7.91	8.81	9.07	10.64
	12H	11.64	11.87	12.81	13.02	14.63	7.76	8.00	8.93	9.14	10.76
12H	4H	10.66	11.00	11.82	12.14	13.70	6.94	7.27	8.10	8.42	9.98
	6H	11.26	11.52	12.42	12.68	14.25	7.51	7.77	8.67	8.92	10.50
	8H	11.48	11.71	12.64	12.86	14.47	7.71	7.95	8.88	9.10	10.71