

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914848

Luminaire Tested: DFN2DIP-SQ4F0-060D060US927-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914848  
REPORT IS A COMBINATION OF REPORTS P900059 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-060D060US927-FLLFLL  
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8912.0 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 95.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.946  
Total Harmonic Distortion (THDi): 0.132  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914848  
CATALOG NUMBER: DFN2DIP-SQ4F0-060D060US927-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P914848

CATALOG NUMBER: DFN2DIP-SQ4F0-060D060US927-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20										
RC	80					70					50					30					10					0					
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																															
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53													
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45													
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37													
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32													
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27													
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24													
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21													
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18													
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16													
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15													
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1298	1298	1298
5°	1300	1280	1289
10°	1289	1263	1272
15°	1270	1242	1245
20°	1245	1214	1217
25°	1219	1179	1185
30°	1187	1148	1145
35°	1157	1110	1101
40°	1120	1072	1061
45°	1082	1034	1019
50°	1042	994	970
55°	999	948	926
60°	951	893	875
65°	899	836	815
70°	832	767	750
75°	739	684	691
80°	628	579	577
85°	454	396	388

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1182 cd/sqm



TEST NUMBER: P914848

CATALOG NUMBER: DFN2DIP-SQ4F0-060D060US927-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.1	2.0
10°-20°	489.8	5.5
20°-30°	719.8	8.1
30°-40°	836.0	9.4
40°-50°	834.9	9.4
50°-60°	728.0	8.2
60°-70°	538.2	6.0
70°-80°	304.5	3.4
80°-90°	84.6	0.9
90°-100°	93.0	1.0
100°-110°	295.6	3.3
110°-120°	505.8	5.7
120°-130°	665.2	7.5
130°-140°	746.6	8.4
140°-150°	732.2	8.2
150°-160°	614.2	6.9
160°-170°	407.3	4.6
170°-180°	142.4	1.6
0°-30°	1383.6	15.5
0°-40°	2219.6	24.9
0°-60°	3782.5	42.4
0°-90°	4709.8	52.8
90°-120°	894.4	10.0
90°-150°	3038.4	34.1
90°-180°	4202.0	47.1
0°-180°	8912.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1823	1837	1834	176
15°	1760	1750	1727	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1375	1357	1328	1318	1309	858
45°	1119	1106	1079	1060	1053	863
55°	847	836	814	793	784	757
65°	571	560	542	526	518	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	81
90°	1	16	44	42	43	9
95°	66	79	81	81	79	74
105°	273	276	279	282	282	288
115°	508	515	512	511	508	502
125°	738	750	746	742	740	660
135°	955	969	972	970	967	738
145°	1159	1168	1176	1177	1172	724
155°	1326	1329	1333	1340	1336	610
165°	1442	1441	1441	1450	1443	407
175°	1500	1497	1494	1503	1496	143
180°	1503	1503	1503	1503	1503	



TEST NUMBER: P914848

CATALOG NUMBER: DFN2DIP-SQ4F0-060D060US927-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1849.4	1849.4	1849.4	1849.4	1849.4
2.5°	1860.2	1851.3	1831.7	1849.4	1846.0
5°	1849.4	1842.5	1822.8	1837.0	1833.6
7.5°	1837.0	1826.5	1806.8	1821.1	1817.6
10°	1817.6	1805.1	1783.8	1797.9	1792.6
12.5°	1790.8	1780.2	1758.9	1767.8	1764.2
15°	1760.5	1750.0	1726.8	1734.0	1725.1
17.5°	1723.2	1712.7	1689.5	1698.3	1689.5
20°	1682.3	1671.7	1646.8	1652.1	1645.1
22.5°	1641.6	1625.5	1602.3	1602.3	1598.7
25°	1593.4	1579.3	1549.0	1552.4	1549.0
27.5°	1540.0	1527.6	1504.5	1499.3	1490.4
30°	1486.8	1472.4	1445.9	1440.6	1433.4
32.5°	1429.8	1419.3	1390.8	1380.0	1372.8
35°	1374.8	1357.0	1328.5	1317.7	1308.8
37.5°	1312.5	1296.4	1268.0	1255.4	1246.6
40°	1248.5	1234.1	1205.7	1189.9	1182.6
42.5°	1186.2	1171.9	1143.6	1125.7	1115.1
45°	1118.7	1106.2	1079.4	1060.0	1052.8
47.5°	1052.8	1040.4	1011.9	992.3	981.7
50°	983.4	974.5	949.7	924.7	915.8
52.5°	915.8	903.4	880.4	860.8	848.3
55°	846.6	835.8	814.5	793.2	784.3
57.5°	777.2	768.3	745.1	723.8	716.6
60°	707.7	700.8	675.9	656.2	650.9
62.5°	640.2	627.7	610.0	592.2	585.1
65°	570.9	560.2	542.5	526.4	517.5
67.5°	499.8	490.8	474.9	462.5	455.3
70°	434.0	426.8	410.7	398.3	391.3
72.5°	366.4	359.3	350.4	337.9	332.6
75°	298.7	295.3	286.2	275.7	279.2
77.5°	238.3	231.2	227.5	222.3	217.0
80°	177.9	176.0	172.5	167.2	163.6
82.5°	121.0	121.0	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	1.3	16.3	44.4	41.7	43.0
92.5°	28.1	38.1	39.5	40.8	40.8
95°	66.1	78.8	81.1	81.1	78.8
97.5°	110.1	121.9	126.9	126.9	126.9
100°	160.9	171.3	174.9	174.9	173.6
102.5°	214.4	222.0	227.0	228.4	227.0
105°	272.8	276.5	279.2	281.5	281.5
107.5°	330.8	336.3	336.3	337.2	330.8
110°	387.1	394.3	394.3	394.3	390.6



TEST NUMBER: P914848

CATALOG NUMBER: DFN2DIP-SQ4F0-060D060US927-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	447.7	455.4	454.1	450.4	447.7
115°	507.6	514.8	512.5	511.2	507.6
117.5°	567.0	576.9	570.5	567.0	563.3
120°	626.8	636.8	626.8	626.8	622.7
122.5°	681.1	693.8	687.5	683.9	681.1
125°	738.2	749.6	745.9	741.9	740.5
127.5°	794.0	808.0	803.0	797.6	794.0
130°	846.1	862.4	860.2	857.5	852.5
132.5°	904.6	917.3	918.1	911.8	908.2
135°	954.9	968.9	971.6	970.3	966.6
137.5°	1011.1	1022.4	1024.7	1023.7	1018.3
140°	1060.5	1071.8	1078.2	1078.2	1073.2
142.5°	1111.2	1122.5	1126.2	1127.5	1122.5
145°	1159.3	1168.3	1175.6	1176.9	1172.0
147.5°	1202.3	1213.6	1219.1	1221.3	1216.3
150°	1246.7	1254.4	1259.4	1263.4	1259.4
152.5°	1286.1	1293.9	1300.2	1305.2	1300.2
155°	1325.6	1329.2	1333.2	1339.7	1335.5
157.5°	1359.5	1362.3	1364.5	1373.6	1367.3
160°	1390.0	1392.7	1394.0	1401.7	1396.3
162.5°	1418.0	1418.0	1419.4	1428.0	1421.6
165°	1442.0	1440.7	1440.7	1449.8	1443.4
167.5°	1463.8	1459.8	1459.8	1468.8	1462.4
170°	1480.1	1476.5	1475.1	1484.2	1476.5
172.5°	1491.4	1487.8	1486.4	1495.5	1487.8
175°	1500.5	1496.9	1494.1	1503.2	1495.5
177.5°	1505.5	1501.9	1499.1	1506.8	1499.1
180°	1503.2	1503.2	1503.2	1503.2	1503.2



TEST NUMBER: P914848  
 CATALOG NUMBER: DFN2DIP-SQ4F0-060D060US927-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.45	9.34	9.38	10.29	11.52	8.00	8.89	8.94	9.84	11.07
	3H	10.11	10.91	11.06	11.87	13.12	9.62	10.42	10.57	11.38	12.63
	4H	10.71	11.46	11.66	12.42	13.69	10.21	10.97	11.17	11.93	13.19
	6H	11.11	11.81	12.08	12.77	14.05	10.61	11.31	11.58	12.27	13.55
	8H	11.22	11.88	12.19	12.87	14.14	10.72	11.38	11.69	12.36	13.64
	12H	11.27	11.90	12.25	12.88	14.18	10.76	11.39	11.74	12.37	13.67
4H	2H	8.91	9.67	9.88	10.63	11.89	8.56	9.31	9.52	10.28	11.54
	3H	10.79	11.41	11.76	12.41	13.68	10.38	11.01	11.35	12.00	13.28
	4H	11.50	12.08	12.49	13.07	14.37	11.08	11.66	12.06	12.64	13.94
	6H	12.03	12.52	13.02	13.53	14.83	11.59	12.09	12.59	13.10	14.40
	8H	12.18	12.64	13.17	13.64	14.96	11.74	12.20	12.74	13.21	14.52
	12H	12.25	12.67	13.27	13.69	15.01	11.81	12.22	12.82	13.24	14.56
8H	4H	11.70	12.17	12.70	13.17	14.48	11.33	11.79	12.32	12.79	14.11
	6H	12.34	12.72	13.36	13.77	15.08	11.96	12.34	12.98	13.39	14.70
	8H	12.57	12.90	13.59	13.93	15.26	12.17	12.51	13.20	13.54	14.87
	12H	12.70	13.00	13.73	14.02	15.40	12.29	12.59	13.32	13.61	14.99
12H	4H	11.69	12.11	12.71	13.13	14.45	11.32	11.74	12.34	12.76	14.08
	6H	12.37	12.71	13.40	13.74	15.07	12.00	12.34	13.03	13.37	14.70
	8H	12.62	12.92	13.65	13.94	15.32	12.24	12.54	13.27	13.56	14.94