

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906801

Luminaire Tested: DFN2DIP-SQ4F0-090D140US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906801
REPORT IS A COMBINATION OF REPORTS P901711 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D140US835-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 22770.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 188.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906801
CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P906801

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33				33
2	87	80	74	68	79	73	67	63	59	56	52	47	45	42	36	34	33	28				28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	23				23
4	72	62	54	48	66	56	50	45	46	41	38	37	34	31	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	30	27	26	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18	15				15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	14				14
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15	12				12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11				11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2457	2457	2457
5°	2461	2424	2440
10°	2441	2391	2408
15°	2405	2352	2357
20°	2357	2298	2305
25°	2308	2233	2244
30°	2248	2173	2167
35°	2191	2102	2086
40°	2120	2030	2008
45°	2050	1958	1929
50°	1973	1882	1837
55°	1892	1794	1753
60°	1801	1690	1657
65°	1702	1583	1543
70°	1575	1452	1421
75°	1400	1295	1309
80°	1189	1095	1094
85°	859	749	735

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2534 cd/sqm



TEST NUMBER: P906801

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	1.4
10°-20°	927.4	4.1
20°-30°	1362.9	6.0
30°-40°	1582.9	7.0
40°-50°	1580.9	6.9
50°-60°	1378.5	6.1
60°-70°	1019.0	4.5
70°-80°	576.6	2.5
80°-90°	160.5	0.7
90°-100°	155.8	0.7
100°-110°	580.8	2.6
110°-120°	1540.3	6.8
120°-130°	2554.8	11.2
130°-140°	2713.8	11.9
140°-150°	2522.1	11.1
150°-160°	2027.7	8.9
160°-170°	1306.6	5.7
170°-180°	449.7	2.0
0°-30°	2619.9	11.5
0°-40°	4202.8	18.5
0°-60°	7162.3	31.5
0°-90°	8918.3	39.2
90°-120°	2276.9	10.0
90°-150°	10067.6	44.2
90°-180°	13852.0	60.8
0°-180°	22770.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	3	41	68	86	92	21
95°	222	109	133	151	147	263
105°	1039	1142	209	246	260	1110
115°	1966	2024	2110	527	280	1935
125°	2779	2824	2889	2913	2923	2479
135°	3440	3494	3525	3559	3552	2657
145°	3990	3986	4044	4068	4051	2495
155°	4393	4363	4404	4424	4397	2024
165°	4629	4609	4619	4643	4619	1308
175°	4735	4711	4718	4742	4708	451
180°	4725	4725	4725	4725	4725	



TEST NUMBER: P906801

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	3.2	41.0	68.2	85.7	92.2
92.5°	85.7	71.9	82.0	88.9	92.2
95°	222.1	109.2	133.2	150.6	147.0
97.5°	399.9	119.8	174.2	184.7	188.0
100°	605.3	136.8	194.9	222.1	229.0
102.5°	830.6	824.1	201.8	239.1	249.7
105°	1039.3	1142.0	208.7	246.0	259.8
107.5°	1282.1	1367.3	215.6	252.9	266.7
110°	1514.7	1586.2	598.4	256.6	270.0



TEST NUMBER: P906801

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1733.5	1794.8	1736.8	263.1	273.6
115°	1965.8	2023.8	2109.5	526.6	280.5
117.5°	2167.5	2235.7	2294.2	1805.0	909.4
120°	2393.3	2444.4	2506.1	2547.1	2085.5
122.5°	2584.5	2639.3	2707.9	2728.2	2731.9
125°	2779.4	2824.0	2889.0	2912.9	2923.1
127.5°	2957.2	3005.1	3056.6	3090.7	3094.0
130°	3124.8	3179.7	3217.0	3254.8	3251.5
132.5°	3295.8	3340.4	3377.8	3408.6	3405.4
135°	3439.5	3494.3	3524.7	3559.2	3552.3
137.5°	3589.7	3630.7	3665.2	3699.3	3689.2
140°	3736.7	3764.3	3801.6	3832.5	3815.4
142.5°	3860.1	3884.0	3928.3	3955.5	3938.4
145°	3990.0	3986.3	4044.4	4068.4	4051.3
147.5°	4102.5	4092.3	4150.4	4167.4	4154.0
150°	4212.1	4188.1	4242.9	4263.2	4246.2
152.5°	4304.2	4277.0	4328.2	4348.9	4324.9
155°	4393.1	4362.7	4403.7	4424.0	4396.8
157.5°	4465.0	4437.8	4468.7	4492.6	4465.0
160°	4526.7	4506.0	4526.7	4547.0	4523.1
162.5°	4581.1	4560.8	4577.9	4601.8	4571.0
165°	4629.0	4608.7	4618.9	4642.8	4618.9
167.5°	4666.8	4646.1	4656.6	4680.6	4649.7
170°	4697.6	4676.9	4683.8	4707.8	4676.9
172.5°	4717.9	4697.6	4704.5	4728.5	4697.6
175°	4735.0	4711.0	4717.9	4741.9	4707.8
177.5°	4741.9	4717.9	4721.6	4745.5	4714.7
180°	4724.8	4724.8	4724.8	4724.8	4724.8



TEST NUMBER: P906801
 CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.32	10.09	10.36	11.14	12.56	8.87	9.64	9.92	10.69	12.11
	3H	10.97	11.67	12.03	12.72	14.16	10.48	11.17	11.54	12.23	13.67
	4H	11.56	12.22	12.63	13.28	14.72	11.07	11.72	12.13	12.78	14.23
	6H	11.96	12.56	13.03	13.63	15.08	11.46	12.06	12.53	13.13	14.58
	8H	12.06	12.64	13.14	13.72	15.17	11.56	12.14	12.64	13.22	14.67
	12H	12.11	12.66	13.19	13.73	15.20	11.60	12.15	12.69	13.22	14.69
4H	2H	9.77	10.42	10.84	11.48	12.93	9.41	10.07	10.48	11.13	12.57
	3H	11.63	12.18	12.71	13.26	14.72	11.22	11.77	12.30	12.86	14.31
	4H	12.34	12.84	13.43	13.92	15.40	11.92	12.42	13.00	13.50	14.98
	6H	12.86	13.29	13.95	14.39	15.86	12.42	12.86	13.52	13.96	15.43
	8H	13.01	13.41	14.10	14.50	15.99	12.57	12.97	13.66	14.07	15.55
	12H	13.08	13.44	14.19	14.55	16.04	12.63	12.99	13.74	14.10	15.59
8H	4H	12.53	12.93	13.63	14.03	15.52	12.16	12.56	13.25	13.65	15.14
	6H	13.16	13.50	14.28	14.63	16.12	12.78	13.11	13.90	14.25	15.73
	8H	13.39	13.68	14.51	14.80	16.30	12.99	13.29	14.12	14.40	15.91
	12H	13.52	13.77	14.64	14.89	16.43	13.11	13.36	14.23	14.48	16.02
12H	4H	12.51	12.88	13.63	13.99	15.48	12.15	12.51	13.26	13.62	15.11
	6H	13.19	13.49	14.32	14.60	16.11	12.82	13.11	13.95	14.23	15.74
	8H	13.43	13.69	14.56	14.80	16.35	13.05	13.31	14.18	14.43	15.97