

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914926

Luminaire Tested: DFN2DIP-SQ4F0-080D070US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914926
REPORT IS A COMBINATION OF REPORTS P900082 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D070US927-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10294.4 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 123.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914926
CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US927-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P914926
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52		
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45		
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43	39		
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	33		
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29		
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29	26		
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23		
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23	20		
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	18		
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19	17		
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	20	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1838	1838	1838
5°	1841	1809	1821
10°	1822	1774	1762
15°	1797	1716	1671
20°	1764	1635	1559
25°	1730	1545	1451
30°	1685	1452	1313
35°	1640	1353	1193
40°	1594	1250	1054
45°	1541	1135	929
50°	1487	1020	806
55°	1430	896	688
60°	1363	767	567
65°	1287	636	511
70°	1195	513	463
75°	1079	453	423
80°	912	381	368
85°	635	256	280

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1541 cd/sqm



TEST NUMBER: P914926

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.5	2.4
10°-20°	673.9	6.5
20°-30°	946.1	9.2
30°-40°	1031.3	10.0
40°-50°	947.9	9.2
50°-60°	744.4	7.2
60°-70°	484.5	4.7
70°-80°	249.4	2.4
80°-90°	68.6	0.7
90°-100°	108.5	1.1
100°-110°	344.8	3.3
110°-120°	590.1	5.7
120°-130°	776.1	7.5
130°-140°	871.1	8.5
140°-150°	854.2	8.3
150°-160°	716.6	7.0
160°-170°	475.2	4.6
170°-180°	166.1	1.6
0°-30°	1865.5	18.1
0°-40°	2896.8	28.1
0°-60°	4589.2	44.6
0°-90°	5391.8	52.4
90°-120°	1043.4	10.1
90°-150°	3544.8	34.4
90°-180°	4903.0	47.6
0°-180°	10294.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2608	2576	2598	2591	248
15°	2491	2465	2385	2340	2316	702
25°	2261	2186	2029	1932	1896	1040
35°	1948	1828	1619	1470	1417	1220
45°	1593	1434	1185	1017	960	1230
55°	1211	1026	770	628	583	1082
65°	818	626	412	332	325	811
75°	436	270	190	173	171	461
85°	102	52	45	45	45	117
90°	2	19	52	49	50	10
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1372	1373	1367	845
155°	1546	1551	1556	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P914926

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2619.3	2619.3	2619.3	2619.3	2619.3
2.5°	2631.1	2619.3	2593.1	2617.0	2612.2
5°	2619.3	2607.5	2576.5	2597.9	2590.8
7.5°	2597.9	2583.8	2550.6	2559.9	2548.1
10°	2569.4	2552.9	2505.6	2498.3	2484.2
12.5°	2534.0	2512.6	2448.5	2434.4	2408.2
15°	2491.3	2465.1	2384.6	2339.6	2315.9
17.5°	2441.4	2403.5	2303.9	2251.9	2213.8
20°	2384.6	2337.1	2218.7	2159.6	2107.2
22.5°	2323.0	2268.4	2130.9	2050.4	2014.9
25°	2261.4	2185.5	2029.0	1932.0	1896.2
27.5°	2187.9	2107.2	1934.2	1822.8	1768.2
30°	2109.7	2019.4	1829.9	1709.1	1645.0
32.5°	2033.8	1924.7	1730.5	1588.2	1528.8
35°	1948.5	1827.6	1619.1	1469.7	1417.4
37.5°	1865.5	1735.0	1514.7	1351.0	1291.9
40°	1777.8	1635.7	1405.6	1237.3	1175.7
42.5°	1687.7	1536.1	1296.6	1121.2	1062.0
45°	1592.9	1434.0	1185.3	1016.8	960.0
47.5°	1502.9	1334.7	1078.6	910.1	858.1
50°	1403.3	1235.1	974.3	810.6	761.0
52.5°	1306.0	1128.1	874.6	718.3	673.3
55°	1211.2	1026.3	770.3	628.2	583.2
57.5°	1114.1	924.5	678.0	545.3	507.2
60°	1014.5	824.9	580.7	459.9	422.0
62.5°	917.4	727.8	497.7	384.0	365.2
65°	817.8	625.7	412.4	332.0	324.6
67.5°	723.0	530.9	332.0	291.4	284.5
70°	623.4	438.6	274.9	251.2	241.7
72.5°	528.6	353.1	229.9	211.0	206.2
75°	436.1	270.1	189.6	173.0	170.8
77.5°	343.8	191.9	149.4	139.8	135.1
80°	258.3	137.6	113.7	104.3	104.3
82.5°	180.1	92.5	78.2	73.4	73.4
85°	101.9	52.0	45.0	45.0	45.0
87.5°	37.9	18.9	18.9	16.6	16.6
90°	1.6	19.0	51.8	48.6	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.7	94.7	92.0
97.5°	128.5	142.2	148.1	148.1	148.1
100°	187.7	199.9	204.1	204.1	202.5
102.5°	250.1	259.0	264.9	266.5	264.9
105°	318.3	322.5	325.7	328.4	328.4
107.5°	386.0	392.3	392.3	393.4	386.0
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P914926

CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.4	531.4	529.8	525.5	522.4
115°	592.2	600.6	598.0	596.4	592.2
117.5°	661.4	673.0	665.7	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.1	797.8	794.6
125°	861.3	874.5	870.3	865.5	864.0
127.5°	926.3	942.7	936.9	930.6	926.3
130°	987.1	1006.1	1003.5	1000.4	994.5
132.5°	1055.3	1070.2	1071.2	1063.8	1059.5
135°	1114.0	1130.4	1133.6	1131.9	1127.7
137.5°	1179.6	1192.8	1195.4	1194.4	1188.0
140°	1237.2	1250.5	1257.8	1257.8	1252.0
142.5°	1296.4	1309.6	1313.8	1315.4	1309.6
145°	1352.5	1363.0	1371.5	1373.1	1367.3
147.5°	1402.7	1415.9	1422.3	1424.9	1419.1
150°	1454.5	1463.5	1469.3	1474.1	1469.3
152.5°	1500.5	1509.5	1516.9	1522.7	1516.9
155°	1546.5	1550.7	1555.5	1562.9	1558.1
157.5°	1586.2	1589.4	1592.0	1602.6	1595.1
160°	1621.6	1624.8	1626.3	1635.3	1629.0
162.5°	1654.4	1654.4	1656.0	1666.0	1658.6
165°	1682.4	1680.8	1680.8	1691.4	1683.9
167.5°	1707.8	1703.0	1703.0	1713.6	1706.2
170°	1726.8	1722.6	1721.0	1731.5	1722.6
172.5°	1740.0	1735.7	1734.2	1744.8	1735.7
175°	1750.6	1746.4	1743.2	1753.7	1744.8
177.5°	1756.4	1752.1	1749.0	1758.0	1749.0
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P914926
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D070US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.49	10.34	10.44	11.30	12.54	5.45	6.30	6.40	7.26	8.50
	3H	11.18	11.94	12.13	12.90	14.16	6.64	7.40	7.60	8.37	9.63
	4H	11.79	12.51	12.76	13.48	14.75	7.10	7.81	8.06	8.78	10.05
	6H	12.21	12.88	13.19	13.85	15.13	7.42	8.08	8.40	9.05	10.34
	8H	12.34	12.97	13.33	13.96	15.24	7.51	8.14	8.50	9.13	10.41
	12H	12.41	13.01	13.40	13.99	15.30	7.55	8.15	8.55	9.14	10.44
4H	2H	9.51	10.23	10.49	11.20	12.47	6.05	6.77	7.03	7.74	9.01
	3H	11.35	11.95	12.33	12.94	14.23	7.41	8.00	8.39	9.00	10.29
	4H	12.05	12.59	13.04	13.58	14.89	7.96	8.50	8.95	9.49	10.80
	6H	12.57	13.03	13.57	14.05	15.36	8.38	8.85	9.38	9.86	11.17
	8H	12.74	13.18	13.75	14.19	15.51	8.51	8.94	9.51	9.95	11.27
	12H	12.84	13.24	13.87	14.26	15.59	8.57	8.97	9.60	9.99	11.32
8H	4H	12.01	12.45	13.02	13.46	14.78	8.24	8.68	9.25	9.69	11.01
	6H	12.59	12.95	13.62	14.00	15.32	8.76	9.12	9.79	10.17	11.49
	8H	12.81	13.12	13.84	14.16	15.50	8.95	9.27	9.99	10.31	11.64
	12H	12.95	13.23	13.99	14.26	15.64	9.07	9.35	10.11	10.38	11.77
12H	4H	11.97	12.36	12.99	13.39	14.71	8.25	8.64	9.27	9.66	10.99
	6H	12.56	12.88	13.60	13.92	15.25	8.81	9.13	9.85	10.17	11.50
	8H	12.79	13.07	13.83	14.10	15.48	9.02	9.30	10.06	10.33	11.72