

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906915

Luminaire Tested: DFN2DIP-SQ4F0-120D160US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906915
REPORT IS A COMBINATION OF REPORTS P901736 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D160US835-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26040.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 239.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906915

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906915

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3480	3480	3480
5°	3486	3425	3448
10°	3451	3359	3337
15°	3403	3249	3164
20°	3341	3096	2952
25°	3276	2925	2747
30°	3190	2750	2487
35°	3105	2561	2259
40°	3019	2366	1996
45°	2919	2149	1759
50°	2815	1931	1527
55°	2707	1697	1303
60°	2582	1452	1074
65°	2438	1204	968
70°	2263	971	877
75°	2044	858	800
80°	1726	722	697
85°	1202	486	531

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2919 cd/sqm

TEST NUMBER: P906915

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.8	1.8
10°-20°	1276.0	4.9
20°-30°	1791.5	6.9
30°-40°	1952.8	7.5
40°-50°	1794.9	6.9
50°-60°	1409.6	5.4
60°-70°	917.5	3.5
70°-80°	472.3	1.8
80°-90°	130.1	0.5
90°-100°	178.0	0.7
100°-110°	663.8	2.5
110°-120°	1760.4	6.8
120°-130°	2919.7	11.2
130°-140°	3101.5	11.9
140°-150°	2882.5	11.1
150°-160°	2317.4	8.9
160°-170°	1493.3	5.7
170°-180°	514.0	2.0
0°-30°	3532.3	13.6
0°-40°	5485.2	21.1
0°-60°	8689.6	33.4
0°-90°	10209.5	39.2
90°-120°	2602.2	10.0
90°-150°	11505.9	44.2
90°-180°	15831.0	60.8
0°-180°	26040.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4960	4960	4960	4960	4960	
5°	4960	4937	4879	4919	4906	470
15°	4717	4668	4515	4430	4385	1329
25°	4282	4138	3842	3658	3590	1969
35°	3690	3460	3066	2783	2684	2309
45°	3016	2715	2244	1925	1818	2329
55°	2293	1943	1459	1190	1104	2049
65°	1549	1185	781	629	615	1535
75°	826	511	359	328	323	873
85°	193	99	85	85	85	221
90°	4	47	78	98	105	24
95°	254	125	152	172	168	301
105°	1188	1305	238	281	297	1269
115°	2247	2313	2411	602	321	2212
125°	3176	3227	3302	3329	3341	2833
135°	3931	3994	4028	4068	4060	3036
145°	4560	4556	4622	4650	4630	2852
155°	5021	4986	5033	5056	5025	2314
165°	5290	5267	5279	5306	5279	1495
175°	5411	5384	5392	5419	5380	515
180°	5400	5400	5400	5400	5400	

TEST NUMBER: P906915

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4959.6	4959.6	4959.6	4959.6	4959.6
2.5°	4982.0	4959.6	4910.1	4955.3	4946.2
5°	4959.6	4937.2	4878.6	4919.1	4905.8
7.5°	4919.1	4892.4	4829.6	4847.2	4824.8
10°	4865.3	4833.9	4744.3	4730.5	4703.9
12.5°	4798.1	4757.7	4636.2	4609.6	4560.1
15°	4717.2	4667.7	4515.3	4430.0	4385.3
17.5°	4622.9	4551.0	4362.4	4263.9	4192.0
20°	4515.3	4425.3	4201.0	4089.1	3990.0
22.5°	4398.6	4295.3	4034.8	3882.4	3815.3
25°	4282.0	4138.1	3841.9	3658.1	3590.5
27.5°	4142.9	3990.0	3662.4	3451.5	3348.1
30°	3994.8	3823.9	3464.8	3236.2	3114.8
32.5°	3851.0	3644.3	3276.7	3007.2	2894.8
35°	3689.6	3460.5	3065.7	2782.9	2683.8
37.5°	3532.4	3285.3	2868.1	2558.1	2446.2
40°	3366.2	3097.2	2661.5	2342.9	2226.2
42.5°	3195.7	2908.6	2455.3	2122.9	2011.0
45°	3016.2	2715.3	2244.3	1925.3	1817.6
47.5°	2845.7	2527.2	2042.4	1723.4	1624.8
50°	2657.2	2338.6	1844.8	1534.8	1441.0
52.5°	2472.9	2136.2	1656.2	1360.0	1274.8
55°	2293.4	1943.4	1458.6	1189.5	1104.3
57.5°	2109.5	1750.5	1283.8	1032.4	960.5
60°	1921.0	1561.9	1099.5	871.0	799.1
62.5°	1737.2	1378.1	942.4	727.2	691.4
65°	1548.6	1184.8	781.0	628.6	614.8
67.5°	1369.1	1005.2	628.6	551.9	538.6
70°	1180.5	830.5	520.5	475.7	457.6
72.5°	1001.0	668.6	435.2	399.5	390.5
75°	825.7	511.4	359.1	327.6	323.3
77.5°	651.0	363.3	282.9	264.8	255.7
80°	489.1	260.5	215.2	197.6	197.6
82.5°	341.0	175.2	148.1	139.0	139.0
85°	192.9	98.6	85.2	85.2	85.2
87.5°	71.9	35.7	35.7	31.4	31.4
90°	3.7	46.9	77.9	97.9	105.3
92.5°	97.9	82.1	93.7	101.6	105.3
95°	253.8	124.8	152.2	172.1	168.0
97.5°	457.0	136.9	199.0	211.1	214.8
100°	691.8	156.4	222.7	253.8	261.7
102.5°	949.3	941.9	230.6	273.3	285.3
105°	1187.8	1305.2	238.5	281.2	296.9
107.5°	1465.2	1562.7	246.4	289.1	304.8
110°	1731.1	1812.8	683.9	293.2	308.5

TEST NUMBER: P906915

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1981.2	2051.3	1984.9	300.7	312.7
115°	2246.6	2312.9	2410.8	601.8	320.6
117.5°	2477.2	2555.1	2622.0	2062.9	1039.3
120°	2735.2	2793.6	2864.1	2911.0	2383.5
122.5°	2953.7	3016.3	3094.7	3117.9	3122.1
125°	3176.4	3227.4	3301.7	3329.1	3340.7
127.5°	3379.6	3434.4	3493.3	3532.3	3536.0
130°	3571.3	3633.9	3676.6	3719.7	3716.0
132.5°	3766.6	3817.6	3860.3	3895.6	3891.9
135°	3930.8	3993.5	4028.3	4067.7	4059.8
137.5°	4102.5	4149.4	4188.8	4227.8	4216.2
140°	4270.5	4302.0	4344.7	4380.0	4360.5
142.5°	4411.5	4438.9	4489.5	4520.6	4501.1
145°	4560.0	4555.8	4622.2	4649.5	4630.1
147.5°	4688.5	4676.9	4743.3	4762.8	4747.4
150°	4813.8	4786.4	4849.1	4872.3	4852.8
152.5°	4919.1	4888.0	4946.5	4970.2	4942.8
155°	5020.7	4985.9	5032.8	5056.0	5024.9
157.5°	5102.9	5071.8	5107.0	5134.4	5102.9
160°	5173.4	5149.7	5173.4	5196.6	5169.2
162.5°	5235.6	5212.4	5231.8	5259.2	5224.0
165°	5290.3	5267.1	5278.7	5306.1	5278.7
167.5°	5333.5	5309.8	5321.9	5349.2	5314.0
170°	5368.7	5345.1	5352.9	5380.3	5345.1
172.5°	5391.9	5368.7	5376.6	5404.0	5368.7
175°	5411.4	5384.0	5391.9	5419.3	5380.3
177.5°	5419.3	5391.9	5396.1	5423.5	5388.2
180°	5399.8	5399.8	5399.8	5399.8	5399.8

TEST NUMBER: P906915

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.39	11.14	11.44	12.19	13.61	6.35	7.10	7.41	8.15	9.57
	3H	12.07	12.74	13.13	13.80	15.24	7.54	8.21	8.60	9.27	10.71
	4H	12.68	13.31	13.75	14.37	15.82	7.98	8.62	9.06	9.68	11.13
	6H	13.10	13.68	14.18	14.75	16.20	8.30	8.89	9.38	9.95	11.41
	8H	13.22	13.78	14.31	14.86	16.31	8.39	8.95	9.48	10.03	11.48
	12H	13.29	13.81	14.38	14.89	16.36	8.43	8.96	9.52	10.03	11.51
4H	2H	10.40	11.04	11.48	12.10	13.54	6.94	7.58	8.02	8.64	10.08
	3H	12.23	12.76	13.31	13.85	15.30	8.29	8.81	9.37	9.90	11.36
	4H	12.92	13.40	14.01	14.48	15.96	8.83	9.32	9.92	10.39	11.87
	6H	13.44	13.85	14.53	14.95	16.43	9.25	9.66	10.35	10.76	12.24
	8H	13.61	14.00	14.71	15.09	16.58	9.38	9.76	10.47	10.86	12.35
	12H	13.71	14.06	14.82	15.16	16.66	9.44	9.79	10.55	10.89	12.39
8H	4H	12.88	13.27	13.98	14.36	15.85	9.11	9.50	10.21	10.59	12.08
	6H	13.45	13.77	14.57	14.91	16.39	9.63	9.94	10.75	11.08	12.57
	8H	13.67	13.95	14.80	15.07	16.57	9.82	10.10	10.94	11.21	12.72
	12H	13.81	14.05	14.94	15.17	16.71	9.93	10.18	11.06	11.29	12.84
12H	4H	12.83	13.18	13.95	14.29	15.78	9.11	9.46	10.23	10.57	12.06
	6H	13.43	13.71	14.55	14.82	16.33	9.68	9.95	10.80	11.07	12.58
	8H	13.65	13.89	14.78	15.01	16.55	9.88	10.13	11.01	11.24	12.79

END OF REPORT