

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914949

Luminaire Tested: DFN2DIP-SQ4F0-080D140US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914949
REPORT IS A COMBINATION OF REPORTS P901709 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D140US927-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17253.7 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 177.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914949
CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P914949

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31				31
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31	26				26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22				22
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23	19				19
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20	16				16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14				14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13				13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11				11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10				10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1730	1730	1730
5°	1733	1707	1718
10°	1719	1684	1695
15°	1694	1657	1660
20°	1660	1618	1623
25°	1626	1573	1580
30°	1583	1530	1526
35°	1542	1480	1469
40°	1493	1429	1414
45°	1443	1378	1358
50°	1389	1325	1294
55°	1332	1264	1234
60°	1268	1190	1166
65°	1198	1115	1086
70°	1109	1022	1000
75°	986	912	922
80°	838	771	770
85°	605	528	517

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2006 cd/sqm



TEST NUMBER: P914949

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	1.3
10°-20°	653.0	3.8
20°-30°	959.7	5.6
30°-40°	1114.6	6.5
40°-50°	1113.2	6.5
50°-60°	970.7	5.6
60°-70°	717.6	4.2
70°-80°	406.0	2.4
80°-90°	113.7	0.7
90°-100°	123.4	0.7
100°-110°	460.1	2.7
110°-120°	1220.2	7.1
120°-130°	2023.8	11.7
130°-140°	2149.8	12.5
140°-150°	1998.0	11.6
150°-160°	1606.3	9.3
160°-170°	1035.1	6.0
170°-180°	356.3	2.1
0°-30°	1844.8	10.7
0°-40°	2959.4	17.2
0°-60°	5043.4	29.2
0°-90°	6280.6	36.4
90°-120°	1803.7	10.5
90°-150°	7975.4	46.2
90°-180°	10973.0	63.6
0°-180°	17253.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2466	2466	2466	2466	2466	
5°	2466	2457	2430	2449	2445	234
15°	2348	2333	2302	2312	2300	661
25°	2125	2106	2066	2070	2066	978
35°	1833	1809	1771	1757	1745	1145
45°	1492	1475	1439	1413	1404	1151
55°	1129	1114	1086	1058	1046	1009
65°	761	747	723	702	690	753
75°	398	394	382	368	372	425
85°	97	95	93	85	83	108
90°	2	32	54	68	73	16
95°	176	86	106	119	116	208
105°	823	905	165	195	206	880
115°	1557	1603	1671	417	222	1533
125°	2202	2237	2289	2308	2316	1964
135°	2725	2768	2792	2820	2814	2105
145°	3161	3158	3204	3223	3209	1977
155°	3480	3456	3488	3505	3483	1604
165°	3667	3651	3659	3678	3659	1036
175°	3751	3732	3737	3756	3729	357
180°	3743	3743	3743	3743	3743	



TEST NUMBER: P914949

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.9	2465.9	2465.9	2465.9	2465.9
2.5°	2480.2	2468.4	2442.3	2465.9	2461.4
5°	2465.9	2456.6	2430.5	2449.3	2444.8
7.5°	2449.3	2435.2	2409.1	2428.2	2423.4
10°	2423.4	2406.8	2378.4	2397.2	2390.2
12.5°	2387.7	2373.6	2345.2	2357.0	2352.2
15°	2347.5	2333.4	2302.4	2312.0	2300.2
17.5°	2297.6	2283.5	2252.6	2264.4	2252.6
20°	2243.1	2229.0	2195.8	2202.8	2193.5
22.5°	2188.7	2167.3	2136.4	2136.4	2131.6
25°	2124.6	2105.7	2065.5	2070.0	2065.5
27.5°	2053.3	2036.8	2006.0	1999.0	1987.2
30°	1982.4	1963.3	1927.9	1920.8	1911.2
32.5°	1906.5	1892.4	1854.3	1840.0	1830.5
35°	1832.9	1809.3	1771.3	1757.0	1745.2
37.5°	1749.9	1728.5	1690.6	1674.0	1662.2
40°	1664.7	1645.5	1607.6	1586.4	1576.8
42.5°	1581.7	1562.5	1524.8	1500.9	1486.8
45°	1491.6	1475.0	1439.2	1413.3	1403.8
47.5°	1403.8	1387.2	1349.2	1323.0	1308.9
50°	1311.2	1299.4	1266.1	1233.0	1221.1
52.5°	1221.1	1204.5	1173.9	1147.7	1131.1
55°	1128.8	1114.4	1086.1	1057.6	1045.8
57.5°	1036.3	1024.4	993.5	965.0	955.4
60°	943.6	934.4	901.1	875.0	867.9
62.5°	853.6	837.0	813.3	789.7	780.1
65°	761.3	746.9	723.3	701.9	690.1
67.5°	666.4	654.3	633.2	616.6	607.0
70°	578.6	569.0	547.7	531.1	521.7
72.5°	488.5	479.0	467.1	450.6	443.5
75°	398.2	393.7	381.7	367.6	372.3
77.5°	317.7	308.2	303.4	296.4	289.3
80°	237.3	234.7	230.0	222.9	218.1
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	2.5	32.5	54.0	67.9	73.0
92.5°	67.9	57.0	65.0	70.4	73.0
95°	175.9	86.5	105.5	119.3	116.5
97.5°	316.8	94.9	138.0	146.3	148.9
100°	479.5	108.4	154.4	175.9	181.4
102.5°	658.0	652.8	159.9	189.4	197.8
105°	823.3	904.7	165.3	194.9	205.8
107.5°	1015.7	1083.1	170.8	200.3	211.3
110°	1199.9	1256.6	474.0	203.3	213.9



TEST NUMBER: P914949

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1373.2	1421.8	1375.9	208.4	216.7
115°	1557.3	1603.2	1671.1	417.2	222.2
117.5°	1717.1	1771.1	1817.4	1429.9	720.4
120°	1895.9	1936.4	1985.3	2017.8	1652.1
122.5°	2047.4	2090.8	2145.1	2161.2	2164.2
125°	2201.8	2237.1	2288.6	2307.5	2315.6
127.5°	2342.6	2380.6	2421.4	2448.4	2451.0
130°	2475.4	2518.9	2548.4	2578.4	2575.8
132.5°	2610.9	2646.2	2675.8	2700.2	2697.7
135°	2724.7	2768.1	2792.2	2819.5	2814.1
137.5°	2843.7	2876.2	2903.5	2930.5	2922.5
140°	2960.1	2982.0	3011.6	3036.0	3022.5
142.5°	3057.9	3076.8	3111.9	3133.5	3119.9
145°	3160.8	3157.9	3203.9	3222.9	3209.4
147.5°	3249.9	3241.8	3287.9	3301.3	3290.7
150°	3336.7	3317.7	3361.1	3377.2	3363.8
152.5°	3409.7	3388.2	3428.7	3445.1	3426.1
155°	3480.1	3456.0	3488.5	3504.6	3483.1
157.5°	3537.1	3515.5	3540.0	3559.0	3537.1
160°	3586.0	3569.6	3586.0	3602.0	3583.1
162.5°	3629.1	3613.0	3626.5	3645.5	3621.1
165°	3667.0	3650.9	3659.0	3677.9	3659.0
167.5°	3697.0	3680.6	3688.9	3707.9	3683.4
170°	3721.4	3705.0	3710.4	3729.4	3705.0
172.5°	3737.4	3721.4	3726.8	3745.8	3721.4
175°	3751.0	3732.0	3737.4	3756.4	3729.4
177.5°	3756.4	3737.4	3740.4	3759.3	3734.9
180°	3742.9	3742.9	3742.9	3742.9	3742.9



TEST NUMBER: P914949
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.78	8.53	8.85	9.60	11.05	7.34	8.09	8.40	9.16	10.61
	3H	9.44	10.11	10.51	11.19	12.66	8.95	9.62	10.02	10.70	12.17
	4H	10.02	10.66	11.11	11.74	13.22	9.53	10.17	10.62	11.25	12.72
	6H	10.42	11.01	11.52	12.09	13.58	9.92	10.51	11.02	11.59	13.08
	8H	10.53	11.08	11.62	12.18	13.67	10.02	10.58	11.12	11.68	13.16
	12H	10.57	11.10	11.68	12.19	13.70	10.06	10.59	11.17	11.68	13.19
4H	2H	8.23	8.87	9.32	9.95	11.43	7.88	8.51	8.97	9.59	11.07
	3H	10.09	10.62	11.19	11.73	13.22	9.68	10.22	10.78	11.32	12.81
	4H	10.80	11.29	11.91	12.39	13.90	10.38	10.87	11.49	11.96	13.48
	6H	11.32	11.74	12.43	12.86	14.36	10.89	11.30	12.00	12.42	13.93
	8H	11.47	11.86	12.58	12.97	14.49	11.03	11.42	12.14	12.53	14.05
	12H	11.54	11.89	12.67	13.01	14.54	11.09	11.44	12.22	12.56	14.09
8H	4H	10.99	11.38	12.10	12.49	14.01	10.62	11.01	11.73	12.12	13.64
	6H	11.62	11.95	12.76	13.10	14.62	11.24	11.56	12.37	12.72	14.23
	8H	11.85	12.13	12.99	13.26	14.80	11.45	11.74	12.59	12.87	14.41
	12H	11.98	12.22	13.12	13.35	14.93	11.56	11.81	12.71	12.94	14.52
12H	4H	10.97	11.33	12.10	12.45	13.98	10.60	10.96	11.73	12.08	13.61
	6H	11.65	11.94	12.79	13.07	14.61	11.28	11.56	12.42	12.70	14.23
	8H	11.89	12.14	13.04	13.27	14.84	11.51	11.76	12.66	12.89	14.46