

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906917

Luminaire Tested: DFN2DIP-SQ4F0-140D060US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906917
REPORT IS A COMBINATION OF REPORTS P901593 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D060US835-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19800.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906917

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906917

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3822	3822	3822
5°	3828	3770	3796
10°	3797	3720	3745
15°	3741	3659	3666
20°	3666	3575	3585
25°	3591	3474	3491
30°	3497	3380	3371
35°	3408	3269	3244
40°	3298	3157	3124
45°	3188	3045	3001
50°	3069	2927	2858
55°	2943	2791	2727
60°	2802	2629	2577
65°	2647	2462	2400
70°	2450	2258	2210
75°	2178	2014	2036
80°	1850	1704	1701
85°	1337	1165	1143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3188 cd/sqm

TEST NUMBER: P906917

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.7	2.6
10°-20°	1442.6	7.3
20°-30°	2120.0	10.7
30°-40°	2462.3	12.4
40°-50°	2459.3	12.4
50°-60°	2144.4	10.8
60°-70°	1585.2	8.0
70°-80°	896.9	4.5
80°-90°	240.3	1.2
90°-100°	66.8	0.3
100°-110°	248.9	1.3
110°-120°	660.2	3.3
120°-130°	1094.9	5.5
130°-140°	1163.0	5.9
140°-150°	1080.9	5.5
150°-160°	869.0	4.4
160°-170°	560.0	2.8
170°-180°	192.7	1.0
0°-30°	4075.3	20.6
0°-40°	6537.6	33.0
0°-60°	11141.3	56.3
0°-90°	13863.6	70.0
90°-120°	975.8	4.9
90°-150°	4314.7	21.8
90°-180°	5936.0	30.0
0°-180°	19800.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5448	5448	5448	5448	5448	
5°	5448	5427	5369	5411	5401	517
15°	5186	5155	5086	5107	5081	1461
25°	4693	4652	4563	4573	4563	2160
35°	4049	3997	3913	3881	3855	2529
45°	3295	3258	3180	3122	3101	2543
55°	2494	2462	2399	2336	2310	2229
65°	1682	1650	1598	1550	1524	1663
75°	880	870	843	812	822	939
85°	214	210	204	188	183	239
90°	1	18	29	37	40	18
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	

TEST NUMBER: P906917

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5447.5	5447.5	5447.5	5447.5	5447.5
2.5°	5479.1	5453.0	5395.2	5447.5	5437.5
5°	5447.5	5426.9	5369.1	5410.8	5400.8
7.5°	5410.8	5379.7	5321.9	5364.1	5353.5
10°	5353.5	5316.9	5254.1	5295.8	5280.2
12.5°	5274.6	5243.5	5180.7	5206.8	5196.3
15°	5185.7	5154.6	5086.2	5107.4	5081.2
17.5°	5075.7	5044.6	4976.2	5002.3	4976.2
20°	4955.1	4924.0	4850.6	4866.2	4845.6
22.5°	4835.0	4787.8	4719.4	4719.4	4708.9
25°	4693.3	4651.6	4562.7	4572.7	4562.7
27.5°	4536.0	4499.4	4431.6	4416.0	4389.9
30°	4379.3	4337.1	4258.7	4243.2	4222.0
32.5°	4211.5	4180.4	4096.4	4064.8	4043.6
35°	4049.2	3997.0	3913.0	3881.4	3855.2
37.5°	3865.8	3818.6	3734.6	3698.0	3671.8
40°	3677.4	3635.2	3551.2	3504.6	3483.4
42.5°	3494.0	3451.8	3368.4	3315.6	3284.5
45°	3295.0	3258.4	3179.5	3122.2	3101.1
47.5°	3101.1	3064.4	2980.5	2922.7	2891.6
50°	2896.6	2870.5	2797.1	2723.7	2697.6
52.5°	2697.6	2660.9	2593.1	2535.3	2498.7
55°	2493.7	2462.0	2399.2	2336.4	2310.3
57.5°	2289.1	2263.0	2194.7	2131.9	2110.7
60°	2084.6	2064.1	1990.7	1932.9	1917.3
62.5°	1885.7	1849.0	1796.7	1744.5	1723.4
65°	1681.7	1650.0	1597.8	1550.5	1524.4
67.5°	1472.2	1445.5	1398.8	1362.1	1341.0
70°	1278.2	1257.1	1209.9	1173.2	1152.6
72.5°	1079.3	1058.1	1032.0	995.4	979.8
75°	879.8	869.8	843.1	812.0	822.5
77.5°	701.9	680.8	670.2	654.7	639.1
80°	524.1	518.5	508.0	492.4	481.8
82.5°	356.2	356.2	351.2	330.1	330.1
85°	214.5	209.5	204.5	188.4	183.4
87.5°	94.5	83.9	73.4	57.8	52.2
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7

TEST NUMBER: P906917

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9

TEST NUMBER: P906917

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US835-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.61	14.69	14.38	15.48	16.43	13.17	14.24	13.93	15.03	15.98
	3H	15.29	16.26	16.07	17.06	18.04	14.80	15.77	15.58	16.57	17.55
	4H	15.89	16.81	16.69	17.61	18.61	15.40	16.31	16.19	17.12	18.11
	6H	16.31	17.15	17.12	17.96	18.97	15.81	16.65	16.62	17.46	18.47
	8H	16.42	17.22	17.24	18.06	19.07	15.92	16.72	16.74	17.55	18.56
	12H	16.48	17.24	17.30	18.07	19.11	15.97	16.73	16.79	17.56	18.60
4H	2H	14.10	15.01	14.90	15.82	16.81	13.75	14.66	14.54	15.46	16.46
	3H	15.99	16.75	16.80	17.59	18.60	15.58	16.34	16.39	17.18	18.19
	4H	16.72	17.41	17.54	18.25	19.29	16.29	16.99	17.12	17.82	18.86
	6H	17.25	17.85	18.09	18.71	19.75	16.82	17.42	17.66	18.28	19.32
	8H	17.41	17.97	18.25	18.82	19.88	16.97	17.53	17.81	18.39	19.44
	12H	17.49	18.00	18.36	18.87	19.94	17.04	17.55	17.91	18.42	19.49
8H	4H	16.93	17.49	17.78	18.35	19.41	16.55	17.12	17.40	17.97	19.03
	6H	17.58	18.04	18.45	18.94	20.00	17.19	17.66	18.07	18.56	19.61
	8H	17.80	18.21	18.69	19.11	20.18	17.41	17.82	18.29	18.72	19.79
	12H	17.95	18.31	18.83	19.19	20.32	17.54	17.90	18.42	18.78	19.91
12H	4H	16.93	17.43	17.79	18.31	19.37	16.56	17.06	17.42	17.94	19.00
	6H	17.61	18.02	18.49	18.91	19.99	17.24	17.65	18.12	18.54	19.62
	8H	17.86	18.23	18.75	19.11	20.24	17.48	17.85	18.37	18.73	19.86