

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906922

Luminaire Tested: DFN2DIP-SQ4F0-140D070US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906922
REPORT IS A COMBINATION OF REPORTS P900092 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D070US835-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18095.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 196
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906922
CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P906922

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				66
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	57				57
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52	49				49
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45	42				42
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40	36				36
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32				32
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31	29				29
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28	26				26
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25	23				23
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23	21				21
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4060	4060	4060
5°	4066	3996	4022
10°	4026	3919	3893
15°	3971	3790	3691
20°	3897	3612	3444
25°	3822	3413	3205
30°	3721	3208	2902
35°	3622	2988	2635
40°	3522	2760	2329
45°	3405	2508	2052
50°	3284	2252	1781
55°	3158	1980	1521
60°	3012	1694	1253
65°	2844	1404	1129
70°	2640	1133	1024
75°	2384	1001	934
80°	2014	842	814
85°	1402	566	619

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3405 cd/sqm



TEST NUMBER: P906922

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	542.3	3.0
10°-20°	1488.7	8.2
20°-30°	2090.1	11.6
30°-40°	2278.3	12.6
40°-50°	2094.0	11.6
50°-60°	1644.5	9.1
60°-70°	1070.4	5.9
70°-80°	551.0	3.0
80°-90°	147.0	0.8
90°-100°	137.0	0.8
100°-110°	435.3	2.4
110°-120°	744.9	4.1
120°-130°	979.6	5.4
130°-140°	1099.6	6.1
140°-150°	1078.3	6.0
150°-160°	904.5	5.0
160°-170°	599.9	3.3
170°-180°	209.7	1.2
0°-30°	4121.0	22.8
0°-40°	6399.4	35.4
0°-60°	10137.9	56.0
0°-90°	11906.3	65.8
90°-120°	1317.2	7.3
90°-150°	4474.7	24.7
90°-180°	6189.0	34.2
0°-180°	18095.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5786	5786	5786	5786	5786	
5°	5786	5760	5692	5739	5723	549
15°	5503	5446	5268	5168	5116	1551
25°	4996	4828	4482	4268	4189	2297
35°	4304	4037	3577	3247	3131	2694
45°	3519	3168	2618	2246	2121	2718
55°	2676	2267	1702	1388	1288	2391
65°	1807	1382	911	733	717	1791
75°	963	597	419	382	377	1019
85°	225	115	99	99	99	258
90°	2	24	65	61	63	18
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	



TEST NUMBER: P906922

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5786.2	5786.2	5786.2	5786.2	5786.2
2.5°	5812.3	5786.2	5728.4	5781.2	5770.6
5°	5786.2	5760.1	5691.7	5739.0	5723.4
7.5°	5739.0	5707.8	5634.5	5655.1	5629.0
10°	5676.2	5639.5	5535.1	5518.9	5487.8
12.5°	5597.8	5550.6	5408.9	5377.8	5320.1
15°	5503.4	5445.6	5267.8	5168.4	5116.2
17.5°	5393.4	5309.5	5089.5	4974.5	4890.6
20°	5267.8	5162.8	4901.2	4770.6	4655.1
22.5°	5131.7	5011.2	4707.3	4529.5	4451.2
25°	4995.6	4827.8	4482.3	4267.8	4188.9
27.5°	4833.4	4655.1	4272.8	4026.7	3906.2
30°	4660.6	4461.2	4042.3	3775.6	3633.9
32.5°	4492.8	4251.7	3822.8	3508.4	3377.3
35°	4304.5	4037.3	3576.7	3246.7	3131.1
37.5°	4121.2	3832.8	3346.1	2984.5	2853.9
40°	3927.3	3613.4	3105.0	2733.4	2597.3
42.5°	3728.4	3393.4	2864.5	2476.7	2346.1
45°	3518.9	3167.8	2618.4	2246.1	2120.6
47.5°	3320.0	2948.4	2382.8	2010.6	1895.6
50°	3100.0	2728.4	2152.2	1790.6	1681.1
52.5°	2885.0	2492.2	1932.2	1586.7	1487.2
55°	2675.6	2267.2	1701.7	1387.8	1288.3
57.5°	2461.1	2042.2	1497.8	1204.5	1120.6
60°	2241.1	1822.2	1282.8	1016.1	932.2
62.5°	2026.7	1607.8	1099.5	848.3	806.7
65°	1806.7	1382.2	911.1	733.3	717.2
67.5°	1597.2	1172.8	733.3	643.9	628.3
70°	1377.2	968.9	607.2	555.0	533.9
72.5°	1167.8	780.0	507.8	466.1	455.6
75°	963.3	596.7	418.9	382.2	377.2
77.5°	759.5	423.9	330.0	308.9	298.3
80°	570.6	303.9	251.1	230.6	230.6
82.5°	397.8	204.4	172.8	162.2	162.2
85°	225.0	115.0	99.4	99.4	99.4
87.5°	83.9	41.7	41.7	36.7	36.7
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3



TEST NUMBER: P906922

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8



TEST NUMBER: P906922
 CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.39	14.37	14.20	15.20	16.23	9.35	10.33	10.16	11.16	12.19
	3H	15.08	15.96	15.91	16.80	17.86	10.55	11.42	11.38	12.27	13.32
	4H	15.70	16.52	16.55	17.37	18.44	11.01	11.83	11.85	12.68	13.75
	6H	16.13	16.89	16.99	17.75	18.83	11.34	12.10	12.19	12.95	14.04
	8H	16.27	16.99	17.13	17.86	18.95	11.43	12.15	12.30	13.03	14.11
	12H	16.33	17.02	17.21	17.89	19.00	11.48	12.17	12.35	13.04	14.14
4H	2H	13.42	14.25	14.27	15.10	16.17	9.96	10.79	10.82	11.64	12.71
	3H	15.27	15.96	16.13	16.84	17.92	11.33	12.01	12.19	12.90	13.98
	4H	15.97	16.60	16.85	17.48	18.59	11.88	12.51	12.76	13.39	14.50
	6H	16.50	17.04	17.39	17.94	19.06	12.31	12.85	13.20	13.75	14.87
	8H	16.68	17.18	17.57	18.08	19.21	12.44	12.95	13.34	13.84	14.97
	12H	16.79	17.24	17.70	18.15	19.29	12.52	12.97	13.43	13.89	15.02
8H	4H	15.95	16.45	16.84	17.35	18.48	12.18	12.68	13.07	13.58	14.70
	6H	16.53	16.94	17.45	17.88	19.01	12.70	13.12	13.62	14.06	15.18
	8H	16.75	17.11	17.68	18.05	19.19	12.89	13.26	13.82	14.20	15.34
	12H	16.90	17.22	17.83	18.14	19.34	13.02	13.34	13.95	14.27	15.46
12H	4H	15.91	16.36	16.82	17.28	18.41	12.19	12.64	13.10	13.56	14.69
	6H	16.50	16.87	17.43	17.80	18.95	12.75	13.12	13.68	14.05	15.20
	8H	16.73	17.06	17.66	17.98	19.18	12.97	13.29	13.90	14.22	15.41