

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906923

Luminaire Tested: DFN2DIP-SQ4F0-140D070US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906923
REPORT IS A COMBINATION OF REPORTS P901612 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D070US835-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18830.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 196
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906923

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906923

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4060	4060	4060
5°	4066	3996	4022
10°	4026	3919	3893
15°	3971	3790	3691
20°	3897	3612	3444
25°	3822	3413	3205
30°	3721	3208	2902
35°	3622	2988	2635
40°	3522	2760	2329
45°	3405	2508	2052
50°	3284	2252	1781
55°	3158	1980	1521
60°	3012	1694	1253
65°	2844	1404	1129
70°	2640	1133	1024
75°	2384	1001	934
80°	2014	842	814
85°	1402	566	619

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3405 cd/sqm

TEST NUMBER: P906923

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	542.3	2.9
10°-20°	1488.7	7.9
20°-30°	2090.1	11.1
30°-40°	2278.3	12.1
40°-50°	2094.0	11.1
50°-60°	1644.5	8.7
60°-70°	1070.4	5.7
70°-80°	551.0	2.9
80°-90°	144.8	0.8
90°-100°	77.9	0.4
100°-110°	290.4	1.5
110°-120°	770.2	4.1
120°-130°	1277.4	6.8
130°-140°	1356.9	7.2
140°-150°	1261.1	6.7
150°-160°	1013.9	5.4
160°-170°	653.3	3.5
170°-180°	224.9	1.2
0°-30°	4121.0	21.9
0°-40°	6399.4	34.0
0°-60°	10137.9	53.8
0°-90°	11904.1	63.2
90°-120°	1138.5	6.0
90°-150°	5033.8	26.7
90°-180°	6926.0	36.8
0°-180°	18830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5786	5786	5786	5786	5786	
5°	5786	5760	5692	5739	5723	549
15°	5503	5446	5268	5168	5116	1551
25°	4996	4828	4482	4268	4189	2297
35°	4304	4037	3577	3247	3131	2694
45°	3519	3168	2618	2246	2121	2718
55°	2676	2267	1702	1388	1288	2391
65°	1807	1382	911	733	717	1791
75°	963	597	419	382	377	1019
85°	225	115	99	99	99	258
90°	2	20	34	43	46	18
95°	111	55	67	75	74	131
105°	520	571	104	123	130	555
115°	983	1012	1055	263	140	968
125°	1390	1412	1444	1456	1462	1239
135°	1720	1747	1762	1780	1776	1328
145°	1995	1993	2022	2034	2026	1248
155°	2197	2181	2202	2212	2198	1012
165°	2314	2304	2309	2321	2309	654
175°	2368	2356	2359	2371	2354	225
180°	2362	2362	2362	2362	2362	

TEST NUMBER: P906923

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5786.2	5786.2	5786.2	5786.2	5786.2
2.5°	5812.3	5786.2	5728.4	5781.2	5770.6
5°	5786.2	5760.1	5691.7	5739.0	5723.4
7.5°	5739.0	5707.8	5634.5	5655.1	5629.0
10°	5676.2	5639.5	5535.1	5518.9	5487.8
12.5°	5597.8	5550.6	5408.9	5377.8	5320.1
15°	5503.4	5445.6	5267.8	5168.4	5116.2
17.5°	5393.4	5309.5	5089.5	4974.5	4890.6
20°	5267.8	5162.8	4901.2	4770.6	4655.1
22.5°	5131.7	5011.2	4707.3	4529.5	4451.2
25°	4995.6	4827.8	4482.3	4267.8	4188.9
27.5°	4833.4	4655.1	4272.8	4026.7	3906.2
30°	4660.6	4461.2	4042.3	3775.6	3633.9
32.5°	4492.8	4251.7	3822.8	3508.4	3377.3
35°	4304.5	4037.3	3576.7	3246.7	3131.1
37.5°	4121.2	3832.8	3346.1	2984.5	2853.9
40°	3927.3	3613.4	3105.0	2733.4	2597.3
42.5°	3728.4	3393.4	2864.5	2476.7	2346.1
45°	3518.9	3167.8	2618.4	2246.1	2120.6
47.5°	3320.0	2948.4	2382.8	2010.6	1895.6
50°	3100.0	2728.4	2152.2	1790.6	1681.1
52.5°	2885.0	2492.2	1932.2	1586.7	1487.2
55°	2675.6	2267.2	1701.7	1387.8	1288.3
57.5°	2461.1	2042.2	1497.8	1204.5	1120.6
60°	2241.1	1822.2	1282.8	1016.1	932.2
62.5°	2026.7	1607.8	1099.5	848.3	806.7
65°	1806.7	1382.2	911.1	733.3	717.2
67.5°	1597.2	1172.8	733.3	643.9	628.3
70°	1377.2	968.9	607.2	555.0	533.9
72.5°	1167.8	780.0	507.8	466.1	455.6
75°	963.3	596.7	418.9	382.2	377.2
77.5°	759.5	423.9	330.0	308.9	298.3
80°	570.6	303.9	251.1	230.6	230.6
82.5°	397.8	204.4	172.8	162.2	162.2
85°	225.0	115.0	99.4	99.4	99.4
87.5°	83.9	41.7	41.7	36.7	36.7
90°	1.6	20.5	34.1	42.8	46.1
92.5°	42.8	35.9	41.0	44.5	46.1
95°	111.0	54.6	66.6	75.3	73.5
97.5°	199.9	59.9	87.1	92.4	94.0
100°	302.7	68.4	97.4	111.0	114.5
102.5°	415.3	412.1	100.9	119.6	124.8
105°	519.7	571.0	104.3	123.0	129.9
107.5°	641.0	683.7	107.8	126.5	133.4
110°	757.4	793.1	299.2	128.3	135.0



TEST NUMBER: P906923

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	866.8	897.4	868.4	131.5	136.8
115°	982.9	1011.9	1054.7	263.3	140.3
117.5°	1083.8	1117.9	1147.1	902.5	454.7
120°	1196.6	1222.2	1253.1	1273.6	1042.8
122.5°	1292.2	1319.6	1354.0	1364.1	1365.9
125°	1389.7	1412.0	1444.5	1456.5	1461.5
127.5°	1478.6	1502.5	1528.3	1545.4	1547.0
130°	1562.4	1589.8	1608.5	1627.4	1625.8
132.5°	1647.9	1670.2	1688.9	1704.3	1702.7
135°	1719.7	1747.1	1762.4	1779.6	1776.2
137.5°	1794.8	1815.4	1832.6	1849.7	1844.6
140°	1868.3	1882.1	1900.8	1916.2	1907.7
142.5°	1930.0	1942.0	1964.1	1977.7	1969.2
145°	1995.0	1993.2	2022.2	2034.2	2025.7
147.5°	2051.2	2046.2	2075.2	2083.7	2077.0
150°	2106.0	2094.1	2121.5	2131.6	2123.1
152.5°	2152.1	2138.5	2164.1	2174.4	2162.5
155°	2196.6	2181.3	2201.8	2212.0	2198.4
157.5°	2232.5	2218.9	2234.3	2246.3	2232.5
160°	2263.4	2253.0	2263.4	2273.5	2261.5
162.5°	2290.6	2280.4	2288.9	2300.9	2285.5
165°	2314.5	2304.4	2309.4	2321.4	2309.4
167.5°	2333.4	2323.0	2328.3	2340.3	2324.9
170°	2348.8	2338.5	2341.9	2353.9	2338.5
172.5°	2359.0	2348.8	2352.3	2364.2	2348.8
175°	2367.5	2355.5	2359.0	2370.9	2353.9
177.5°	2370.9	2359.0	2360.8	2372.8	2357.3
180°	2362.4	2362.4	2362.4	2362.4	2362.4

TEST NUMBER: P906923

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.18	14.13	14.02	14.99	16.06	9.14	10.09	9.98	10.95	12.02
	3H	14.87	15.72	15.73	16.59	17.69	10.34	11.19	11.19	12.06	13.16
	4H	15.49	16.29	16.36	17.17	18.28	10.80	11.60	11.67	12.47	13.58
	6H	15.92	16.66	16.80	17.54	18.66	11.12	11.86	12.01	12.74	13.87
	8H	16.05	16.75	16.94	17.65	18.78	11.22	11.92	12.11	12.82	13.94
	12H	16.12	16.79	17.02	17.68	18.83	11.27	11.93	12.16	12.83	13.98
4H	2H	13.21	14.02	14.09	14.89	16.00	9.75	10.56	10.63	11.43	12.54
	3H	15.06	15.72	15.94	16.63	17.76	11.12	11.78	12.00	12.69	13.81
	4H	15.76	16.36	16.66	17.27	18.42	11.67	12.28	12.57	13.18	14.33
	6H	16.28	16.81	17.20	17.73	18.89	12.10	12.62	13.01	13.55	14.70
	8H	16.46	16.95	17.38	17.87	19.04	12.23	12.72	13.14	13.64	14.80
	12H	16.57	17.01	17.50	17.95	19.12	12.30	12.74	13.23	13.68	14.85
8H	4H	15.74	16.22	16.65	17.14	18.31	11.96	12.45	12.88	13.37	14.54
	6H	16.31	16.71	17.25	17.68	18.84	12.48	12.89	13.43	13.85	15.02
	8H	16.53	16.89	17.48	17.84	19.03	12.68	13.03	13.63	13.99	15.17
	12H	16.68	16.99	17.63	17.94	19.17	12.80	13.12	13.76	14.06	15.30
12H	4H	15.69	16.13	16.63	17.07	18.24	11.97	12.41	12.91	13.35	14.52
	6H	16.29	16.64	17.24	17.60	18.78	12.54	12.89	13.49	13.85	15.03
	8H	16.52	16.83	17.47	17.78	19.01	12.75	13.07	13.71	14.01	15.25