

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906932

Luminaire Tested: DFN2DIP-SQ4F0-140D100US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906932
REPORT IS A COMBINATION OF REPORTS P900145 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D100US835-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22710.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 218.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906932

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906932

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	48	37	30	25	33	27	23	30	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3822	3822	3822
5°	3828	3770	3796
10°	3797	3720	3745
15°	3741	3659	3666
20°	3666	3575	3585
25°	3591	3474	3491
30°	3497	3380	3371
35°	3408	3269	3244
40°	3298	3157	3124
45°	3188	3045	3001
50°	3069	2927	2858
55°	2943	2791	2727
60°	2802	2629	2577
65°	2647	2462	2400
70°	2450	2258	2210
75°	2178	2014	2036
80°	1850	1704	1701
85°	1337	1165	1143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3188 cd/sqm

TEST NUMBER: P906932

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.7	2.3
10°-20°	1442.6	6.4
20°-30°	2120.0	9.3
30°-40°	2462.3	10.8
40°-50°	2459.3	10.8
50°-60°	2144.4	9.4
60°-70°	1585.2	7.0
70°-80°	896.9	3.9
80°-90°	245.7	1.1
90°-100°	195.7	0.9
100°-110°	621.8	2.7
110°-120°	1064.1	4.7
120°-130°	1399.5	6.2
130°-140°	1570.9	6.9
140°-150°	1540.4	6.8
150°-160°	1292.2	5.7
160°-170°	856.9	3.8
170°-180°	299.5	1.3
0°-30°	4075.3	17.9
0°-40°	6537.6	28.8
0°-60°	11141.3	49.1
0°-90°	13869.0	61.1
90°-120°	1881.6	8.3
90°-150°	6392.4	28.1
90°-180°	8841.0	38.9
0°-180°	22710.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5448	5448	5448	5448	5448	
5°	5448	5427	5369	5411	5401	517
15°	5186	5155	5086	5107	5081	1461
25°	4693	4652	4563	4573	4563	2160
35°	4049	3997	3913	3881	3855	2529
45°	3295	3258	3180	3122	3101	2543
55°	2494	2462	2399	2336	2310	2229
65°	1682	1650	1598	1550	1524	1663
75°	880	870	843	812	822	939
85°	214	210	204	188	183	239
90°	3	34	93	88	91	22
95°	139	166	171	171	166	155
105°	574	582	587	592	592	606
115°	1068	1083	1078	1076	1068	1056
125°	1553	1577	1569	1561	1558	1388
135°	2009	2038	2044	2041	2034	1553
145°	2439	2458	2473	2476	2466	1524
155°	2789	2796	2805	2818	2810	1284
165°	3034	3031	3031	3050	3037	856
175°	3157	3149	3144	3163	3146	300
180°	3163	3163	3163	3163	3163	

TEST NUMBER: P906932

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5447.5	5447.5	5447.5	5447.5	5447.5
2.5°	5479.1	5453.0	5395.2	5447.5	5437.5
5°	5447.5	5426.9	5369.1	5410.8	5400.8
7.5°	5410.8	5379.7	5321.9	5364.1	5353.5
10°	5353.5	5316.9	5254.1	5295.8	5280.2
12.5°	5274.6	5243.5	5180.7	5206.8	5196.3
15°	5185.7	5154.6	5086.2	5107.4	5081.2
17.5°	5075.7	5044.6	4976.2	5002.3	4976.2
20°	4955.1	4924.0	4850.6	4866.2	4845.6
22.5°	4835.0	4787.8	4719.4	4719.4	4708.9
25°	4693.3	4651.6	4562.7	4572.7	4562.7
27.5°	4536.0	4499.4	4431.6	4416.0	4389.9
30°	4379.3	4337.1	4258.7	4243.2	4222.0
32.5°	4211.5	4180.4	4096.4	4064.8	4043.6
35°	4049.2	3997.0	3913.0	3881.4	3855.2
37.5°	3865.8	3818.6	3734.6	3698.0	3671.8
40°	3677.4	3635.2	3551.2	3504.6	3483.4
42.5°	3494.0	3451.8	3368.4	3315.6	3284.5
45°	3295.0	3258.4	3179.5	3122.2	3101.1
47.5°	3101.1	3064.4	2980.5	2922.7	2891.6
50°	2896.6	2870.5	2797.1	2723.7	2697.6
52.5°	2697.6	2660.9	2593.1	2535.3	2498.7
55°	2493.7	2462.0	2399.2	2336.4	2310.3
57.5°	2289.1	2263.0	2194.7	2131.9	2110.7
60°	2084.6	2064.1	1990.7	1932.9	1917.3
62.5°	1885.7	1849.0	1796.7	1744.5	1723.4
65°	1681.7	1650.0	1597.8	1550.5	1524.4
67.5°	1472.2	1445.5	1398.8	1362.1	1341.0
70°	1278.2	1257.1	1209.9	1173.2	1152.6
72.5°	1079.3	1058.1	1032.0	995.4	979.8
75°	879.8	869.8	843.1	812.0	822.5
77.5°	701.9	680.8	670.2	654.7	639.1
80°	524.1	518.5	508.0	492.4	481.8
82.5°	356.2	356.2	351.2	330.1	330.1
85°	214.5	209.5	204.5	188.4	183.4
87.5°	94.5	83.9	73.4	57.8	52.2
90°	2.9	34.3	93.4	87.7	90.6
92.5°	59.1	80.1	83.0	85.8	85.8
95°	139.2	165.9	170.7	170.7	165.9
97.5°	231.7	256.5	267.0	267.0	267.0
100°	338.5	360.4	368.0	368.0	365.2
102.5°	451.0	467.2	477.7	480.5	477.7
105°	574.0	581.6	587.3	592.1	592.1
107.5°	696.0	707.5	707.5	709.4	696.0
110°	814.3	829.5	829.5	829.5	821.9

TEST NUMBER: P906932

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	942.0	958.2	955.4	947.7	942.0
115°	1067.9	1083.1	1078.4	1075.5	1067.9
117.5°	1192.8	1213.8	1200.4	1192.8	1185.1
120°	1318.6	1339.6	1318.6	1318.6	1310.1
122.5°	1433.0	1459.7	1446.4	1438.8	1433.0
125°	1553.2	1577.0	1569.4	1560.8	1558.0
127.5°	1670.5	1700.0	1689.5	1678.1	1670.5
130°	1780.1	1814.4	1809.7	1803.9	1793.5
132.5°	1903.1	1929.8	1931.7	1918.4	1910.7
135°	2008.9	2038.5	2044.2	2041.4	2033.7
137.5°	2127.2	2151.0	2155.8	2153.9	2142.4
140°	2231.1	2254.9	2268.3	2268.3	2257.8
142.5°	2337.9	2361.7	2369.3	2372.2	2361.7
145°	2438.9	2458.0	2473.3	2476.1	2465.6
147.5°	2529.5	2553.4	2564.8	2569.6	2559.1
150°	2623.0	2639.2	2649.7	2658.2	2649.7
152.5°	2705.9	2722.1	2735.5	2746.0	2735.5
155°	2788.9	2796.5	2805.1	2818.4	2809.8
157.5°	2860.4	2866.1	2870.9	2889.9	2876.6
160°	2924.3	2930.0	2932.8	2949.0	2937.6
162.5°	2983.4	2983.4	2986.2	3004.3	2991.0
165°	3033.9	3031.0	3031.0	3050.1	3036.8
167.5°	3079.7	3071.1	3071.1	3090.2	3076.8
170°	3114.0	3106.4	3103.5	3122.6	3106.4
172.5°	3137.8	3130.2	3127.3	3146.4	3130.2
175°	3156.9	3149.3	3143.6	3162.6	3146.4
177.5°	3167.4	3159.8	3154.0	3170.2	3154.0
180°	3162.6	3162.6	3162.6	3162.6	3162.6

TEST NUMBER: P906932

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.91	13.88	13.76	14.75	15.86	12.46	13.43	13.32	14.31	15.41
	3H	14.58	15.45	15.45	16.34	17.47	14.09	14.96	14.96	15.85	16.98
	4H	15.17	16.00	16.06	16.89	18.03	14.68	15.50	15.56	16.40	17.54
	6H	15.58	16.34	16.48	17.24	18.40	15.08	15.84	15.98	16.74	17.90
	8H	15.69	16.42	16.60	17.33	18.49	15.19	15.91	16.09	16.83	17.98
	12H	15.75	16.43	16.66	17.35	18.53	15.24	15.93	16.15	16.84	18.02
4H	2H	13.38	14.20	14.27	15.10	16.24	13.03	13.85	13.91	14.74	15.88
	3H	15.26	15.95	16.16	16.87	18.03	14.85	15.54	15.75	16.47	17.62
	4H	15.98	16.61	16.89	17.53	18.71	15.56	16.19	16.47	17.11	18.29
	6H	16.51	17.05	17.43	17.99	19.18	16.08	16.62	17.00	17.56	18.74
	8H	16.66	17.17	17.59	18.11	19.30	16.23	16.73	17.15	17.67	18.87
	12H	16.74	17.20	17.69	18.16	19.36	16.29	16.75	17.24	17.71	18.91
8H	4H	16.19	16.69	17.12	17.63	18.83	15.81	16.32	16.74	17.26	18.45
	6H	16.83	17.25	17.78	18.23	19.42	16.45	16.86	17.40	17.84	19.04
	8H	17.05	17.42	18.02	18.39	19.61	16.66	17.03	17.63	18.00	19.22
	12H	17.19	17.52	18.16	18.48	19.74	16.78	17.11	17.75	18.07	19.33
12H	4H	16.18	16.64	17.13	17.59	18.79	15.81	16.27	16.76	17.22	18.43
	6H	16.86	17.23	17.82	18.20	19.41	16.49	16.86	17.45	17.83	19.04
	8H	17.11	17.44	18.08	18.40	19.66	16.73	17.06	17.70	18.02	19.28