

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914985

Luminaire Tested: DFN2DIP-SQ4F0-090D140US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914985
REPORT IS A COMBINATION OF REPORTS P901711 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D140US927-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18037.9 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 188.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914985

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914985

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39
2	87	80	74	68	79	73	67	63	59	56	52	47	45	42	36	34	33
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28
4	72	62	54	48	66	56	50	45	46	41	38	37	34	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	30	27	26	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18
7	56	44	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1947	1947	1947
5°	1950	1920	1933
10°	1934	1894	1907
15°	1905	1864	1867
20°	1867	1821	1826
25°	1829	1769	1778
30°	1781	1721	1717
35°	1735	1665	1652
40°	1679	1608	1591
45°	1624	1551	1528
50°	1563	1491	1455
55°	1499	1421	1389
60°	1427	1339	1312
65°	1348	1254	1222
70°	1248	1150	1125
75°	1109	1026	1037
80°	942	867	866
85°	681	594	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2006 cd/sqm

TEST NUMBER: P914985

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.1	1.4
10°-20°	734.7	4.1
20°-30°	1079.6	6.0
30°-40°	1253.9	7.0
40°-50°	1252.4	6.9
50°-60°	1092.1	6.1
60°-70°	807.3	4.5
70°-80°	456.7	2.5
80°-90°	127.1	0.7
90°-100°	123.4	0.7
100°-110°	460.1	2.6
110°-120°	1220.2	6.8
120°-130°	2023.8	11.2
130°-140°	2149.8	11.9
140°-150°	1998.0	11.1
150°-160°	1606.3	8.9
160°-170°	1035.1	5.7
170°-180°	356.3	2.0
0°-30°	2075.4	11.5
0°-40°	3329.4	18.5
0°-60°	5673.8	31.5
0°-90°	7064.9	39.2
90°-120°	1803.7	10.0
90°-150°	7975.4	44.2
90°-180°	10973.0	60.8
0°-180°	18037.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2774	2774	2774	2774	2774	
5°	2774	2764	2734	2756	2750	263
15°	2641	2625	2590	2601	2588	744
25°	2390	2369	2324	2329	2324	1100
35°	2062	2036	1993	1977	1963	1288
45°	1678	1659	1619	1590	1579	1295
55°	1270	1254	1222	1190	1176	1135
65°	856	840	814	790	776	847
75°	448	443	429	414	419	478
85°	109	107	104	96	93	122
90°	2	32	54	68	73	17
95°	176	86	106	119	116	208
105°	823	905	165	195	206	880
115°	1557	1603	1671	417	222	1533
125°	2202	2237	2289	2308	2316	1964
135°	2725	2768	2792	2820	2814	2105
145°	3161	3158	3204	3223	3209	1977
155°	3480	3456	3488	3505	3483	1604
165°	3667	3651	3659	3678	3659	1036
175°	3751	3732	3737	3756	3729	357
180°	3743	3743	3743	3743	3743	

TEST NUMBER: P914985

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2774.1	2774.1	2774.1	2774.1	2774.1
2.5°	2790.3	2777.0	2747.6	2774.1	2769.1
5°	2774.1	2763.7	2734.3	2755.5	2750.4
7.5°	2755.5	2739.7	2710.2	2731.8	2726.4
10°	2726.4	2707.7	2675.7	2696.9	2689.0
12.5°	2686.1	2670.3	2638.4	2651.6	2646.3
15°	2640.9	2625.1	2590.2	2601.0	2587.7
17.5°	2584.8	2569.0	2534.2	2547.5	2534.2
20°	2523.4	2507.6	2470.2	2478.1	2467.6
22.5°	2462.3	2438.3	2403.4	2403.4	2398.0
25°	2390.1	2368.9	2323.6	2328.7	2323.6
27.5°	2310.0	2291.3	2256.8	2248.9	2235.6
30°	2230.2	2208.7	2168.8	2160.8	2150.1
32.5°	2144.8	2128.9	2086.1	2070.0	2059.3
35°	2062.1	2035.5	1992.7	1976.7	1963.3
37.5°	1968.7	1944.6	1901.9	1883.3	1869.9
40°	1872.7	1851.2	1808.5	1784.7	1774.0
42.5°	1779.3	1757.8	1715.4	1688.5	1672.7
45°	1678.0	1659.4	1619.1	1590.0	1579.3
47.5°	1579.3	1560.6	1517.8	1488.4	1472.6
50°	1475.1	1461.8	1424.4	1387.1	1373.8
52.5°	1373.8	1355.1	1320.6	1291.2	1272.5
55°	1269.9	1253.8	1221.8	1189.9	1176.5
57.5°	1165.8	1152.5	1117.7	1085.7	1074.9
60°	1061.6	1051.1	1013.8	984.4	976.4
62.5°	960.3	941.6	915.0	888.4	877.7
65°	856.4	840.3	813.6	789.6	776.3
67.5°	749.7	736.2	712.3	693.7	682.9
70°	650.9	640.2	616.2	597.5	587.0
72.5°	549.6	538.8	525.5	506.9	499.0
75°	448.1	442.9	429.4	413.5	418.9
77.5°	357.4	346.7	341.4	333.4	325.5
80°	266.9	264.0	258.6	250.7	245.4
82.5°	181.4	181.4	178.9	168.1	168.1
85°	109.2	106.7	104.2	95.9	93.4
87.5°	48.1	42.7	37.4	29.5	26.6
90°	2.5	32.5	54.0	67.9	73.0
92.5°	67.9	57.0	65.0	70.4	73.0
95°	175.9	86.5	105.5	119.3	116.5
97.5°	316.8	94.9	138.0	146.3	148.9
100°	479.5	108.4	154.4	175.9	181.4
102.5°	658.0	652.8	159.9	189.4	197.8
105°	823.3	904.7	165.3	194.9	205.8
107.5°	1015.7	1083.1	170.8	200.3	211.3
110°	1199.9	1256.6	474.0	203.3	213.9

TEST NUMBER: P914985

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1373.2	1421.8	1375.9	208.4	216.7
115°	1557.3	1603.2	1671.1	417.2	222.2
117.5°	1717.1	1771.1	1817.4	1429.9	720.4
120°	1895.9	1936.4	1985.3	2017.8	1652.1
122.5°	2047.4	2090.8	2145.1	2161.2	2164.2
125°	2201.8	2237.1	2288.6	2307.5	2315.6
127.5°	2342.6	2380.6	2421.4	2448.4	2451.0
130°	2475.4	2518.9	2548.4	2578.4	2575.8
132.5°	2610.9	2646.2	2675.8	2700.2	2697.7
135°	2724.7	2768.1	2792.2	2819.5	2814.1
137.5°	2843.7	2876.2	2903.5	2930.5	2922.5
140°	2960.1	2982.0	3011.6	3036.0	3022.5
142.5°	3057.9	3076.8	3111.9	3133.5	3119.9
145°	3160.8	3157.9	3203.9	3222.9	3209.4
147.5°	3249.9	3241.8	3287.9	3301.3	3290.7
150°	3336.7	3317.7	3361.1	3377.2	3363.8
152.5°	3409.7	3388.2	3428.7	3445.1	3426.1
155°	3480.1	3456.0	3488.5	3504.6	3483.1
157.5°	3537.1	3515.5	3540.0	3559.0	3537.1
160°	3586.0	3569.6	3586.0	3602.0	3583.1
162.5°	3629.1	3613.0	3626.5	3645.5	3621.1
165°	3667.0	3650.9	3659.0	3677.9	3659.0
167.5°	3697.0	3680.6	3688.9	3707.9	3683.4
170°	3721.4	3705.0	3710.4	3729.4	3705.0
172.5°	3737.4	3721.4	3726.8	3745.8	3721.4
175°	3751.0	3732.0	3737.4	3756.4	3729.4
177.5°	3756.4	3737.4	3740.4	3759.3	3734.9
180°	3742.9	3742.9	3742.9	3742.9	3742.9

TEST NUMBER: P914985

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.51	9.28	9.55	10.33	11.75	8.06	8.83	9.11	9.88	11.30
	3H	10.16	10.86	11.22	11.91	13.35	9.67	10.37	10.73	11.42	12.86
	4H	10.75	11.41	11.82	12.47	13.91	10.26	10.91	11.32	11.97	13.42
	6H	11.15	11.75	12.23	12.82	14.27	10.65	11.25	11.72	12.32	13.77
	8H	11.25	11.83	12.33	12.91	14.36	10.75	11.33	11.83	12.41	13.86
	12H	11.30	11.85	12.39	12.92	14.39	10.79	11.34	11.88	12.41	13.89
4H	2H	8.96	9.61	10.03	10.67	12.12	8.60	9.26	9.68	10.32	11.76
	3H	10.82	11.37	11.90	12.45	13.91	10.41	10.96	11.49	12.05	13.50
	4H	11.53	12.04	12.62	13.11	14.59	11.11	11.61	12.20	12.69	14.17
	6H	12.05	12.48	13.14	13.58	15.05	11.62	12.05	12.71	13.15	14.62
	8H	12.20	12.60	13.29	13.69	15.18	11.76	12.16	12.85	13.26	14.74
	12H	12.27	12.63	13.38	13.74	15.23	11.82	12.18	12.93	13.29	14.78
8H	4H	11.72	12.13	12.82	13.22	14.71	11.35	11.75	12.44	12.84	14.33
	6H	12.36	12.69	13.47	13.82	15.31	11.97	12.30	13.09	13.44	14.92
	8H	12.58	12.87	13.70	13.99	15.49	12.19	12.48	13.31	13.59	15.10
	12H	12.71	12.96	13.84	14.08	15.62	12.30	12.55	13.42	13.67	15.21
12H	4H	11.70	12.07	12.82	13.18	14.67	11.34	11.70	12.45	12.81	14.30
	6H	12.38	12.68	13.51	13.79	15.30	12.01	12.30	13.14	13.42	14.93
	8H	12.63	12.88	13.75	14.00	15.54	12.25	12.50	13.37	13.62	15.16