

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906945

Luminaire Tested: DFN2DIP-SQ4F0-140D140US835-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P906945  
REPORT IS A COMBINATION OF REPORTS P901719 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-140D140US835-FLLONL  
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 27720.0 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 249.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P906945  
CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US835-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P906945  
 CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US835-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3822	3822	3822
5°	3828	3770	3796
10°	3797	3720	3745
15°	3741	3659	3666
20°	3666	3575	3585
25°	3591	3474	3491
30°	3497	3380	3371
35°	3408	3269	3244
40°	3298	3157	3124
45°	3188	3045	3001
50°	3069	2927	2858
55°	2943	2791	2727
60°	2802	2629	2577
65°	2647	2462	2400
70°	2450	2258	2210
75°	2178	2014	2036
80°	1850	1704	1701
85°	1337	1165	1143

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3188 cd/sqm



TEST NUMBER: P906945

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US835-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	512.7	1.8
10°-20°	1442.6	5.2
20°-30°	2120.0	7.6
30°-40°	2462.3	8.9
40°-50°	2459.3	8.9
50°-60°	2144.4	7.7
60°-70°	1585.2	5.7
70°-80°	896.9	3.2
80°-90°	245.0	0.9
90°-100°	155.8	0.6
100°-110°	580.8	2.1
110°-120°	1540.3	5.6
120°-130°	2554.8	9.2
130°-140°	2713.8	9.8
140°-150°	2522.1	9.1
150°-160°	2027.7	7.3
160°-170°	1306.6	4.7
170°-180°	449.7	1.6
0°-30°	4075.3	14.7
0°-40°	6537.6	23.6
0°-60°	11141.3	40.2
0°-90°	13868.3	50.0
90°-120°	2276.9	8.2
90°-150°	10067.6	36.3
90°-180°	13852.0	50.0
0°-180°	27720.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5448	5448	5448	5448	5448	
5°	5448	5427	5369	5411	5401	517
15°	5186	5155	5086	5107	5081	1461
25°	4693	4652	4563	4573	4563	2160
35°	4049	3997	3913	3881	3855	2529
45°	3295	3258	3180	3122	3101	2543
55°	2494	2462	2399	2336	2310	2229
65°	1682	1650	1598	1550	1524	1663
75°	880	870	843	812	822	939
85°	214	210	204	188	183	239
90°	3	41	68	86	92	26
95°	222	109	133	151	147	263
105°	1039	1142	209	246	260	1110
115°	1966	2024	2110	527	280	1935
125°	2779	2824	2889	2913	2923	2479
135°	3440	3494	3525	3559	3552	2657
145°	3990	3986	4044	4068	4051	2495
155°	4393	4363	4404	4424	4397	2024
165°	4629	4609	4619	4643	4619	1308
175°	4735	4711	4718	4742	4708	451
180°	4725	4725	4725	4725	4725	



TEST NUMBER: P906945

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US835-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5447.5	5447.5	5447.5	5447.5	5447.5
2.5°	5479.1	5453.0	5395.2	5447.5	5437.5
5°	5447.5	5426.9	5369.1	5410.8	5400.8
7.5°	5410.8	5379.7	5321.9	5364.1	5353.5
10°	5353.5	5316.9	5254.1	5295.8	5280.2
12.5°	5274.6	5243.5	5180.7	5206.8	5196.3
15°	5185.7	5154.6	5086.2	5107.4	5081.2
17.5°	5075.7	5044.6	4976.2	5002.3	4976.2
20°	4955.1	4924.0	4850.6	4866.2	4845.6
22.5°	4835.0	4787.8	4719.4	4719.4	4708.9
25°	4693.3	4651.6	4562.7	4572.7	4562.7
27.5°	4536.0	4499.4	4431.6	4416.0	4389.9
30°	4379.3	4337.1	4258.7	4243.2	4222.0
32.5°	4211.5	4180.4	4096.4	4064.8	4043.6
35°	4049.2	3997.0	3913.0	3881.4	3855.2
37.5°	3865.8	3818.6	3734.6	3698.0	3671.8
40°	3677.4	3635.2	3551.2	3504.6	3483.4
42.5°	3494.0	3451.8	3368.4	3315.6	3284.5
45°	3295.0	3258.4	3179.5	3122.2	3101.1
47.5°	3101.1	3064.4	2980.5	2922.7	2891.6
50°	2896.6	2870.5	2797.1	2723.7	2697.6
52.5°	2697.6	2660.9	2593.1	2535.3	2498.7
55°	2493.7	2462.0	2399.2	2336.4	2310.3
57.5°	2289.1	2263.0	2194.7	2131.9	2110.7
60°	2084.6	2064.1	1990.7	1932.9	1917.3
62.5°	1885.7	1849.0	1796.7	1744.5	1723.4
65°	1681.7	1650.0	1597.8	1550.5	1524.4
67.5°	1472.2	1445.5	1398.8	1362.1	1341.0
70°	1278.2	1257.1	1209.9	1173.2	1152.6
72.5°	1079.3	1058.1	1032.0	995.4	979.8
75°	879.8	869.8	843.1	812.0	822.5
77.5°	701.9	680.8	670.2	654.7	639.1
80°	524.1	518.5	508.0	492.4	481.8
82.5°	356.2	356.2	351.2	330.1	330.1
85°	214.5	209.5	204.5	188.4	183.4
87.5°	94.5	83.9	73.4	57.8	52.2
90°	3.2	41.0	68.2	85.7	92.2
92.5°	85.7	71.9	82.0	88.9	92.2
95°	222.1	109.2	133.2	150.6	147.0
97.5°	399.9	119.8	174.2	184.7	188.0
100°	605.3	136.8	194.9	222.1	229.0
102.5°	830.6	824.1	201.8	239.1	249.7
105°	1039.3	1142.0	208.7	246.0	259.8
107.5°	1282.1	1367.3	215.6	252.9	266.7
110°	1514.7	1586.2	598.4	256.6	270.0



TEST NUMBER: P906945

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US835-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1733.5	1794.8	1736.8	263.1	273.6
115°	1965.8	2023.8	2109.5	526.6	280.5
117.5°	2167.5	2235.7	2294.2	1805.0	909.4
120°	2393.3	2444.4	2506.1	2547.1	2085.5
122.5°	2584.5	2639.3	2707.9	2728.2	2731.9
125°	2779.4	2824.0	2889.0	2912.9	2923.1
127.5°	2957.2	3005.1	3056.6	3090.7	3094.0
130°	3124.8	3179.7	3217.0	3254.8	3251.5
132.5°	3295.8	3340.4	3377.8	3408.6	3405.4
135°	3439.5	3494.3	3524.7	3559.2	3552.3
137.5°	3589.7	3630.7	3665.2	3699.3	3689.2
140°	3736.7	3764.3	3801.6	3832.5	3815.4
142.5°	3860.1	3884.0	3928.3	3955.5	3938.4
145°	3990.0	3986.3	4044.4	4068.4	4051.3
147.5°	4102.5	4092.3	4150.4	4167.4	4154.0
150°	4212.1	4188.1	4242.9	4263.2	4246.2
152.5°	4304.2	4277.0	4328.2	4348.9	4324.9
155°	4393.1	4362.7	4403.7	4424.0	4396.8
157.5°	4465.0	4437.8	4468.7	4492.6	4465.0
160°	4526.7	4506.0	4526.7	4547.0	4523.1
162.5°	4581.1	4560.8	4577.9	4601.8	4571.0
165°	4629.0	4608.7	4618.9	4642.8	4618.9
167.5°	4666.8	4646.1	4656.6	4680.6	4649.7
170°	4697.6	4676.9	4683.8	4707.8	4676.9
172.5°	4717.9	4697.6	4704.5	4728.5	4697.6
175°	4735.0	4711.0	4717.9	4741.9	4707.8
177.5°	4741.9	4717.9	4721.6	4745.5	4714.7
180°	4724.8	4724.8	4724.8	4724.8	4724.8



TEST NUMBER: P906945  
 CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US835-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.95	12.81	12.90	13.78	15.05	11.50	12.36	12.46	13.34	14.61
	3H	13.61	14.38	14.58	15.36	16.66	13.12	13.89	14.09	14.87	16.17
	4H	14.20	14.93	15.18	15.92	17.22	13.71	14.44	14.69	15.42	16.73
	6H	14.60	15.28	15.60	16.27	17.58	14.10	14.78	15.10	15.77	17.08
	8H	14.71	15.35	15.71	16.36	17.67	14.21	14.85	15.21	15.86	17.17
	12H	14.76	15.37	15.77	16.37	17.71	14.25	14.86	15.26	15.86	17.20
4H	2H	12.41	13.14	13.40	14.12	15.43	12.05	12.78	13.04	13.77	15.07
	3H	14.28	14.89	15.28	15.90	17.22	13.87	14.48	14.87	15.50	16.81
	4H	15.00	15.55	16.00	16.56	17.90	14.57	15.13	15.58	16.14	17.48
	6H	15.52	16.00	16.53	17.03	18.36	15.08	15.56	16.10	16.59	17.93
	8H	15.67	16.12	16.69	17.14	18.49	15.23	15.68	16.25	16.70	18.05
	12H	15.74	16.15	16.78	17.19	18.54	15.29	15.70	16.33	16.74	18.09
8H	4H	15.19	15.64	16.21	16.67	18.02	14.82	15.27	15.83	16.29	17.64
	6H	15.83	16.20	16.87	17.27	18.61	15.45	15.82	16.49	16.88	18.23
	8H	16.05	16.38	17.10	17.43	18.80	15.66	15.99	16.71	17.04	18.41
	12H	16.19	16.48	17.24	17.52	18.93	15.78	16.06	16.83	17.11	18.52
12H	4H	15.18	15.58	16.22	16.62	17.98	14.81	15.22	15.85	16.26	17.61
	6H	15.86	16.19	16.91	17.24	18.61	15.49	15.82	16.54	16.87	18.23
	8H	16.10	16.39	17.16	17.44	18.85	15.72	16.01	16.78	17.06	18.47