

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914991

Luminaire Tested: DFN2DIP-SQ4F0-090D160US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914991
REPORT IS A COMBINATION OF REPORTS P901730 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D160US927-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18608.4 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 204.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914991

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914991

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	47	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2068	2068	2068
5°	2071	2035	2048
10°	2050	1996	1982
15°	2022	1930	1880
20°	1985	1840	1754
25°	1947	1738	1632
30°	1895	1634	1478
35°	1845	1522	1342
40°	1794	1406	1186
45°	1734	1277	1045
50°	1672	1147	907
55°	1608	1008	774
60°	1534	863	638
65°	1448	715	575
70°	1345	577	521
75°	1214	510	475
80°	1026	429	414
85°	714	288	315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2292 cd/sqm

TEST NUMBER: P914991

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.2	1.5
10°-20°	758.1	4.1
20°-30°	1064.4	5.7
30°-40°	1160.3	6.2
40°-50°	1066.4	5.7
50°-60°	837.5	4.5
60°-70°	545.1	2.9
70°-80°	280.6	1.5
80°-90°	79.2	0.4
90°-100°	141.0	0.8
100°-110°	525.8	2.8
110°-120°	1394.6	7.5
120°-130°	2313.0	12.4
130°-140°	2456.9	13.2
140°-150°	2283.4	12.3
150°-160°	1835.8	9.9
160°-170°	1182.9	6.4
170°-180°	407.2	2.2
0°-30°	2098.7	11.3
0°-40°	3258.9	17.5
0°-60°	5162.8	27.7
0°-90°	6067.7	32.6
90°-120°	2061.4	11.1
90°-150°	9114.7	49.0
90°-180°	12541.0	67.4
0°-180°	18608.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2947	2947	2947	2947	2947	
5°	2947	2933	2899	2923	2915	279
15°	2803	2773	2683	2632	2606	790
25°	2544	2459	2283	2173	2133	1170
35°	2192	2056	1822	1653	1595	1372
45°	1792	1613	1333	1144	1080	1384
55°	1363	1155	867	707	656	1218
65°	920	704	464	373	365	912
75°	491	304	213	195	192	519
85°	114	58	51	51	51	132
90°	3	37	62	78	83	17
95°	201	99	121	136	133	238
105°	941	1034	189	223	235	1005
115°	1780	1832	1910	477	254	1752
125°	2516	2557	2616	2637	2646	2244
135°	3114	3164	3191	3222	3216	2405
145°	3612	3609	3662	3683	3668	2259
155°	3977	3950	3987	4005	3981	1833
165°	4191	4172	4182	4203	4182	1184
175°	4287	4265	4271	4293	4262	408
180°	4278	4278	4278	4278	4278	

TEST NUMBER: P914991

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.7	2946.7	2946.7	2946.7	2946.7
2.5°	2960.0	2946.7	2917.2	2944.1	2938.8
5°	2946.7	2933.4	2898.6	2922.6	2914.7
7.5°	2922.6	2906.8	2869.4	2879.9	2866.6
10°	2890.7	2872.0	2818.8	2810.6	2794.7
12.5°	2850.7	2826.7	2754.6	2738.7	2709.3
15°	2802.7	2773.3	2682.7	2632.0	2605.5
17.5°	2746.7	2704.0	2591.9	2533.3	2490.6
20°	2682.7	2629.2	2495.9	2429.5	2370.6
22.5°	2613.4	2552.0	2397.2	2306.7	2266.8
25°	2544.1	2458.6	2282.7	2173.4	2133.3
27.5°	2461.5	2370.6	2176.0	2050.6	1989.2
30°	2373.5	2271.9	2058.6	1922.8	1850.6
32.5°	2288.0	2165.2	1946.8	1786.7	1719.9
35°	2192.1	2056.0	1821.5	1653.4	1594.6
37.5°	2098.7	1951.9	1704.1	1519.9	1453.4
40°	2000.0	1840.2	1581.3	1392.0	1322.7
42.5°	1898.7	1728.1	1458.7	1261.3	1194.8
45°	1792.1	1613.3	1333.4	1143.8	1079.9
47.5°	1690.8	1501.5	1213.5	1023.9	965.4
50°	1578.7	1389.4	1096.1	911.9	856.1
52.5°	1469.3	1269.2	984.0	808.0	757.4
55°	1362.6	1154.6	866.6	706.8	656.1
57.5°	1253.4	1040.1	762.8	613.4	570.7
60°	1141.3	928.0	653.3	517.5	474.8
62.5°	1032.1	818.8	559.9	432.1	410.8
65°	920.0	703.9	464.0	373.4	365.3
67.5°	813.4	597.2	373.4	327.9	320.0
70°	701.4	493.4	309.3	282.7	271.9
72.5°	594.7	397.2	258.6	237.3	232.0
75°	490.6	303.9	213.3	194.6	192.1
77.5°	386.7	215.9	168.0	157.3	151.9
80°	290.6	154.8	127.9	117.4	117.4
82.5°	202.6	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	2.9	37.2	61.7	77.6	83.4
92.5°	77.6	65.0	74.2	80.5	83.4
95°	201.1	98.9	120.6	136.3	133.1
97.5°	362.0	108.4	157.6	167.2	170.2
100°	548.0	123.9	176.4	201.1	207.3
102.5°	752.0	746.2	182.7	216.5	226.0
105°	941.0	1034.0	188.9	222.8	235.2
107.5°	1160.7	1237.9	195.2	229.0	241.5
110°	1371.3	1436.1	541.8	232.3	244.4



TEST NUMBER: P914991

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1569.5	1625.0	1572.4	238.2	247.7
115°	1779.7	1832.2	1909.8	476.7	254.0
117.5°	1962.4	2024.1	2077.1	1634.2	823.3
120°	2166.8	2213.0	2268.9	2306.0	1888.2
122.5°	2339.9	2389.5	2451.6	2469.9	2473.3
125°	2516.3	2556.7	2615.5	2637.3	2646.4
127.5°	2677.3	2720.7	2767.3	2798.2	2801.2
130°	2829.1	2878.7	2912.5	2946.7	2943.7
132.5°	2983.8	3024.2	3058.1	3086.0	3083.1
135°	3113.9	3163.6	3191.1	3222.4	3216.1
137.5°	3249.9	3287.1	3318.3	3349.2	3340.0
140°	3383.0	3408.0	3441.8	3469.8	3454.3
142.5°	3494.7	3516.4	3556.5	3581.1	3565.7
145°	3612.3	3609.0	3661.6	3683.2	3667.9
147.5°	3714.1	3705.0	3757.6	3773.0	3760.8
150°	3813.4	3791.7	3841.4	3859.7	3844.3
152.5°	3896.8	3872.2	3918.5	3937.3	3915.6
155°	3977.3	3949.7	3986.9	4005.3	3980.6
157.5°	4042.4	4017.8	4045.7	4067.4	4042.4
160°	4098.3	4079.5	4098.3	4116.6	4094.9
162.5°	4147.5	4129.2	4144.5	4166.2	4138.4
165°	4190.9	4172.5	4181.7	4203.4	4181.7
167.5°	4225.1	4206.3	4215.9	4237.5	4209.7
170°	4253.0	4234.3	4240.5	4262.2	4234.3
172.5°	4271.4	4253.0	4259.2	4280.9	4253.0
175°	4286.8	4265.1	4271.4	4293.1	4262.2
177.5°	4293.1	4271.4	4274.7	4296.4	4268.4
180°	4277.6	4277.6	4277.6	4277.6	4277.6

TEST NUMBER: P914991

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.80	8.50	8.90	9.60	11.10	3.76	4.46	4.86	5.56	7.06
	3H	9.47	10.10	10.58	11.20	12.72	4.94	5.57	6.05	6.67	8.19
	4H	10.08	10.67	11.19	11.78	13.30	5.38	5.98	6.50	7.08	8.61
	6H	10.49	11.05	11.62	12.15	13.69	5.70	6.25	6.82	7.35	8.89
	8H	10.62	11.14	11.75	12.26	13.79	5.79	6.31	6.91	7.43	8.96
	12H	10.68	11.18	11.81	12.29	13.84	5.83	6.32	6.96	7.44	8.99
4H	2H	7.80	8.40	8.93	9.50	11.03	4.34	4.94	5.47	6.04	7.57
	3H	9.62	10.12	10.75	11.25	12.79	5.68	6.18	6.81	7.31	8.84
	4H	10.31	10.77	11.45	11.89	13.45	6.22	6.68	7.36	7.80	9.36
	6H	10.83	11.22	11.97	12.36	13.91	6.64	7.03	7.78	8.17	9.72
	8H	11.00	11.37	12.14	12.50	14.06	6.76	7.13	7.90	8.26	9.83
	12H	11.09	11.42	12.25	12.57	14.14	6.82	7.15	7.98	8.30	9.87
8H	4H	10.27	10.64	11.41	11.77	13.33	6.50	6.86	7.64	8.00	9.56
	6H	10.84	11.14	12.00	12.31	13.88	7.01	7.31	8.17	8.49	10.05
	8H	11.06	11.32	12.22	12.47	14.06	7.20	7.47	8.37	8.62	10.20
	12H	11.19	11.43	12.36	12.58	14.19	7.32	7.55	8.49	8.70	10.32
12H	4H	10.22	10.55	11.37	11.69	13.26	6.50	6.83	7.65	7.97	9.54
	6H	10.81	11.08	11.98	12.23	13.81	7.06	7.33	8.23	8.48	10.06
	8H	11.03	11.26	12.20	12.41	14.03	7.27	7.50	8.44	8.65	10.27