

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915037

Luminaire Tested: DFN2DIP-SQ4F0-110D080US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915037
REPORT IS A COMBINATION OF REPORTS P901625 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D080US927-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14900.9 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915037
CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915037

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58			58
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54	49			49
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45	41			41
3	83	73	66	60	77	68	62	57	60	54	50	51	47	44	44	41	38	35			35
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30			30
5	70	58	50	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26			26
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23			23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20			20
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18			18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16			16
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15			15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2379	2379	2379
5°	2383	2346	2362
10°	2364	2315	2331
15°	2329	2278	2282
20°	2282	2225	2231
25°	2235	2162	2173
30°	2176	2104	2098
35°	2121	2035	2019
40°	2053	1965	1944
45°	1985	1895	1868
50°	1910	1822	1779
55°	1832	1737	1697
60°	1744	1637	1604
65°	1648	1533	1494
70°	1525	1405	1375
75°	1355	1254	1267
80°	1151	1061	1059
85°	833	725	712

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1985 cd/sqm



TEST NUMBER: P915037

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.1	2.1
10°-20°	897.9	6.0
20°-30°	1319.6	8.9
30°-40°	1532.6	10.3
40°-50°	1530.7	10.3
50°-60°	1334.7	9.0
60°-70°	986.7	6.6
70°-80°	558.2	3.7
80°-90°	151.1	1.0
90°-100°	70.5	0.5
100°-110°	262.9	1.8
110°-120°	697.3	4.7
120°-130°	1156.5	7.8
130°-140°	1228.4	8.2
140°-150°	1141.7	7.7
150°-160°	917.9	6.2
160°-170°	591.5	4.0
170°-180°	203.6	1.4
0°-30°	2536.6	17.0
0°-40°	4069.2	27.3
0°-60°	6934.6	46.5
0°-90°	8630.6	57.9
90°-120°	1030.7	6.9
90°-150°	4557.3	30.6
90°-180°	6270.0	42.1
0°-180°	14900.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3391	3391	3391	3391	3391	
5°	3391	3378	3342	3368	3362	322
15°	3228	3208	3166	3179	3163	909
25°	2921	2895	2840	2846	2840	1344
35°	2520	2488	2436	2416	2400	1574
45°	2051	2028	1979	1943	1930	1583
55°	1552	1532	1493	1454	1438	1388
65°	1047	1027	994	965	949	1035
75°	548	541	525	505	512	585
85°	134	130	127	117	114	149
90°	2	18	31	39	42	14
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	



TEST NUMBER: P915037

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3390.7	3390.7	3390.7	3390.7	3390.7
2.5°	3410.3	3394.1	3358.1	3390.7	3384.4
5°	3390.7	3377.9	3341.9	3367.8	3361.6
7.5°	3367.8	3348.5	3312.5	3338.8	3332.2
10°	3332.2	3309.3	3270.3	3296.2	3286.5
12.5°	3283.1	3263.7	3224.7	3240.9	3234.3
15°	3227.7	3208.3	3165.8	3178.9	3162.7
17.5°	3159.2	3139.9	3097.3	3113.6	3097.3
20°	3084.2	3064.8	3019.2	3028.8	3016.1
22.5°	3009.5	2980.0	2937.5	2937.5	2930.9
25°	2921.2	2895.3	2840.0	2846.2	2840.0
27.5°	2823.3	2800.5	2758.3	2748.6	2732.4
30°	2725.8	2699.5	2650.7	2641.1	2627.9
32.5°	2621.3	2602.0	2549.7	2530.0	2516.8
35°	2520.3	2487.8	2435.6	2415.8	2399.6
37.5°	2406.2	2376.8	2324.6	2301.7	2285.4
40°	2288.9	2262.6	2210.4	2181.4	2168.2
42.5°	2174.8	2148.5	2096.6	2063.7	2044.4
45°	2051.0	2028.1	1978.9	1943.4	1930.2
47.5°	1930.2	1907.4	1855.1	1819.2	1799.8
50°	1802.9	1786.7	1741.0	1695.3	1679.1
52.5°	1679.1	1656.2	1614.1	1578.0	1555.2
55°	1552.1	1532.4	1493.3	1454.2	1438.0
57.5°	1424.8	1408.6	1366.0	1326.9	1313.8
60°	1297.5	1284.8	1239.1	1203.1	1193.4
62.5°	1173.7	1150.9	1118.3	1085.8	1072.7
65°	1046.7	1027.0	994.5	965.1	948.9
67.5°	916.3	899.8	870.7	847.9	834.7
70°	795.6	782.4	753.0	730.2	717.4
72.5°	671.8	658.6	642.4	619.6	609.8
75°	547.6	541.4	524.7	505.4	512.0
77.5°	436.9	423.7	417.2	407.5	397.8
80°	326.2	322.7	316.2	306.5	299.9
82.5°	221.7	221.7	218.6	205.5	205.5
85°	133.6	130.4	127.3	117.2	114.2
87.5°	58.8	52.2	45.6	36.0	32.5
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2



TEST NUMBER: P915037

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8



TEST NUMBER: P915037
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.00	11.93	11.88	12.84	13.99	10.55	11.49	11.44	12.40	13.55
	3H	12.67	13.51	13.57	14.42	15.60	12.18	13.02	13.07	13.93	15.11
	4H	13.26	14.06	14.17	14.98	16.17	12.77	13.56	13.68	14.48	15.67
	6H	13.67	14.40	14.59	15.33	16.53	13.17	13.90	14.09	14.83	16.03
	8H	13.78	14.48	14.71	15.42	16.62	13.28	13.97	14.21	14.92	16.12
	12H	13.83	14.49	14.77	15.43	16.66	13.32	13.98	14.26	14.92	16.15
4H	2H	11.47	12.26	12.39	13.18	14.37	11.11	11.91	12.03	12.83	14.02
	3H	13.34	14.01	14.27	14.96	16.16	12.94	13.60	13.87	14.55	15.76
	4H	14.07	14.67	15.01	15.62	16.85	13.64	14.25	14.58	15.19	16.42
	6H	14.59	15.11	15.54	16.08	17.31	14.16	14.68	15.11	15.65	16.88
	8H	14.74	15.23	15.70	16.20	17.44	14.31	14.79	15.26	15.76	17.00
	12H	14.82	15.26	15.80	16.24	17.49	14.37	14.81	15.35	15.80	17.04
8H	4H	14.27	14.76	15.22	15.72	16.96	13.89	14.38	14.85	15.35	16.59
	6H	14.91	15.31	15.89	16.32	17.56	14.52	14.93	15.51	15.94	17.18
	8H	15.13	15.49	16.12	16.48	17.74	14.74	15.10	15.73	16.09	17.35
	12H	15.27	15.59	16.26	16.57	17.88	14.86	15.17	15.85	16.16	17.47
12H	4H	14.26	14.70	15.23	15.68	16.93	13.89	14.33	14.86	15.31	16.56
	6H	14.94	15.30	15.93	16.29	17.55	14.57	14.92	15.56	15.92	17.18
	8H	15.19	15.50	16.18	16.49	17.80	14.81	15.12	15.80	16.11	17.42