

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909550

Luminaire Tested: DFN2DIP-SQ4F0-100D090US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909550
REPORT IS A COMBINATION OF REPORTS P900122 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D090US840-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16627.4 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 159.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909550
CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US840-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P909550

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52	52	52	52
1	99	94	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50	45	45	45	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38	38	38	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33	33	33	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32	29	29	29	29
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25	25	25	25
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22	22	22	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20	20	20	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18	18	18	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	16	16	16	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2929	2929	2929
5°	2933	2883	2901
10°	2904	2827	2808
15°	2864	2734	2663
20°	2811	2606	2484
25°	2757	2462	2312
30°	2684	2314	2093
35°	2613	2156	1901
40°	2540	1991	1680
45°	2456	1809	1480
50°	2369	1625	1285
55°	2278	1428	1097
60°	2173	1222	904
65°	2051	1013	814
70°	1904	817	738
75°	1720	722	674
80°	1452	608	587
85°	1011	409	447

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2456 cd/sqm



TEST NUMBER: P909550

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	2.4
10°-20°	1073.8	6.5
20°-30°	1507.6	9.1
30°-40°	1643.4	9.9
40°-50°	1510.5	9.1
50°-60°	1186.3	7.1
60°-70°	772.1	4.6
70°-80°	397.5	2.4
80°-90°	109.6	0.7
90°-100°	177.9	1.1
100°-110°	565.2	3.4
110°-120°	967.2	5.8
120°-130°	1272.0	7.6
130°-140°	1427.7	8.6
140°-150°	1400.0	8.4
150°-160°	1174.4	7.1
160°-170°	778.9	4.7
170°-180°	272.2	1.6
0°-30°	2972.6	17.9
0°-40°	4616.1	27.8
0°-60°	7312.8	44.0
0°-90°	8592.0	51.7
90°-120°	1710.2	10.3
90°-150°	5809.9	34.9
90°-180°	8035.0	48.3
0°-180°	16627.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4106	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3604	3482	3233	3078	3022	1657
35°	3105	2912	2580	2342	2259	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1636	1228	1001	929	1725
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	3	31	85	80	82	16
95°	126	151	155	155	151	141
105°	522	529	534	538	538	551
115°	971	984	980	978	971	960
125°	1412	1433	1426	1419	1416	1261
135°	1826	1853	1858	1855	1848	1411
145°	2217	2234	2248	2250	2241	1385
155°	2535	2542	2550	2562	2554	1167
165°	2757	2755	2755	2772	2760	778
175°	2869	2862	2857	2874	2860	273
180°	2874	2874	2874	2874	2874	



TEST NUMBER: P909550

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.8	4173.8	4173.8	4173.8	4173.8
2.5°	4192.6	4173.8	4132.1	4170.1	4162.6
5°	4173.8	4154.9	4105.6	4139.7	4128.4
7.5°	4139.7	4117.2	4064.3	4079.1	4060.4
10°	4094.4	4067.9	3992.6	3981.0	3958.6
12.5°	4037.9	4003.8	3901.6	3879.2	3837.5
15°	3969.8	3928.1	3799.8	3728.1	3690.5
17.5°	3890.4	3829.9	3671.3	3588.3	3527.8
20°	3799.8	3724.1	3535.3	3441.2	3357.8
22.5°	3701.7	3614.7	3395.5	3267.3	3210.8
25°	3603.5	3482.5	3233.2	3078.5	3021.6
27.5°	3486.5	3357.8	3082.1	2904.6	2817.6
30°	3361.8	3217.9	2915.8	2723.5	2621.3
32.5°	3240.9	3066.9	2757.5	2530.7	2436.1
35°	3104.9	2912.3	2580.0	2342.0	2258.6
37.5°	2972.7	2764.7	2413.7	2152.8	2058.6
40°	2832.9	2606.5	2239.8	1971.7	1873.5
42.5°	2689.4	2447.7	2066.3	1786.6	1692.3
45°	2538.3	2285.0	1888.8	1620.2	1529.6
47.5°	2394.9	2126.8	1718.8	1450.3	1367.4
50°	2236.1	1968.0	1552.5	1291.6	1212.6
52.5°	2081.0	1797.8	1393.8	1144.5	1072.8
55°	1930.0	1635.5	1227.5	1001.1	929.3
57.5°	1775.3	1473.1	1080.5	868.8	808.3
60°	1616.6	1314.4	925.3	733.0	672.5
62.5°	1461.9	1159.7	793.0	612.0	581.9
65°	1303.2	997.0	657.2	529.0	517.4
67.5°	1152.2	846.0	529.0	464.4	453.2
70°	993.4	698.9	438.0	400.3	385.2
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.9	430.4	302.2	275.7	272.1
77.5°	547.9	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	2.6	31.2	84.9	79.7	82.3
92.5°	53.7	72.8	75.4	78.0	78.0
95°	126.5	150.8	155.1	155.1	150.8
97.5°	210.6	233.1	242.7	242.7	242.7
100°	307.6	327.6	334.5	334.5	331.9
102.5°	409.9	424.6	434.1	436.8	434.1
105°	521.7	528.6	533.8	538.2	538.2
107.5°	632.6	643.0	643.0	644.7	632.6
110°	740.0	754.0	754.0	754.0	747.0



TEST NUMBER: P909550

CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	856.2	870.9	868.3	861.4	856.2
115°	970.6	984.4	980.1	977.5	970.6
117.5°	1084.1	1103.2	1091.1	1084.1	1077.1
120°	1198.5	1217.5	1198.5	1198.5	1190.6
122.5°	1302.4	1326.8	1314.6	1307.7	1302.4
125°	1411.7	1433.3	1426.4	1418.6	1416.0
127.5°	1518.2	1545.1	1535.6	1525.2	1518.2
130°	1617.9	1649.1	1644.8	1639.5	1630.0
132.5°	1729.7	1753.9	1755.7	1743.5	1736.7
135°	1825.8	1852.7	1858.0	1855.3	1848.5
137.5°	1933.3	1955.0	1959.3	1957.6	1947.2
140°	2027.8	2049.4	2061.5	2061.5	2052.0
142.5°	2124.9	2146.5	2153.4	2156.1	2146.5
145°	2216.8	2234.0	2247.9	2250.5	2241.0
147.5°	2299.1	2320.7	2331.1	2335.4	2325.9
150°	2384.0	2398.7	2408.2	2416.0	2408.2
152.5°	2459.3	2474.1	2486.2	2495.8	2486.2
155°	2534.8	2541.6	2549.5	2561.6	2553.8
157.5°	2599.7	2604.9	2609.3	2626.6	2614.4
160°	2657.8	2663.0	2665.6	2680.3	2669.9
162.5°	2711.5	2711.5	2714.1	2730.6	2718.5
165°	2757.4	2754.8	2754.8	2772.2	2760.1
167.5°	2799.0	2791.3	2791.3	2808.5	2796.4
170°	2830.2	2823.3	2820.8	2838.0	2823.3
172.5°	2851.9	2845.0	2842.4	2859.7	2845.0
175°	2869.2	2862.3	2857.1	2874.5	2859.7
177.5°	2878.7	2871.9	2866.6	2881.3	2866.6
180°	2874.5	2874.5	2874.5	2874.5	2874.5



TEST NUMBER: P909550
 CATALOG NUMBER: DFN2DIP-SQ4F0-100D090US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.05	11.89	12.00	12.85	14.10	7.01	7.85	7.96	8.81	10.06
	3H	12.73	13.48	13.69	14.45	15.73	8.20	8.95	9.16	9.92	11.20
	4H	13.34	14.06	14.32	15.03	16.31	8.65	9.36	9.62	10.34	11.62
	6H	13.77	14.42	14.75	15.40	16.70	8.97	9.63	9.96	10.61	11.90
	8H	13.90	14.52	14.89	15.52	16.81	9.06	9.69	10.05	10.68	11.97
	12H	13.96	14.55	14.96	15.54	16.86	9.11	9.70	10.10	10.69	12.01
4H	2H	11.07	11.78	12.05	12.75	14.04	7.61	8.32	8.59	9.29	10.58
	3H	12.90	13.49	13.89	14.50	15.79	8.96	9.55	9.95	10.56	11.85
	4H	13.60	14.14	14.60	15.14	16.46	9.51	10.05	10.51	11.05	12.37
	6H	14.12	14.58	15.13	15.60	16.92	9.93	10.39	10.94	11.41	12.73
	8H	14.30	14.73	15.31	15.74	17.08	10.06	10.49	11.07	11.51	12.84
	12H	14.39	14.79	15.42	15.82	17.15	10.13	10.52	11.15	11.55	12.88
8H	4H	13.57	14.00	14.58	15.01	16.35	9.79	10.23	10.80	11.24	12.57
	6H	14.14	14.50	15.17	15.55	16.88	10.31	10.67	11.35	11.73	13.06
	8H	14.36	14.67	15.40	15.72	17.06	10.50	10.82	11.55	11.86	13.21
	12H	14.50	14.78	15.55	15.81	17.21	10.62	10.90	11.67	11.94	13.33
12H	4H	13.52	13.91	14.55	14.94	16.28	9.80	10.19	10.83	11.22	12.56
	6H	14.11	14.43	15.16	15.47	16.82	10.36	10.68	11.41	11.72	13.07
	8H	14.34	14.62	15.38	15.65	17.04	10.58	10.85	11.62	11.89	13.28