

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909590

Luminaire Tested: DFN2DIP-SQ4F0-110D100US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P909590  
REPORT IS A COMBINATION OF REPORTS P900142 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-110D100US840-RLLFLL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18379.6 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 179.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P909590  
CATALOG NUMBER: DFN2DIP-SQ4F0-110D100US840-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P909590

CATALOG NUMBER: DFN2DIP-SQ4F0-110D100US840-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	63	61	59	52	50	49	52	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42	46	44	42	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	37	34	32	28
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	28	25	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	28	25	23	20
8	55	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3222	3222	3222
5°	3227	3171	3192
10°	3195	3109	3089
15°	3151	3007	2929
20°	3092	2866	2733
25°	3033	2708	2543
30°	2953	2546	2302
35°	2874	2371	2091
40°	2794	2190	1848
45°	2702	1990	1628
50°	2606	1787	1413
55°	2506	1571	1207
60°	2390	1344	994
65°	2257	1114	896
70°	2095	899	812
75°	1892	794	741
80°	1598	668	646
85°	1112	450	492

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2702 cd/sqm



TEST NUMBER: P909590

CATALOG NUMBER: DFN2DIP-SQ4F0-110D100US840-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	430.3	2.3
10°-20°	1181.2	6.4
20°-30°	1658.4	9.0
30°-40°	1807.8	9.8
40°-50°	1661.5	9.0
50°-60°	1304.9	7.1
60°-70°	849.4	4.6
70°-80°	437.2	2.4
80°-90°	120.7	0.7
90°-100°	197.6	1.1
100°-110°	627.9	3.4
110°-120°	1074.6	5.8
120°-130°	1413.3	7.7
130°-140°	1586.4	8.6
140°-150°	1555.6	8.5
150°-160°	1304.9	7.1
160°-170°	865.4	4.7
170°-180°	302.5	1.6
0°-30°	3269.9	17.8
0°-40°	5077.7	27.6
0°-60°	8044.1	43.8
0°-90°	9451.3	51.4
90°-120°	1900.2	10.3
90°-150°	6455.4	35.1
90°-180°	8928.0	48.6
0°-180°	18379.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4591	4591	4591	4591	4591	
5°	4591	4570	4516	4554	4541	435
15°	4367	4321	4180	4101	4060	1231
25°	3964	3831	3556	3386	3324	1823
35°	3416	3203	2838	2576	2484	2138
45°	2792	2514	2078	1782	1683	2156
55°	2123	1799	1350	1101	1022	1897
65°	1434	1097	723	582	569	1421
75°	764	473	332	303	299	808
85°	178	91	79	79	79	205
90°	3	35	94	89	92	18
95°	141	168	172	172	168	156
105°	580	587	593	598	598	612
115°	1078	1094	1089	1086	1078	1067
125°	1568	1593	1585	1576	1573	1402
135°	2029	2059	2064	2062	2054	1568
145°	2463	2482	2498	2500	2490	1539
155°	2816	2824	2833	2846	2838	1296
165°	3064	3061	3061	3080	3067	864
175°	3188	3180	3175	3194	3177	303
180°	3194	3194	3194	3194	3194	



TEST NUMBER: P909590

CATALOG NUMBER: DFN2DIP-SQ4F0-110D100US840-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4591.2	4591.2	4591.2	4591.2	4591.2
2.5°	4611.9	4591.2	4545.3	4587.2	4578.8
5°	4591.2	4570.4	4516.2	4553.7	4541.4
7.5°	4553.7	4528.9	4470.8	4487.1	4466.3
10°	4503.9	4474.7	4391.9	4379.1	4354.4
12.5°	4441.7	4404.2	4291.8	4267.1	4221.2
15°	4366.8	4320.9	4179.8	4101.0	4059.5
17.5°	4279.5	4213.0	4038.4	3947.1	3880.5
20°	4179.8	4096.5	3888.9	3785.3	3693.6
22.5°	4071.9	3976.1	3735.1	3594.0	3531.8
25°	3963.8	3830.7	3556.5	3386.4	3323.8
27.5°	3835.2	3693.6	3390.3	3195.0	3099.4
30°	3698.0	3539.8	3207.4	2995.8	2883.4
32.5°	3564.9	3373.6	3033.2	2783.8	2679.8
35°	3415.5	3203.4	2838.0	2576.2	2484.5
37.5°	3270.0	3041.2	2655.0	2368.0	2264.5
40°	3116.1	2867.1	2463.8	2168.8	2060.8
42.5°	2958.3	2692.5	2272.9	1965.2	1861.6
45°	2792.2	2513.6	2077.6	1782.2	1682.6
47.5°	2634.3	2339.5	1890.7	1595.3	1504.1
50°	2459.7	2164.8	1707.8	1420.8	1333.9
52.5°	2289.2	1977.5	1533.2	1259.0	1180.0
55°	2122.9	1799.0	1350.2	1101.2	1022.3
57.5°	1952.9	1620.4	1188.4	955.7	889.1
60°	1778.3	1445.9	1017.8	806.3	739.7
62.5°	1608.1	1275.8	872.4	673.2	640.1
65°	1433.5	1096.7	723.0	581.9	569.1
67.5°	1267.4	930.6	581.9	510.9	498.6
70°	1092.8	768.8	481.8	440.4	423.6
72.5°	926.6	618.9	402.9	369.8	361.4
75°	764.4	473.4	332.3	303.3	299.3
77.5°	602.6	336.4	261.9	245.1	236.7
80°	452.7	241.2	199.2	183.0	183.0
82.5°	315.6	162.2	137.1	128.8	128.8
85°	178.5	91.3	78.9	78.9	78.9
87.5°	66.6	33.0	33.0	29.1	29.1
90°	2.9	34.6	94.3	88.6	91.5
92.5°	59.7	80.9	83.8	86.6	86.6
95°	140.6	167.5	172.4	172.4	167.5
97.5°	234.0	259.0	269.6	269.6	269.6
100°	341.8	364.0	371.6	371.6	368.8
102.5°	455.4	471.8	482.4	485.2	482.4
105°	579.7	587.3	593.1	597.9	597.9
107.5°	702.9	714.5	714.5	716.4	702.9
110°	822.3	837.7	837.7	837.7	830.0



TEST NUMBER: P909590

CATALOG NUMBER: DFN2DIP-SQ4F0-110D100US840-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	951.3	967.7	964.8	957.0	951.3
115°	1078.4	1093.8	1089.0	1086.1	1078.4
117.5°	1204.6	1225.8	1212.2	1204.6	1196.8
120°	1331.6	1352.8	1331.6	1331.6	1323.0
122.5°	1447.1	1474.1	1460.7	1453.0	1447.1
125°	1568.5	1592.6	1584.9	1576.2	1573.4
127.5°	1687.0	1716.8	1706.2	1694.7	1687.0
130°	1797.7	1832.3	1827.6	1821.7	1811.2
132.5°	1921.9	1948.8	1950.8	1937.3	1929.6
135°	2028.7	2058.6	2064.4	2061.5	2053.8
137.5°	2148.2	2172.2	2177.1	2175.1	2163.5
140°	2253.1	2277.1	2290.7	2290.7	2280.1
142.5°	2361.0	2385.0	2392.7	2395.6	2385.0
145°	2463.0	2482.2	2497.7	2500.5	2489.9
147.5°	2554.5	2578.6	2590.1	2595.0	2584.3
150°	2648.9	2665.2	2675.8	2684.4	2675.8
152.5°	2732.6	2749.0	2762.5	2773.1	2762.5
155°	2816.4	2824.1	2832.8	2846.2	2837.5
157.5°	2888.6	2894.4	2899.2	2918.4	2905.0
160°	2953.1	2958.9	2961.7	2978.1	2966.6
162.5°	3012.8	3012.8	3015.7	3033.9	3020.5
165°	3063.8	3060.9	3060.9	3080.2	3066.8
167.5°	3110.1	3101.4	3101.4	3120.7	3107.2
170°	3144.7	3137.0	3134.1	3153.4	3137.0
172.5°	3168.8	3161.1	3158.2	3177.4	3161.1
175°	3188.0	3180.4	3174.6	3193.8	3177.4
177.5°	3198.6	3191.0	3185.1	3201.5	3185.1
180°	3193.8	3193.8	3193.8	3193.8	3193.8



TEST NUMBER: P909590  
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D100US840-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.35	12.20	12.31	13.16	14.41	7.32	8.16	8.27	9.12	10.37
	3H	13.04	13.79	14.00	14.76	16.04	8.51	9.26	9.47	10.23	11.51
	4H	13.65	14.36	14.63	15.34	16.62	8.96	9.67	9.93	10.64	11.93
	6H	14.08	14.73	15.06	15.71	17.01	9.28	9.93	10.27	10.92	12.21
	8H	14.20	14.83	15.20	15.83	17.12	9.37	9.99	10.36	10.99	12.29
	12H	14.27	14.86	15.27	15.85	17.17	9.42	10.01	10.41	11.00	12.32
4H	2H	11.37	12.09	12.36	13.06	14.35	7.91	8.63	8.90	9.60	10.89
	3H	13.21	13.80	14.20	14.81	16.11	9.27	9.86	10.26	10.86	12.16
	4H	13.91	14.45	14.91	15.44	16.77	9.82	10.36	10.82	11.36	12.68
	6H	14.43	14.89	15.44	15.91	17.23	10.24	10.70	11.25	11.72	13.04
	8H	14.60	15.04	15.62	16.05	17.39	10.37	10.80	11.38	11.82	13.15
	12H	14.70	15.09	15.73	16.12	17.46	10.43	10.82	11.46	11.85	13.19
8H	4H	13.87	14.31	14.89	15.32	16.66	10.10	10.53	11.11	11.55	12.88
	6H	14.45	14.80	15.48	15.86	17.19	10.62	10.98	11.66	12.03	13.37
	8H	14.67	14.98	15.71	16.02	17.37	10.81	11.13	11.86	12.17	13.52
	12H	14.81	15.08	15.86	16.12	17.52	10.93	11.21	11.98	12.25	13.64
12H	4H	13.83	14.22	14.86	15.25	16.59	10.11	10.50	11.14	11.53	12.87
	6H	14.42	14.74	15.47	15.78	17.13	10.67	10.99	11.72	12.03	13.38
	8H	14.65	14.92	15.69	15.96	17.35	10.88	11.16	11.93	12.20	13.59