

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915162

Luminaire Tested: DFN2DIP-SQ4F0-160D120US927-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P915162  
REPORT IS A COMBINATION OF REPORTS P900184 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-160D120US927-RLLFLL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19186.6 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 256.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P915162  
CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US927-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P915162

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US927-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53	48	48	48	48
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41	41	41	41
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30	27	27	27	27
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27	24	24	24	24
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3676	3676	3676
5°	3682	3618	3642
10°	3645	3548	3524
15°	3595	3431	3342
20°	3528	3270	3118
25°	3460	3090	2902
30°	3369	2905	2627
35°	3280	2705	2386
40°	3188	2499	2109
45°	3083	2270	1858
50°	2973	2039	1612
55°	2859	1792	1377
60°	2727	1534	1134
65°	2575	1271	1022
70°	2390	1026	927
75°	2159	906	845
80°	1823	763	737
85°	1269	513	562

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3083 cd/sqm



TEST NUMBER: P915162

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US927-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	491.0	2.6
10°-20°	1347.8	7.0
20°-30°	1892.2	9.9
30°-40°	2062.7	10.8
40°-50°	1895.8	9.9
50°-60°	1488.9	7.8
60°-70°	969.1	5.1
70°-80°	498.8	2.6
80°-90°	135.9	0.7
90°-100°	186.0	1.0
100°-110°	591.1	3.1
110°-120°	1011.6	5.3
120°-130°	1330.4	6.9
130°-140°	1493.3	7.8
140°-150°	1464.3	7.6
150°-160°	1228.4	6.4
160°-170°	814.6	4.2
170°-180°	284.7	1.5
0°-30°	3731.0	19.4
0°-40°	5793.7	30.2
0°-60°	9178.3	47.8
0°-90°	10782.2	56.2
90°-120°	1788.7	9.3
90°-150°	6076.6	31.7
90°-180°	8404.0	43.8
0°-180°	19186.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5238	5238	5238	5238	5238	
5°	5238	5215	5153	5196	5182	497
15°	4982	4930	4769	4679	4632	1404
25°	4523	4371	4058	3864	3792	2080
35°	3897	3655	3238	2939	2835	2439
45°	3186	2868	2370	2034	1920	2460
55°	2422	2053	1541	1256	1166	2165
65°	1636	1251	825	664	649	1622
75°	872	540	379	346	342	922
85°	204	104	90	90	90	234
90°	3	33	89	83	86	19
95°	132	158	162	162	158	147
105°	546	553	558	563	563	576
115°	1015	1030	1025	1022	1015	1004
125°	1476	1499	1492	1484	1481	1319
135°	1910	1938	1943	1940	1933	1476
145°	2318	2337	2351	2354	2344	1449
155°	2651	2658	2667	2679	2671	1220
165°	2884	2881	2881	2900	2887	814
175°	3001	2994	2988	3006	2991	285
180°	3006	3006	3006	3006	3006	



TEST NUMBER: P915162

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US927-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5238.5	5238.5	5238.5	5238.5	5238.5
2.5°	5262.1	5238.5	5186.2	5234.0	5224.4
5°	5238.5	5214.8	5153.0	5195.8	5181.7
7.5°	5195.8	5167.6	5101.2	5119.8	5096.2
10°	5139.0	5105.8	5011.2	4996.6	4968.4
12.5°	5068.0	5025.3	4897.0	4868.8	4816.5
15°	4982.5	4930.2	4769.2	4679.2	4631.9
17.5°	4882.9	4807.0	4607.8	4503.6	4427.7
20°	4769.2	4674.2	4437.2	4319.1	4214.5
22.5°	4646.0	4536.8	4261.7	4100.8	4029.8
25°	4522.8	4370.9	4058.0	3863.9	3792.5
27.5°	4375.9	4214.5	3868.4	3645.6	3536.5
30°	4219.5	4038.9	3659.6	3418.3	3290.0
32.5°	4067.6	3849.3	3461.0	3176.3	3057.6
35°	3897.1	3655.1	3238.2	2939.4	2834.8
37.5°	3731.1	3470.1	3029.5	2702.0	2583.8
40°	3555.5	3271.4	2811.1	2474.6	2351.4
42.5°	3375.5	3072.2	2593.4	2242.3	2124.1
45°	3185.8	2868.0	2370.5	2033.5	1919.9
47.5°	3005.8	2669.3	2157.3	1820.3	1716.2
50°	2806.6	2470.1	1948.5	1621.1	1522.0
52.5°	2612.0	2256.4	1749.4	1436.5	1346.5
55°	2422.3	2052.6	1540.6	1256.4	1166.4
57.5°	2228.2	1849.0	1356.1	1090.4	1014.5
60°	2029.0	1649.8	1161.3	920.0	844.0
62.5°	1834.8	1455.6	995.4	768.0	730.3
65°	1635.7	1251.4	824.9	663.9	649.4
67.5°	1446.0	1061.8	663.9	583.0	568.9
70°	1246.9	877.2	549.8	502.5	483.4
72.5°	1057.2	706.2	459.7	422.0	412.4
75°	872.2	540.2	379.2	346.0	341.5
77.5°	687.5	383.7	298.7	279.6	270.1
80°	516.6	275.1	227.4	208.7	208.7
82.5°	360.1	185.1	156.5	146.9	146.9
85°	203.7	104.1	90.1	90.1	90.1
87.5°	76.0	37.7	37.7	33.2	33.2
90°	2.7	32.6	88.8	83.4	86.1
92.5°	56.2	76.1	78.8	81.6	81.6
95°	132.3	157.7	162.2	162.2	157.7
97.5°	220.2	243.8	253.8	253.8	253.8
100°	321.8	342.6	349.8	349.8	347.1
102.5°	428.7	444.1	454.1	456.9	454.1
105°	545.7	552.9	558.3	562.8	562.8
107.5°	661.6	672.6	672.6	674.3	661.6
110°	774.0	788.5	788.5	788.5	781.3



TEST NUMBER: P915162

CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US927-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	895.5	910.9	908.2	900.9	895.5
115°	1015.1	1029.7	1025.1	1022.4	1015.1
117.5°	1133.8	1153.8	1141.1	1133.8	1126.6
120°	1253.5	1273.4	1253.5	1253.5	1245.4
122.5°	1362.3	1387.7	1375.0	1367.7	1362.3
125°	1476.5	1499.1	1491.9	1483.8	1481.0
127.5°	1588.0	1616.0	1606.1	1595.2	1588.0
130°	1692.2	1724.8	1720.3	1714.8	1704.9
132.5°	1809.1	1834.5	1836.3	1823.6	1816.4
135°	1909.7	1937.8	1943.3	1940.5	1933.3
137.5°	2022.1	2044.8	2049.3	2047.5	2036.6
140°	2120.9	2143.6	2156.2	2156.2	2146.3
142.5°	2222.5	2245.1	2252.3	2255.0	2245.1
145°	2318.5	2336.6	2351.1	2353.9	2343.9
147.5°	2404.6	2427.2	2438.2	2442.7	2432.7
150°	2493.5	2508.8	2518.8	2527.0	2518.8
152.5°	2572.3	2587.7	2600.4	2610.4	2600.4
155°	2651.1	2658.4	2666.6	2679.2	2671.1
157.5°	2719.2	2724.5	2729.1	2747.2	2734.5
160°	2779.8	2785.3	2788.0	2803.4	2792.5
162.5°	2836.0	2836.0	2838.8	2856.0	2843.3
165°	2884.1	2881.4	2881.4	2899.5	2886.8
167.5°	2927.6	2919.4	2919.4	2937.6	2924.9
170°	2960.2	2952.9	2950.2	2968.4	2952.9
172.5°	2982.9	2975.6	2972.9	2991.0	2975.6
175°	3001.0	2993.7	2988.3	3006.4	2991.0
177.5°	3011.0	3003.7	2998.2	3013.7	2998.2
180°	3006.4	3006.4	3006.4	3006.4	3006.4



TEST NUMBER: P915162  
 CATALOG NUMBER: DFN2DIP-SQ4F0-160D120US927-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.24	13.12	13.15	14.05	15.23	8.20	9.09	9.11	10.01	11.19
	3H	13.93	14.72	14.85	15.65	16.86	9.40	10.19	10.32	11.12	12.33
	4H	14.54	15.29	15.48	16.23	17.44	9.85	10.59	10.78	11.53	12.75
	6H	14.97	15.66	15.92	16.60	17.83	10.17	10.86	11.12	11.80	13.03
	8H	15.10	15.75	16.05	16.71	17.94	10.27	10.92	11.22	11.88	13.11
	12H	15.16	15.79	16.12	16.74	17.99	10.31	10.93	11.27	11.89	13.14
4H	2H	12.27	13.01	13.21	13.95	15.17	8.81	9.55	9.75	10.49	11.71
	3H	14.10	14.72	15.06	15.69	16.92	10.16	10.78	11.11	11.75	12.98
	4H	14.80	15.37	15.76	16.33	17.59	10.71	11.28	11.67	12.24	13.50
	6H	15.32	15.81	16.30	16.80	18.05	11.14	11.62	12.11	12.61	13.86
	8H	15.50	15.96	16.48	16.94	18.21	11.27	11.72	12.24	12.70	13.97
	12H	15.60	16.01	16.60	17.01	18.28	11.33	11.74	12.33	12.74	14.01
8H	4H	14.77	15.23	15.75	16.21	17.48	11.00	11.45	11.97	12.43	13.70
	6H	15.35	15.72	16.35	16.74	18.01	11.52	11.90	12.52	12.92	14.18
	8H	15.57	15.90	16.58	16.91	18.19	11.71	12.04	12.72	13.05	14.34
	12H	15.71	16.00	16.72	17.00	18.34	11.84	12.13	12.85	13.13	14.46
12H	4H	14.73	15.14	15.72	16.13	17.41	11.01	11.42	12.00	12.41	13.69
	6H	15.32	15.65	16.33	16.66	17.95	11.57	11.90	12.58	12.91	14.20
	8H	15.55	15.84	16.56	16.84	18.17	11.79	12.08	12.80	13.08	14.41