

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915169

Luminaire Tested: DFN2DIP-SQ4F0-160D160US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915169
REPORT IS A COMBINATION OF REPORTS P901739 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D160US927-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25096.3 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 288.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915169

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915169

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3461	3461	3461
5°	3466	3413	3436
10°	3438	3368	3391
15°	3387	3313	3319
20°	3319	3237	3246
25°	3251	3145	3160
30°	3166	3060	3052
35°	3085	2960	2937
40°	2986	2858	2828
45°	2887	2757	2717
50°	2778	2650	2587
55°	2665	2527	2469
60°	2536	2380	2333
65°	2397	2229	2172
70°	2218	2044	2000
75°	1972	1824	1843
80°	1674	1542	1540
85°	1210	1055	1035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2887 cd/sqm

TEST NUMBER: P915169

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.2	1.8
10°-20°	1306.0	5.2
20°-30°	1919.4	7.6
30°-40°	2229.2	8.9
40°-50°	2226.5	8.9
50°-60°	1941.4	7.7
60°-70°	1435.1	5.7
70°-80°	812.0	3.2
80°-90°	221.8	0.9
90°-100°	141.0	0.6
100°-110°	525.8	2.1
110°-120°	1394.6	5.6
120°-130°	2313.0	9.2
130°-140°	2456.9	9.8
140°-150°	2283.4	9.1
150°-160°	1835.8	7.3
160°-170°	1182.9	4.7
170°-180°	407.2	1.6
0°-30°	3689.6	14.7
0°-40°	5918.9	23.6
0°-60°	10086.7	40.2
0°-90°	12555.7	50.0
90°-120°	2061.4	8.2
90°-150°	9114.7	36.3
90°-180°	12541.0	50.0
0°-180°	25096.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4932	4932	4932	4932	4932	
5°	4932	4913	4861	4899	4890	468
15°	4695	4667	4605	4624	4600	1322
25°	4249	4211	4131	4140	4131	1955
35°	3666	3619	3543	3514	3490	2289
45°	2983	2950	2878	2827	2808	2302
55°	2258	2229	2172	2115	2092	2018
65°	1522	1494	1446	1404	1380	1505
75°	796	787	763	735	745	850
85°	194	190	185	171	166	217
90°	3	37	62	78	83	23
95°	201	99	121	136	133	238
105°	941	1034	189	223	235	1005
115°	1780	1832	1910	477	254	1752
125°	2516	2557	2616	2637	2646	2244
135°	3114	3164	3191	3222	3216	2405
145°	3612	3609	3662	3683	3668	2259
155°	3977	3950	3987	4005	3981	1833
165°	4191	4172	4182	4203	4182	1184
175°	4287	4265	4271	4293	4262	408
180°	4278	4278	4278	4278	4278	

TEST NUMBER: P915169

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4931.9	4931.9	4931.9	4931.9	4931.9
2.5°	4960.6	4936.9	4884.6	4931.9	4922.8
5°	4931.9	4913.3	4860.9	4898.7	4889.6
7.5°	4898.7	4870.5	4818.1	4856.4	4846.8
10°	4846.8	4813.6	4756.8	4794.5	4780.4
12.5°	4775.4	4747.2	4690.3	4714.0	4704.4
15°	4694.9	4666.7	4604.8	4624.0	4600.3
17.5°	4595.3	4567.1	4505.2	4528.8	4505.2
20°	4486.0	4457.9	4391.5	4405.6	4386.9
22.5°	4377.4	4334.7	4272.7	4272.7	4263.2
25°	4249.1	4211.4	4130.8	4139.9	4130.8
27.5°	4106.7	4073.5	4012.1	3998.1	3974.4
30°	3964.8	3926.6	3855.6	3841.5	3822.4
32.5°	3812.8	3784.7	3708.7	3680.0	3660.9
35°	3666.0	3618.7	3542.6	3514.0	3490.4
37.5°	3499.9	3457.2	3381.2	3347.9	3324.3
40°	3329.3	3291.1	3215.1	3172.8	3153.8
42.5°	3163.3	3125.1	3049.6	3001.8	2973.6
45°	2983.2	2949.9	2878.5	2826.7	2807.6
47.5°	2807.6	2774.4	2698.4	2646.0	2617.9
50°	2622.4	2598.8	2532.4	2465.9	2442.3
52.5°	2442.3	2409.1	2347.7	2295.3	2262.2
55°	2257.6	2229.0	2172.1	2115.2	2091.6
57.5°	2072.5	2048.8	1986.9	1930.1	1911.0
60°	1887.3	1868.7	1802.3	1749.9	1735.8
62.5°	1707.2	1674.0	1626.7	1579.4	1560.3
65°	1522.5	1493.8	1446.5	1403.8	1380.1
67.5°	1332.8	1308.7	1266.5	1233.2	1214.1
70°	1157.2	1138.1	1095.3	1062.2	1043.5
72.5°	977.1	958.0	934.4	901.1	887.1
75°	796.5	787.4	763.3	735.1	744.7
77.5°	635.5	616.4	606.8	592.7	578.6
80°	474.4	469.4	459.9	445.8	436.3
82.5°	322.5	322.5	318.0	298.9	298.9
85°	194.2	189.6	185.1	170.6	166.0
87.5°	85.6	76.0	66.4	52.4	47.3
90°	2.9	37.2	61.7	77.6	83.4
92.5°	77.6	65.0	74.2	80.5	83.4
95°	201.1	98.9	120.6	136.3	133.1
97.5°	362.0	108.4	157.6	167.2	170.2
100°	548.0	123.9	176.4	201.1	207.3
102.5°	752.0	746.2	182.7	216.5	226.0
105°	941.0	1034.0	188.9	222.8	235.2
107.5°	1160.7	1237.9	195.2	229.0	241.5
110°	1371.3	1436.1	541.8	232.3	244.4

TEST NUMBER: P915169

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1569.5	1625.0	1572.4	238.2	247.7
115°	1779.7	1832.2	1909.8	476.7	254.0
117.5°	1962.4	2024.1	2077.1	1634.2	823.3
120°	2166.8	2213.0	2268.9	2306.0	1888.2
122.5°	2339.9	2389.5	2451.6	2469.9	2473.3
125°	2516.3	2556.7	2615.5	2637.3	2646.4
127.5°	2677.3	2720.7	2767.3	2798.2	2801.2
130°	2829.1	2878.7	2912.5	2946.7	2943.7
132.5°	2983.8	3024.2	3058.1	3086.0	3083.1
135°	3113.9	3163.6	3191.1	3222.4	3216.1
137.5°	3249.9	3287.1	3318.3	3349.2	3340.0
140°	3383.0	3408.0	3441.8	3469.8	3454.3
142.5°	3494.7	3516.4	3556.5	3581.1	3565.7
145°	3612.3	3609.0	3661.6	3683.2	3667.9
147.5°	3714.1	3705.0	3757.6	3773.0	3760.8
150°	3813.4	3791.7	3841.4	3859.7	3844.3
152.5°	3896.8	3872.2	3918.5	3937.3	3915.6
155°	3977.3	3949.7	3986.9	4005.3	3980.6
157.5°	4042.4	4017.8	4045.7	4067.4	4042.4
160°	4098.3	4079.5	4098.3	4116.6	4094.9
162.5°	4147.5	4129.2	4144.5	4166.2	4138.4
165°	4190.9	4172.5	4181.7	4203.4	4181.7
167.5°	4225.1	4206.3	4215.9	4237.5	4209.7
170°	4253.0	4234.3	4240.5	4262.2	4234.3
172.5°	4271.4	4253.0	4259.2	4280.9	4253.0
175°	4286.8	4265.1	4271.4	4293.1	4262.2
177.5°	4293.1	4271.4	4274.7	4296.4	4268.4
180°	4277.6	4277.6	4277.6	4277.6	4277.6

TEST NUMBER: P915169

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.60	12.46	12.56	13.43	14.71	11.16	12.02	12.11	12.99	14.26
	3H	13.27	14.04	14.23	15.02	16.31	12.78	13.55	13.74	14.53	15.82
	4H	13.86	14.59	14.84	15.57	16.87	13.36	14.09	14.34	15.08	16.38
	6H	14.26	14.93	15.25	15.92	17.24	13.76	14.43	14.75	15.42	16.74
	8H	14.37	15.01	15.36	16.01	17.33	13.86	14.51	14.86	15.51	16.82
	12H	14.42	15.03	15.42	16.03	17.36	13.91	14.52	14.91	15.52	16.85
4H	2H	12.06	12.79	13.05	13.78	15.08	11.71	12.44	12.70	13.42	14.73
	3H	13.93	14.54	14.93	15.56	16.87	13.53	14.14	14.52	15.15	16.47
	4H	14.65	15.21	15.66	16.22	17.56	14.23	14.79	15.23	15.79	17.13
	6H	15.17	15.65	16.19	16.68	18.02	14.74	15.22	15.75	16.25	17.59
	8H	15.32	15.77	16.34	16.79	18.15	14.88	15.33	15.90	16.36	17.71
	12H	15.40	15.80	16.43	16.84	18.20	14.95	15.35	15.98	16.39	17.75
8H	4H	14.85	15.30	15.87	16.32	17.67	14.47	14.92	15.49	15.94	17.29
	6H	15.48	15.86	16.53	16.92	18.27	15.10	15.47	16.14	16.54	17.89
	8H	15.71	16.03	16.76	17.09	18.45	15.31	15.64	16.37	16.69	18.06
	12H	15.84	16.13	16.90	17.18	18.59	15.43	15.72	16.48	16.76	18.17
12H	4H	14.83	15.24	15.87	16.28	17.63	14.47	14.87	15.50	15.91	17.27
	6H	15.51	15.84	16.56	16.89	18.26	15.14	15.47	16.19	16.52	17.89
	8H	15.76	16.05	16.81	17.09	18.50	15.38	15.67	16.43	16.71	18.12