

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915170

Luminaire Tested: DFN2DIP-SQ4F0-160D160US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915170
REPORT IS A COMBINATION OF REPORTS P900220 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D160US927-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21991.7 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 288.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915170

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915170

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3676	3676	3676
5°	3682	3618	3642
10°	3645	3548	3524
15°	3595	3431	3342
20°	3528	3270	3118
25°	3460	3090	2902
30°	3369	2905	2627
35°	3280	2705	2386
40°	3188	2499	2109
45°	3083	2270	1858
50°	2973	2039	1612
55°	2859	1792	1377
60°	2727	1534	1134
65°	2575	1271	1022
70°	2390	1026	927
75°	2159	906	845
80°	1823	763	737
85°	1269	513	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3155 cd/sqm

TEST NUMBER: P915170

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	491.0	2.2
10°-20°	1347.8	6.1
20°-30°	1892.2	8.6
30°-40°	2062.7	9.4
40°-50°	1895.8	8.6
50°-60°	1488.9	6.8
60°-70°	969.1	4.4
70°-80°	498.8	2.3
80°-90°	138.8	0.6
90°-100°	248.1	1.1
100°-110°	788.2	3.6
110°-120°	1348.9	6.1
120°-130°	1774.0	8.1
130°-140°	1991.2	9.1
140°-150°	1952.6	8.9
150°-160°	1637.9	7.4
160°-170°	1086.2	4.9
170°-180°	379.7	1.7
0°-30°	3731.0	17.0
0°-40°	5793.7	26.3
0°-60°	9178.3	41.7
0°-90°	10785.1	49.0
90°-120°	2385.1	10.8
90°-150°	8102.8	36.8
90°-180°	11207.0	51.0
0°-180°	21991.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5238	5238	5238	5238	5238	
5°	5238	5215	5153	5196	5182	497
15°	4982	4930	4769	4679	4632	1404
25°	4523	4371	4058	3864	3792	2080
35°	3897	3655	3238	2939	2835	2439
45°	3186	2868	2370	2034	1920	2460
55°	2422	2053	1541	1256	1166	2165
65°	1636	1251	825	664	649	1622
75°	872	540	379	346	342	922
85°	204	104	90	90	90	234
90°	4	44	118	111	115	22
95°	176	210	216	216	210	196
105°	728	737	744	750	750	768
115°	1354	1373	1367	1363	1354	1339
125°	1969	1999	1989	1978	1975	1759
135°	2546	2584	2591	2588	2578	1968
145°	3092	3116	3135	3139	3125	1932
155°	3535	3545	3556	3573	3562	1627
165°	3846	3842	3842	3866	3849	1085
175°	4002	3992	3985	4009	3988	380
180°	4009	4009	4009	4009	4009	

TEST NUMBER: P915170

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5238.5	5238.5	5238.5	5238.5	5238.5
2.5°	5262.1	5238.5	5186.2	5234.0	5224.4
5°	5238.5	5214.8	5153.0	5195.8	5181.7
7.5°	5195.8	5167.6	5101.2	5119.8	5096.2
10°	5139.0	5105.8	5011.2	4996.6	4968.4
12.5°	5068.0	5025.3	4897.0	4868.8	4816.5
15°	4982.5	4930.2	4769.2	4679.2	4631.9
17.5°	4882.9	4807.0	4607.8	4503.6	4427.7
20°	4769.2	4674.2	4437.2	4319.1	4214.5
22.5°	4646.0	4536.8	4261.7	4100.8	4029.8
25°	4522.8	4370.9	4058.0	3863.9	3792.5
27.5°	4375.9	4214.5	3868.4	3645.6	3536.5
30°	4219.5	4038.9	3659.6	3418.3	3290.0
32.5°	4067.6	3849.3	3461.0	3176.3	3057.6
35°	3897.1	3655.1	3238.2	2939.4	2834.8
37.5°	3731.1	3470.1	3029.5	2702.0	2583.8
40°	3555.5	3271.4	2811.1	2474.6	2351.4
42.5°	3375.5	3072.2	2593.4	2242.3	2124.1
45°	3185.8	2868.0	2370.5	2033.5	1919.9
47.5°	3005.8	2669.3	2157.3	1820.3	1716.2
50°	2806.6	2470.1	1948.5	1621.1	1522.0
52.5°	2612.0	2256.4	1749.4	1436.5	1346.5
55°	2422.3	2052.6	1540.6	1256.4	1166.4
57.5°	2228.2	1849.0	1356.1	1090.4	1014.5
60°	2029.0	1649.8	1161.3	920.0	844.0
62.5°	1834.8	1455.6	995.4	768.0	730.3
65°	1635.7	1251.4	824.9	663.9	649.4
67.5°	1446.0	1061.8	663.9	583.0	568.9
70°	1246.9	877.2	549.8	502.5	483.4
72.5°	1057.2	706.2	459.7	422.0	412.4
75°	872.2	540.2	379.2	346.0	341.5
77.5°	687.5	383.7	298.7	279.6	270.1
80°	516.6	275.1	227.4	208.7	208.7
82.5°	360.1	185.1	156.5	146.9	146.9
85°	203.7	104.1	90.1	90.1	90.1
87.5°	76.0	37.7	37.7	33.2	33.2
90°	3.6	43.5	118.4	111.2	114.8
92.5°	74.9	101.6	105.1	108.8	108.8
95°	176.4	210.3	216.3	216.3	210.3
97.5°	293.7	325.1	338.4	338.4	338.4
100°	429.0	456.9	466.5	466.5	462.9
102.5°	571.6	592.2	605.5	609.1	605.5
105°	727.5	737.2	744.5	750.5	750.5
107.5°	882.3	896.7	896.7	899.2	882.3
110°	1032.1	1051.5	1051.5	1051.5	1041.8



TEST NUMBER: P915170

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1194.1	1214.7	1211.0	1201.3	1194.1
115°	1353.6	1372.9	1366.9	1363.3	1353.6
117.5°	1512.0	1538.5	1521.6	1512.0	1502.3
120°	1671.5	1698.0	1671.5	1671.5	1660.6
122.5°	1816.5	1850.4	1833.4	1823.8	1816.5
125°	1968.8	1999.0	1989.3	1978.5	1974.8
127.5°	2117.4	2154.9	2141.6	2127.1	2117.4
130°	2256.4	2299.9	2293.9	2286.6	2273.3
132.5°	2412.4	2446.2	2448.6	2431.7	2422.0
135°	2546.5	2583.9	2591.2	2587.6	2577.9
137.5°	2696.3	2726.5	2732.6	2730.2	2715.7
140°	2828.1	2858.3	2875.2	2875.2	2861.9
142.5°	2963.5	2993.7	3003.3	3007.0	2993.7
145°	3091.6	3115.7	3135.1	3138.7	3125.4
147.5°	3206.4	3236.6	3251.1	3257.1	3243.8
150°	3324.8	3345.4	3358.7	3369.5	3358.7
152.5°	3430.0	3450.5	3467.5	3480.7	3467.5
155°	3535.1	3544.8	3555.6	3572.6	3561.7
157.5°	3625.7	3633.0	3639.0	3663.2	3646.3
160°	3706.7	3714.0	3717.6	3738.1	3723.6
162.5°	3781.6	3781.6	3785.3	3808.3	3791.3
165°	3845.7	3842.1	3842.1	3866.2	3849.4
167.5°	3903.7	3892.9	3892.9	3917.0	3900.1
170°	3947.2	3937.5	3934.0	3958.1	3937.5
172.5°	3977.5	3967.8	3964.2	3988.3	3967.8
175°	4001.6	3992.0	3984.7	4008.9	3988.3
177.5°	4014.9	4005.3	3998.0	4018.6	3998.0
180°	4008.9	4008.9	4008.9	4008.9	4008.9

TEST NUMBER: P915170

CATALOG NUMBER: DFN2DIP-SQ4F0-160D160US927-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.59	12.41	12.56	13.39	14.68	7.55	8.37	8.52	9.35	10.64
	3H	13.27	14.01	14.25	15.00	16.31	8.74	9.47	9.72	10.47	11.78
	4H	13.88	14.58	14.88	15.57	16.89	9.19	9.89	10.19	10.88	12.20
	6H	14.31	14.95	15.31	15.95	17.28	9.51	10.15	10.52	11.15	12.48
	8H	14.44	15.04	15.45	16.06	17.39	9.60	10.21	10.61	11.23	12.55
	12H	14.50	15.08	15.52	16.09	17.44	9.65	10.22	10.66	11.23	12.58
4H	2H	11.61	12.30	12.61	13.30	14.62	8.15	8.84	9.15	9.84	11.16
	3H	13.44	14.02	14.45	15.04	16.37	9.50	10.08	10.51	11.10	12.43
	4H	14.14	14.66	15.15	15.68	17.03	10.05	10.57	11.07	11.59	12.95
	6H	14.65	15.11	15.68	16.15	17.50	10.47	10.92	11.50	11.96	13.31
	8H	14.83	15.26	15.86	16.29	17.65	10.60	11.02	11.63	12.05	13.42
	12H	14.93	15.31	15.98	16.36	17.73	10.66	11.04	11.71	12.09	13.46
8H	4H	14.10	14.53	15.13	15.56	16.92	10.33	10.75	11.36	11.78	13.15
	6H	14.67	15.02	15.73	16.10	17.46	10.85	11.20	11.90	12.27	13.64
	8H	14.89	15.20	15.96	16.26	17.64	11.04	11.35	12.10	12.41	13.79
	12H	15.03	15.31	16.10	16.36	17.78	11.16	11.43	12.22	12.48	13.91
12H	4H	14.06	14.44	15.10	15.48	16.86	10.33	10.72	11.38	11.76	13.13
	6H	14.65	14.96	15.71	16.02	17.40	10.90	11.21	11.96	12.26	13.65
	8H	14.87	15.14	15.94	16.20	17.62	11.11	11.38	12.17	12.43	13.86

END OF REPORT