

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909629

Luminaire Tested: DFN2DIP-SQ4F0-120D110US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909629
REPORT IS A COMBINATION OF REPORTS P901681 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D110US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22994.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 200.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909629

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909629

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	87	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3309	3309	3309
5°	3314	3263	3285
10°	3287	3220	3242
15°	3239	3168	3173
20°	3173	3095	3103
25°	3108	3007	3022
30°	3027	2926	2918
35°	2950	2830	2808
40°	2855	2733	2704
45°	2760	2636	2597
50°	2656	2534	2474
55°	2548	2416	2360
60°	2425	2276	2230
65°	2291	2131	2077
70°	2121	1955	1913
75°	1885	1743	1762
80°	1601	1475	1472
85°	1157	1009	990

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2760 cd/sqm

TEST NUMBER: P909629

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.8	1.9
10°-20°	1248.7	5.4
20°-30°	1835.1	8.0
30°-40°	2131.4	9.3
40°-50°	2128.7	9.3
50°-60°	1856.2	8.1
60°-70°	1372.1	6.0
70°-80°	776.3	3.4
80°-90°	211.5	0.9
90°-100°	123.6	0.5
100°-110°	460.8	2.0
110°-120°	1222.2	5.3
120°-130°	2027.1	8.8
130°-140°	2153.3	9.4
140°-150°	2001.2	8.7
150°-160°	1608.9	7.0
160°-170°	1036.7	4.5
170°-180°	356.8	1.6
0°-30°	3527.6	15.3
0°-40°	5659.0	24.6
0°-60°	9643.8	41.9
0°-90°	12003.8	52.2
90°-120°	1806.7	7.9
90°-150°	7988.3	34.7
90°-180°	10991.0	47.8
0°-180°	22994.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4715	4715	4715	4715	4715	
5°	4715	4698	4648	4684	4675	448
15°	4489	4462	4403	4421	4398	1264
25°	4062	4026	3950	3958	3950	1869
35°	3505	3460	3387	3360	3337	2189
45°	2852	2820	2752	2703	2684	2201
55°	2158	2131	2077	2022	2000	1930
65°	1456	1428	1383	1342	1320	1439
75°	762	753	730	703	712	813
85°	186	181	177	163	159	207
90°	3	32	54	68	73	21
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1536
125°	2205	2241	2292	2311	2319	1967
135°	2729	2773	2797	2824	2819	2108
145°	3166	3163	3209	3228	3215	1980
155°	3486	3462	3494	3510	3489	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3744	3763	3736	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P909629

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US840-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4715.4	4715.4	4715.4	4715.4	4715.4
2.5°	4742.7	4720.1	4670.1	4715.4	4706.7
5°	4715.4	4697.5	4647.5	4683.6	4674.9
7.5°	4683.6	4656.6	4606.6	4643.2	4634.1
10°	4634.1	4602.3	4547.9	4584.0	4570.6
12.5°	4565.7	4538.7	4484.4	4507.0	4497.8
15°	4488.8	4461.8	4402.6	4420.9	4398.3
17.5°	4393.5	4366.6	4307.4	4330.0	4307.4
20°	4289.1	4262.1	4198.7	4212.1	4194.4
22.5°	4185.2	4144.3	4085.1	4085.1	4076.0
25°	4062.5	4026.4	3949.5	3958.2	3949.5
27.5°	3926.4	3894.6	3836.0	3822.4	3799.9
30°	3790.7	3754.2	3686.3	3672.9	3654.6
32.5°	3645.4	3618.6	3545.8	3518.5	3500.2
35°	3504.9	3459.8	3387.1	3359.7	3337.1
37.5°	3346.2	3305.4	3232.7	3201.0	3178.3
40°	3183.2	3146.6	3073.9	3033.5	3015.3
42.5°	3024.4	2987.9	2915.7	2870.0	2843.1
45°	2852.2	2820.5	2752.1	2702.6	2684.3
47.5°	2684.3	2652.5	2579.9	2529.9	2503.0
50°	2507.3	2484.7	2421.2	2357.6	2335.0
52.5°	2335.0	2303.3	2244.6	2194.5	2162.8
55°	2158.5	2131.1	2076.7	2022.4	1999.7
57.5°	1981.5	1958.8	1899.7	1845.3	1827.0
60°	1804.4	1786.7	1723.1	1673.1	1659.6
62.5°	1632.2	1600.4	1555.3	1510.1	1491.8
65°	1455.7	1428.3	1383.0	1342.1	1319.6
67.5°	1274.3	1251.2	1210.8	1179.1	1160.8
70°	1106.4	1088.1	1047.2	1015.5	997.7
72.5°	934.2	915.9	893.3	861.6	848.1
75°	761.5	752.9	729.7	702.9	712.0
77.5°	607.5	589.3	580.2	566.6	553.2
80°	453.6	448.8	439.7	426.3	417.1
82.5°	308.3	308.3	304.1	285.8	285.8
85°	185.7	181.4	177.0	163.1	158.8
87.5°	81.8	72.6	63.5	50.0	45.2
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.2
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.9	160.1	189.8	198.1
105°	824.7	906.2	165.6	195.2	206.2
107.5°	1017.3	1084.9	171.1	200.7	211.7
110°	1201.8	1258.6	474.8	203.6	214.2

TEST NUMBER: P909629

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US840-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.5	1424.1	1378.1	208.7	217.1
115°	1559.7	1605.8	1673.9	417.8	222.6
117.5°	1719.9	1774.0	1820.4	1432.2	721.5
120°	1899.0	1939.5	1988.5	2021.0	1654.8
122.5°	2050.7	2094.2	2148.6	2164.7	2167.7
125°	2205.3	2240.8	2292.3	2311.3	2319.4
127.5°	2346.4	2384.4	2425.3	2452.4	2455.0
130°	2479.4	2522.9	2552.5	2582.5	2580.0
132.5°	2615.0	2650.5	2680.2	2704.6	2702.1
135°	2729.2	2772.6	2796.7	2824.2	2818.6
137.5°	2848.3	2880.8	2908.2	2935.3	2927.2
140°	2965.0	2986.8	3016.5	3040.9	3027.4
142.5°	3062.8	3081.8	3116.9	3138.6	3125.0
145°	3165.9	3163.0	3209.0	3228.1	3214.6
147.5°	3255.2	3247.1	3293.2	3306.7	3296.1
150°	3342.2	3323.2	3366.6	3382.7	3369.2
152.5°	3415.3	3393.7	3434.2	3450.7	3431.7
155°	3485.9	3461.6	3494.1	3510.3	3488.7
157.5°	3542.8	3521.2	3545.7	3564.7	3542.8
160°	3591.8	3575.3	3591.8	3607.8	3588.9
162.5°	3634.9	3618.9	3632.4	3651.4	3626.9
165°	3673.0	3656.8	3664.9	3683.9	3664.9
167.5°	3702.9	3686.5	3694.9	3713.9	3689.4
170°	3727.4	3711.0	3716.4	3735.5	3711.0
172.5°	3743.5	3727.4	3732.9	3751.9	3727.4
175°	3757.0	3738.0	3743.5	3762.6	3735.5
177.5°	3762.6	3743.5	3746.4	3765.4	3740.9
180°	3749.0	3749.0	3749.0	3749.0	3749.0

TEST NUMBER: P909629

CATALOG NUMBER: DFN2DIP-SQ4F0-120D110US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.64	12.52	12.58	13.48	14.72	11.20	12.08	12.14	13.04	14.27
	3H	13.31	14.10	14.26	15.06	16.33	12.82	13.61	13.77	14.57	15.84
	4H	13.90	14.65	14.86	15.62	16.89	13.41	14.15	14.37	15.12	16.39
	6H	14.31	14.99	15.28	15.97	17.25	13.81	14.49	14.78	15.47	16.75
	8H	14.41	15.07	15.39	16.06	17.34	13.91	14.57	14.89	15.56	16.84
	12H	14.46	15.09	15.45	16.07	17.38	13.95	14.58	14.94	15.56	16.87
4H	2H	12.11	12.86	13.08	13.82	15.10	11.75	12.50	12.72	13.47	14.74
	3H	13.98	14.60	14.96	15.60	16.89	13.57	14.20	14.55	15.19	16.48
	4H	14.70	15.27	15.69	16.26	17.57	14.27	14.85	15.26	15.84	17.15
	6H	15.22	15.71	16.22	16.73	18.03	14.79	15.28	15.79	16.29	17.60
	8H	15.37	15.83	16.37	16.84	18.16	14.93	15.39	15.94	16.40	17.72
	12H	15.45	15.86	16.47	16.89	18.21	15.00	15.41	16.02	16.44	17.76
8H	4H	14.90	15.36	15.90	16.36	17.69	14.52	14.98	15.52	15.99	17.31
	6H	15.53	15.91	16.56	16.96	18.28	15.15	15.53	16.18	16.58	17.90
	8H	15.76	16.09	16.79	17.13	18.47	15.37	15.70	16.40	16.74	18.08
	12H	15.89	16.19	16.93	17.22	18.60	15.48	15.78	16.52	16.81	18.19
12H	4H	14.88	15.30	15.90	16.32	17.65	14.52	14.93	15.54	15.95	17.28
	6H	15.56	15.90	16.60	16.94	18.27	15.19	15.53	16.23	16.56	17.90
	8H	15.81	16.11	16.85	17.14	18.52	15.43	15.73	16.47	16.76	18.14