

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917598

Luminaire Tested: DFN2DIP-SQ4F0-060D110US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917598
REPORT IS A COMBINATION OF REPORTS P900150 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D110US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12094.9 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 132.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917598

CATALOG NUMBER: DFN2DIP-SQ4F0-060D110US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917598

CATALOG NUMBER: DFN2DIP-SQ4F0-060D110US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	37	36
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	30	28	27
4	72	62	55	49	65	56	50	45	46	41	38	36	33	30	27	25	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16
8	53	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1419	1419	1419
5°	1421	1396	1405
10°	1407	1369	1360
15°	1387	1324	1290
20°	1362	1262	1203
25°	1336	1192	1120
30°	1300	1121	1014
35°	1266	1044	921
40°	1231	965	814
45°	1190	876	717
50°	1148	787	622
55°	1103	692	531
60°	1052	592	438
65°	994	491	394
70°	923	396	358
75°	833	350	326
80°	703	294	284
85°	490	198	216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2232 cd/sqm

TEST NUMBER: P917598

CATALOG NUMBER: DFN2DIP-SQ4F0-060D110US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	1.6
10°-20°	520.2	4.3
20°-30°	730.3	6.0
30°-40°	796.1	6.6
40°-50°	731.7	6.0
50°-60°	574.6	4.8
60°-70°	374.0	3.1
70°-80°	192.5	1.6
80°-90°	57.2	0.5
90°-100°	175.5	1.5
100°-110°	557.7	4.6
110°-120°	954.3	7.9
120°-130°	1255.1	10.4
130°-140°	1408.8	11.6
140°-150°	1381.5	11.4
150°-160°	1158.9	9.6
160°-170°	768.5	6.4
170°-180°	268.6	2.2
0°-30°	1439.9	11.9
0°-40°	2236.0	18.5
0°-60°	3542.3	29.3
0°-90°	4166.1	34.4
90°-120°	1687.5	14.0
90°-150°	5732.8	47.4
90°-180°	7929.0	65.6
0°-180°	12094.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	2	31	84	79	81	12
95°	125	149	153	153	149	139
105°	515	522	527	531	531	543
115°	958	971	967	965	958	947
125°	1393	1414	1407	1400	1397	1245
135°	1802	1828	1833	1831	1824	1393
145°	2187	2204	2218	2221	2211	1367
155°	2501	2508	2516	2528	2520	1151
165°	2721	2718	2718	2735	2723	768
175°	2831	2824	2819	2836	2822	269
180°	2836	2836	2836	2836	2836	

TEST NUMBER: P917598

CATALOG NUMBER: DFN2DIP-SQ4F0-060D110US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	2.5	30.8	83.8	78.7	81.2
92.5°	53.0	71.8	74.4	77.0	77.0
95°	124.8	148.8	153.0	153.0	148.8
97.5°	207.8	230.0	239.5	239.5	239.5
100°	303.5	323.2	330.0	330.0	327.5
102.5°	404.5	419.0	428.4	431.0	428.4
105°	514.8	521.6	526.8	531.0	531.0
107.5°	624.2	634.5	634.5	636.2	624.2
110°	730.3	744.0	744.0	744.0	737.1

TEST NUMBER: P917598

CATALOG NUMBER: DFN2DIP-SQ4F0-060D110US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	844.8	859.3	856.8	849.9	844.8
115°	957.7	971.3	967.1	964.6	957.7
117.5°	1069.8	1088.5	1076.5	1069.8	1062.9
120°	1182.6	1201.4	1182.6	1182.6	1174.9
122.5°	1285.2	1309.1	1297.1	1290.3	1285.2
125°	1392.9	1414.3	1407.4	1399.8	1397.2
127.5°	1498.1	1524.6	1515.2	1505.0	1498.1
130°	1596.4	1627.3	1622.9	1617.8	1608.4
132.5°	1706.7	1730.7	1732.4	1720.4	1713.6
135°	1801.6	1828.1	1833.3	1830.8	1823.9
137.5°	1907.7	1929.1	1933.3	1931.6	1921.4
140°	2000.9	2022.3	2034.3	2034.3	2024.9
142.5°	2096.7	2118.1	2124.9	2127.4	2118.1
145°	2187.3	2204.4	2218.1	2220.6	2211.3
147.5°	2268.6	2289.9	2300.2	2304.4	2295.1
150°	2352.4	2366.9	2376.3	2384.0	2376.3
152.5°	2426.7	2441.2	2453.2	2462.7	2453.2
155°	2501.2	2507.9	2515.7	2527.7	2519.9
157.5°	2565.3	2570.4	2574.6	2591.8	2579.8
160°	2622.6	2627.7	2630.2	2644.8	2634.6
162.5°	2675.6	2675.6	2678.2	2694.4	2682.4
165°	2720.9	2718.3	2718.3	2735.4	2723.4
167.5°	2761.9	2754.2	2754.2	2771.4	2759.4
170°	2792.7	2785.9	2783.3	2800.4	2785.9
172.5°	2814.1	2807.2	2804.7	2821.8	2807.2
175°	2831.2	2824.4	2819.2	2836.3	2821.8
177.5°	2840.6	2833.7	2828.6	2843.2	2828.6
180°	2836.3	2836.3	2836.3	2836.3	2836.3

TEST NUMBER: P917598

CATALOG NUMBER: DFN2DIP-SQ4F0-060D110US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.72	7.43	7.80	8.51	9.99	2.68	3.40	3.76	4.48	5.96
	3H	8.39	9.03	9.48	10.12	11.62	3.86	4.50	4.95	5.59	7.09
	4H	9.00	9.60	10.10	10.70	12.20	4.30	4.91	5.41	6.00	7.51
	6H	9.42	9.97	10.53	11.07	12.58	4.62	5.18	5.73	6.27	7.79
	8H	9.54	10.07	10.66	11.18	12.69	4.71	5.24	5.82	6.35	7.86
	12H	9.60	10.11	10.72	11.21	12.74	4.75	5.25	5.87	6.36	7.89
4H	2H	6.72	7.33	7.83	8.42	9.92	3.26	3.87	4.37	4.96	6.46
	3H	8.54	9.05	9.66	10.17	11.68	4.60	5.11	5.72	6.23	7.74
	4H	9.24	9.70	10.36	10.81	12.34	5.15	5.61	6.27	6.72	8.25
	6H	9.75	10.15	10.88	11.28	12.81	5.56	5.96	6.69	7.09	8.62
	8H	9.92	10.30	11.05	11.42	12.96	5.69	6.06	6.82	7.18	8.73
	12H	10.02	10.35	11.16	11.49	13.04	5.75	6.08	6.89	7.22	8.77
8H	4H	9.20	9.57	10.32	10.69	12.23	5.42	5.79	6.55	6.91	8.46
	6H	9.76	10.07	10.91	11.23	12.77	5.94	6.24	7.09	7.41	8.95
	8H	9.98	10.25	11.14	11.39	12.95	6.13	6.40	7.28	7.54	9.10
	12H	10.12	10.35	11.28	11.49	13.09	6.24	6.48	7.40	7.62	9.22
12H	4H	9.14	9.48	10.29	10.61	12.16	5.42	5.76	6.57	6.89	8.44
	6H	9.74	10.00	10.89	11.15	12.71	5.99	6.25	7.14	7.40	8.96
	8H	9.96	10.19	11.11	11.33	12.93	6.19	6.43	7.35	7.57	9.17

END OF REPORT