

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909678

Luminaire Tested: DFN2DIP-SQ4F0-140D160US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909678
REPORT IS A COMBINATION OF REPORTS P900218 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D160US840-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26318.1 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 265.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909678

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909678

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4100	4100	4100
5°	4107	4036	4062
10°	4066	3957	3931
15°	4010	3827	3728
20°	3936	3648	3478
25°	3860	3446	3237
30°	3758	3240	2930
35°	3658	3018	2661
40°	3557	2788	2352
45°	3439	2532	2072
50°	3316	2275	1799
55°	3189	1999	1536
60°	3042	1711	1265
65°	2872	1418	1140
70°	2666	1144	1034
75°	2408	1011	943
80°	2034	851	822
85°	1416	572	626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 4021 cd/sqm

TEST NUMBER: P909678

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.6	2.1
10°-20°	1503.4	5.7
20°-30°	2110.7	8.0
30°-40°	2300.8	8.7
40°-50°	2114.7	8.0
50°-60°	1660.7	6.3
60°-70°	1081.0	4.1
70°-80°	556.5	2.1
80°-90°	156.6	0.6
90°-100°	316.2	1.2
100°-110°	1004.8	3.8
110°-120°	1719.5	6.5
120°-130°	2261.4	8.6
130°-140°	2538.3	9.6
140°-150°	2489.1	9.5
150°-160°	2088.0	7.9
160°-170°	1384.7	5.3
170°-180°	484.0	1.8
0°-30°	4161.7	15.8
0°-40°	6462.5	24.6
0°-60°	10237.9	38.9
0°-90°	12031.9	45.7
90°-120°	3040.5	11.6
90°-150°	10329.4	39.2
90°-180°	14286.0	54.3
0°-180°	26318.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5843	5843	5843	5843	5843	
5°	5843	5817	5748	5796	5780	554
15°	5558	5499	5320	5219	5167	1566
25°	5045	4875	4526	4310	4230	2320
35°	4347	4077	3612	3279	3162	2721
45°	3554	3199	2644	2268	2142	2744
55°	2702	2290	1718	1402	1301	2414
65°	1824	1396	920	740	724	1809
75°	973	603	423	386	381	1029
85°	227	116	100	100	100	261
90°	5	55	151	142	146	26
95°	225	268	276	276	268	250
105°	928	940	949	957	957	979
115°	1726	1750	1742	1738	1726	1707
125°	2510	2548	2536	2522	2518	2243
135°	3246	3294	3303	3299	3286	2509
145°	3941	3972	3996	4001	3984	2462
155°	4506	4519	4533	4554	4540	2074
165°	4902	4898	4898	4929	4907	1383
175°	5101	5089	5080	5110	5084	485
180°	5110	5110	5110	5110	5110	

TEST NUMBER: P909678

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5843.3	5843.3	5843.3	5843.3	5843.3
2.5°	5869.6	5843.3	5784.9	5838.2	5827.5
5°	5843.3	5816.9	5747.9	5795.6	5779.9
7.5°	5795.6	5764.1	5690.1	5710.9	5684.5
10°	5732.2	5695.1	5589.7	5573.3	5541.9
12.5°	5653.0	5605.4	5462.3	5430.9	5372.6
15°	5557.7	5499.3	5319.8	5219.4	5166.7
17.5°	5446.6	5361.9	5139.7	5023.6	4938.8
20°	5319.8	5213.7	4949.6	4817.7	4701.0
22.5°	5182.3	5060.6	4753.7	4574.2	4495.1
25°	5044.9	4875.4	4526.5	4309.9	4230.2
27.5°	4881.1	4701.0	4315.0	4066.4	3944.7
30°	4706.6	4505.2	4082.2	3812.8	3669.8
32.5°	4537.1	4293.6	3860.5	3543.0	3410.6
35°	4347.0	4077.1	3612.0	3278.7	3162.0
37.5°	4161.9	3870.6	3379.1	3013.9	2882.1
40°	3966.0	3649.0	3135.6	2760.4	2622.9
42.5°	3765.2	3426.9	2892.8	2501.1	2369.2
45°	3553.6	3199.1	2644.2	2268.3	2141.5
47.5°	3352.8	2977.5	2406.3	2030.4	1914.3
50°	3130.6	2755.3	2173.4	1808.3	1697.7
52.5°	2913.5	2516.8	1951.3	1602.4	1501.9
55°	2702.0	2289.6	1718.5	1401.5	1301.0
57.5°	2485.4	2062.3	1512.6	1216.4	1131.7
60°	2263.2	1840.2	1295.5	1026.1	941.4
62.5°	2046.7	1623.7	1110.3	856.7	814.7
65°	1824.5	1395.8	920.1	740.5	724.3
67.5°	1613.0	1184.4	740.5	650.3	634.5
70°	1390.8	978.5	613.2	560.5	539.2
72.5°	1179.3	787.7	512.8	470.7	460.1
75°	972.8	602.6	423.0	386.0	380.9
77.5°	767.0	428.1	333.3	311.9	301.2
80°	576.2	306.9	253.6	232.9	232.9
82.5°	401.7	206.4	174.5	163.8	163.8
85°	227.2	116.1	100.4	100.4	100.4
87.5°	84.7	42.1	42.1	37.1	37.1
90°	4.6	55.4	151.0	141.8	146.3
92.5°	95.5	129.5	134.0	138.7	138.7
95°	224.9	268.1	275.8	275.8	268.1
97.5°	374.4	414.4	431.4	431.4	431.4
100°	546.9	582.4	594.7	594.7	590.1
102.5°	728.7	755.0	771.8	776.5	771.8
105°	927.5	939.8	949.1	956.7	956.7
107.5°	1124.7	1143.2	1143.2	1146.3	1124.7
110°	1315.8	1340.4	1340.4	1340.4	1328.1

TEST NUMBER: P909678

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1522.2	1548.4	1543.8	1531.5	1522.2
115°	1725.6	1750.2	1742.5	1737.9	1725.6
117.5°	1927.4	1961.3	1939.7	1927.4	1915.1
120°	2130.8	2164.6	2130.8	2130.8	2116.9
122.5°	2315.6	2358.8	2337.2	2324.9	2315.6
125°	2509.8	2548.3	2536.0	2522.1	2517.5
127.5°	2699.3	2747.0	2730.1	2711.6	2699.3
130°	2876.5	2931.9	2924.3	2915.0	2898.0
132.5°	3075.2	3118.4	3121.4	3099.9	3087.6
135°	3246.2	3294.0	3303.3	3298.6	3286.3
137.5°	3437.3	3475.8	3483.5	3480.4	3461.9
140°	3605.2	3643.7	3665.3	3665.3	3648.3
142.5°	3777.8	3816.3	3828.6	3833.2	3816.3
145°	3941.1	3971.9	3996.5	4001.2	3984.2
147.5°	4087.4	4126.0	4144.5	4152.2	4135.2
150°	4238.4	4264.7	4281.6	4295.5	4281.6
152.5°	4372.5	4398.7	4420.3	4437.1	4420.3
155°	4506.5	4518.8	4532.7	4554.3	4540.5
157.5°	4622.1	4631.3	4639.0	4669.8	4648.3
160°	4725.3	4734.6	4739.2	4765.4	4746.9
162.5°	4820.8	4820.8	4825.4	4854.7	4833.1
165°	4902.5	4897.8	4897.8	4928.6	4907.1
167.5°	4976.4	4962.6	4962.6	4993.4	4971.8
170°	5031.9	5019.5	5015.0	5045.8	5019.5
172.5°	5070.4	5058.1	5053.5	5084.3	5058.1
175°	5101.2	5088.9	5079.6	5110.5	5084.3
177.5°	5118.2	5105.9	5096.6	5122.8	5096.6
180°	5110.5	5110.5	5110.5	5110.5	5110.5

TEST NUMBER: P909678

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.65	12.44	12.65	13.45	14.78	7.61	8.40	8.61	9.41	10.74
	3H	13.33	14.04	14.34	15.05	16.41	8.79	9.51	9.80	10.52	11.88
	4H	13.94	14.61	14.96	15.63	16.99	9.24	9.92	10.27	10.93	12.30
	6H	14.36	14.98	15.39	16.00	17.38	9.56	10.18	10.60	11.21	12.58
	8H	14.49	15.08	15.53	16.12	17.49	9.65	10.24	10.69	11.28	12.65
	12H	14.55	15.11	15.59	16.14	17.54	9.70	10.26	10.74	11.29	12.68
4H	2H	11.66	12.33	12.69	13.35	14.71	8.20	8.87	9.23	9.89	11.26
	3H	13.49	14.05	14.53	15.10	16.47	9.55	10.11	10.59	11.16	12.53
	4H	14.19	14.70	15.23	15.74	17.13	10.10	10.61	11.14	11.65	13.05
	6H	14.70	15.14	15.76	16.20	17.60	10.51	10.95	11.57	12.02	13.41
	8H	14.88	15.29	15.93	16.34	17.75	10.64	11.05	11.70	12.11	13.52
	12H	14.98	15.35	16.05	16.42	17.83	10.71	11.08	11.78	12.15	13.56
8H	4H	14.15	14.56	15.21	15.62	17.02	10.38	10.79	11.43	11.84	13.25
	6H	14.72	15.06	15.80	16.16	17.56	10.89	11.23	11.97	12.33	13.74
	8H	14.94	15.24	16.02	16.32	17.74	11.09	11.38	12.17	12.46	13.89
	12H	15.08	15.34	16.17	16.42	17.88	11.20	11.47	12.29	12.54	14.01
12H	4H	14.10	14.47	15.17	15.54	16.95	10.38	10.75	11.45	11.82	13.23
	6H	14.70	14.99	15.78	16.07	17.50	10.95	11.24	12.03	12.32	13.75
	8H	14.92	15.18	16.01	16.25	17.72	11.16	11.42	12.24	12.49	13.96