

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909696

Luminaire Tested: DFN2DIP-SQ4F0-160D100US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909696
REPORT IS A COMBINATION OF REPORTS P900147 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D100US840-FLLFL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24933.5 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 241.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909696

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909696

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91		80	80	80		69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75		70	68	66		61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62		62	58	56		54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52		55	50	47		48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45		49	44	40		43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39		44	39	35		38	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34		40	35	31		35	31	28	25
7	60	48	40	34	56	45	38	32	40	34	30		36	31	27		32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27		33	28	24		29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24		30	26	22		27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4412	4412	4412
5°	4418	4351	4381
10°	4383	4293	4323
15°	4318	4223	4231
20°	4231	4126	4137
25°	4144	4009	4029
30°	4036	3901	3891
35°	3933	3773	3744
40°	3806	3644	3605
45°	3680	3514	3463
50°	3542	3379	3298
55°	3397	3221	3147
60°	3233	3034	2974
65°	3055	2842	2770
70°	2828	2606	2550
75°	2513	2325	2350
80°	2135	1966	1963
85°	1543	1345	1319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3680 cd/sqm

TEST NUMBER: P909696

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	591.7	2.4
10°-20°	1664.9	6.7
20°-30°	2446.8	9.8
30°-40°	2841.8	11.4
40°-50°	2838.3	11.4
50°-60°	2474.9	9.9
60°-70°	1829.5	7.3
70°-80°	1035.1	4.2
80°-90°	282.3	1.1
90°-100°	197.6	0.8
100°-110°	627.9	2.5
110°-120°	1074.6	4.3
120°-130°	1413.3	5.7
130°-140°	1586.4	6.4
140°-150°	1555.6	6.2
150°-160°	1304.9	5.2
160°-170°	865.4	3.5
170°-180°	302.5	1.2
0°-30°	4703.5	18.9
0°-40°	7545.3	30.3
0°-60°	12858.5	51.6
0°-90°	16005.3	64.2
90°-120°	1900.2	7.6
90°-150°	6455.4	25.9
90°-180°	8928.0	35.8
0°-180°	24933.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6287	6287	6287	6287	6287	
5°	6287	6263	6197	6245	6233	597
15°	5985	5949	5870	5895	5864	1686
25°	5417	5369	5266	5278	5266	2492
35°	4673	4613	4516	4480	4450	2918
45°	3803	3760	3670	3603	3579	2935
55°	2878	2842	2769	2696	2666	2573
65°	1941	1904	1844	1790	1759	1919
75°	1015	1004	973	937	949	1084
85°	248	242	236	217	212	276
90°	3	35	94	89	92	24
95°	141	168	172	172	168	156
105°	580	587	593	598	598	612
115°	1078	1094	1089	1086	1078	1067
125°	1568	1593	1585	1576	1573	1402
135°	2029	2059	2064	2062	2054	1568
145°	2463	2482	2498	2500	2490	1539
155°	2816	2824	2833	2846	2838	1296
165°	3064	3061	3061	3080	3067	864
175°	3188	3180	3175	3194	3177	303
180°	3194	3194	3194	3194	3194	

TEST NUMBER: P909696

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6287.1	6287.1	6287.1	6287.1	6287.1
2.5°	6323.7	6293.5	6226.8	6287.1	6275.5
5°	6287.1	6263.4	6196.6	6244.8	6233.2
7.5°	6244.8	6208.9	6142.1	6190.9	6178.7
10°	6178.7	6136.3	6063.9	6112.0	6094.0
12.5°	6087.7	6051.7	5979.2	6009.4	5997.2
15°	5985.0	5949.1	5870.1	5894.6	5864.4
17.5°	5858.0	5822.1	5743.2	5773.3	5743.2
20°	5718.8	5682.9	5598.2	5616.2	5592.4
22.5°	5580.3	5525.8	5446.8	5446.8	5434.7
25°	5416.7	5368.6	5265.9	5277.6	5265.9
27.5°	5235.1	5192.8	5114.6	5096.7	5066.5
30°	5054.3	5005.6	4915.1	4897.1	4872.8
32.5°	4860.6	4824.7	4727.8	4691.2	4666.9
35°	4673.4	4613.1	4516.1	4479.6	4449.5
37.5°	4461.7	4407.2	4310.3	4267.9	4237.8
40°	4244.2	4195.5	4098.6	4044.7	4020.4
42.5°	4032.6	3983.8	3887.6	3826.7	3790.7
45°	3803.0	3760.5	3669.5	3603.4	3579.1
47.5°	3579.1	3536.8	3439.9	3373.2	3337.3
50°	3343.1	3312.9	3228.2	3143.5	3113.4
52.5°	3113.4	3071.1	2992.8	2926.1	2883.8
55°	2878.0	2841.5	2769.0	2696.4	2666.3
57.5°	2642.0	2611.8	2532.9	2460.4	2436.1
60°	2405.9	2382.2	2297.5	2230.8	2212.8
62.5°	2176.3	2133.9	2073.7	2013.4	1989.0
65°	1940.9	1904.3	1844.0	1789.6	1759.4
67.5°	1699.1	1668.3	1614.5	1572.1	1547.7
70°	1475.2	1450.9	1396.3	1354.0	1330.3
72.5°	1245.6	1221.2	1191.1	1148.7	1130.8
75°	1015.3	1003.8	973.0	937.1	949.3
77.5°	810.1	785.8	773.6	755.6	737.6
80°	604.8	598.4	586.2	568.3	556.1
82.5°	411.1	411.1	405.4	381.0	381.0
85°	247.6	241.8	236.0	217.4	211.7
87.5°	109.1	96.8	84.6	66.8	60.3
90°	2.9	34.6	94.3	88.6	91.5
92.5°	59.7	80.9	83.8	86.6	86.6
95°	140.6	167.5	172.4	172.4	167.5
97.5°	234.0	259.0	269.6	269.6	269.6
100°	341.8	364.0	371.6	371.6	368.8
102.5°	455.4	471.8	482.4	485.2	482.4
105°	579.7	587.3	593.1	597.9	597.9
107.5°	702.9	714.5	714.5	716.4	702.9
110°	822.3	837.7	837.7	837.7	830.0

TEST NUMBER: P909696

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US840-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	951.3	967.7	964.8	957.0	951.3
115°	1078.4	1093.8	1089.0	1086.1	1078.4
117.5°	1204.6	1225.8	1212.2	1204.6	1196.8
120°	1331.6	1352.8	1331.6	1331.6	1323.0
122.5°	1447.1	1474.1	1460.7	1453.0	1447.1
125°	1568.5	1592.6	1584.9	1576.2	1573.4
127.5°	1687.0	1716.8	1706.2	1694.7	1687.0
130°	1797.7	1832.3	1827.6	1821.7	1811.2
132.5°	1921.9	1948.8	1950.8	1937.3	1929.6
135°	2028.7	2058.6	2064.4	2061.5	2053.8
137.5°	2148.2	2172.2	2177.1	2175.1	2163.5
140°	2253.1	2277.1	2290.7	2290.7	2280.1
142.5°	2361.0	2385.0	2392.7	2395.6	2385.0
145°	2463.0	2482.2	2497.7	2500.5	2489.9
147.5°	2554.5	2578.6	2590.1	2595.0	2584.3
150°	2648.9	2665.2	2675.8	2684.4	2675.8
152.5°	2732.6	2749.0	2762.5	2773.1	2762.5
155°	2816.4	2824.1	2832.8	2846.2	2837.5
157.5°	2888.6	2894.4	2899.2	2918.4	2905.0
160°	2953.1	2958.9	2961.7	2978.1	2966.6
162.5°	3012.8	3012.8	3015.7	3033.9	3020.5
165°	3063.8	3060.9	3060.9	3080.2	3066.8
167.5°	3110.1	3101.4	3101.4	3120.7	3107.2
170°	3144.7	3137.0	3134.1	3153.4	3137.0
172.5°	3168.8	3161.1	3158.2	3177.4	3161.1
175°	3188.0	3180.4	3174.6	3193.8	3177.4
177.5°	3198.6	3191.0	3185.1	3201.5	3185.1
180°	3193.8	3193.8	3193.8	3193.8	3193.8

TEST NUMBER: P909696

CATALOG NUMBER: DFN2DIP-SQ4F0-160D100US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.66	14.66	14.48	15.51	16.56	13.21	14.22	14.04	15.06	16.12
	3H	15.33	16.23	16.17	17.09	18.17	14.84	15.74	15.68	16.60	17.68
	4H	15.93	16.78	16.78	17.65	18.74	15.43	16.29	16.29	17.15	18.24
	6H	16.34	17.13	17.21	18.00	19.10	15.84	16.63	16.71	17.50	18.60
	8H	16.45	17.20	17.32	18.09	19.19	15.95	16.70	16.82	17.59	18.69
	12H	16.50	17.22	17.39	18.10	19.23	15.99	16.71	16.88	17.59	18.72
4H	2H	14.13	14.99	14.99	15.85	16.94	13.78	14.63	14.64	15.50	16.59
	3H	16.02	16.73	16.89	17.63	18.73	15.61	16.32	16.48	17.22	18.33
	4H	16.74	17.39	17.62	18.28	19.42	16.32	16.97	17.20	17.86	18.99
	6H	17.27	17.83	18.17	18.75	19.88	16.84	17.40	17.73	18.32	19.45
	8H	17.42	17.95	18.32	18.86	20.01	16.99	17.51	17.89	18.42	19.57
	12H	17.51	17.98	18.43	18.91	20.06	17.06	17.53	17.98	18.46	19.61
8H	4H	16.95	17.47	17.85	18.39	19.54	16.57	17.10	17.47	18.01	19.16
	6H	17.59	18.03	18.52	18.98	20.13	17.21	17.64	18.14	18.60	19.74
	8H	17.82	18.20	18.75	19.15	20.31	17.42	17.81	18.36	18.75	19.92
	12H	17.96	18.30	18.90	19.24	20.45	17.55	17.89	18.49	18.82	20.04
12H	4H	16.94	17.42	17.86	18.35	19.50	16.57	17.05	17.50	17.98	19.13
	6H	17.62	18.01	18.56	18.95	20.12	17.25	17.64	18.19	18.58	19.75
	8H	17.88	18.21	18.82	19.15	20.37	17.50	17.83	18.44	18.77	19.99