

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909709

Luminaire Tested: DFN2DIP-SQ4F0-160D140US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909709
REPORT IS A COMBINATION OF REPORTS P901721 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D140US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29993.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 272.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909709

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909709

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4412	4412	4412
5°	4418	4351	4381
10°	4383	4293	4323
15°	4318	4223	4231
20°	4231	4126	4137
25°	4144	4009	4029
30°	4036	3901	3891
35°	3933	3773	3744
40°	3806	3644	3605
45°	3680	3514	3463
50°	3542	3379	3298
55°	3397	3221	3147
60°	3233	3034	2974
65°	3055	2842	2770
70°	2828	2606	2550
75°	2513	2325	2350
80°	2135	1966	1963
85°	1543	1345	1319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3680 cd/sqm

TEST NUMBER: P909709

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	591.7	2.0
10°-20°	1664.9	5.6
20°-30°	2446.8	8.2
30°-40°	2841.8	9.5
40°-50°	2838.3	9.5
50°-60°	2474.9	8.3
60°-70°	1829.5	6.1
70°-80°	1035.1	3.5
80°-90°	281.6	0.9
90°-100°	157.3	0.5
100°-110°	586.5	2.0
110°-120°	1555.5	5.2
120°-130°	2580.0	8.6
130°-140°	2740.5	9.1
140°-150°	2547.0	8.5
150°-160°	2047.7	6.8
160°-170°	1319.5	4.4
170°-180°	454.2	1.5
0°-30°	4703.5	15.7
0°-40°	7545.3	25.2
0°-60°	12858.5	42.9
0°-90°	16004.6	53.4
90°-120°	2299.4	7.7
90°-150°	10166.9	33.9
90°-180°	13988.0	46.6
0°-180°	29993.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6287	6287	6287	6287	6287	
5°	6287	6263	6197	6245	6233	597
15°	5985	5949	5870	5895	5864	1686
25°	5417	5369	5266	5278	5266	2492
35°	4673	4613	4516	4480	4450	2918
45°	3803	3760	3670	3603	3579	2935
55°	2878	2842	2769	2696	2666	2573
65°	1941	1904	1844	1790	1759	1919
75°	1015	1004	973	937	949	1084
85°	248	242	236	217	212	276
90°	3	41	69	86	93	28
95°	224	110	134	152	148	266
105°	1050	1153	211	248	262	1121
115°	1985	2044	2130	532	283	1954
125°	2807	2852	2918	2942	2952	2503
135°	3473	3529	3560	3594	3587	2683
145°	4029	4026	4084	4108	4091	2520
155°	4436	4406	4447	4468	4440	2044
165°	4675	4654	4664	4689	4664	1321
175°	4782	4758	4764	4789	4754	455
180°	4771	4771	4771	4771	4771	

TEST NUMBER: P909709

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US840-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6287.1	6287.1	6287.1	6287.1	6287.1
2.5°	6323.7	6293.5	6226.8	6287.1	6275.5
5°	6287.1	6263.4	6196.6	6244.8	6233.2
7.5°	6244.8	6208.9	6142.1	6190.9	6178.7
10°	6178.7	6136.3	6063.9	6112.0	6094.0
12.5°	6087.7	6051.7	5979.2	6009.4	5997.2
15°	5985.0	5949.1	5870.1	5894.6	5864.4
17.5°	5858.0	5822.1	5743.2	5773.3	5743.2
20°	5718.8	5682.9	5598.2	5616.2	5592.4
22.5°	5580.3	5525.8	5446.8	5446.8	5434.7
25°	5416.7	5368.6	5265.9	5277.6	5265.9
27.5°	5235.1	5192.8	5114.6	5096.7	5066.5
30°	5054.3	5005.6	4915.1	4897.1	4872.8
32.5°	4860.6	4824.7	4727.8	4691.2	4666.9
35°	4673.4	4613.1	4516.1	4479.6	4449.5
37.5°	4461.7	4407.2	4310.3	4267.9	4237.8
40°	4244.2	4195.5	4098.6	4044.7	4020.4
42.5°	4032.6	3983.8	3887.6	3826.7	3790.7
45°	3803.0	3760.5	3669.5	3603.4	3579.1
47.5°	3579.1	3536.8	3439.9	3373.2	3337.3
50°	3343.1	3312.9	3228.2	3143.5	3113.4
52.5°	3113.4	3071.1	2992.8	2926.1	2883.8
55°	2878.0	2841.5	2769.0	2696.4	2666.3
57.5°	2642.0	2611.8	2532.9	2460.4	2436.1
60°	2405.9	2382.2	2297.5	2230.8	2212.8
62.5°	2176.3	2133.9	2073.7	2013.4	1989.0
65°	1940.9	1904.3	1844.0	1789.6	1759.4
67.5°	1699.1	1668.3	1614.5	1572.1	1547.7
70°	1475.2	1450.9	1396.3	1354.0	1330.3
72.5°	1245.6	1221.2	1191.1	1148.7	1130.8
75°	1015.3	1003.8	973.0	937.1	949.3
77.5°	810.1	785.8	773.6	755.6	737.6
80°	604.8	598.4	586.2	568.3	556.1
82.5°	411.1	411.1	405.4	381.0	381.0
85°	247.6	241.8	236.0	217.4	211.7
87.5°	109.1	96.8	84.6	66.8	60.3
90°	3.2	41.4	68.9	86.5	93.1
92.5°	86.5	72.6	82.8	89.8	93.1
95°	224.3	110.3	134.5	152.1	148.5
97.5°	403.8	121.0	175.9	186.5	189.9
100°	611.3	138.1	196.8	224.3	231.3
102.5°	838.8	832.2	203.8	241.5	252.2
105°	1049.6	1153.3	210.8	248.4	262.4
107.5°	1294.7	1380.8	217.7	255.4	269.3
110°	1529.6	1601.8	604.3	259.1	272.7

TEST NUMBER: P909709

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1750.6	1812.5	1753.9	265.7	276.3
115°	1985.2	2043.8	2130.3	531.8	283.3
117.5°	2188.9	2257.8	2316.8	1822.8	918.4
120°	2416.9	2468.5	2530.8	2572.2	2106.1
122.5°	2610.0	2665.3	2734.6	2755.1	2758.9
125°	2806.8	2851.9	2917.5	2941.6	2951.9
127.5°	2986.4	3034.7	3086.8	3121.2	3124.5
130°	3155.6	3211.1	3248.7	3286.9	3283.6
132.5°	3328.3	3373.4	3411.1	3442.2	3439.0
135°	3473.4	3528.8	3559.5	3594.3	3587.3
137.5°	3625.1	3666.5	3701.4	3735.8	3725.6
140°	3773.6	3801.4	3839.1	3870.3	3853.0
142.5°	3898.2	3922.3	3967.1	3994.5	3977.3
145°	4029.4	4025.6	4084.3	4108.5	4091.3
147.5°	4143.0	4132.7	4191.3	4208.5	4195.0
150°	4253.7	4229.4	4284.8	4305.3	4288.1
152.5°	4346.7	4319.2	4370.9	4391.8	4367.6
155°	4436.4	4405.7	4447.1	4467.6	4440.2
157.5°	4509.0	4481.6	4512.8	4536.9	4509.0
160°	4571.4	4550.5	4571.4	4591.9	4567.7
162.5°	4626.3	4605.8	4623.1	4647.2	4616.1
165°	4674.7	4654.2	4664.5	4688.6	4664.5
167.5°	4712.8	4691.9	4702.5	4726.8	4695.6
170°	4743.9	4723.0	4730.0	4754.2	4723.0
172.5°	4764.4	4743.9	4750.9	4775.1	4743.9
175°	4781.7	4757.5	4764.4	4788.7	4754.2
177.5°	4788.7	4764.4	4768.2	4792.3	4761.2
180°	4771.4	4771.4	4771.4	4771.4	4771.4

TEST NUMBER: P909709

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.75	13.64	13.67	14.58	15.81	12.30	13.19	13.23	14.14	15.36
	3H	14.41	15.21	15.35	16.17	17.41	13.92	14.72	14.86	15.68	16.92
	4H	15.01	15.76	15.96	16.72	17.98	14.51	15.27	15.47	16.23	17.48
	6H	15.41	16.11	16.38	17.07	18.34	14.91	15.61	15.88	16.57	17.84
	8H	15.52	16.18	16.49	17.16	18.43	15.02	15.68	15.99	16.66	17.93
	12H	15.57	16.20	16.55	17.18	18.47	15.06	15.69	16.04	16.67	17.96
4H	2H	13.21	13.97	14.17	14.93	16.18	12.86	13.61	13.82	14.57	15.83
	3H	15.09	15.72	16.05	16.71	17.98	14.68	15.31	15.65	16.30	17.57
	4H	15.80	16.38	16.78	17.37	18.66	15.38	15.96	16.36	16.94	18.23
	6H	16.33	16.82	17.32	17.83	19.12	15.89	16.39	16.88	17.40	18.69
	8H	16.48	16.94	17.47	17.94	19.25	16.04	16.51	17.03	17.51	18.81
	12H	16.55	16.97	17.57	17.99	19.30	16.11	16.53	17.12	17.54	18.85
8H	4H	16.00	16.47	17.00	17.47	18.77	15.63	16.09	16.62	17.09	18.40
	6H	16.64	17.03	17.66	18.07	19.37	16.26	16.64	17.28	17.68	18.99
	8H	16.87	17.20	17.89	18.23	19.56	16.47	16.81	17.50	17.84	19.16
	12H	17.00	17.30	18.03	18.32	19.69	16.59	16.89	17.62	17.91	19.28
12H	4H	15.99	16.41	17.00	17.43	18.74	15.62	16.04	16.63	17.06	18.37
	6H	16.67	17.01	17.70	18.04	19.36	16.30	16.64	17.33	17.67	18.99
	8H	16.92	17.22	17.95	18.24	19.61	16.54	16.84	17.57	17.86	19.23