

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917679

Luminaire Tested: DFN2DIP-SQ4F0-080D140US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917679
REPORT IS A COMBINATION OF REPORTS P901710 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D140US930-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16844.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 177.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917679
CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P917679

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				33
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	35	35	28				28
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30	24				24
3	79	70	63	57	71	63	57	53	51	47	43	39	37	34	29	27	26	21				21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22	18				18
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	24	21	20	16				16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17	14				14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13				13
8	52	41	33	28	47	37	31	26	30	25	22	24	21	18	18	16	14	12				12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10				10
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1892	1892	1892
5°	1895	1862	1874
10°	1876	1826	1813
15°	1850	1766	1720
20°	1816	1683	1604
25°	1781	1590	1493
30°	1734	1495	1352
35°	1688	1392	1228
40°	1641	1286	1085
45°	1586	1168	956
50°	1530	1049	830
55°	1471	922	708
60°	1403	789	584
65°	1325	654	526
70°	1230	528	477
75°	1111	466	435
80°	938	392	379
85°	653	264	289

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2067 cd/sqm



TEST NUMBER: P917679

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	1.5
10°-20°	693.6	4.1
20°-30°	973.7	5.8
30°-40°	1061.4	6.3
40°-50°	975.6	5.8
50°-60°	766.2	4.5
60°-70°	498.7	3.0
70°-80°	256.7	1.5
80°-90°	72.3	0.4
90°-100°	127.0	0.8
100°-110°	473.5	2.8
110°-120°	1255.8	7.5
120°-130°	2082.9	12.4
130°-140°	2212.5	13.1
140°-150°	2056.3	12.2
150°-160°	1653.2	9.8
160°-170°	1065.3	6.3
170°-180°	366.7	2.2
0°-30°	1919.9	11.4
0°-40°	2981.4	17.7
0°-60°	4723.1	28.0
0°-90°	5550.8	33.0
90°-120°	1856.4	11.0
90°-150°	8208.1	48.7
90°-180°	11293.0	67.0
0°-180°	16844.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	3	33	56	70	75	16
95°	181	89	109	123	120	214
105°	847	931	170	201	212	905
115°	1603	1650	1720	429	229	1578
125°	2266	2302	2355	2375	2383	2021
135°	2804	2849	2874	2902	2896	2166
145°	3253	3250	3297	3317	3303	2035
155°	3582	3557	3590	3607	3585	1650
165°	3774	3758	3766	3785	3766	1066
175°	3860	3841	3846	3866	3838	367
180°	3852	3852	3852	3852	3852	



TEST NUMBER: P917679

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	2.6	33.4	55.6	69.9	75.2
92.5°	69.9	58.6	66.9	72.5	75.2
95°	181.1	89.0	108.6	122.8	119.8
97.5°	326.0	97.7	142.0	150.6	153.3
100°	493.5	111.5	158.9	181.1	186.7
102.5°	677.2	671.9	164.5	194.9	203.6
105°	847.3	931.1	170.2	200.6	211.8
107.5°	1045.3	1114.8	175.8	206.2	217.4
110°	1234.9	1293.2	487.9	209.2	220.1



TEST NUMBER: P917679

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US930-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1413.3	1463.3	1416.0	214.5	223.1
115°	1602.7	1650.0	1719.9	429.3	228.7
117.5°	1767.2	1822.8	1870.5	1471.6	741.4
120°	1951.3	1992.9	2043.2	2076.6	1700.3
122.5°	2107.1	2151.8	2207.7	2224.3	2227.3
125°	2266.0	2302.4	2355.4	2374.9	2383.2
127.5°	2411.0	2450.1	2492.0	2519.8	2522.5
130°	2547.6	2592.4	2622.8	2653.6	2650.9
132.5°	2687.1	2723.4	2753.9	2779.0	2776.4
135°	2804.2	2848.9	2873.7	2901.8	2896.2
137.5°	2926.7	2960.1	2988.2	3016.0	3007.8
140°	3046.5	3069.0	3099.4	3124.6	3110.7
142.5°	3147.1	3166.6	3202.7	3224.9	3211.0
145°	3253.0	3250.0	3297.4	3317.0	3303.0
147.5°	3344.8	3336.4	3383.8	3397.7	3386.7
150°	3434.1	3414.6	3459.2	3475.8	3461.9
152.5°	3509.2	3487.0	3528.8	3545.7	3526.1
155°	3581.7	3556.9	3590.3	3606.9	3584.7
157.5°	3640.3	3618.1	3643.3	3662.8	3640.3
160°	3690.6	3673.7	3690.6	3707.2	3687.7
162.5°	3735.0	3718.4	3732.4	3751.8	3726.7
165°	3774.0	3757.5	3765.8	3785.3	3765.8
167.5°	3804.8	3788.0	3796.5	3816.1	3790.9
170°	3829.9	3813.1	3818.7	3838.3	3813.1
172.5°	3846.5	3829.9	3835.6	3855.1	3829.9
175°	3860.4	3840.9	3846.5	3866.1	3838.3
177.5°	3866.1	3846.5	3849.5	3869.0	3843.9
180°	3852.1	3852.1	3852.1	3852.1	3852.1



TEST NUMBER: P917679
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.53	8.24	8.63	9.33	10.83	3.49	4.20	4.59	5.29	6.79
	3H	9.21	9.84	10.31	10.94	12.45	4.67	5.31	5.78	6.41	7.92
	4H	9.81	10.41	10.93	11.51	13.03	5.12	5.72	6.23	6.82	8.34
	6H	10.23	10.78	11.35	11.88	13.42	5.43	5.99	6.56	7.09	8.62
	8H	10.36	10.88	11.48	12.00	13.52	5.52	6.05	6.65	7.16	8.69
	12H	10.41	10.91	11.55	12.02	13.57	5.56	6.06	6.69	7.17	8.72
4H	2H	7.54	8.14	8.66	9.24	10.76	4.08	4.68	5.20	5.78	7.30
	3H	9.36	9.86	10.49	10.98	12.52	5.42	5.92	6.54	7.04	8.57
	4H	10.05	10.51	11.18	11.62	13.18	5.96	6.42	7.09	7.53	9.09
	6H	10.56	10.95	11.70	12.09	13.64	6.37	6.77	7.51	7.90	9.45
	8H	10.74	11.10	11.87	12.23	13.80	6.50	6.87	7.64	8.00	9.56
	12H	10.83	11.16	11.98	12.30	13.87	6.56	6.89	7.71	8.03	9.60
8H	4H	10.01	10.37	11.15	11.51	13.07	6.23	6.60	7.37	7.73	9.29
	6H	10.57	10.88	11.73	12.05	13.61	6.75	7.05	7.91	8.22	9.78
	8H	10.79	11.06	11.96	12.21	13.79	6.94	7.20	8.10	8.36	9.93
	12H	10.93	11.16	12.10	12.31	13.92	7.05	7.29	8.22	8.44	10.05
12H	4H	9.95	10.29	11.11	11.43	12.99	6.23	6.57	7.39	7.71	9.27
	6H	10.55	10.81	11.71	11.97	13.54	6.80	7.06	7.96	8.21	9.79
	8H	10.77	11.00	11.94	12.15	13.76	7.01	7.24	8.17	8.39	10.00