

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912150

Luminaire Tested: DFN2DIP-SQ4F0-060D140US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912150
REPORT IS A COMBINATION OF REPORTS P900186 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D140US850-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19396.4 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 155.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912150

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912150

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	32	32
2	85	78	72	68	76	70	66	61	56	52	49	42	40	38	29	28	27
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20
5	65	54	47	41	59	49	43	38	39	35	31	30	27	24	21	19	18
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1930	1930	1930
5°	1933	1899	1912
10°	1914	1863	1850
15°	1887	1801	1754
20°	1852	1717	1637
25°	1817	1622	1523
30°	1769	1525	1379
35°	1722	1420	1252
40°	1674	1312	1107
45°	1618	1192	975
50°	1561	1071	846
55°	1501	941	723
60°	1432	805	595
65°	1352	667	537
70°	1255	539	486
75°	1133	476	444
80°	957	400	387
85°	666	269	294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3864 cd/sqm

TEST NUMBER: P912150

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	1.3
10°-20°	707.6	3.6
20°-30°	993.4	5.1
30°-40°	1082.8	5.6
40°-50°	995.2	5.1
50°-60°	781.6	4.0
60°-70°	508.8	2.6
70°-80°	261.9	1.4
80°-90°	80.8	0.4
90°-100°	303.8	1.6
100°-110°	965.4	5.0
110°-120°	1652.1	8.5
120°-130°	2172.8	11.2
130°-140°	2438.9	12.6
140°-150°	2391.6	12.3
150°-160°	2006.2	10.3
160°-170°	1330.5	6.9
170°-180°	465.0	2.4
0°-30°	1958.7	10.1
0°-40°	3041.5	15.7
0°-60°	4818.4	24.8
0°-90°	5669.9	29.2
90°-120°	2921.4	15.1
90°-150°	9924.8	51.2
90°-180°	13727.0	70.8
0°-180°	19396.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	4	53	145	136	141	19
95°	216	258	265	265	258	241
105°	891	903	912	919	919	940
115°	1658	1682	1674	1670	1658	1640
125°	2412	2448	2437	2423	2419	2155
135°	3119	3165	3174	3169	3158	2411
145°	3787	3816	3840	3844	3828	2366
155°	4330	4342	4355	4376	4363	1993
165°	4710	4706	4706	4736	4715	1329
175°	4901	4890	4881	4910	4885	466
180°	4910	4910	4910	4910	4910	

TEST NUMBER: P912150

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	4.4	53.3	145.1	136.2	140.6
92.5°	91.8	124.3	128.8	133.2	133.2
95°	216.1	257.6	264.9	264.9	257.6
97.5°	359.8	398.2	414.5	414.5	414.5
100°	525.6	559.6	571.4	571.4	566.9
102.5°	700.2	725.4	741.7	746.1	741.7
105°	891.2	903.1	911.9	919.3	919.3
107.5°	1080.6	1098.5	1098.5	1101.3	1080.6
110°	1264.3	1287.9	1287.9	1287.9	1276.0

TEST NUMBER: P912150

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1462.5	1487.7	1483.3	1471.4	1462.5
115°	1658.0	1681.7	1674.3	1669.8	1658.0
117.5°	1851.9	1884.5	1863.8	1851.9	1840.1
120°	2047.3	2079.9	2047.3	2047.3	2034.0
122.5°	2225.0	2266.4	2245.7	2233.9	2225.0
125°	2411.5	2448.5	2436.6	2423.3	2418.8
127.5°	2593.5	2639.4	2623.1	2605.4	2593.5
130°	2763.7	2817.1	2809.7	2800.8	2784.5
132.5°	2954.7	2996.2	2999.2	2978.4	2966.6
135°	3119.1	3165.0	3173.8	3169.4	3157.5
137.5°	3302.6	3339.6	3347.1	3344.1	3326.3
140°	3464.0	3501.0	3521.7	3521.7	3505.4
142.5°	3629.8	3666.8	3678.7	3683.1	3666.8
145°	3786.7	3816.3	3840.0	3844.5	3828.2
147.5°	3927.3	3964.3	3982.1	3989.5	3973.2
150°	4072.4	4097.5	4113.8	4127.1	4113.8
152.5°	4201.2	4226.4	4247.1	4263.3	4247.1
155°	4330.0	4341.8	4355.2	4375.9	4362.6
157.5°	4441.0	4449.9	4457.3	4486.9	4466.2
160°	4540.2	4549.1	4553.6	4578.7	4560.9
162.5°	4632.0	4632.0	4636.4	4664.6	4643.8
165°	4710.5	4706.0	4706.0	4735.7	4714.9
167.5°	4781.5	4768.1	4768.1	4797.8	4777.0
170°	4834.8	4822.9	4818.5	4848.1	4822.9
172.5°	4871.8	4860.0	4855.5	4885.1	4860.0
175°	4901.4	4889.6	4880.7	4910.3	4885.1
177.5°	4917.6	4905.9	4897.0	4922.1	4897.0
180°	4910.3	4910.3	4910.3	4910.3	4910.3

TEST NUMBER: P912150

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.10	7.79	8.22	8.90	10.44	3.06	3.75	4.18	4.86	6.40
	3H	8.77	9.38	9.90	10.50	12.06	4.24	4.85	5.37	5.97	7.53
	4H	9.38	9.96	10.52	11.08	12.64	4.68	5.27	5.82	6.39	7.95
	6H	9.79	10.33	10.94	11.45	13.03	5.00	5.53	6.15	6.66	8.23
	8H	9.92	10.43	11.07	11.57	13.13	5.09	5.59	6.24	6.73	8.30
	12H	9.98	10.46	11.13	11.59	13.18	5.12	5.61	6.28	6.74	8.33
4H	2H	7.10	7.68	8.25	8.80	10.37	3.64	4.22	4.79	5.34	6.91
	3H	8.92	9.41	10.07	10.55	12.13	4.98	5.46	6.13	6.61	8.19
	4H	9.61	10.06	10.77	11.19	12.79	5.52	5.97	6.68	7.10	8.70
	6H	10.12	10.50	11.28	11.66	13.25	5.94	6.32	7.10	7.47	9.06
	8H	10.30	10.65	11.46	11.80	13.41	6.06	6.42	7.22	7.57	9.17
	12H	10.39	10.71	11.56	11.87	13.48	6.12	6.44	7.30	7.60	9.21
8H	4H	9.57	9.92	10.73	11.07	12.68	5.79	6.15	6.95	7.30	8.90
	6H	10.13	10.43	11.31	11.62	13.22	6.31	6.60	7.49	7.79	9.39
	8H	10.35	10.61	11.54	11.78	13.40	6.50	6.76	7.69	7.93	9.55
	12H	10.49	10.71	11.68	11.88	13.53	6.61	6.84	7.80	8.01	9.66
12H	4H	9.51	9.84	10.69	11.00	12.60	5.79	6.12	6.97	7.28	8.88
	6H	10.11	10.36	11.29	11.54	13.15	6.36	6.61	7.54	7.79	9.40
	8H	10.33	10.55	11.51	11.72	13.37	6.56	6.79	7.75	7.96	9.61

END OF REPORT