

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912153

Luminaire Tested: DFN2DIP-SQ4F0-060D160US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912153
REPORT IS A COMBINATION OF REPORTS P901723 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D160US850-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24154.0 lumens
Efficiency: N/A
Efficacy: 140.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912153

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912153

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1817	1817	1817
5°	1820	1792	1804
10°	1805	1768	1780
15°	1778	1739	1742
20°	1742	1699	1704
25°	1707	1651	1659
30°	1662	1606	1602
35°	1620	1554	1542
40°	1567	1501	1485
45°	1515	1447	1426
50°	1458	1391	1358
55°	1399	1327	1296
60°	1332	1250	1225
65°	1258	1170	1140
70°	1165	1073	1050
75°	1035	957	968
80°	879	810	808
85°	635	553	543

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3210 cd/sqm

TEST NUMBER: P912153

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	1.0
10°-20°	685.6	2.8
20°-30°	1007.6	4.2
30°-40°	1170.3	4.8
40°-50°	1168.8	4.8
50°-60°	1019.2	4.2
60°-70°	753.4	3.1
70°-80°	426.3	1.8
80°-90°	123.0	0.5
90°-100°	197.5	0.8
100°-110°	736.1	3.0
110°-120°	1952.3	8.1
120°-130°	3238.0	13.4
130°-140°	3439.5	14.2
140°-150°	3196.6	13.2
150°-160°	2570.0	10.6
160°-170°	1656.0	6.9
170°-180°	570.0	2.4
0°-30°	1937.0	8.0
0°-40°	3107.2	12.9
0°-60°	5295.3	21.9
0°-90°	6597.9	27.3
90°-120°	2885.9	11.9
90°-150°	12760.0	52.8
90°-180°	17556.0	72.7
0°-180°	24154.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	114
90°	4	52	86	109	117	22
95°	282	138	169	191	186	333
105°	1317	1448	264	312	329	1407
115°	2492	2565	2674	667	356	2453
125°	3523	3579	3662	3692	3705	3142
135°	4359	4429	4467	4511	4502	3367
145°	5057	5052	5126	5156	5135	3163
155°	5568	5529	5581	5607	5573	2566
165°	5867	5841	5854	5884	5854	1658
175°	6001	5971	5980	6010	5967	571
180°	5988	5988	5988	5988	5988	

TEST NUMBER: P912153

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	4.1	52.0	86.4	108.6	116.8
92.5°	108.6	91.0	103.9	112.7	116.8
95°	281.5	138.4	168.8	190.9	186.3
97.5°	506.8	151.8	220.7	234.1	238.2
100°	767.2	173.4	247.0	281.5	290.2
102.5°	1052.8	1044.6	255.7	303.1	316.4
105°	1317.3	1447.5	264.5	311.9	329.3
107.5°	1624.9	1733.0	273.3	320.6	338.0
110°	1919.8	2010.4	758.4	325.2	342.1

TEST NUMBER: P912153

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	2197.2	2274.9	2201.3	333.5	346.8
115°	2491.5	2565.0	2673.6	667.4	355.5
117.5°	2747.2	2833.6	2907.8	2287.8	1152.6
120°	3033.3	3098.1	3176.3	3228.3	2643.3
122.5°	3275.7	3345.1	3432.0	3457.8	3462.4
125°	3522.6	3579.2	3661.6	3692.0	3704.8
127.5°	3748.0	3808.7	3874.1	3917.3	3921.4
130°	3960.6	4030.0	4077.3	4125.1	4121.0
132.5°	4177.2	4233.7	4281.1	4320.2	4316.1
135°	4359.3	4428.8	4467.4	4511.1	4502.3
137.5°	4549.7	4601.7	4645.4	4688.6	4675.8
140°	4736.0	4770.9	4818.3	4857.4	4835.8
142.5°	4892.4	4922.7	4978.9	5013.3	4991.7
145°	5057.0	5052.4	5126.0	5156.3	5134.8
147.5°	5199.5	5186.7	5260.3	5281.9	5264.9
150°	5338.5	5308.1	5377.7	5403.4	5381.8
152.5°	5455.3	5420.8	5485.7	5512.0	5481.6
155°	5568.0	5529.4	5581.4	5607.1	5572.6
157.5°	5659.1	5624.6	5663.7	5694.0	5659.1
160°	5737.3	5711.0	5737.3	5763.0	5732.6
162.5°	5806.3	5780.6	5802.1	5832.5	5793.4
165°	5866.9	5841.2	5854.1	5884.5	5854.1
167.5°	5914.9	5888.6	5902.0	5932.3	5893.2
170°	5953.9	5927.7	5936.4	5966.8	5927.7
172.5°	5979.6	5953.9	5962.6	5993.0	5953.9
175°	6001.2	5970.9	5979.6	6010.0	5966.8
177.5°	6010.0	5979.6	5984.3	6014.7	5975.5
180°	5988.4	5988.4	5988.4	5988.4	5988.4

TEST NUMBER: P912153

CATALOG NUMBER: DFN2DIP-SQ4F0-060D160US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.76	7.45	7.89	8.57	10.14	6.32	7.01	7.45	8.13	9.69
	3H	8.42	9.03	9.55	10.16	11.74	7.93	8.54	9.06	9.67	11.25
	4H	9.00	9.58	10.15	10.71	12.30	8.50	9.09	9.65	10.22	11.80
	6H	9.39	9.93	10.55	11.06	12.66	8.89	9.43	10.05	10.56	12.16
	8H	9.49	10.01	10.65	11.16	12.74	8.99	9.51	10.15	10.65	12.24
	12H	9.54	10.02	10.70	11.17	12.78	9.03	9.52	10.19	10.66	12.27
4H	2H	7.20	7.79	8.36	8.92	10.50	6.85	7.44	8.01	8.57	10.15
	3H	9.06	9.55	10.22	10.70	12.30	8.65	9.14	9.81	10.30	11.89
	4H	9.77	10.22	10.93	11.36	12.98	9.35	9.80	10.51	10.94	12.56
	6H	10.28	10.66	11.45	11.83	13.44	9.85	10.23	11.01	11.40	13.00
	8H	10.43	10.79	11.59	11.95	13.57	9.99	10.35	11.16	11.51	13.13
	12H	10.49	10.82	11.68	11.99	13.62	10.04	10.37	11.23	11.54	13.17
8H	4H	9.95	10.31	11.12	11.47	13.09	9.58	9.94	10.74	11.09	12.72
	6H	10.58	10.88	11.77	12.08	13.70	10.20	10.49	11.39	11.70	13.31
	8H	10.80	11.06	12.00	12.24	13.88	10.41	10.67	11.60	11.85	13.49
	12H	10.93	11.16	12.13	12.33	14.00	10.52	10.75	11.71	11.92	13.59
12H	4H	9.93	10.26	11.11	11.43	13.05	9.56	9.89	10.75	11.06	12.68
	6H	10.61	10.87	11.80	12.05	13.69	10.24	10.50	11.43	11.68	13.32
	8H	10.85	11.07	12.04	12.25	13.92	10.47	10.69	11.66	11.87	13.54

END OF REPORT