

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917714

Luminaire Tested: DFN2DIP-SQ4F0-090D140US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917714
REPORT IS A COMBINATION OF REPORTS P900192 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D140US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16338.6 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 188.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917714

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917714

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	50	66	57	51	46	47	43	39	38	35	32	29	27	25
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2128	2128	2128
5°	2131	2095	2108
10°	2110	2054	2040
15°	2081	1986	1935
20°	2043	1893	1805
25°	2003	1789	1680
30°	1950	1681	1521
35°	1899	1566	1381
40°	1846	1447	1221
45°	1785	1314	1075
50°	1721	1181	933
55°	1655	1038	797
60°	1579	888	657
65°	1491	736	592
70°	1384	594	536
75°	1250	525	489
80°	1056	441	426
85°	735	297	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2842 cd/sqm

TEST NUMBER: P917714

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	1.7
10°-20°	780.3	4.8
20°-30°	1095.5	6.7
30°-40°	1194.1	7.3
40°-50°	1097.5	6.7
50°-60°	861.9	5.3
60°-70°	561.0	3.4
70°-80°	288.8	1.8
80°-90°	84.0	0.5
90°-100°	223.4	1.4
100°-110°	709.8	4.3
110°-120°	1214.6	7.4
120°-130°	1597.4	9.8
130°-140°	1793.0	11.0
140°-150°	1758.2	10.8
150°-160°	1474.9	9.0
160°-170°	978.1	6.0
170°-180°	341.9	2.1
0°-30°	2159.9	13.2
0°-40°	3354.0	20.5
0°-60°	5313.5	32.5
0°-90°	6247.3	38.2
90°-120°	2147.7	13.1
90°-150°	7296.4	44.7
90°-180°	10091.0	61.8
0°-180°	16338.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3033	3033	3033	3033	3033	
5°	3033	3019	2983	3008	3000	288
15°	2884	2854	2761	2709	2682	813
25°	2618	2530	2349	2237	2196	1204
35°	2256	2116	1875	1702	1641	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	947	724	478	384	376	939
75°	505	313	220	200	198	534
85°	118	60	52	52	52	135
90°	3	39	107	100	103	16
95°	159	189	195	195	189	177
105°	655	664	670	676	676	691
115°	1219	1236	1231	1228	1219	1206
125°	1773	1800	1791	1782	1778	1584
135°	2293	2327	2333	2330	2321	1772
145°	2784	2806	2823	2826	2814	1739
155°	3183	3192	3202	3217	3207	1465
165°	3463	3460	3460	3482	3466	977
175°	3603	3595	3588	3610	3591	342
180°	3610	3610	3610	3610	3610	

TEST NUMBER: P917714

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3032.7	3032.7	3032.7	3032.7	3032.7
2.5°	3046.4	3032.7	3002.3	3030.1	3024.5
5°	3032.7	3019.0	2983.2	3007.9	2999.7
7.5°	3007.9	2991.6	2953.2	2963.9	2950.2
10°	2975.0	2955.8	2901.1	2892.6	2876.3
12.5°	2933.9	2909.2	2835.0	2818.6	2788.3
15°	2884.4	2854.2	2761.0	2708.8	2681.5
17.5°	2826.8	2782.9	2667.5	2607.2	2563.3
20°	2761.0	2706.0	2568.8	2500.4	2439.8
22.5°	2689.7	2626.5	2467.2	2374.0	2333.0
25°	2618.3	2530.4	2349.3	2236.9	2195.5
27.5°	2533.3	2439.8	2239.5	2110.5	2047.3
30°	2442.7	2338.2	2118.6	1978.9	1904.6
32.5°	2354.7	2228.4	2003.6	1838.8	1770.1
35°	2256.1	2116.0	1874.6	1701.7	1641.1
37.5°	2160.0	2008.9	1753.8	1564.2	1495.8
40°	2058.4	1893.9	1627.4	1432.6	1361.3
42.5°	1954.1	1778.6	1501.3	1298.1	1229.6
45°	1844.4	1660.4	1372.3	1177.2	1111.4
47.5°	1740.1	1545.3	1248.9	1053.8	993.5
50°	1624.8	1430.0	1128.0	938.5	881.1
52.5°	1512.1	1306.3	1012.8	831.6	779.5
55°	1402.3	1188.3	891.9	727.4	675.2
57.5°	1290.0	1070.4	785.1	631.3	587.3
60°	1174.6	955.0	672.4	532.6	488.6
62.5°	1062.3	842.7	576.3	444.7	422.8
65°	946.9	724.5	477.5	384.3	375.9
67.5°	837.1	614.7	384.3	337.5	329.3
70°	721.9	507.8	318.3	290.9	279.8
72.5°	612.0	408.8	266.1	244.3	238.8
75°	504.9	312.7	219.6	200.3	197.7
77.5°	398.0	222.2	172.9	161.9	156.4
80°	299.1	159.3	131.6	120.8	120.8
82.5°	208.5	107.1	90.6	85.0	85.0
85°	117.9	60.3	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	3.3	39.2	106.6	100.1	103.4
92.5°	67.5	91.4	94.7	97.9	97.9
95°	158.9	189.4	194.8	194.8	189.4
97.5°	264.5	292.8	304.8	304.8	304.8
100°	386.4	411.4	420.0	420.0	416.8
102.5°	514.8	533.3	545.3	548.5	545.3
105°	655.2	663.9	670.4	675.8	675.8
107.5°	794.4	807.6	807.6	809.7	794.4
110°	929.4	946.8	946.8	946.8	938.1

TEST NUMBER: P917714

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1075.2	1093.7	1090.5	1081.7	1075.2
115°	1218.9	1236.3	1230.9	1227.6	1218.9
117.5°	1361.5	1385.4	1370.2	1361.5	1352.7
120°	1505.1	1529.1	1505.1	1505.1	1495.3
122.5°	1635.7	1666.1	1651.0	1642.3	1635.7
125°	1772.9	1800.0	1791.3	1781.5	1778.2
127.5°	1906.7	1940.4	1928.4	1915.4	1906.7
130°	2031.8	2071.0	2065.6	2059.0	2047.1
132.5°	2172.2	2202.7	2204.9	2189.6	2180.9
135°	2293.0	2326.8	2333.3	2330.0	2321.3
137.5°	2428.0	2455.2	2460.7	2458.5	2445.4
140°	2546.6	2573.8	2589.1	2589.1	2577.1
142.5°	2668.5	2695.7	2704.4	2707.7	2695.7
145°	2783.8	2805.6	2823.1	2826.3	2814.3
147.5°	2887.2	2914.4	2927.5	2933.0	2921.0
150°	2993.9	3012.4	3024.3	3034.1	3024.3
152.5°	3088.6	3107.1	3122.3	3134.3	3122.3
155°	3183.3	3192.0	3201.8	3217.0	3207.2
157.5°	3264.9	3271.4	3276.8	3298.6	3283.4
160°	3337.8	3344.4	3347.6	3366.1	3353.0
162.5°	3405.3	3405.3	3408.5	3429.2	3414.0
165°	3463.0	3459.7	3459.7	3481.5	3466.2
167.5°	3515.2	3505.4	3505.4	3527.1	3511.9
170°	3554.4	3545.7	3542.4	3564.2	3545.7
172.5°	3581.6	3572.9	3569.6	3591.4	3572.9
175°	3603.4	3594.6	3588.1	3609.9	3591.4
177.5°	3615.3	3606.6	3600.1	3618.5	3600.1
180°	3609.9	3609.9	3609.9	3609.9	3609.9

TEST NUMBER: P917714

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.57	9.32	9.63	10.37	11.81	4.53	5.28	5.59	6.33	7.77
	3H	10.25	10.91	11.32	11.98	13.43	5.72	6.38	6.78	7.45	8.90
	4H	10.86	11.49	11.93	12.55	14.01	6.16	6.79	7.24	7.86	9.32
	6H	11.28	11.86	12.36	12.93	14.40	6.48	7.06	7.57	8.13	9.60
	8H	11.40	11.95	12.49	13.04	14.50	6.57	7.12	7.66	8.21	9.67
	12H	11.46	11.99	12.56	13.07	14.55	6.61	7.13	7.71	8.21	9.70
4H	2H	8.58	9.21	9.67	10.28	11.74	5.12	5.75	6.21	6.82	8.28
	3H	10.41	10.93	11.50	12.03	13.50	6.46	6.99	7.56	8.08	9.55
	4H	11.10	11.58	12.20	12.66	14.16	7.01	7.49	8.11	8.57	10.07
	6H	11.61	12.02	12.72	13.13	14.62	7.42	7.84	8.53	8.94	10.43
	8H	11.79	12.17	12.89	13.27	14.77	7.55	7.94	8.66	9.04	10.54
	12H	11.88	12.23	13.00	13.34	14.85	7.61	7.96	8.74	9.07	10.58
8H	4H	11.06	11.44	12.16	12.54	14.04	7.29	7.67	8.39	8.77	10.27
	6H	11.63	11.94	12.75	13.09	14.58	7.80	8.12	8.93	9.26	10.76
	8H	11.85	12.12	12.98	13.25	14.76	7.99	8.27	9.13	9.39	10.91
	12H	11.98	12.23	13.12	13.35	14.90	8.11	8.35	9.25	9.47	11.03
12H	4H	11.01	11.36	12.13	12.47	13.97	7.29	7.63	8.41	8.75	10.25
	6H	11.60	11.88	12.74	13.00	14.52	7.85	8.13	8.98	9.25	10.77
	8H	11.82	12.07	12.96	13.19	14.74	8.06	8.30	9.20	9.42	10.98

END OF REPORT