

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912160

Luminaire Tested: DFN2DIP-SQ4F0-070D070US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912160
REPORT IS A COMBINATION OF REPORTS P900079 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D070US850-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14555.7 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912160
CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US850-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P912160
 CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53		
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45		
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37		
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32		
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27		
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24		
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21		
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18		
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16		
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15		
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2119	2119	2119
5°	2123	2090	2105
10°	2106	2063	2077
15°	2075	2029	2033
20°	2033	1982	1988
25°	1991	1926	1936
30°	1939	1874	1869
35°	1890	1813	1799
40°	1829	1751	1732
45°	1768	1688	1664
50°	1702	1623	1585
55°	1632	1548	1512
60°	1553	1458	1429
65°	1468	1365	1331
70°	1359	1252	1225
75°	1207	1117	1129
80°	1026	945	943
85°	742	647	634

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1932 cd/sqm



TEST NUMBER: P912160
 CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	2.0
10°-20°	799.9	5.5
20°-30°	1175.6	8.1
30°-40°	1365.3	9.4
40°-50°	1363.6	9.4
50°-60°	1189.1	8.2
60°-70°	879.0	6.0
70°-80°	497.3	3.4
80°-90°	138.2	0.9
90°-100°	151.9	1.0
100°-110°	482.7	3.3
110°-120°	826.1	5.7
120°-130°	1086.4	7.5
130°-140°	1219.5	8.4
140°-150°	1195.8	8.2
150°-160°	1003.1	6.9
160°-170°	665.3	4.6
170°-180°	232.5	1.6
0°-30°	2259.8	15.5
0°-40°	3625.1	24.9
0°-60°	6177.8	42.4
0°-90°	7692.3	52.8
90°-120°	1460.7	10.0
90°-150°	4962.4	34.1
90°-180°	6863.0	47.2
0°-180°	14555.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	133
90°	2	27	72	68	70	14
95°	108	129	132	132	129	120
105°	446	452	456	460	460	470
115°	829	841	837	835	829	820
125°	1206	1224	1218	1212	1210	1077
135°	1560	1582	1587	1585	1579	1205
145°	1893	1908	1920	1922	1914	1183
155°	2165	2171	2178	2188	2181	997
165°	2355	2353	2353	2368	2357	664
175°	2451	2445	2440	2455	2443	233
180°	2455	2455	2455	2455	2455	



TEST NUMBER: P912160

CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	2.2	26.6	72.5	68.1	70.3
92.5°	45.9	62.2	64.4	66.7	66.7
95°	108.0	128.8	132.5	132.5	128.8
97.5°	179.9	199.1	207.3	207.3	207.3
100°	262.7	279.8	285.7	285.7	283.5
102.5°	350.1	362.6	370.8	373.1	370.8
105°	445.6	451.5	455.9	459.7	459.7
107.5°	540.3	549.2	549.2	550.7	540.3
110°	632.1	644.0	644.0	644.0	638.0



TEST NUMBER: P912160

CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	731.3	743.9	741.7	735.7	731.3
115°	829.0	840.8	837.2	835.0	829.0
117.5°	925.9	942.2	931.9	925.9	920.0
120°	1023.6	1039.9	1023.6	1023.6	1017.0
122.5°	1112.4	1133.2	1122.9	1116.9	1112.4
125°	1205.7	1224.2	1218.3	1211.7	1209.5
127.5°	1296.8	1319.7	1311.6	1302.7	1296.8
130°	1381.9	1408.5	1404.9	1400.4	1392.2
132.5°	1477.4	1498.1	1499.6	1489.3	1483.3
135°	1559.6	1582.4	1587.0	1584.7	1578.8
137.5°	1651.3	1669.8	1673.5	1672.0	1663.2
140°	1732.0	1750.6	1760.9	1760.9	1752.8
142.5°	1814.9	1833.4	1839.3	1841.5	1833.4
145°	1893.4	1908.1	1920.0	1922.2	1914.1
147.5°	1963.7	1982.2	1991.1	1994.8	1986.7
150°	2036.2	2048.8	2057.0	2063.6	2057.0
152.5°	2100.6	2113.2	2123.5	2131.7	2123.5
155°	2165.0	2170.9	2177.6	2187.9	2181.3
157.5°	2220.6	2225.0	2228.6	2243.5	2233.1
160°	2270.1	2274.6	2276.8	2289.3	2280.4
162.5°	2316.0	2316.0	2318.3	2332.2	2321.9
165°	2355.2	2353.0	2353.0	2367.8	2357.4
167.5°	2390.8	2384.1	2384.1	2398.9	2388.6
170°	2417.4	2411.5	2409.3	2424.1	2411.5
172.5°	2435.9	2429.9	2427.7	2442.6	2429.9
175°	2450.7	2444.8	2440.4	2455.1	2442.6
177.5°	2458.9	2452.9	2448.5	2461.1	2448.5
180°	2455.1	2455.1	2455.1	2455.1	2455.1



TEST NUMBER: P912160
 CATALOG NUMBER: DFN2DIP-SQ4F0-070D070US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.15	11.04	11.08	11.99	13.22	9.71	10.60	10.64	11.55	12.78
	3H	11.82	12.62	12.76	13.57	14.83	11.33	12.12	12.27	13.08	14.34
	4H	12.41	13.16	13.37	14.13	15.39	11.92	12.67	12.87	13.63	14.90
	6H	12.82	13.51	13.79	14.48	15.75	12.32	13.01	13.28	13.98	15.25
	8H	12.92	13.58	13.90	14.57	15.84	12.42	13.08	13.40	14.07	15.34
	12H	12.97	13.60	13.96	14.58	15.88	12.46	13.09	13.45	14.07	15.37
4H	2H	10.62	11.37	11.58	12.33	13.60	10.26	11.02	11.23	11.98	13.24
	3H	12.49	13.12	13.46	14.11	15.39	12.08	12.71	13.06	13.70	14.98
	4H	13.21	13.78	14.19	14.77	16.07	12.79	13.36	13.77	14.35	15.65
	6H	13.73	14.23	14.72	15.24	16.53	13.30	13.79	14.29	14.80	16.10
	8H	13.88	14.35	14.88	15.35	16.66	13.45	13.91	14.44	14.91	16.22
	12H	13.96	14.38	14.97	15.40	16.72	13.51	13.93	14.52	14.95	16.27
8H	4H	13.41	13.87	14.40	14.87	16.19	13.03	13.49	14.03	14.50	15.81
	6H	14.05	14.43	15.07	15.47	16.78	13.66	14.04	14.68	15.09	16.40
	8H	14.27	14.61	15.30	15.64	16.97	13.88	14.21	14.91	15.25	16.58
	12H	14.41	14.70	15.44	15.73	17.10	13.99	14.29	15.03	15.32	16.69
12H	4H	13.40	13.81	14.41	14.83	16.15	13.03	13.45	14.04	14.46	15.78
	6H	14.08	14.41	15.11	15.45	16.78	13.70	14.04	14.73	15.07	16.40
	8H	14.32	14.62	15.36	15.65	17.02	13.94	14.24	14.98	15.27	16.64