

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917718

Luminaire Tested: DFN2DIP-SQ4F0-090D160US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917718
REPORT IS A COMBINATION OF REPORTS P900210 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D160US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17782.5 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 204.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917718

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US930-RLFL

Luminous Intensity Polar Plot



TEST NUMBER: P917718

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	28	27
4	73	62	55	49	65	57	50	45	46	41	38	36	33	31	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2128	2128	2128
5°	2131	2095	2108
10°	2110	2054	2040
15°	2081	1986	1935
20°	2043	1893	1805
25°	2003	1789	1680
30°	1950	1681	1521
35°	1899	1566	1381
40°	1846	1447	1221
45°	1785	1314	1075
50°	1721	1181	933
55°	1655	1038	797
60°	1579	888	657
65°	1491	736	592
70°	1384	594	536
75°	1250	525	489
80°	1056	441	426
85°	735	297	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3246 cd/sqm

TEST NUMBER: P917718

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	1.6
10°-20°	780.3	4.4
20°-30°	1095.5	6.2
30°-40°	1194.1	6.7
40°-50°	1097.5	6.2
50°-60°	861.9	4.8
60°-70°	561.0	3.2
70°-80°	288.8	1.6
80°-90°	85.4	0.5
90°-100°	255.3	1.4
100°-110°	811.2	4.6
110°-120°	1388.2	7.8
120°-130°	1825.7	10.3
130°-140°	2049.3	11.5
140°-150°	2009.6	11.3
150°-160°	1685.7	9.5
160°-170°	1117.9	6.3
170°-180°	390.8	2.2
0°-30°	2159.9	12.1
0°-40°	3354.0	18.9
0°-60°	5313.5	29.9
0°-90°	6248.8	35.1
90°-120°	2454.7	13.8
90°-150°	8339.3	46.9
90°-180°	11534.0	64.9
0°-180°	17782.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3033	3033	3033	3033	3033	
5°	3033	3019	2983	3008	3000	288
15°	2884	2854	2761	2709	2682	813
25°	2618	2530	2349	2237	2196	1204
35°	2256	2116	1875	1702	1641	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	947	724	478	384	376	939
75°	505	313	220	200	198	534
85°	118	60	52	52	52	135
90°	4	45	122	114	118	18
95°	182	216	223	223	216	202
105°	749	759	766	772	772	790
115°	1393	1413	1407	1403	1393	1378
125°	2026	2057	2047	2036	2032	1811
135°	2621	2659	2667	2663	2653	2026
145°	3182	3207	3226	3230	3217	1988
155°	3638	3648	3659	3677	3666	1675
165°	3958	3954	3954	3979	3962	1117
175°	4118	4108	4101	4126	4105	391
180°	4126	4126	4126	4126	4126	

TEST NUMBER: P917718

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3032.7	3032.7	3032.7	3032.7	3032.7
2.5°	3046.4	3032.7	3002.3	3030.1	3024.5
5°	3032.7	3019.0	2983.2	3007.9	2999.7
7.5°	3007.9	2991.6	2953.2	2963.9	2950.2
10°	2975.0	2955.8	2901.1	2892.6	2876.3
12.5°	2933.9	2909.2	2835.0	2818.6	2788.3
15°	2884.4	2854.2	2761.0	2708.8	2681.5
17.5°	2826.8	2782.9	2667.5	2607.2	2563.3
20°	2761.0	2706.0	2568.8	2500.4	2439.8
22.5°	2689.7	2626.5	2467.2	2374.0	2333.0
25°	2618.3	2530.4	2349.3	2236.9	2195.5
27.5°	2533.3	2439.8	2239.5	2110.5	2047.3
30°	2442.7	2338.2	2118.6	1978.9	1904.6
32.5°	2354.7	2228.4	2003.6	1838.8	1770.1
35°	2256.1	2116.0	1874.6	1701.7	1641.1
37.5°	2160.0	2008.9	1753.8	1564.2	1495.8
40°	2058.4	1893.9	1627.4	1432.6	1361.3
42.5°	1954.1	1778.6	1501.3	1298.1	1229.6
45°	1844.4	1660.4	1372.3	1177.2	1111.4
47.5°	1740.1	1545.3	1248.9	1053.8	993.5
50°	1624.8	1430.0	1128.0	938.5	881.1
52.5°	1512.1	1306.3	1012.8	831.6	779.5
55°	1402.3	1188.3	891.9	727.4	675.2
57.5°	1290.0	1070.4	785.1	631.3	587.3
60°	1174.6	955.0	672.4	532.6	488.6
62.5°	1062.3	842.7	576.3	444.7	422.8
65°	946.9	724.5	477.5	384.3	375.9
67.5°	837.1	614.7	384.3	337.5	329.3
70°	721.9	507.8	318.3	290.9	279.8
72.5°	612.0	408.8	266.1	244.3	238.8
75°	504.9	312.7	219.6	200.3	197.7
77.5°	398.0	222.2	172.9	161.9	156.4
80°	299.1	159.3	131.6	120.8	120.8
82.5°	208.5	107.1	90.6	85.0	85.0
85°	117.9	60.3	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	3.8	44.8	121.9	114.5	118.1
92.5°	77.1	104.5	108.2	111.9	111.9
95°	181.6	216.5	222.7	222.7	216.5
97.5°	302.2	334.6	348.3	348.3	348.3
100°	441.6	470.2	480.1	480.1	476.4
102.5°	588.3	609.5	623.1	626.9	623.1
105°	748.8	758.7	766.2	772.4	772.4
107.5°	908.0	922.9	922.9	925.4	908.0
110°	1062.3	1082.1	1082.1	1082.1	1072.2

TEST NUMBER: P917718

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1228.9	1250.1	1246.3	1236.4	1228.9
115°	1393.1	1413.0	1406.8	1403.0	1393.1
117.5°	1556.1	1583.4	1566.0	1556.1	1546.1
120°	1720.3	1747.6	1720.3	1720.3	1709.0
122.5°	1869.5	1904.4	1886.9	1877.0	1869.5
125°	2026.3	2057.3	2047.4	2036.2	2032.5
127.5°	2179.2	2217.8	2204.1	2189.2	2179.2
130°	2322.3	2367.1	2360.9	2353.4	2339.7
132.5°	2482.7	2517.6	2520.0	2502.6	2492.7
135°	2620.8	2659.3	2666.8	2663.1	2653.1
137.5°	2775.0	2806.1	2812.4	2809.8	2794.9
140°	2910.6	2941.7	2959.1	2959.1	2945.4
142.5°	3049.9	3081.0	3091.0	3094.7	3081.0
145°	3181.8	3206.6	3226.5	3230.3	3216.6
147.5°	3299.9	3331.1	3346.0	3352.2	3338.5
150°	3421.8	3443.0	3456.7	3467.9	3456.7
152.5°	3530.1	3551.2	3568.6	3582.3	3568.6
155°	3638.3	3648.2	3659.4	3676.8	3665.7
157.5°	3731.5	3739.0	3745.2	3770.1	3752.7
160°	3814.9	3822.4	3826.1	3847.2	3832.3
162.5°	3892.0	3892.0	3895.7	3919.4	3901.9
165°	3957.9	3954.2	3954.2	3979.1	3961.7
167.5°	4017.6	4006.5	4006.5	4031.3	4013.9
170°	4062.4	4052.4	4048.8	4073.6	4052.4
172.5°	4093.5	4083.6	4079.8	4104.7	4083.6
175°	4118.4	4108.5	4101.0	4125.9	4104.7
177.5°	4132.1	4122.1	4114.6	4135.8	4114.6
180°	4125.9	4125.9	4125.9	4125.9	4125.9

TEST NUMBER: P917718

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.21	8.93	9.29	10.01	11.48	4.17	4.89	5.25	5.97	7.44
	3H	9.88	10.53	10.97	11.62	13.10	5.35	6.00	6.44	7.08	8.57
	4H	10.49	11.10	11.59	12.19	13.68	5.80	6.41	6.90	7.50	8.99
	6H	10.91	11.47	12.02	12.56	14.07	6.11	6.68	7.22	7.77	9.27
	8H	11.04	11.57	12.15	12.68	14.18	6.20	6.74	7.31	7.84	9.34
	12H	11.10	11.60	12.21	12.70	14.23	6.24	6.75	7.36	7.85	9.37
4H	2H	8.22	8.83	9.32	9.91	11.41	4.76	5.37	5.86	6.45	7.95
	3H	10.04	10.55	11.15	11.66	13.17	6.10	6.61	7.21	7.72	9.23
	4H	10.73	11.20	11.85	12.30	13.83	6.64	7.11	7.76	8.21	9.74
	6H	11.24	11.64	12.37	12.77	14.29	7.06	7.46	8.18	8.58	10.10
	8H	11.42	11.79	12.54	12.91	14.45	7.18	7.56	8.31	8.67	10.21
	12H	11.51	11.85	12.65	12.98	14.52	7.24	7.58	8.38	8.71	10.25
8H	4H	10.69	11.06	11.81	12.18	13.72	6.92	7.29	8.04	8.41	9.94
	6H	11.26	11.57	12.40	12.73	14.26	7.43	7.74	8.58	8.90	10.43
	8H	11.48	11.75	12.63	12.89	14.44	7.62	7.89	8.77	9.03	10.59
	12H	11.61	11.85	12.77	12.99	14.58	7.74	7.97	8.89	9.11	10.70
12H	4H	10.64	10.98	11.78	12.11	13.65	6.92	7.25	8.06	8.39	9.93
	6H	11.23	11.50	12.38	12.64	14.20	7.48	7.75	8.63	8.89	10.44
	8H	11.45	11.69	12.61	12.83	14.41	7.69	7.92	8.84	9.06	10.65