

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917723

Luminaire Tested: DFN2DIP-SQ4F0-100D060US930-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P917723  
REPORT IS A COMBINATION OF REPORTS P901588 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-100D060US930-RLLONL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11772.9 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 137.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P917723  
CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US930-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P917723

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US930-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55	51			
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48	43			
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37			
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26			
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19			
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2364	2364	2364
5°	2368	2327	2342
10°	2345	2282	2267
15°	2312	2207	2150
20°	2270	2104	2006
25°	2226	1987	1866
30°	2167	1868	1690
35°	2109	1740	1534
40°	2051	1608	1356
45°	1983	1460	1195
50°	1912	1312	1037
55°	1839	1153	885
60°	1754	987	730
65°	1656	818	658
70°	1538	660	596
75°	1389	583	544
80°	1173	491	474
85°	816	330	361

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1983 cd/sqm



TEST NUMBER: P917723

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US930-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	315.8	2.7
10°-20°	866.9	7.4
20°-30°	1217.2	10.3
30°-40°	1326.8	11.3
40°-50°	1219.5	10.4
50°-60°	957.7	8.1
60°-70°	623.4	5.3
70°-80°	320.9	2.7
80°-90°	84.8	0.7
90°-100°	54.4	0.5
100°-110°	202.9	1.7
110°-120°	538.2	4.6
120°-130°	892.7	7.6
130°-140°	948.2	8.1
140°-150°	881.3	7.5
150°-160°	708.5	6.0
160°-170°	456.5	3.9
170°-180°	157.1	1.3
0°-30°	2399.9	20.4
0°-40°	3726.7	31.7
0°-60°	5903.9	50.1
0°-90°	6933.0	58.9
90°-120°	795.6	6.8
90°-150°	3517.8	29.9
90°-180°	4840.0	41.1
0°-180°	11772.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3370	3370	3370	3370	3370	
5°	3370	3354	3315	3342	3333	320
15°	3205	3171	3068	3010	2979	903
25°	2909	2812	2610	2485	2440	1338
35°	2507	2351	2083	1891	1823	1569
45°	2049	1845	1525	1308	1235	1583
55°	1558	1320	991	808	750	1392
65°	1052	805	531	427	418	1043
75°	561	348	244	223	220	593
85°	131	67	58	58	58	150
90°	1	14	24	30	32	11
95°	78	38	47	53	51	92
105°	363	399	73	86	91	388
115°	687	707	737	184	98	676
125°	971	987	1009	1018	1021	866
135°	1202	1221	1232	1244	1241	928
145°	1394	1393	1413	1422	1416	872
155°	1535	1524	1539	1546	1536	707
165°	1618	1610	1614	1622	1614	457
175°	1654	1646	1648	1657	1645	157
180°	1651	1651	1651	1651	1651	



TEST NUMBER: P917723

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US930-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3369.6	3369.6	3369.6	3369.6	3369.6
2.5°	3384.8	3369.6	3336.0	3366.7	3360.6
5°	3369.6	3354.4	3314.6	3342.2	3333.0
7.5°	3342.2	3324.0	3281.2	3293.2	3278.1
10°	3305.5	3284.2	3223.4	3214.0	3195.9
12.5°	3260.0	3232.4	3149.9	3131.8	3098.1
15°	3204.9	3171.3	3067.7	3009.8	2979.4
17.5°	3140.9	3092.0	2963.9	2896.9	2848.1
20°	3067.7	3006.6	2854.2	2778.2	2710.9
22.5°	2988.5	2918.3	2741.3	2637.8	2592.2
25°	2909.2	2811.6	2610.3	2485.4	2439.5
27.5°	2814.7	2710.9	2488.3	2345.0	2274.8
30°	2714.1	2597.9	2354.0	2198.8	2116.3
32.5°	2616.5	2476.0	2226.3	2043.1	1966.7
35°	2506.7	2351.2	2082.9	1890.8	1823.4
37.5°	2400.0	2232.0	1948.6	1738.1	1662.0
40°	2287.1	2104.3	1808.2	1591.8	1512.5
42.5°	2171.2	1976.1	1668.2	1442.3	1366.3
45°	2049.3	1844.8	1524.9	1308.1	1234.9
47.5°	1933.5	1717.0	1387.6	1170.8	1103.9
50°	1805.3	1588.9	1253.4	1042.8	979.0
52.5°	1680.1	1451.4	1125.3	924.0	866.1
55°	1558.1	1320.4	991.0	808.2	750.2
57.5°	1433.3	1189.3	872.3	701.4	652.6
60°	1305.1	1061.2	747.1	591.7	542.9
62.5°	1180.2	936.3	640.3	494.1	469.8
65°	1052.1	804.9	530.6	427.1	417.7
67.5°	930.2	683.0	427.1	375.0	365.9
70°	802.0	564.3	353.6	323.2	311.0
72.5°	680.0	454.2	295.7	271.4	265.3
75°	561.0	347.5	243.9	222.6	219.6
77.5°	442.3	246.9	192.2	179.9	173.7
80°	332.2	177.0	146.3	134.3	134.3
82.5°	231.6	119.0	100.6	94.5	94.5
85°	131.0	66.9	57.9	57.9	57.9
87.5°	48.8	24.3	24.3	21.4	21.4
90°	1.1	14.3	23.8	29.9	32.2
92.5°	29.9	25.1	28.6	31.1	32.2
95°	77.6	38.2	46.6	52.7	51.4
97.5°	139.7	41.8	60.8	64.6	65.7
100°	211.5	47.8	68.1	77.6	80.0
102.5°	290.2	288.0	70.5	83.6	87.2
105°	363.1	399.0	72.9	85.9	90.8
107.5°	448.0	477.8	75.3	88.4	93.2
110°	529.3	554.2	209.1	89.7	94.3



TEST NUMBER: P917723

CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US930-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	605.7	627.1	606.8	91.9	95.6
115°	686.9	707.2	737.1	184.0	98.0
117.5°	757.3	781.2	801.6	630.7	317.7
120°	836.3	854.1	875.7	890.0	728.7
122.5°	903.0	922.2	946.2	953.2	954.6
125°	971.2	986.8	1009.4	1017.8	1021.3
127.5°	1033.3	1050.0	1068.0	1079.9	1081.1
130°	1091.8	1111.0	1124.1	1137.3	1136.1
132.5°	1151.6	1167.2	1180.2	1191.0	1189.8
135°	1201.8	1221.0	1231.6	1243.7	1241.2
137.5°	1254.3	1268.6	1280.7	1292.6	1289.1
140°	1305.6	1315.3	1328.4	1339.1	1333.2
142.5°	1348.7	1357.1	1372.6	1382.1	1376.1
145°	1394.2	1392.9	1413.2	1421.6	1415.6
147.5°	1433.5	1429.9	1450.2	1456.1	1451.5
150°	1471.8	1463.4	1482.5	1489.6	1483.7
152.5°	1504.0	1494.4	1512.3	1519.6	1511.2
155°	1535.0	1524.4	1538.7	1545.8	1536.3
157.5°	1560.2	1550.6	1561.4	1569.8	1560.2
160°	1581.7	1574.4	1581.7	1588.8	1580.5
162.5°	1600.7	1593.6	1599.5	1607.9	1597.2
165°	1617.5	1610.4	1613.9	1622.3	1613.9
167.5°	1630.6	1623.4	1627.1	1635.5	1624.6
170°	1641.4	1634.2	1636.6	1644.9	1634.2
172.5°	1648.5	1641.4	1643.8	1652.2	1641.4
175°	1654.5	1646.1	1648.5	1656.8	1644.9
177.5°	1656.8	1648.5	1649.8	1658.2	1647.4
180°	1650.9	1650.9	1650.9	1650.9	1650.9



TEST NUMBER: P917723  
 CATALOG NUMBER: DFN2DIP-SQ4F0-100D060US930-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.94	11.85	11.83	12.75	13.89	6.90	7.81	7.79	8.71	9.85
	3H	12.63	13.44	13.53	14.35	15.52	8.10	8.91	8.99	9.82	10.99
	4H	13.24	14.01	14.16	14.93	16.10	8.55	9.32	9.46	10.23	11.41
	6H	13.67	14.38	14.60	15.30	16.49	8.88	9.58	9.80	10.50	11.69
	8H	13.80	14.48	14.74	15.41	16.60	8.97	9.64	9.90	10.58	11.77
	12H	13.87	14.51	14.81	15.44	16.65	9.02	9.66	9.95	10.59	11.80
4H	2H	10.97	11.74	11.89	12.65	13.83	7.51	8.28	8.43	9.19	10.37
	3H	12.81	13.45	13.74	14.39	15.58	8.87	9.50	9.79	10.45	11.64
	4H	13.51	14.09	14.45	15.03	16.25	9.42	10.00	10.36	10.94	12.16
	6H	14.03	14.53	14.98	15.50	16.71	9.84	10.34	10.79	11.31	12.52
	8H	14.21	14.68	15.16	15.64	16.87	9.97	10.44	10.93	11.40	12.63
	12H	14.31	14.73	15.28	15.71	16.94	10.04	10.46	11.02	11.44	12.67
8H	4H	13.48	13.95	14.44	14.91	16.14	9.71	10.17	10.66	11.13	12.36
	6H	14.06	14.44	15.03	15.44	16.67	10.23	10.62	11.21	11.62	12.84
	8H	14.28	14.62	15.26	15.61	16.85	10.42	10.76	11.41	11.75	13.00
	12H	14.42	14.72	15.41	15.70	17.00	10.55	10.85	11.54	11.83	13.12
12H	4H	13.44	13.86	14.41	14.83	16.07	9.72	10.14	10.69	11.11	12.35
	6H	14.03	14.37	15.02	15.36	16.61	10.28	10.62	11.27	11.61	12.86
	8H	14.26	14.56	15.25	15.54	16.84	10.50	10.80	11.49	11.78	13.07