

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917730

Luminaire Tested: DFN2DIP-SQ4F0-100D080US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917730
REPORT IS A COMBINATION OF REPORTS P900104 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D080US930-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12702.4 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 152.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917730

CATALOG NUMBER: DFN2DIP-SQ4F0-100D080US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917730

CATALOG NUMBER: DFN2DIP-SQ4F0-100D080US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		86	86	86		73	73	73		60	60	60
1	99	95	91	88		92	89	85	82		76	74	72		65	63	62		54	53	52
2	91	84	78	73		84	78	73	69		67	63	60		57	55	52		48	46	45
3	83	74	67	61		77	69	63	58		60	55	51		51	48	45		43	41	39
4	76	66	58	52		71	62	55	50		54	48	44		46	42	39		39	36	34
5	70	59	51	45		65	55	48	43		48	43	38		42	37	34		35	32	30
6	65	53	45	40		60	50	43	38		44	38	34		38	33	30		32	29	26
7	60	48	40	35		56	45	38	33		40	34	30		35	30	27		30	26	24
8	56	44	36	31		52	41	34	30		36	31	27		32	27	24		27	24	21
9	52	40	33	28		49	38	31	27		34	28	24		29	25	22		25	22	19
10	49	37	30	25		46	35	28	24		31	26	22		27	23	20		24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2364	2364	2364
5°	2368	2327	2342
10°	2345	2282	2267
15°	2312	2207	2150
20°	2270	2104	2006
25°	2226	1987	1866
30°	2167	1868	1690
35°	2109	1740	1534
40°	2051	1608	1356
45°	1983	1460	1195
50°	1912	1312	1037
55°	1839	1153	885
60°	1754	987	730
65°	1656	818	658
70°	1538	660	596
75°	1389	583	544
80°	1173	491	474
85°	816	330	361

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1983 cd/sqm

TEST NUMBER: P917730

CATALOG NUMBER: DFN2DIP-SQ4F0-100D080US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.8	2.5
10°-20°	866.9	6.8
20°-30°	1217.2	9.6
30°-40°	1326.8	10.4
40°-50°	1219.5	9.6
50°-60°	957.7	7.5
60°-70°	623.4	4.9
70°-80°	320.9	2.5
80°-90°	87.8	0.7
90°-100°	127.6	1.0
100°-110°	405.6	3.2
110°-120°	694.1	5.5
120°-130°	912.8	7.2
130°-140°	1024.6	8.1
140°-150°	1004.7	7.9
150°-160°	842.8	6.6
160°-170°	558.9	4.4
170°-180°	195.4	1.5
0°-30°	2399.9	18.9
0°-40°	3726.7	29.3
0°-60°	5903.9	46.5
0°-90°	6935.9	54.6
90°-120°	1227.3	9.7
90°-150°	4169.4	32.8
90°-180°	5766.0	45.4
0°-180°	12702.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3370	3370	3370	3370	3370	
5°	3370	3354	3315	3342	3333	320
15°	3205	3171	3068	3010	2979	903
25°	2909	2812	2610	2485	2440	1338
35°	2507	2351	2083	1891	1823	1569
45°	2049	1845	1525	1308	1235	1583
55°	1558	1320	991	808	750	1392
65°	1052	805	531	427	418	1043
75°	561	348	244	223	220	593
85°	131	67	58	58	58	150
90°	2	22	61	57	59	12
95°	91	108	111	111	108	101
105°	374	379	383	386	386	395
115°	696	706	703	702	696	689
125°	1013	1029	1024	1018	1016	905
135°	1310	1330	1333	1332	1326	1013
145°	1591	1603	1613	1615	1608	994
155°	1819	1824	1830	1838	1833	837
165°	1979	1977	1977	1989	1981	558
175°	2059	2054	2050	2063	2052	196
180°	2063	2063	2063	2063	2063	

TEST NUMBER: P917730

CATALOG NUMBER: DFN2DIP-SQ4F0-100D080US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3369.6	3369.6	3369.6	3369.6	3369.6
2.5°	3384.8	3369.6	3336.0	3366.7	3360.6
5°	3369.6	3354.4	3314.6	3342.2	3333.0
7.5°	3342.2	3324.0	3281.2	3293.2	3278.1
10°	3305.5	3284.2	3223.4	3214.0	3195.9
12.5°	3260.0	3232.4	3149.9	3131.8	3098.1
15°	3204.9	3171.3	3067.7	3009.8	2979.4
17.5°	3140.9	3092.0	2963.9	2896.9	2848.1
20°	3067.7	3006.6	2854.2	2778.2	2710.9
22.5°	2988.5	2918.3	2741.3	2637.8	2592.2
25°	2909.2	2811.6	2610.3	2485.4	2439.5
27.5°	2814.7	2710.9	2488.3	2345.0	2274.8
30°	2714.1	2597.9	2354.0	2198.8	2116.3
32.5°	2616.5	2476.0	2226.3	2043.1	1966.7
35°	2506.7	2351.2	2082.9	1890.8	1823.4
37.5°	2400.0	2232.0	1948.6	1738.1	1662.0
40°	2287.1	2104.3	1808.2	1591.8	1512.5
42.5°	2171.2	1976.1	1668.2	1442.3	1366.3
45°	2049.3	1844.8	1524.9	1308.1	1234.9
47.5°	1933.5	1717.0	1387.6	1170.8	1103.9
50°	1805.3	1588.9	1253.4	1042.8	979.0
52.5°	1680.1	1451.4	1125.3	924.0	866.1
55°	1558.1	1320.4	991.0	808.2	750.2
57.5°	1433.3	1189.3	872.3	701.4	652.6
60°	1305.1	1061.2	747.1	591.7	542.9
62.5°	1180.2	936.3	640.3	494.1	469.8
65°	1052.1	804.9	530.6	427.1	417.7
67.5°	930.2	683.0	427.1	375.0	365.9
70°	802.0	564.3	353.6	323.2	311.0
72.5°	680.0	454.2	295.7	271.4	265.3
75°	561.0	347.5	243.9	222.6	219.6
77.5°	442.3	246.9	192.2	179.9	173.7
80°	332.2	177.0	146.3	134.3	134.3
82.5°	231.6	119.0	100.6	94.5	94.5
85°	131.0	66.9	57.9	57.9	57.9
87.5°	48.8	24.3	24.3	21.4	21.4
90°	1.9	22.4	61.0	57.2	59.1
92.5°	38.6	52.3	54.1	55.9	55.9
95°	90.8	108.2	111.3	111.3	108.2
97.5°	151.2	167.3	174.1	174.1	174.1
100°	220.8	235.1	240.0	240.0	238.1
102.5°	294.2	304.8	311.5	313.4	311.5
105°	374.4	379.4	383.1	386.2	386.2
107.5°	454.0	461.5	461.5	462.7	454.0
110°	531.1	541.0	541.0	541.0	536.1

TEST NUMBER: P917730

CATALOG NUMBER: DFN2DIP-SQ4F0-100D080US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	614.4	625.0	623.1	618.2	614.4
115°	696.5	706.5	703.4	701.5	696.5
117.5°	778.0	791.7	782.9	778.0	773.0
120°	860.1	873.8	860.1	860.1	854.4
122.5°	934.7	952.1	943.4	938.4	934.7
125°	1013.0	1028.6	1023.6	1018.0	1016.2
127.5°	1089.6	1108.8	1102.0	1094.5	1089.6
130°	1161.1	1183.4	1180.3	1176.6	1169.8
132.5°	1241.3	1258.7	1260.0	1251.2	1246.3
135°	1310.3	1329.6	1333.3	1331.5	1326.5
137.5°	1387.4	1403.0	1406.1	1404.8	1397.3
140°	1455.2	1470.7	1479.4	1479.4	1472.6
142.5°	1524.9	1540.4	1545.4	1547.3	1540.4
145°	1590.8	1603.2	1613.1	1615.0	1608.2
147.5°	1649.8	1665.4	1672.8	1676.0	1669.2
150°	1710.8	1721.3	1728.2	1733.8	1728.2
152.5°	1764.9	1775.5	1784.2	1791.0	1784.2
155°	1819.0	1824.0	1829.6	1838.3	1832.7
157.5°	1865.6	1869.4	1872.5	1884.9	1876.2
160°	1907.3	1911.1	1912.9	1923.5	1916.0
162.5°	1945.9	1945.9	1947.7	1959.6	1950.8
165°	1978.8	1976.9	1976.9	1989.4	1980.7
167.5°	2008.7	2003.1	2003.1	2015.5	2006.8
170°	2031.1	2026.1	2024.2	2036.7	2026.1
172.5°	2046.6	2041.7	2039.8	2052.2	2041.7
175°	2059.0	2054.1	2050.3	2062.8	2052.2
177.5°	2065.9	2060.9	2057.2	2067.8	2057.2
180°	2062.8	2062.8	2062.8	2062.8	2062.8

TEST NUMBER: P917730

CATALOG NUMBER: DFN2DIP-SQ4F0-100D080US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.57	11.44	11.49	12.37	13.58	6.53	7.40	7.45	8.33	9.54
	3H	12.25	13.03	13.19	13.98	15.21	7.72	8.50	8.66	9.44	10.68
	4H	12.87	13.60	13.82	14.55	15.79	8.17	8.91	9.12	9.86	11.10
	6H	13.29	13.97	14.25	14.93	16.18	8.50	9.17	9.46	10.13	11.38
	8H	13.42	14.07	14.39	15.04	16.29	8.59	9.23	9.56	10.21	11.46
	12H	13.49	14.10	14.46	15.07	16.34	8.63	9.25	9.61	10.21	11.49
4H	2H	10.59	11.33	11.55	12.28	13.52	7.13	7.87	8.09	8.82	10.06
	3H	12.43	13.04	13.39	14.02	15.27	8.49	9.10	9.45	10.08	11.33
	4H	13.13	13.68	14.10	14.66	15.94	9.04	9.59	10.01	10.57	11.85
	6H	13.65	14.13	14.63	15.12	16.40	9.46	9.94	10.44	10.94	12.21
	8H	13.83	14.27	14.81	15.26	16.56	9.59	10.04	10.58	11.03	12.32
	12H	13.92	14.33	14.93	15.34	16.63	9.66	10.06	10.66	11.07	12.36
8H	4H	13.10	13.54	14.08	14.54	15.83	9.32	9.77	10.31	10.76	12.05
	6H	13.67	14.04	14.68	15.07	16.36	9.84	10.21	10.86	11.25	12.53
	8H	13.89	14.21	14.91	15.23	16.54	10.04	10.36	11.06	11.38	12.69
	12H	14.03	14.32	15.06	15.33	16.69	10.16	10.44	11.18	11.46	12.81
12H	4H	13.05	13.45	14.06	14.46	15.76	9.33	9.73	10.34	10.74	12.04
	6H	13.64	13.97	14.67	14.99	16.30	9.89	10.22	10.91	11.24	12.55
	8H	13.87	14.16	14.89	15.17	16.52	10.11	10.39	11.13	11.41	12.76