

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917828

Luminaire Tested: DFN2DIP-SQ4F0-140D060US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917828
REPORT IS A COMBINATION OF REPORTS P900073 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D060US930-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15629.3 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917828

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917828

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US930-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	66	65
2	94	86	80	74	89	82	76	71	74	69	65	66	63	60	60	57	55
3	85	76	68	62	81	72	65	60	65	60	55	59	54	51	53	49	46
4	78	67	59	52	74	64	56	51	58	52	47	52	48	44	47	43	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	27
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3116	3116	3116
5°	3121	3074	3095
10°	3096	3033	3053
15°	3050	2983	2989
20°	2989	2915	2923
25°	2928	2832	2846
30°	2851	2756	2748
35°	2778	2665	2645
40°	2689	2574	2547
45°	2599	2483	2446
50°	2502	2387	2330
55°	2400	2276	2223
60°	2284	2144	2101
65°	2158	2007	1956
70°	1998	1841	1801
75°	1775	1642	1660
80°	1508	1389	1386
85°	1090	950	932

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2599 cd/sqm

TEST NUMBER: P917828

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	418.0	2.7
10°-20°	1176.1	7.5
20°-30°	1728.5	11.1
30°-40°	2007.5	12.8
40°-50°	2005.0	12.8
50°-60°	1748.3	11.2
60°-70°	1292.4	8.3
70°-80°	731.2	4.7
80°-90°	197.4	1.3
90°-100°	95.7	0.6
100°-110°	304.2	1.9
110°-120°	520.6	3.3
120°-130°	684.6	4.4
130°-140°	768.4	4.9
140°-150°	753.5	4.8
150°-160°	632.1	4.0
160°-170°	419.2	2.7
170°-180°	146.5	0.9
0°-30°	3322.6	21.3
0°-40°	5330.1	34.1
0°-60°	9083.5	58.1
0°-90°	11304.4	72.3
90°-120°	920.5	5.9
90°-150°	3127.0	20.0
90°-180°	4325.0	27.7
0°-180°	15629.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4441	4441	4441	4441	4441	
5°	4441	4424	4377	4411	4403	422
15°	4228	4202	4147	4164	4143	1191
25°	3826	3792	3720	3728	3720	1761
35°	3301	3259	3190	3164	3143	2062
45°	2686	2657	2592	2546	2528	2073
55°	2033	2007	1956	1905	1884	1818
65°	1371	1345	1303	1264	1243	1356
75°	717	709	687	662	671	766
85°	175	171	167	154	150	195
90°	1	17	46	43	44	15
95°	68	81	84	84	81	76
105°	281	284	287	290	290	296
115°	522	530	528	526	522	517
125°	760	771	768	764	762	679
135°	983	997	1000	999	995	760
145°	1193	1202	1210	1211	1206	745
155°	1364	1368	1372	1379	1374	628
165°	1484	1483	1483	1492	1486	419
175°	1544	1541	1538	1547	1539	147
180°	1547	1547	1547	1547	1547	

TEST NUMBER: P917828

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4441.3	4441.3	4441.3	4441.3	4441.3
2.5°	4467.1	4445.8	4398.7	4441.3	4433.2
5°	4441.3	4424.5	4377.4	4411.4	4403.3
7.5°	4411.4	4386.1	4338.9	4373.3	4364.7
10°	4364.7	4334.9	4283.7	4317.7	4304.9
12.5°	4300.4	4275.0	4223.8	4245.1	4236.5
15°	4227.9	4202.5	4146.8	4164.1	4142.7
17.5°	4138.2	4112.9	4057.1	4078.4	4057.1
20°	4039.9	4014.5	3954.7	3967.4	3950.6
22.5°	3942.0	3903.5	3847.7	3847.7	3839.2
25°	3826.4	3792.4	3720.0	3728.1	3720.0
27.5°	3698.2	3668.4	3613.1	3600.4	3579.1
30°	3570.4	3536.0	3472.1	3459.5	3442.2
32.5°	3433.6	3408.3	3339.8	3314.0	3296.7
35°	3301.3	3258.7	3190.3	3164.5	3143.1
37.5°	3151.8	3113.3	3044.8	3015.0	2993.6
40°	2998.2	2963.8	2895.3	2857.3	2840.0
42.5°	2848.7	2814.2	2746.3	2703.2	2677.8
45°	2686.4	2656.6	2592.2	2545.5	2528.3
47.5°	2528.3	2498.4	2430.0	2382.9	2357.5
50°	2361.6	2340.3	2280.5	2220.6	2199.3
52.5°	2199.3	2169.4	2114.1	2067.0	2037.2
55°	2033.1	2007.3	1956.1	1904.9	1883.6
57.5°	1866.3	1845.0	1789.3	1738.1	1720.9
60°	1699.6	1682.9	1623.0	1575.9	1563.2
62.5°	1537.4	1507.5	1464.8	1422.3	1405.1
65°	1371.1	1345.2	1302.7	1264.1	1242.8
67.5°	1200.3	1178.5	1140.4	1110.5	1093.3
70°	1042.1	1024.9	986.4	956.5	939.7
72.5°	880.0	862.7	841.4	811.5	798.8
75°	717.3	709.1	687.4	662.0	670.6
77.5°	572.3	555.1	546.4	533.8	521.1
80°	427.3	422.7	414.2	401.5	392.8
82.5°	290.4	290.4	286.3	269.1	269.1
85°	174.9	170.8	166.7	153.6	149.5
87.5°	77.0	68.4	59.8	47.1	42.6
90°	1.4	16.8	45.7	42.9	44.3
92.5°	28.9	39.2	40.6	42.0	42.0
95°	68.1	81.1	83.5	83.5	81.1
97.5°	113.3	125.5	130.6	130.6	130.6
100°	165.6	176.3	180.0	180.0	178.6
102.5°	220.6	228.5	233.7	235.1	233.7
105°	280.8	284.5	287.3	289.7	289.7
107.5°	340.5	346.1	346.1	347.0	340.5
110°	398.4	405.8	405.8	405.8	402.0

TEST NUMBER: P917828

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.8	468.7	467.3	463.6	460.8
115°	522.4	529.9	527.5	526.1	522.4
117.5°	583.5	593.8	587.2	583.5	579.8
120°	645.1	655.3	645.1	645.1	640.8
122.5°	701.0	714.0	707.5	703.8	701.0
125°	759.8	771.4	767.7	763.5	762.1
127.5°	817.2	831.6	826.5	820.9	817.2
130°	870.8	887.6	885.3	882.5	877.3
132.5°	931.0	944.0	944.9	938.4	934.7
135°	982.8	997.2	1000.0	998.6	994.8
137.5°	1040.6	1052.2	1054.6	1053.6	1048.1
140°	1091.4	1103.1	1109.6	1109.6	1104.5
142.5°	1143.6	1155.3	1159.0	1160.4	1155.3
145°	1193.1	1202.4	1209.9	1211.3	1206.2
147.5°	1237.4	1249.0	1254.7	1256.9	1251.8
150°	1283.1	1291.0	1296.2	1300.3	1296.2
152.5°	1323.6	1331.6	1338.1	1343.3	1338.1
155°	1364.2	1368.0	1372.1	1378.8	1374.5
157.5°	1399.2	1402.1	1404.4	1413.7	1407.2
160°	1430.5	1433.3	1434.7	1442.6	1437.0
162.5°	1459.4	1459.4	1460.8	1469.7	1463.1
165°	1484.1	1482.7	1482.7	1492.1	1485.6
167.5°	1506.5	1502.4	1502.4	1511.6	1505.1
170°	1523.3	1519.6	1518.2	1527.5	1519.6
172.5°	1535.0	1531.2	1529.8	1539.1	1531.2
175°	1544.3	1540.6	1537.7	1547.1	1539.1
177.5°	1549.4	1545.7	1542.9	1550.8	1542.9
180°	1547.1	1547.1	1547.1	1547.1	1547.1

TEST NUMBER: P917828

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.08	14.18	13.82	14.94	15.86	12.63	13.74	13.37	14.50	15.41
	3H	14.76	15.76	15.51	16.52	17.47	14.27	15.26	15.02	16.03	16.98
	4H	15.36	16.30	16.13	17.08	18.03	14.87	15.81	15.64	16.59	17.54
	6H	15.78	16.64	16.56	17.43	18.40	15.28	16.14	16.06	16.93	17.90
	8H	15.89	16.72	16.69	17.52	18.50	15.39	16.22	16.18	17.02	17.99
	12H	15.95	16.74	16.75	17.54	18.54	15.44	16.23	16.24	17.03	18.03
4H	2H	13.57	14.51	14.34	15.29	16.24	13.21	14.15	13.99	14.93	15.89
	3H	15.46	16.25	16.25	17.06	18.03	15.05	15.84	15.84	16.65	17.62
	4H	16.19	16.90	16.99	17.72	18.72	15.77	16.48	16.57	17.29	18.29
	6H	16.72	17.34	17.54	18.18	19.18	16.29	16.91	17.11	17.75	18.75
	8H	16.88	17.46	17.70	18.29	19.31	16.44	17.02	17.26	17.85	18.87
	12H	16.97	17.49	17.81	18.34	19.37	16.52	17.04	17.36	17.89	18.92
8H	4H	16.41	16.98	17.23	17.82	18.83	16.03	16.61	16.85	17.44	18.46
	6H	17.05	17.53	17.90	18.41	19.42	16.67	17.15	17.52	18.02	19.04
	8H	17.28	17.70	18.14	18.57	19.61	16.89	17.31	17.75	18.18	19.22
	12H	17.42	17.80	18.29	18.66	19.75	17.01	17.39	17.88	18.25	19.34
12H	4H	16.40	16.92	17.25	17.78	18.80	16.04	16.55	16.88	17.41	18.43
	6H	17.08	17.51	17.95	18.38	19.42	16.71	17.14	17.57	18.01	19.05
	8H	17.34	17.72	18.21	18.58	19.67	16.96	17.34	17.83	18.20	19.29