

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912260

Luminaire Tested: DFN2DIP-SQ4F0-090D160US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912260
REPORT IS A COMBINATION OF REPORTS P900209 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D160US850-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25585.7 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 204.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912260

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912260

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	39
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	32
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	31	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2725	2725	2725
5°	2729	2688	2706
10°	2707	2652	2670
15°	2667	2609	2614
20°	2614	2549	2556
25°	2560	2477	2489
30°	2493	2410	2403
35°	2429	2331	2313
40°	2351	2251	2227
45°	2273	2171	2139
50°	2188	2087	2037
55°	2098	1990	1944
60°	1997	1874	1837
65°	1887	1755	1711
70°	1747	1610	1575
75°	1553	1436	1451
80°	1319	1214	1213
85°	953	831	815

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 4416 cd/sqm

TEST NUMBER: P912260

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	1.4
10°-20°	1028.5	4.0
20°-30°	1511.4	5.9
30°-40°	1755.4	6.9
40°-50°	1753.3	6.9
50°-60°	1528.8	6.0
60°-70°	1130.1	4.4
70°-80°	639.4	2.5
80°-90°	184.7	0.7
90°-100°	347.3	1.4
100°-110°	1103.4	4.3
110°-120°	1888.3	7.4
120°-130°	2483.4	9.7
130°-140°	2787.5	10.9
140°-150°	2733.5	10.7
150°-160°	2293.0	9.0
160°-170°	1520.7	5.9
170°-180°	531.5	2.1
0°-30°	2905.4	11.4
0°-40°	4660.9	18.2
0°-60°	7942.9	31.0
0°-90°	9897.1	38.7
90°-120°	3339.0	13.1
90°-150°	11343.4	44.3
90°-180°	15689.0	61.3
0°-180°	25585.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3884	3884	3884	3884	3884	
5°	3884	3869	3828	3858	3850	369
15°	3697	3675	3626	3641	3622	1041
25°	3346	3316	3253	3260	3253	1540
35°	2887	2850	2790	2767	2748	1803
45°	2349	2323	2267	2226	2211	1813
55°	1778	1755	1710	1666	1647	1589
65°	1199	1176	1139	1106	1087	1185
75°	627	620	601	579	586	670
85°	153	149	146	134	131	171
90°	5	61	166	156	161	25
95°	247	294	303	303	294	275
105°	1018	1032	1042	1051	1051	1075
115°	1895	1922	1914	1908	1895	1874
125°	2756	2798	2785	2770	2765	2463
135°	3565	3617	3628	3622	3609	2756
145°	4328	4362	4389	4394	4375	2704
155°	4949	4962	4978	5001	4986	2278
165°	5384	5379	5379	5412	5389	1519
175°	5602	5588	5578	5612	5583	532
180°	5612	5612	5612	5612	5612	

TEST NUMBER: P912260

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3883.6	3883.6	3883.6	3883.6	3883.6
2.5°	3906.2	3887.6	3846.5	3883.6	3876.5
5°	3883.6	3869.0	3827.8	3857.5	3850.3
7.5°	3857.5	3835.4	3794.1	3824.3	3816.7
10°	3816.7	3790.6	3745.8	3775.5	3764.4
12.5°	3760.4	3738.2	3693.5	3712.0	3704.6
15°	3697.1	3674.9	3626.1	3641.2	3622.5
17.5°	3618.6	3596.4	3547.7	3566.3	3547.7
20°	3532.6	3510.4	3458.1	3469.2	3454.5
22.5°	3447.0	3413.4	3364.6	3364.6	3357.1
25°	3346.0	3316.2	3252.9	3260.0	3252.9
27.5°	3233.8	3207.7	3159.4	3148.3	3129.7
30°	3122.2	3092.0	3036.1	3025.0	3010.0
32.5°	3002.5	2980.3	2920.4	2897.9	2882.8
35°	2886.8	2849.6	2789.7	2767.2	2748.5
37.5°	2756.1	2722.4	2662.5	2636.4	2617.8
40°	2621.7	2591.6	2531.7	2498.5	2483.5
42.5°	2490.9	2460.9	2401.4	2363.8	2341.7
45°	2349.1	2323.0	2266.7	2225.9	2210.9
47.5°	2210.9	2184.7	2124.8	2083.7	2061.5
50°	2065.1	2046.4	1994.1	1941.9	1923.2
52.5°	1923.2	1897.1	1848.7	1807.6	1781.4
55°	1777.8	1755.2	1710.4	1665.7	1647.1
57.5°	1632.0	1613.4	1564.7	1519.9	1504.8
60°	1486.2	1471.5	1419.2	1378.0	1367.0
62.5°	1344.3	1318.2	1280.9	1243.7	1228.7
65°	1198.9	1176.3	1139.1	1105.5	1086.8
67.5°	1049.6	1030.6	997.2	971.2	956.1
70°	911.3	896.2	862.6	836.4	821.8
72.5°	769.4	754.3	735.7	709.6	698.6
75°	627.3	620.0	601.1	578.9	586.4
77.5°	500.4	485.4	477.9	466.8	455.7
80°	373.6	369.6	362.1	351.0	343.6
82.5°	254.0	254.0	250.4	235.3	235.3
85°	152.9	149.4	145.8	134.3	130.8
87.5°	67.3	59.8	52.3	41.3	37.3
90°	5.1	60.9	165.8	155.7	160.7
92.5°	104.9	142.2	147.2	152.3	152.3
95°	247.0	294.4	302.9	302.9	294.4
97.5°	411.1	455.1	473.8	473.8	473.8
100°	600.6	639.6	653.1	653.1	648.0
102.5°	800.3	829.1	847.6	852.7	847.6
105°	1018.5	1032.0	1042.2	1050.7	1050.7
107.5°	1235.1	1255.4	1255.4	1258.8	1235.1
110°	1444.9	1472.0	1472.0	1472.0	1458.4

TEST NUMBER: P912260

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1671.6	1700.4	1695.3	1681.8	1671.6
115°	1894.9	1922.0	1913.6	1908.5	1894.9
117.5°	2116.6	2153.8	2130.2	2116.6	2103.1
120°	2340.0	2377.1	2340.0	2340.0	2324.7
122.5°	2542.9	2590.4	2566.7	2553.1	2542.9
125°	2756.2	2798.5	2784.9	2769.7	2764.6
127.5°	2964.2	3016.7	2998.1	2977.8	2964.2
130°	3158.9	3219.8	3211.3	3201.1	3182.5
132.5°	3377.1	3424.5	3427.8	3404.2	3390.7
135°	3564.9	3617.3	3627.5	3622.4	3608.9
137.5°	3774.7	3817.0	3825.5	3822.1	3801.8
140°	3959.1	4001.4	4025.1	4025.1	4006.5
142.5°	4148.7	4190.9	4204.4	4209.5	4190.9
145°	4328.0	4361.8	4388.9	4394.0	4375.3
147.5°	4488.7	4531.0	4551.3	4559.8	4541.1
150°	4654.5	4683.3	4701.9	4717.1	4701.9
152.5°	4801.7	4830.5	4854.2	4872.7	4854.2
155°	4948.9	4962.4	4977.6	5001.4	4986.2
157.5°	5075.8	5086.0	5094.4	5128.2	5104.6
160°	5189.1	5199.3	5204.4	5233.1	5212.9
162.5°	5294.0	5294.0	5299.1	5331.3	5307.6
165°	5383.8	5378.6	5378.6	5412.5	5388.9
167.5°	5464.9	5449.7	5449.7	5483.6	5459.8
170°	5525.8	5512.3	5507.3	5541.1	5512.3
172.5°	5568.2	5554.6	5549.5	5583.4	5554.6
175°	5602.0	5588.5	5578.3	5612.2	5583.4
177.5°	5620.6	5607.1	5596.9	5625.7	5596.9
180°	5612.2	5612.2	5612.2	5612.2	5612.2

TEST NUMBER: P912260

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.62	10.39	10.67	11.44	12.86	9.17	9.94	10.22	11.00	12.42
	3H	11.28	11.96	12.33	13.03	14.47	10.79	11.47	11.84	12.54	13.98
	4H	11.86	12.52	12.93	13.58	15.03	11.37	12.02	12.44	13.09	14.54
	6H	12.26	12.86	13.34	13.93	15.39	11.76	12.36	12.84	13.43	14.89
	8H	12.37	12.94	13.45	14.02	15.48	11.86	12.44	12.95	13.52	14.98
	12H	12.41	12.96	13.50	14.03	15.51	11.90	12.45	12.99	13.52	15.00
4H	2H	10.07	10.72	11.15	11.79	13.24	9.71	10.37	10.79	11.43	12.88
	3H	11.93	12.48	13.01	13.57	15.03	11.52	12.07	12.61	13.16	14.62
	4H	12.64	13.14	13.73	14.23	15.71	12.22	12.72	13.31	13.80	15.29
	6H	13.16	13.59	14.26	14.69	16.17	12.73	13.16	13.82	14.26	15.74
	8H	13.31	13.71	14.41	14.81	16.30	12.87	13.27	13.97	14.37	15.86
	12H	13.38	13.74	14.49	14.85	16.35	12.93	13.29	14.04	14.40	15.90
8H	4H	12.83	13.23	13.93	14.33	15.83	12.46	12.86	13.56	13.96	15.45
	6H	13.47	13.80	14.59	14.94	16.43	13.08	13.41	14.20	14.55	16.04
	8H	13.69	13.98	14.82	15.10	16.61	13.30	13.59	14.42	14.71	16.22
	12H	13.82	14.07	14.95	15.19	16.74	13.41	13.66	14.54	14.78	16.33
12H	4H	12.82	13.18	13.93	14.29	15.79	12.45	12.81	13.56	13.92	15.42
	6H	13.50	13.79	14.62	14.91	16.42	13.12	13.41	14.25	14.54	16.04
	8H	13.74	13.99	14.87	15.11	16.66	13.36	13.61	14.49	14.73	16.28